

Coaxial Broadband Amplifier

ZFL-2000GH+

50Ω Variable Gain 10 to 2000 MHz

Features

- wideband, 10 to 2000 MHz
- rugged, shielded case
- gain control range: 60 dB typ.
- gain control voltage: 0 to +5V
- gain, +34 to -26 dB

Applications

- cellular
- VHF/UHF
- AGC applications



Generic photo used for illustration purposes only

CASE STYLE: Y39

Connectors	Model
SMA	ZFL-2000GH+
BRACKET (OPTION "B")	

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C, $V_{CTRL}=0V$ (or open)


Parameter	Condition (MHz)	Min.	Typ.	Max.	Units
Frequency Range		10	—	2000	MHz
Gain	10-2000	27	32	—	dB
Gain Flatness	10-2000	—	±2.5	—	dB
Output Power at 1dB compression	10-2000	—	+14	—	dBm
Output Power at 3dB compression	10-2000	—	+16	—	dBm
Noise Figure	10-2000	—	5.5	—	dB
Output third order intercept point	10-2000	—	+25	—	dBm
Output second order intercept point	10-2000	—	+50	—	dBm
Input VSWR	10-2000	—	1.4	—	:1
Output VSWR	10-2000	—	1.5	—	:1
DC Supply Voltage		—	15	—	V
Supply Current		—	—	230	mA

Open load is not recommended, potentially can cause damage.

With no load derate max input power by 20 dB

V_{CTRL} : Gain Control Voltage.

Outline Drawing



Gain Flatness, $V_{CC}=15V$, 10-2000 MHz

V_{CTRL} (V)	Gain Flatness (dB) Typ.
0 or open	±2.5
1	±3.0
2	±4.5
3	±8.2
4	±2.2
5	±2.3

Maximum Ratings

Parameter	Ratings
Operating Temperature	-20°C to 71°C
Storage Temperature	-55°C to 100°C
DC Voltage	+17V
V_{CTRL}	0 to +5.5V
Input RF Power (no damage)	+10 dBm

Outline Dimensions (inch/mm)










A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt.
1.25	1.25	.75	.63	.36	1.000	1.000	.125	.125	.46	2.18	1.688	.06	.750	.50	.80	.45	.29	grams
31.75	31.75	19.05	16.00	9.14	25.40	25.40	3.18	3.18	11.68	55.37	42.88	1.52	19.05	12.70	20.32	11.43	7.37	38

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



FREQUENCY (MHz)	GAIN (dB)	DIRECTIVITY (dB)	VSWR (:1)		POUT at 1 dB COMPR. (dBm)	POUT at 3 dB COMPR. (dBm)	NOISE FIGURE (dB)	IP3 (dBm)	IP2 (dBm)
			IN	OUT					
10.00	33.86	13.91	1.21	1.50	15.17	16.74	6.21	31.32	51.99
200.00	34.31	53.92	1.12	1.34	16.35	17.49	4.92	33.33	54.02
400.00	33.65	41.32	1.17	1.51	17.30	17.82	4.68	31.09	54.99
600.00	33.27	47.04	1.24	1.57	17.57	17.92	4.86	28.70	53.34
800.00	32.93	53.89	1.27	1.53	17.40	17.76	4.92	26.78	52.99
1000.00	32.52	36.54	1.31	1.44	16.81	17.70	4.81	24.53	52.46
1200.00	31.95	35.67	1.35	1.33	16.27	16.58	4.99	22.97	55.74
1400.00	31.30	38.09	1.45	1.27	15.31	15.69	5.30	21.32	61.31
1600.00	30.72	35.47	1.55	1.18	14.33	14.79	5.32	19.39	51.28
1800.00	30.12	31.20	1.71	1.15	13.39	13.93	5.54	17.38	45.16
2000.00	29.47	34.79	1.84	1.16	12.25	12.93	5.66	15.14	40.39



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Broadband Amplifier

ZFL-2000GH+

Typical Performance Data

Vctrl=0V @ 25°C									
FREQUENCY (MHz)	GAIN (dB) 15V	DIRECTIVITY (dB) 15V	VSWR IN (:1) 15V	VSWR OUT (:1) 15V	NOISE FIGURE (dB) 15V	Pout at 1dB Comp. (dBm) 15V	Pout at 3dB Comp. (dBm) 15V	Output IP2 (dBm) 15V	Output IP3 (dBm) 15V
10.0	33.86	13.91	1.21	1.50	6.21	15.17	16.74	51.99	31.32
50.0	34.34	19.18	1.17	1.26	5.24	15.73	16.79	50.30	32.59
100.0	34.36	37.95	1.15	1.25	4.86	16.01	17.13	51.13	33.86
200.0	34.31	53.92	1.12	1.34	4.92	16.35	17.49	54.02	33.33
300.0	34.00	42.75	1.14	1.43	4.55	16.99	17.95	56.51	32.84
400.0	33.65	41.32	1.17	1.51	4.68	17.30	17.82	54.99	31.09
500.0	33.42	41.56	1.21	1.55	4.81	17.51	17.89	52.37	29.62
600.0	33.27	47.04	1.24	1.57	4.86	17.57	17.92	53.34	28.70
700.0	33.10	36.80	1.26	1.57	5.04	17.60	17.98	53.06	27.84
800.0	32.93	53.89	1.27	1.53	4.92	17.40	17.76	52.99	26.78
900.0	32.74	38.42	1.29	1.49	4.83	17.40	17.75	53.53	25.72
1000.0	32.52	36.54	1.31	1.44	4.81	16.81	17.70	52.46	24.53
1100.0	32.25	39.49	1.33	1.38	5.16	16.70	17.02	53.92	23.89
1200.0	31.95	35.67	1.35	1.33	4.99	16.27	16.58	55.74	22.97
1300.0	31.60	38.81	1.37	1.29	5.46	15.74	16.10	63.83	22.18
1400.0	31.30	38.09	1.45	1.27	5.30	15.31	15.69	61.31	21.32
1500.0	31.03	32.55	1.47	1.21	5.26	14.82	15.23	55.40	20.24
1600.0	30.72	35.47	1.55	1.18	5.32	14.33	14.79	51.28	19.39
1700.0	30.43	33.70	1.63	1.16	5.41	14.03	14.48	48.40	18.47
1800.0	30.12	31.20	1.71	1.15	5.54	13.39	13.93	45.16	17.38
1900.0	29.81	31.63	1.79	1.15	5.59	12.81	13.40	43.04	16.21
2000.0	29.47	34.79	1.84	1.16	5.66	12.25	12.93	40.39	15.14



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. OR
ZFL-2000GH+
11/11/2014
Page 1 of 2

Broadband Amplifier

ZFL-2000GH+

Typical Performance Data

FREQUENCY (MHz)	GAIN @ Vdc=15V & 25°C						FREQUENCY (MHz)	GAIN CONTROL RANGE @ Vdc=15V & 25°C (dB)	FREQUENCY (MHz)	GAIN @ Vdc=15V & Vctrl=0V		
	Vctrl (V) = 0	Vctrl (V) = 1	Vctrl (V) = 2	Vctrl (V) = 3	Vctrl (V) = 4	Vctrl (V) = 5				-20°C	+25°C	+71°C
10.0	33.86	25.79	7.79	-9.53	-24.37	-26.29	10.0	60.15	10.0	34.77	34.34	33.76
50.0	34.34	26.21	8.21	-9.19	-23.46	-25.89	50.0	60.23	50.0	34.97	34.52	34.06
100.0	34.36	26.17	8.12	-9.24	-23.59	-25.77	100.0	60.12	100.0	34.90	34.46	33.98
200.0	34.31	26.01	7.90	-9.44	-23.49	-25.60	200.0	59.91	200.0	34.66	34.18	33.68
300.0	34.00	25.73	7.63	-9.73	-23.50	-25.50	300.0	59.49	300.0	34.40	33.91	33.41
400.0	33.65	25.41	7.30	-10.15	-23.67	-25.58	400.0	59.22	400.0	34.10	33.63	33.15
500.0	33.42	25.15	6.95	-10.67	-23.85	-25.63	500.0	59.05	500.0	33.92	33.48	33.01
600.0	33.27	24.91	6.59	-11.22	-23.68	-25.31	600.0	58.58	600.0	33.76	33.33	32.84
700.0	33.10	24.64	6.22	-11.63	-23.31	-24.89	700.0	57.99	700.0	33.66	33.21	32.70
800.0	32.93	24.38	5.83	-12.17	-23.66	-25.23	800.0	58.16	800.0	33.56	33.06	32.53
900.0	32.74	24.11	5.42	-12.94	-24.30	-25.87	900.0	58.61	900.0	33.39	32.85	32.30
1000.0	32.52	23.83	4.99	-13.82	-24.76	-26.27	1000.0	58.79	1000.0	33.20	32.64	32.06
1100.0	32.25	23.53	4.53	-14.77	-24.95	-26.37	1100.0	58.62	1100.0	32.98	32.38	31.76
1200.0	31.95	23.20	4.04	-15.78	-25.01	-26.38	1200.0	58.32	1200.0	32.77	32.12	31.44
1300.0	31.60	22.85	3.52	-16.81	-25.01	-26.35	1300.0	57.96	1300.0	32.52	31.8	31.07
1400.0	31.30	22.49	2.97	-17.98	-25.35	-26.73	1400.0	58.03	1400.0	32.29	31.55	30.81
1500.0	31.03	22.14	2.39	-19.33	-25.82	-27.28	1500.0	58.31	1500.0	32.12	31.32	30.52
1600.0	30.72	21.75	1.78	-20.69	-26.16	-27.69	1600.0	58.41	1600.0	31.87	31.02	30.20
1700.0	30.43	21.36	1.16	-22.08	-26.55	-28.19	1700.0	58.62	1700.0	31.64	30.76	29.93
1800.0	30.12	20.96	0.51	-23.42	-27.00	-28.72	1800.0	58.84	1800.0	31.36	30.47	29.65
1900.0	29.81	20.55	-0.17	-24.64	-27.34	-29.18	1900.0	58.98	1900.0	31.07	30.18	29.38
2000.0	29.47	20.12	-0.90	-25.58	-27.67	-29.59	2000.0	59.06	2000.0	30.73	29.86	29.10











P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com







IF/RF MICROWAVE COMPONENTS

REV. OR
 ZFL-2000GH+
 11/11/2014
 Page 2 of 2

Typical Performance Curves



Typical Performance Curves





Case Style

Y

Y39

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
Y39	1.25 (31.75)	1.25 (31.75)	.75 (19.05)	.63 (16.0)	.36 (9.15)	1.000 (25.4)	1.000 (25.4)	.125 (3.2)	.125 (3.2)	.46 (11.7)	2.18 (55.4)	1.688 (42.9)	.06 (1.5)

CASE#	P	Q	R	S	T	WT. GRAMS
Y39	.750 (19.0)	.50 (12.7)	.80 (20.3)	.45 (11.4)	.29 (7.4)	38

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

1. Case material: Aluminum alloy.
2. Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
3. Mounting bracket available on request. Add suffix B to part number
4. Gain terminal may exist on some models, refer catalog data sheet for details..

Mini-Circuits®

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-20° to 71° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Stabilization Bake	(non-operating) 125°C, 24 hours	- - -
Burn-in at Elevated Temp.	(DC on) 160 hours at 85° C	MIL-STD-202, Method 108
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, except 100°C