

Coaxial Power Splitter/Combiner

ZFSC-24-11

24 Way-0° 50Ω 1 to 200 MHz


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1W max.
Internal Dissipation	0.87W max.
Permanent damage may occur if any of these limits are exceeded.	

Coaxial Connections

SUM PORT	S (COM)
PORT 1,2,3,4.....,24	1,2,3,4.....,24

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H
9.31	1.60	1.50	8.84	.24	.88	.36	.160
236.47	40.64	38.10	224.54	6.10	22.35	9.14	4.06
J	K	L	M	N	P	Q	wt.
.40	.69	.54	.66	8.34	.81	.06	grams
10.16	17.53	13.72	16.76	211.84	20.57	1.52	490.0

Features

- rugged shielded case
- good isolation, 22 dB typ.

Applications

- HF/VHF
- test set-ups
- instrumentation



Generic photo used for illustration purposes only

BNC version shown

CASE STYLE: R31

Connectors	Model
BNC	ZFSC-24-11
SMA	ZFSC-24-11-S

Electrical Specifications


FREQ. RANGE (MHz)	ISOLATION (dB)						INSERTION LOSS (dB) ABOVE 13.8 dB						AMPLITUDE UNBALANCE (dB)		
	L		M		U		L		M		U		L	M	U
	Typ.	Min.	Typ.	Min.	Typ.	Typ.	Typ.	Max.	Typ.	Max.	Typ.	Max.	Max.	Max.	Max.
1-200	33	25	22	20	20	17	0.9	1.7	1.0	1.8	1.3	2.2	0.6	0.8	0.8

L = low range [f_L to $10 f_L$] M = mid range [$10 f_L$ to $f_U/2$] U = upper range [$f_U/2$ to f_U]


Typical Performance Data

Freq. (MHz)	Total Loss¹ (dB)	Amplitude Unbalance (dB)	Isolation (dB)		VSWR S	VSWR OUTPUT
	S-1		Adjacent	Opposite		
1.00	14.92	0.03	34.27	28.56	1.42	1.47
5.00	14.58	0.01	34.41	31.97	1.17	1.25
12.90	14.63	0.02	35.13	32.76	1.13	1.20
24.90	14.70	0.03	32.14	32.17	1.17	1.19
37.30	14.75	0.04	29.30	31.14	1.21	1.21
55.20	14.86	0.03	26.29	29.48	1.29	1.21
73.10	14.99	0.03	24.20	28.05	1.34	1.22
100.00	15.16	0.04	22.02	26.27	1.36	1.23
109.50	15.20	0.04	21.45	25.74	1.35	1.24
121.40	15.25	0.05	20.83	25.11	1.32	1.24
139.80	15.32	0.05	20.05	24.27	1.27	1.24
151.70	15.36	0.07	19.66	23.77	1.22	1.25
169.70	15.47	0.07	19.22	23.12	1.15	1.25
182.10	15.55	0.08	18.98	22.71	1.13	1.25
200.00	15.63	0.09	18.71	22.10	1.17	1.24

ZFSC-24-11
TOTAL LOSS




ZFSC-24-11
VSWR



1. Total Loss = Insertion Loss + 13.8dB splitter loss.

ZFSC-24-11
ISOLATION



electrical schematic



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B
M151107
ZFSC-24-11
HY/TD/CP/AM
200828

24 Way-0° Power Splitter/Combiner

ZFSC-24-11

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)	AMP. UNBAL. (dB)	ISOLATION (dB)		FREQ. (MHz)	VSWR (:1)	
			Adjacent	Opposite		S	OUTPUTS
1.0	14.92	0.03	34.27	28.56	1.0	1.42	1.47
5.0	14.58	0.01	34.41	31.97	5.0	1.17	1.25
12.9	14.63	0.02	35.13	32.76	12.9	1.13	1.20
24.9	14.70	0.03	32.14	32.17	24.9	1.17	1.19
37.3	14.75	0.04	29.30	31.14	37.3	1.21	1.21
55.2	14.86	0.03	26.29	29.48	55.2	1.29	1.21
73.1	14.99	0.03	24.20	28.05	73.1	1.34	1.22
100.0	15.16	0.04	22.02	26.27	100.0	1.36	1.23
109.5	15.20	0.04	21.45	25.74	109.5	1.35	1.24
121.4	15.25	0.05	20.83	25.11	121.4	1.32	1.24
139.8	15.32	0.05	20.05	24.27	139.8	1.27	1.24
151.7	15.36	0.07	19.66	23.77	151.7	1.22	1.25
169.7	15.47	0.07	19.22	23.12	169.7	1.15	1.25
182.1	15.55	0.08	18.98	22.71	182.1	1.13	1.25
200.0	15.63	0.09	18.71	22.10	200.0	1.17	1.24

¹ Total Loss = Insertion Loss+ 13.8dB Splitter Loss

REV. X2
ZFSC-24-11
100627
Page 1 of 1







The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see

Mini-Circuits®


IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



Typical Performance Curves



Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
R31	9.31 (236.47)	1.60 (40.64)	1.50 (38.10)	8.84 (224.54)	.24 (6.10)	.88 (22.35)	.36 (9.14)	.160 (4.06)	.40 (10.16)	.69 (17.53)	.54 (13.72)	.66 (16.76)	8.34 (211.84)

CASE#	P	Q	WT. GRAMS
R31	.81 (20.57)	.06 (1.53)	490.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B