

3 Way-0° 50Ω 2 to 750 MHz


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1W max.
Internal Dissipation	0.5W max.
Permanent damage may occur if any of these limits are exceeded.	

Coaxial Connections

SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H
1.25	1.25	.75	.63	.38	1.000	.125	1.000
31.75	31.75	19.05	16.00	9.65	25.40	3.18	25.40

J	K	L	M	N	P	Q	wt
--	--	.125	1.688	2.18	.75	.07	grams
--	--	3.18	42.88	55.37	19.05	1.78	75.0

For option B with N-Type connectors, dimension "C" increases to 0.94 inches.

Features

- wideband, 2 to 750 MHz
- low insertion loss, 0.5 dB typ.
- high isolation, 30 dB typ.
- rugged shielded case

Applications

- VHF/UHF
- instrumentation
- communication style

Generic photo used for illustration purposes only
CASE STYLE: J17

Connectors	Model
BNC	ZFSC-3-1W+
SMA	ZFSC-3-1W-S+
N-TYPE	ZFSC-3-1W-N+
BRACKET (OPTION "B")	

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Electrical Specifications

FREQ. RANGE (MHz)	ISOLATION (dB)						INSERTION LOSS (dB) ABOVE 4.8 dB						PHASE UNBALANCE (Degrees)			AMPLITUDE UNBALANCE (dB)		
	L		M		U		L		M		U		L		M		U	
f_L - f_U	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Max.	Typ.	Max.	Typ.	Max.	L	Max.	M	Max.	U	Max.
2-750	30	20	30	20	25	18	0.4	0.75	0.5	1.0	1.0	1.6	3.0		5.0		7.0	

L = low range [f_L to $10 f_L$] M = mid range [$10 f_L$ to $f_U/2$] U = upper range [$f_U/2$ to f_U]

Typical Performance Data

Freq. (MHz)	Total Loss ¹ (dB)			Amp. Unbal. (dB)	Isolation (dB)			Phase Unbal. (deg.)	VSWR			
	S-1	S-2	S-3		1-2	1-3	2-3		S	1	2	3
2.00	5.05	5.04	5.04	0.00	31.97	32.43	32.13	0.05	1.17	1.15	1.15	1.15
6.80	4.99	4.99	4.99	0.00	31.59	32.02	31.67	0.02	1.14	1.14	1.15	1.14
16.40	5.00	5.00	5.00	0.00	31.51	31.92	31.59	0.03	1.13	1.14	1.15	1.14
20.00	5.00	5.01	5.01	0.01	31.49	31.94	31.56	0.03	1.13	1.14	1.15	1.14
104.00	5.10	5.10	5.11	0.01	29.46	29.98	29.29	0.06	1.18	1.16	1.16	1.16
188.00	5.18	5.19	5.21	0.02	26.83	27.40	26.51	0.11	1.26	1.19	1.20	1.19
272.00	5.21	5.23	5.25	0.04	24.83	25.45	24.42	0.10	1.34	1.23	1.24	1.23
330.00	5.29	5.31	5.34	0.05	23.82	24.48	23.36	0.09	1.39	1.26	1.27	1.26
375.00	5.42	5.46	5.50	0.08	23.45	24.14	22.97	0.15	1.42	1.28	1.29	1.28
442.50	5.34	5.39	5.44	0.10	22.89	23.66	22.37	0.13	1.45	1.30	1.32	1.31
532.50	5.44	5.53	5.59	0.15	22.98	23.90	22.36	0.11	1.44	1.33	1.35	1.33
600.00	5.45	5.56	5.64	0.19	23.59	24.79	22.87	0.16	1.39	1.34	1.37	1.35
660.00	5.41	5.54	5.63	0.22	24.60	26.31	23.75	0.20	1.32	1.33	1.38	1.36
720.00	5.37	5.53	5.64	0.27	25.76	28.49	24.81	0.37	1.21	1.32	1.38	1.35
750.00	5.38	5.55	5.67	0.29	26.13	29.46	25.26	0.46	1.15	1.31	1.37	1.34



electrical schematic



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



3 Way-0° Power Splitter/Combiner

ZFSC-3-1W+

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹			AMP. UNBAL. (dB)	ISOLATION			PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR			
	S-1	S-2	S-3		1-2	1-3	2-3			S	1	2	3
2.0	5.05	5.04	5.04	0.00	31.97	32.43	32.13	0.05	2.0	1.17	1.15	1.15	1.15
4.4	5.00	5.00	5.00	0.00	31.65	32.08	31.73	0.03	4.4	1.14	1.14	1.15	1.14
6.8	4.99	4.99	4.99	0.00	31.59	32.02	31.67	0.02	6.8	1.14	1.14	1.15	1.14
9.2	4.99	5.00	5.00	0.01	31.55	31.99	31.64	0.02	9.2	1.13	1.14	1.15	1.14
11.6	4.99	4.99	5.00	0.01	31.52	31.96	31.59	0.04	11.6	1.13	1.14	1.15	1.14
14.0	4.99	4.99	4.99	0.00	31.50	31.93	31.58	0.02	14.0	1.13	1.14	1.15	1.14
15.2	4.99	5.00	5.00	0.00	31.51	31.92	31.57	0.04	15.2	1.13	1.14	1.15	1.14
16.4	5.00	5.00	5.00	0.00	31.51	31.92	31.59	0.03	16.4	1.13	1.14	1.15	1.14
17.6	5.00	5.00	5.00	0.00	31.51	31.91	31.57	0.04	17.6	1.13	1.14	1.15	1.14
18.8	5.00	5.00	5.00	0.00	31.50	31.93	31.54	0.02	18.8	1.13	1.14	1.15	1.14
20.0	5.00	5.01	5.01	0.01	31.49	31.94	31.56	0.03	20.0	1.13	1.14	1.15	1.14
48.0	5.03	5.03	5.03	0.00	31.12	31.58	31.13	0.02	48.0	1.14	1.15	1.15	1.14
76.0	5.07	5.08	5.08	0.01	30.34	30.83	30.25	0.06	76.0	1.16	1.15	1.15	1.15
104.0	5.10	5.10	5.11	0.01	29.46	29.98	29.29	0.06	104.0	1.18	1.16	1.16	1.16
132.0	5.14	5.14	5.15	0.01	28.48	29.02	28.24	0.09	132.0	1.21	1.17	1.17	1.17
160.0	5.14	5.14	5.16	0.02	27.58	28.13	27.28	0.07	160.0	1.23	1.18	1.18	1.18
188.0	5.18	5.19	5.21	0.02	26.83	27.40	26.51	0.11	188.0	1.26	1.19	1.20	1.19
216.0	5.27	5.28	5.30	0.03	26.06	26.65	25.70	0.12	216.0	1.29	1.21	1.21	1.20
244.0	5.22	5.23	5.25	0.03	25.34	25.93	24.95	0.11	244.0	1.32	1.22	1.22	1.22
272.0	5.21	5.23	5.25	0.04	24.83	25.45	24.42	0.10	272.0	1.34	1.23	1.24	1.23
300.0	5.43	5.46	5.48	0.05	24.42	25.07	24.00	0.19	300.0	1.37	1.25	1.25	1.24
315.0	5.38	5.39	5.42	0.04	24.08	24.74	23.63	0.14	315.0	1.38	1.25	1.26	1.25
330.0	5.29	5.31	5.34	0.05	23.82	24.48	23.36	0.09	330.0	1.39	1.26	1.27	1.26
345.0	5.25	5.28	5.31	0.06	23.64	24.32	23.18	0.11	345.0	1.40	1.27	1.27	1.26
360.0	5.29	5.32	5.35	0.07	23.51	24.18	23.04	0.16	360.0	1.41	1.27	1.28	1.27
375.0	5.42	5.46	5.50	0.08	23.45	24.14	22.97	0.15	375.0	1.42	1.28	1.29	1.28
397.5	5.50	5.54	5.58	0.08	23.23	23.95	22.74	0.16	397.5	1.43	1.29	1.30	1.29
420.0	5.36	5.40	5.45	0.09	22.96	23.69	22.45	0.17	420.0	1.44	1.30	1.31	1.30
442.5	5.34	5.39	5.44	0.10	22.89	23.66	22.37	0.13	442.5	1.45	1.30	1.32	1.31
465.0	5.51	5.57	5.63	0.11	22.95	23.75	22.40	0.17	465.0	1.45	1.31	1.33	1.31
487.5	5.50	5.56	5.62	0.13	22.86	23.71	22.30	0.13	487.5	1.45	1.32	1.34	1.32
510.0	5.40	5.46	5.53	0.13	22.85	23.74	22.26	0.12	510.0	1.45	1.32	1.34	1.33
532.5	5.44	5.53	5.59	0.15	22.98	23.90	22.36	0.11	532.5	1.44	1.33	1.35	1.33
555.0	5.49	5.58	5.65	0.16	23.15	24.14	22.50	0.11	555.0	1.43	1.33	1.36	1.34
577.5	5.46	5.55	5.63	0.17	23.33	24.43	22.66	0.13	577.5	1.41	1.34	1.37	1.35
600.0	5.45	5.56	5.64	0.19	23.59	24.79	22.87	0.16	600.0	1.39	1.34	1.37	1.35
630.0	5.44	5.56	5.66	0.22	24.02	25.42	23.25	0.17	630.0	1.36	1.34	1.38	1.35
660.0	5.41	5.54	5.63	0.22	24.60	26.31	23.75	0.20	660.0	1.32	1.33	1.38	1.36
690.0	5.46	5.60	5.70	0.24	25.29	27.44	24.39	0.30	690.0	1.27	1.33	1.38	1.35
720.0	5.37	5.53	5.64	0.27	25.76	28.49	24.81	0.37	720.0	1.21	1.32	1.38	1.35
750.0	5.38	5.55	5.67	0.29	26.13	29.46	25.26	0.46	750.0	1.15	1.31	1.37	1.34

¹ Total Loss = Insertion Loss + 4.8dB Splitter Loss

REV. X2
ZFSC-3-1W+
100721
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661








The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




3 Way-0° Power Splitter/Combiner

ZFSC-3-1W+

Typical Performance Curves



Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
J17	1.25 (31.75)	1.25 (31.75)	.75 (19.05)	.63 (16.00)	.38 (9.65)	1.000 (25.40)	.125 (3.18)	1.000 (25.40)	--	--	.125 (3.18)	1.688 (42.88)	2.18 (55.37)

CASE#	P	Q	WT. GRAMS
J17	.75 (19.05)	.07 (1.78)	75.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Mounting bracket available on request. Add suffix B to part number
- For bracket version, option B, dimension "C" changes from .75 to .94 inches when connectors are type N.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I