

Coaxial Directional Coupler

75Ω

100 to 1500 MHz

ZFDC-20-5-75



Generic photo used for illustration purposes only

CASE STYLE: K18

Connectors Model
BNC ZFDC-20-5-75

Maximum Ratings

Operating Temperature -55°C to 100°C

Storage Temperature -55°C to 100°C

Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

INPUT	1
OUTPUT	2
COUPLED	3


Features

- very wideband, 100 to 1500 MHz
- excellent directivity, 25 dB typ.
- mainline loss, 0.9 dB typ.
- rugged shielded case

Applications

- catv
- cellular
- communications receivers & transmitters

Outline Drawing



Outline Dimensions (inch mm)

A	B	C	D	E	F	G	H
1.25	1.25	.75	.63	.38	1.00	.125	1.000
31.75	31.75	19.05	16.00	9.65	25.40	3.18	25.40
J	K	L	M	N	P	Q	wt
--	--	.125	1.688	2.18	.75	.07	grams
--	--	3.18	42.88	55.37	19.05	1.78	70.0

Electrical Specifications




FREQ. RANGE (MHz)	COUPLING (dB)		MAINLINE LOSS¹ (dB)						DIRECTIVITY (dB)						VSWR (:1)	POWER INPUT (W)	
			L		M		U		L		M		U				
	f _L -f _U	Nom.	Flatness	Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Max.
100-1500	20±0.5	±0.75	0.9	1.3	0.9	1.2	1.1	1.5	30	20	25	18	22	13	1.3	1.0	1.0

L = 100-500 MHz M = 500-1000 MHz U = 1000-1500 MHz


1. Mainline loss includes theoretical power loss at coupled port.

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB)		Cpl
				In	Out	
100.00	0.87	19.71	37.48	20.21	22.84	22.65
360.00	0.83	19.73	32.02	22.37	24.31	20.76
620.00	0.86	19.84	24.40	20.31	19.42	18.00
780.00	0.90	19.90	23.19	18.18	17.21	16.60
840.00	0.94	19.92	23.27	17.62	16.70	16.22
920.00	0.97	19.95	23.93	17.13	16.33	15.83
1020.00	0.98	19.93	25.69	16.79	16.26	15.48
1140.00	0.99	19.91	31.05	16.93	16.78	15.24
1340.00	1.04	19.88	30.64	18.18	19.34	14.84
1500.00	1.12	19.90	21.26	19.83	23.70	14.44



Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMERS THAT ROUTES DC FROM RF PORTS TO GROUND.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B
M151107
ZFDC-20-5-75
WZ/TD/CP/AM
200811

Directional Coupler

ZFDC-20-5-75

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	OUT	CPL
100.0	0.87	19.71	37.48	20.21	22.84	22.65
165.0	0.85	19.70	44.85	21.04	24.10	22.51
230.0	0.83	19.69	42.77	21.54	24.63	21.91
295.0	0.82	19.70	35.62	22.05	24.76	21.40
360.0	0.83	19.73	32.02	22.37	24.31	20.76
425.0	0.83	19.76	29.22	22.32	23.32	20.07
490.0	0.83	19.78	27.06	21.90	21.98	19.34
555.0	0.84	19.82	25.52	21.12	20.60	18.59
620.0	0.86	19.84	24.40	20.31	19.42	18.00
685.0	0.87	19.87	23.73	19.44	18.39	17.42
750.0	0.89	19.91	23.20	18.56	17.55	16.86
765.0	0.90	19.90	23.16	18.36	17.37	16.72
780.0	0.90	19.90	23.19	18.18	17.21	16.60
795.0	0.91	19.92	23.15	18.03	17.07	16.50
810.0	0.92	19.92	23.22	17.89	16.94	16.42
825.0	0.93	19.93	23.14	17.75	16.82	16.32
840.0	0.94	19.92	23.27	17.62	16.70	16.22
855.0	0.92	19.91	23.33	17.48	16.59	16.13
870.0	0.93	19.92	23.47	17.40	16.51	16.05
885.0	0.95	19.93	23.47	17.29	16.44	15.97
900.0	0.96	19.94	23.62	17.22	16.38	15.91
920.0	0.97	19.95	23.93	17.13	16.33	15.83
940.0	0.95	19.93	24.13	17.04	16.28	15.76
960.0	0.95	19.92	24.56	16.94	16.24	15.67
980.0	0.96	19.93	24.87	16.88	16.24	15.61
1000.0	0.98	19.94	25.17	16.83	16.25	15.55
1020.0	0.98	19.93	25.69	16.79	16.26	15.48
1040.0	0.97	19.91	26.21	16.76	16.28	15.42
1060.0	0.97	19.92	27.03	16.76	16.33	15.37
1080.0	0.98	19.93	27.67	16.80	16.44	15.35
1100.0	0.99	19.92	28.49	16.85	16.54	15.32
1140.0	0.99	19.91	31.05	16.93	16.78	15.24
1180.0	0.99	19.90	34.27	17.06	17.11	15.16
1220.0	1.03	19.91	41.72	17.24	17.52	15.06
1260.0	1.00	19.88	43.45	17.48	17.98	14.96
1300.0	1.04	19.91	35.09	17.84	18.63	14.93
1340.0	1.04	19.88	30.64	18.18	19.34	14.84
1380.0	1.05	19.89	27.27	18.61	20.24	14.80
1420.0	1.09	19.90	24.83	19.00	21.25	14.71
1460.0	1.07	19.89	22.94	19.36	22.33	14.55
1500.0	1.12	19.90	21.26	19.83	23.70	14.44

REV. X1

ZFDC-20-5-75

060718

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661







For detailed performance specs & shopping online see



Directional Coupler

Typical Performance Curves

ZFDC-20-5-75




Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



REV. X1
ZFDC-20-5-75
060718
Page 1 of 1

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
K18	1.25 (31.75)	1.25 (31.75)	.75 (19.05)	.63 (16.00)	.38 (9.65)	1.000 (25.40)	.125 (3.18)	1.000 (25.40)	--	--	.125 (3.18)	1.688 (42.88)	2.18 (55.37)

CASE#	P	Q	WT. GRAMS
K18	.75 (19.05)	.07 (1.78)	70.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Mounting bracket available on request. Add suffix B to part number.
- For port marking 1, 2, and 3 see specifications data sheet.
- For bracket version, option B, dimension "C" changes from .75 to .94 inches when connectors are type N.
- Refer to the individual model data sheet for the type of connectors available.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I