

Engineering Development Model

Power Splitter/Combiner

ZFSC-ED11817/1

10 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : RR93

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		0.05		340 MHz
Isolation	0.05 - 0.5 MHz		30	dB
	0.5 - 170 MHz		36	dB
	170 - 340 MHz		27	dB
Insertion Loss Above 10.0 dB	0.05 - 0.5 MHz		0.60	dB
	0.5 - 170 MHz		0.40	dB
	170 - 340 MHz		1.20	dB
Phase Unbalance	0.05 - 0.5 MHz		0.541	deg.
	0.5 - 170 MHz		0.450	deg.
	170 - 340 MHz		2.887	deg.
Amplitude Unbalance	0.05 - 0.5 MHz		0.063	dB
	0.5 - 170 MHz		0.031	dB
	170 - 340 MHz		0.215	dB
VSWR	SUM Port		1.26	(:1)
	OUT Ports		1.22	(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

Functional Diagram



10 Way-0°Power Splitter/Combiner ZFSC-ED11817/1

Typical Performance Data






FREQ. (MHz)	TOTAL LOSS ¹ (dB)	AMP. UNBAL. (dB)	ISOLATION (dB)		PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)	
			Adjacent	Opposite			S	OUTPUTS
0.03	11.76	0.18	18.73	28.44	0.66	0.03	2.41	2.73
0.04	11.27	0.14	19.84	30.44	0.70	0.04	2.06	2.31
0.05	10.98	0.10	20.90	32.50	0.72	0.05	1.85	2.05
0.06	10.80	0.07	21.91	34.49	0.72	0.06	1.70	1.87
0.07	10.69	0.06	22.83	36.45	0.69	0.07	1.60	1.74
0.08	10.62	0.07	23.69	38.11	0.63	0.08	1.53	1.65
0.09	10.56	0.07	24.48	39.53	0.51	0.09	1.47	1.57
0.10	10.53	0.06	25.23	40.72	0.54	0.10	1.43	1.51
0.30	10.39	0.04	32.83	42.29	0.28	0.30	1.22	1.21
0.50	10.35	0.03	35.79	41.27	0.24	0.50	1.19	1.16
0.70	10.33	0.03	37.56	41.12	0.11	0.70	1.17	1.14
0.90	10.31	0.02	38.81	41.29	0.20	0.90	1.16	1.13
1.00	10.30	0.02	39.33	41.31	0.16	1.00	1.16	1.12
1.80	10.27	0.02	41.92	41.34	0.18	1.80	1.14	1.10
2.60	10.26	0.02	43.21	40.96	0.14	2.60	1.13	1.09
3.40	10.26	0.02	43.91	40.56	0.12	3.40	1.12	1.08
4.20	10.27	0.02	44.35	40.26	0.19	4.20	1.12	1.08
5.00	10.26	0.03	44.46	39.94	0.16	5.00	1.12	1.07
14.00	10.32	0.02	42.74	38.12	0.15	14.00	1.11	1.07
23.00	10.35	0.02	40.52	36.88	0.19	23.00	1.12	1.06
32.00	10.38	0.02	38.62	35.72	0.34	32.00	1.13	1.06
41.00	10.40	0.02	37.02	34.68	0.40	41.00	1.14	1.06
50.00	10.43	0.02	35.76	33.85	0.52	50.00	1.15	1.06
60.00	10.45	0.03	34.54	32.93	0.61	60.00	1.17	1.06
70.00	10.48	0.03	33.52	32.16	0.60	70.00	1.19	1.06
80.00	10.51	0.03	32.70	31.52	0.81	80.00	1.20	1.06
90.00	10.52	0.05	31.95	30.91	0.80	90.00	1.22	1.06
100.00	10.55	0.05	31.29	30.36	0.99	100.00	1.24	1.06
125.00	10.62	0.06	30.07	29.30	1.14	125.00	1.27	1.06
150.00	10.66	0.09	29.16	28.55	1.41	150.00	1.29	1.07
200.00	10.78	0.12	28.17	27.73	1.89	200.00	1.31	1.10
228.00	10.82	0.16	27.91	27.56	2.21	228.00	1.30	1.12
256.00	10.90	0.19	27.74	27.50	2.63	256.00	1.29	1.15
284.00	10.99	0.23	27.64	27.55	3.02	284.00	1.26	1.18
312.00	11.09	0.26	27.50	27.57	3.52	312.00	1.23	1.21
340.00	11.19	0.33	27.20	27.48	4.05	340.00	1.19	1.24
368.00	11.36	0.37	26.57	27.06	4.75	368.00	1.12	1.28
396.00	11.58	0.42	25.34	25.93	5.63	396.00	1.10	1.31
424.00	11.95	0.49	23.41	23.95	6.64	424.00	1.27	1.33
452.00	12.60	0.55	21.06	21.43	7.77	452.00	1.61	1.34
480.00	13.68	0.62	18.74	18.90	9.13	480.00	2.19	1.33

¹ Total Loss = Insertion Loss + 10dB Splitter Loss

10 Way-0° Power Splitter/Combiner


ZFSC-ED11817/1

Typical Performance Curves



REV. X2
ZFSC-ED11817/1
100707
Page 1 of 1

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
RR93	4.06 (103.12)	1.60 (40.64)	2.125 (53.98)	3.56 (90.42)	.25 (6.35)	.88 (22.35)	.36 (9.14)	.160 (4.06)	.40 (10.16)	.69 (17.53)	.58 (14.73)	.66 (16.76)	3.13 (79.50)

CASE#	P	Q	R	WT. GRAMS
RR93	.80 (20.32)	.06 (1.52)	.33 (8.38)	350.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:

For RoHS Case Styles:

Clear chemical conversion coating, non-chrome or trivalent chrome based.



INTERNET <http://www.minicircuits.com>
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I