

Power Splitter/Combiner

ZFSC-ED6435/2

3 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : J17

ELECTRICAL SPECIFICATIONS 75Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		0.28		1250 MHz
Isolation	0.28 - 2.8 MHz		29	dB
	2.8 - 625 MHz		27	dB
	625 - 1250 MHz		21	dB
Insertion Loss Above 4.8 dB	0.28 - 2.8 MHz		0.27	dB
	2.8 - 625 MHz		0.35	dB
	625 - 1250 MHz		1.15	dB
Phase Unbalance	0.28 - 2.8 MHz		0.068	deg.
	2.8 - 625 MHz		0.209	deg.
	625 - 1250 MHz		1.631	deg.
Amplitude Unbalance	0.28 - 2.8 MHz		0.004	dB
	2.8 - 625 MHz		0.056	dB
	625 - 1250 MHz		0.330	dB
VSWR	SUM Port		1.18	(:1)
	OUT Ports		1.31	(:1)

Note: Denotes 75 Ohm model, for coax connector models 75 Ohm BNC connectors are standard.

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3

Functional Diagram



3 Way-0° Power Splitter/Combiner

ZFSC-ED6435/2

Typical Performance Data






FREQ. (MHz)	TOTAL LOSS ¹ (dB)			AMP. UNBAL. (dB)	ISOLATION (dB)		PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)			
	S-1	S-2	S-3		1-2	2-3			S	1	2	3
0.28	5.08	5.07	5.08	0.01	26.90	27.17	0.13	0.28	1.37	1.60	1.59	1.60
0.37	5.06	5.06	5.07	0.00	27.69	27.81	0.08	0.37	1.27	1.48	1.47	1.47
0.46	5.07	5.07	5.07	0.01	28.35	28.51	0.12	0.46	1.21	1.41	1.40	1.40
0.55	5.07	5.06	5.07	0.00	28.90	29.07	0.03	0.55	1.21	1.36	1.36	1.36
0.64	5.07	5.07	5.07	0.00	29.41	29.61	0.07	0.64	1.18	1.33	1.33	1.33
0.73	5.07	5.06	5.07	0.01	29.91	30.10	0.03	0.73	1.15	1.31	1.30	1.30
0.82	5.07	5.08	5.08	0.00	30.38	30.60	0.03	0.82	1.14	1.29	1.28	1.29
0.91	5.08	5.08	5.07	0.01	30.83	31.04	0.06	0.91	1.12	1.27	1.27	1.27
1.00	5.07	5.08	5.07	0.00	31.27	31.46	0.06	1.00	1.11	1.26	1.26	1.26
72.35	5.03	5.01	5.02	0.01	34.12	33.73	0.02	72.35	1.02	1.12	1.12	1.12
143.71	5.07	5.05	5.06	0.01	31.46	31.16	0.03	143.71	1.02	1.11	1.11	1.11
215.07	5.10	5.08	5.08	0.02	29.12	28.90	0.10	215.07	1.03	1.10	1.10	1.10
286.42	5.13	5.10	5.11	0.03	27.35	27.12	0.18	286.42	1.03	1.10	1.10	1.10
357.78	5.18	5.11	5.15	0.06	25.96	25.68	0.41	357.78	1.04	1.11	1.10	1.11
429.14	5.21	5.14	5.26	0.12	24.94	24.70	0.25	429.14	1.06	1.13	1.11	1.13
500.50	5.28	5.19	5.26	0.08	24.04	23.78	0.40	500.50	1.08	1.16	1.13	1.16
571.85	5.35	5.23	5.30	0.12	23.96	23.07	0.28	571.85	1.12	1.19	1.15	1.18
643.21	5.42	5.28	5.36	0.14	22.91	22.55	0.38	643.21	1.15	1.23	1.19	1.23
714.57	5.47	5.31	5.42	0.16	22.67	22.23	0.43	714.57	1.19	1.28	1.23	1.28
785.92	5.59	5.39	5.54	0.20	22.70	22.16	0.53	785.92	1.23	1.33	1.28	1.33
857.28	5.69	5.45	5.63	0.24	23.10	22.39	0.79	857.28	1.26	1.40	1.33	1.39
928.64	5.80	5.51	5.75	0.29	23.92	22.99	0.98	928.64	1.28	1.46	1.39	1.46
1000.00	5.91	5.58	5.85	0.33	24.75	23.49	1.40	1000.00	1.25	1.51	1.42	1.50
1041.67	6.02	5.68	5.98	0.34	24.61	23.38	1.48	1041.67	1.21	1.53	1.43	1.53
1083.33	6.12	5.74	6.09	0.37	23.40	22.46	1.81	1083.33	1.16	1.55	1.44	1.55
1125.00	6.23	5.83	6.23	0.40	21.31	20.78	2.23	1125.00	1.14	1.54	1.43	1.54
1166.67	6.47	6.06	6.50	0.43	18.88	18.61	2.59	1166.67	1.20	1.50	1.40	1.52
1208.33	6.80	6.36	6.85	0.49	16.61	16.53	3.11	1208.33	1.34	1.45	1.35	1.48
1250.00	7.17	6.72	7.30	0.57	14.54	14.56	3.84	1250.00	1.56	1.39	1.28	1.43

¹ Total Loss = Insertion Loss + 4.8dB Splitter Loss

3 Way-0° Power Splitter/Combiner


ZFSC-ED6435/2

Typical Performance Curves



REV. X2
ZFSC-ED6435/2
100707
Page 1 of 1

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
J17	1.25 (31.75)	1.25 (31.75)	.75 (19.05)	.63 (16.00)	.38 (9.65)	1.000 (25.40)	.125 (3.18)	1.000 (25.40)	--	--	.125 (3.18)	1.688 (42.88)	2.18 (55.37)

CASE#	P	Q	WT. GRAMS
J17	.75 (19.05)	.07 (1.78)	75.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Mounting bracket available on request. Add suffix B to part number
- For bracket version, option B, dimension "C" changes from .75 to .94 inches when connectors are type N.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I