

Limiter

50Ω Broadband 100 to 2500 MHz

ZFLM-252-1WL-S+



CASE STYLE: H16

Connectors Model
SMA ZFLM-252-1WL-S+
BRACKET (OPTION "B")

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings



Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Input Power	1.5W

Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

INPUT	SMA female
OUTPUT	SMA male

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H
1.25	1.25	.75	.63	.38	1.000	.125	1.000
31.75	31.75	19.05	16.00	9.65	25.40	3.18	25.40
J	K	L	M	N	P	Q	wt
--	--	.125	1.688	2.18	.750	.06	grams
--	--	3.18	42.88	55.37	19.05	1.52	70.0

Features

- low insertion loss, 0.7 dB typ.
- very low output power 0 dBm typ. at 30 dBm input
- low cost

Applications






- stabilizing generator outputs
- reducing amplitude variations
- protects low noise amplifiers and other devices from ESD or input power damage

Electrical Specifications

Parameter	Condition	Min.	Typ.	Max.	Units
Frequency Range		100	—	2500	MHz
Linear Range					
Max Input Power	<0.1 dB compression	—	—	-10	dBm
Insertion Loss	<-10 dBm	—	0.7	1.4	dB
VSWR	<-10 dBm	—	1.35	1.6	:1
Limiting Range					
Input Power	>1dB compression filtered signal frequency	+5	—	+30	dBm
Output Power		—	0	—	dBm
Δ Output/1dB Δ Input	Input Power Range (dBm)				
	5 to 10	—	0.1	—	
	10 to 20	—	0.05	—	dB/dB
	20 to 30	—	0.1	—	
Recovery Time	1 watt pulse 50 μsec pw 1kHz duty cycle recovery to within 90% of final value	—	8	—	nsec
Response Time	-30 to +30 dBm input 50 μsec PW 1 kHz duty cycle	—	2	—	nsec

Typical Performance Data

Freq. (MHz)	I. Loss in Linear Range (dB)	VSWR in Linear Range (:1)	Power Output (dBm)				Δ Output / 1dB Δ Input		
			+5 dBm Input	+10 dBm Input	+20 dBm Input	+30 dBm Input	+5 to +10 dBm Input	+10 to +20 dBm Input	+20 to +30 dBm Input
100.00	0.18	1.12	-0.30	0.94	3.24	5.96	0.25	0.23	0.27
200.00	0.23	1.15	-0.41	0.79	2.96	4.14	0.24	0.22	0.12
300.00	0.28	1.20	-0.44	0.68	2.60	3.17	0.22	0.19	0.06
400.00	0.33	1.25	-0.53	0.66	2.11	2.43	0.24	0.15	0.03
500.00	0.39	1.29	-0.52	0.65	1.70	1.88	0.23	0.11	0.02
600.00	0.44	1.34	-0.54	0.56	1.39	1.36	0.22	0.08	0.00
800.00	0.57	1.40	-0.50	0.40	0.97	0.40	0.18	0.06	-0.06
1000.00	0.57	1.41	-0.55	0.30	0.38	-0.20	0.17	0.01	-0.06
1200.00	0.57	1.36	-0.56	0.12	0.07	-0.89	0.14	-0.01	-0.10
1400.00	0.58	1.29	-0.68	-0.31	-0.53	-1.49	0.07	-0.02	-0.10
1500.00	0.59	1.25	-0.99	-0.48	-0.85	-2.49	0.10	-0.04	-0.16
1600.00	0.59	1.23	-1.14	-0.74	-1.12	-3.11	0.08	-0.04	-0.20
1800.00	0.64	1.22	-1.52	-1.15	-1.69	-2.56	0.07	-0.05	-0.09
2000.00	0.72	1.26	-2.07	-1.74	-2.77	-2.91	0.07	-0.10	-0.01
2200.00	0.80	1.28	-2.41	-2.37	-2.51	-5.58	0.01	-0.01	-0.31
2400.00	0.88	1.25	-3.02	-3.02	-3.29	-5.78	0.00	-0.03	-0.25
2500.00	0.91	1.21	-3.29	-3.46	-3.66	-5.29	-0.03	-0.02	-0.16



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

REV. B
M171494
ZFLM-252-1WL-S+
ED-14683
DJ/CP/AM
190110



Typical Performance Data

FREQUENCY (MHz)	LOW INPUT POWER			POWER OUTPUT (dBm)				DELTA OUTPUT/1dB DELTA INPUT (dB/dB)		
	INSERTION LOSS (dB)	VSWR		+5 dBm INPUT	+10 dBm INPUT	+20 dBm INPUT	+30 dBm INPUT	+5 to +10 dBm INPUT	+10 to +20 dBm INPUT	+20 to +30 dBm INPUT
		Input (:1)	Output (:1)							
100	0.18	1.12	1.12	-0.30	0.94	3.24	5.96	0.25	0.23	0.27
200	0.23	1.15	1.15	-0.41	0.79	2.96	4.14	0.24	0.22	0.12
300	0.28	1.20	1.19	-0.44	0.68	2.60	3.17	0.22	0.19	0.06
400	0.33	1.25	1.24	-0.53	0.66	2.11	2.43	0.24	0.15	0.03
500	0.39	1.29	1.30	-0.52	0.65	1.70	1.88	0.23	0.11	0.02
600	0.44	1.34	1.34	-0.54	0.56	1.39	1.36	0.22	0.08	0.00
700	0.51	1.36	1.38	-0.52	0.48	1.17	0.82	0.20	0.07	-0.04
800	0.57	1.40	1.41	-0.50	0.40	0.97	0.40	0.18	0.06	-0.06
900	0.56	1.42	1.43	-0.38	0.36	0.45	0.03	0.15	0.01	-0.04
1000	0.57	1.41	1.42	-0.55	0.30	0.38	-0.20	0.17	0.01	-0.06
1100	0.57	1.39	1.40	-0.51	0.19	0.21	-0.61	0.14	0.00	-0.08
1200	0.57	1.36	1.37	-0.56	0.12	0.07	-0.89	0.14	-0.01	-0.10
1300	0.58	1.33	1.33	-0.72	-0.09	-0.21	-1.33	0.13	-0.01	-0.11
1400	0.58	1.29	1.28	-0.68	-0.31	-0.53	-1.49	0.07	-0.02	-0.10
1500	0.59	1.25	1.24	-0.99	-0.48	-0.85	-2.49	0.10	-0.04	-0.16
1600	0.59	1.23	1.20	-1.14	-0.74	-1.12	-3.11	0.08	-0.04	-0.20
1700	0.61	1.21	1.18	-1.32	-0.94	-1.33	-3.01	0.08	-0.04	-0.17
1800	0.64	1.22	1.19	-1.52	-1.15	-1.69	-2.56	0.07	-0.05	-0.09
1900	0.68	1.24	1.20	-1.78	-1.36	-2.43	-2.42	0.08	-0.11	0.00
2000	0.72	1.26	1.23	-2.07	-1.74	-2.77	-2.91	0.07	-0.10	-0.01
2100	0.76	1.28	1.24	-2.24	-2.04	-2.93	-4.50	0.04	-0.09	-0.16
2200	0.80	1.28	1.25	-2.41	-2.37	-2.51	-5.58	0.01	-0.01	-0.31
2300	0.84	1.28	1.25	-2.78	-2.74	-3.51	-7.65	0.01	-0.08	-0.41
2400	0.88	1.25	1.23	-3.02	-3.02	-3.29	-5.78	0.00	-0.03	-0.25
2500	0.91	1.21	1.19	-3.29	-3.46	-3.66	-5.29	-0.03	-0.02	-0.16



Coaxial Limiter

ZFLM-252-1WL+

Typical Performance Data

POWER INPUT	POWER OUTPUT	POWER INPUT	POWER OUTPUT	POWER INPUT	POWER OUTPUT
@ 100 MHz		@ 1500 MHz		@ 2500 MHz	
(dBm)		(dBm)		(dBm)	
-10	-10.23	-10	-10.51	-10	-10.92
-5	-5.44	-5	-5.65	-5	-6.49
0	-1.94	0	-1.95	0	-4.17
5	-0.30	5	-0.56	5	-3.29
10	0.94	10	0.12	10	-3.46
20	3.24	20	0.07	20	-3.66
30	5.96	30	-0.89	30	-5.29



ISO 9001 ISO 14001 AS 9100 CERTIFIED



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS


REV. OR
ZFLM-252-1WL+
10/2/2012
Page 2 of 2

Typical Performance Curves


Insertion Loss vs Frequency




Power Output vs Power Input




Power Output vs Frequency




Delta Output / Delta 1dB Input



Input VSWR




Output VSWR



Outline Dimensions

H16



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
H16	1.25 (31.75)	1.25 (31.75)	.750 (19.05)	.63 (16.00)	.38 (9.65)	1.000 (25.40)	.125 (3.18)	1.000 (25.40)	--	--	.125 (3.18)	1.688 (42.88)	2.18 (55.37)

CASE#	P	Q	WT.GRAMS
H16	.750 (19.05)	.06 (1.52)	70

Dimensions are in inches (mm). Tolerances: 2PL. ± .03; 3PL. ± .015

Notes:

1. Case material: Aluminum alloy.
2. Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
3. Mounting bracket available on request. Add suffix B to part number.
4. Bracket version, option B, dimension "C" changes from .75 to .94 inches when connectors are type N.
5. Refer to the individual model data sheet for the type of connectors available.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I