

Engineering Development Model

DC Pass, High Power Directional Coupler

ZGDC10-ED13569

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : HT1394

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency		380		3600	MHz
Coupling	Nominal		11.3±1.8		dB
	Flatness		±1.2		dB
Mainline Loss (1)	380-5000 MHz		0.50		dB
Directivity	380-5000 MHz		27		dB
VSWR	380-5000 MHz		1.10		(:1)
RF Power Input (2)	380-2700 MHz			250	W
	2700-3600 MHz			160	

(1) Mainline loss includes theoretical coupled power loss of 0.335 dB at 11.3 dB coupling.


(2) At 20°C, derate linearly to 100W (380-2700 MHz) and to 64W (2700-3600 MHz) from 25°C to 100°C. Output load VSWR 2.0:1 Max.

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
DC Current	3A
Supplied Termination (3)	10W

(3) Derate linearly by 0.18W/°C from 70°C to 100°C

COAXIAL CONNECTIONS	
INPUT	IN
OUTPUT	OUT
COUPLED	CPL
INTERNAL TERMINATION (50 Ω)	TERM

Electrical Schematic



* ELECTRICAL SCHEMATIC FOR DIRECTIONAL COUPLER THAT IS DESIGNED WITHOUT INTERNAL TRANSFORMERS.





Directional Coupler

ZGDC10-ED13569

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	OUT	CPL
380.0	0.28	12.71	30.18	34.76	35.60	34.27
390.0	0.29	12.57	30.44	34.71	35.67	33.89
400.0	0.30	12.42	30.17	34.78	35.71	33.52
500.0	0.38	11.34	30.06	35.24	36.86	31.37
600.0	0.43	10.76	30.77	34.53	36.18	30.79
700.0	0.46	10.50	33.16	34.15	34.76	31.19
800.0	0.45	10.45	39.59	34.18	33.04	31.56
900.0	0.47	10.56	39.26	33.72	31.78	31.51
1000.0	0.45	10.68	30.68	33.32	31.81	32.06
1200.0	0.47	10.71	24.28	33.36	37.86	36.87
1400.0	0.52	10.47	24.28	29.81	33.41	25.04
1600.0	0.52	10.43	30.07	24.59	25.41	22.41
1800.0	0.51	10.55	29.32	26.57	26.85	29.13
2000.0	0.50	10.60	19.70	29.45	32.06	26.88
2200.0	0.54	10.50	18.36	21.48	21.34	21.45
2400.0	0.58	10.32	20.76	20.31	20.75	27.21
2500.0	0.56	10.24	23.18	22.87	23.28	36.08
2600.0	0.54	10.28	26.81	28.21	30.09	25.97
2700.0	0.55	10.39	33.43	26.97	25.44	21.57
2800.0	0.56	10.44	30.35	21.99	19.96	20.17
2900.0	0.58	10.46	24.61	19.52	18.01	20.94
3000.0	0.59	10.46	21.77	18.53	17.83	24.08
3200.0	0.56	10.29	22.30	22.29	23.04	27.18
3400.0	0.53	10.19	29.89	31.39	28.96	20.75
3600.0	0.56	10.31	32.25	23.06	21.77	21.79
3800.0	0.53	10.42	28.68	24.79	23.12	25.33
4000.0	0.48	10.36	24.12	32.05	29.77	26.66
4200.0	0.49	10.36	19.75	33.56	33.10	32.64
4400.0	0.51	10.13	21.13	28.67	31.15	28.36
4600.0	0.47	10.28	22.92	26.02	34.54	25.57
4800.0	0.49	10.44	21.51	20.22	20.34	22.73
5000.0	0.56	10.36	17.89	15.74	15.64	23.33

Typical Performance Curves




Case Style

HT

HT1394
HT1412

Outline Dimensions



CASE #	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAM
HT1394	5.93 (150.62)	2.40 (60.96)	1.00 (25.40)	.18 (4.57)	5.565 (141.35)	.18 (4.57)	2.040 (51.82)	.200 (5.08)	.50 (12.70)	.99 (25.15)	1.09 (27.69)	1.09 (27.69)	700.0
HT1412	5.58 (141.73)	2.50 (63.50)			5.215 (132.46)		2.140 (54.36)						

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:

For RoHS Case Styles:

Clear Chemical conversion coating, non-chrome or trivalent chrome based.

Mini-Circuits®

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified