

Engineering Development Model

Resistive Power Splitter/Combiner

ZFRSC-ED13066

2 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : JJJ245

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency		1		18000	MHz
Isolation	1-10 MHz		6		dB
	10-9000 MHz		7		dB
	9000-18000 MHz		7		dB
Insertion loss above 6 dB	1-10 MHz		0.05		dB
	10-9000 MHz		0.50		dB
	9000-18000 MHz		1.00		dB
Phase Unbalance	1-10 MHz		0.20		Deg
	10-9000 MHz		1.90		Deg
	9000-18000 MHz		5.60		Deg
Amplitude Unbalance	1-10 MHz		0.01		dB
	10-9000 MHz		0.10		dB
	9000-18000 MHz		0.20		dB
VSWR	SUM Port		1.15		(:1)
	OUT Ports		1.00		(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

COAXIAL CONNECTIONS	
SUM PORT	3
PORT 1	1
PORT 2	2

Functional Diagram



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS



REV. X2
ZFRSC-ED13066
9/27/2010
Page 1 of 1






Typical Performance Data

FREQUENCY (MHz)	TOTAL LOSS ¹ (dB)		AMPLITUDE UNBALANCE (dB)	ISOLATION (dB)	PHASE UNBALANCE (deg.)	FREQUENCY (MHz)	VSWR		
	S-1	S-2					S	(:1) 1	2
1.0	6.01	6.00	0.01	6.00	0.04	1.0	1.01	1.01	1.01
500.0	6.09	6.11	0.03	6.06	0.38	500.0	1.00	1.01	1.01
1000.0	6.09	6.10	0.01	6.09	0.49	1000.0	1.01	1.01	1.01
1250.0	6.11	6.10	0.01	6.12	0.63	1250.0	1.01	1.01	1.01
1500.0	6.14	6.12	0.01	6.15	0.80	1500.0	1.02	1.01	1.00
1750.0	6.14	6.14	0.01	6.16	1.00	1750.0	1.03	1.01	1.01
2000.0	6.12	6.12	0.01	6.19	1.07	2000.0	1.05	1.01	1.01
2250.0	6.13	6.12	0.01	6.21	1.16	2250.0	1.06	1.02	1.02
2500.0	6.17	6.15	0.02	6.25	1.27	2500.0	1.07	1.02	1.02
2750.0	6.22	6.19	0.03	6.29	1.45	2750.0	1.07	1.03	1.03
3000.0	6.22	6.20	0.02	6.33	1.53	3000.0	1.09	1.03	1.04
3250.0	6.23	6.19	0.04	6.35	1.61	3250.0	1.09	1.03	1.04
3500.0	6.25	6.21	0.04	6.36	1.88	3500.0	1.10	1.03	1.03
3750.0	6.27	6.25	0.02	6.37	2.06	3750.0	1.09	1.03	1.03
4000.0	6.30	6.26	0.03	6.38	2.01	4000.0	1.09	1.03	1.02
4250.0	6.31	6.26	0.05	6.41	2.04	4250.0	1.09	1.02	1.02
4500.0	6.33	6.24	0.09	6.41	2.13	4500.0	1.09	1.03	1.02
4750.0	6.35	6.25	0.10	6.41	2.51	4750.0	1.09	1.03	1.02
5000.0	6.34	6.28	0.05	6.39	2.71	5000.0	1.08	1.04	1.03
5250.0	6.32	6.27	0.05	6.40	2.43	5250.0	1.08	1.05	1.04
5500.0	6.35	6.24	0.11	6.41	2.24	5500.0	1.08	1.05	1.05
5750.0	6.40	6.24	0.15	6.43	2.30	5750.0	1.08	1.06	1.06
6000.0	6.42	6.25	0.17	6.43	2.75	6000.0	1.07	1.07	1.07
6250.0	6.39	6.26	0.13	6.43	2.78	6250.0	1.08	1.07	1.08
6500.0	6.36	6.25	0.11	6.44	2.40	6500.0	1.08	1.08	1.07
6750.0	6.40	6.25	0.15	6.46	2.25	6750.0	1.09	1.08	1.08
7000.0	6.42	6.26	0.17	6.48	2.43	7000.0	1.10	1.08	1.08
7250.0	6.44	6.27	0.18	6.50	2.49	7250.0	1.11	1.08	1.08
7500.0	6.41	6.27	0.14	6.51	2.50	7500.0	1.13	1.08	1.08
7750.0	6.39	6.26	0.13	6.51	2.24	7750.0	1.14	1.09	1.08
8000.0	6.39	6.28	0.11	6.52	2.40	8000.0	1.15	1.08	1.08
8250.0	6.40	6.29	0.11	6.53	2.50	8250.0	1.16	1.08	1.07
8500.0	6.40	6.30	0.11	6.54	2.46	8500.0	1.17	1.07	1.08
8750.0	6.45	6.31	0.14	6.56	2.84	8750.0	1.18	1.07	1.07
9000.0	6.48	6.35	0.13	6.56	2.92	9000.0	1.18	1.07	1.07
9250.0	6.44	6.35	0.09	6.56	3.21	9250.0	1.18	1.06	1.06
9500.0	6.41	6.33	0.08	6.58	3.29	9500.0	1.20	1.06	1.06
9750.0	6.44	6.38	0.07	6.60	3.56	9750.0	1.20	1.05	1.06
10000.0	6.52	6.43	0.10	6.61	3.69	10000.0	1.20	1.05	1.06
10250.0	6.54	6.45	0.09	6.61	3.69	10250.0	1.19	1.04	1.04
10500.0	6.49	6.40	0.09	6.59	4.07	10500.0	1.19	1.04	1.04
10750.0	6.44	6.43	0.01	6.58	4.23	10750.0	1.20	1.03	1.03
11000.0	6.47	6.49	0.02	6.54	4.11	11000.0	1.20	1.03	1.02
11250.0	6.54	6.51	0.02	6.53	4.08	11250.0	1.18	1.05	1.02
11500.0	6.58	6.49	0.09	6.48	4.54	11500.0	1.17	1.06	1.02
11750.0	6.55	6.49	0.05	6.42	4.95	11750.0	1.17	1.09	1.03
12000.0	6.56	6.60	0.04	6.38	4.56	12000.0	1.17	1.10	1.05
12250.0	6.59	6.66	0.06	6.32	3.90	12250.0	1.16	1.13	1.08
12500.0	6.67	6.68	0.01	6.33	4.17	12500.0	1.14	1.17	1.11
12750.0	6.74	6.71	0.03	6.34	5.08	12750.0	1.13	1.20	1.12
13000.0	6.80	6.84	0.04	6.36	5.36	13000.0	1.13	1.23	1.13
13250.0	6.90	6.97	0.07	6.38	5.16	13250.0	1.13	1.23	1.13
13500.0	6.94	7.01	0.07	6.42	4.63	13500.0	1.12	1.26	1.14
13750.0	6.97	7.03	0.05	6.48	4.98	13750.0	1.10	1.26	1.15
14000.0	7.03	7.14	0.11	6.61	5.57	14000.0	1.09	1.27	1.13
14250.0	7.13	7.23	0.11	6.76	6.05	14250.0	1.07	1.27	1.13
14500.0	7.18	7.25	0.07	6.88	5.96	14500.0	1.08	1.24	1.12
14750.0	7.12	7.23	0.12	6.97	6.47	14750.0	1.09	1.26	1.15
15000.0	7.09	7.22	0.13	7.09	6.03	15000.0	1.11	1.26	1.18
15250.0	7.20	7.27	0.07	7.20	5.90	15250.0	1.14	1.28	1.21
15500.0	7.28	7.31	0.04	7.28	6.30	15500.0	1.18	1.31	1.25
15750.0	7.27	7.24	0.03	7.28	7.04	15750.0	1.22	1.31	1.29
16000.0	7.14	7.19	0.06	7.24	7.47	16000.0	1.26	1.34	1.32
16250.0	6.97	7.12	0.15	7.19	7.09	16250.0	1.29	1.35	1.34
16500.0	6.89	7.09	0.20	7.11	6.82	16500.0	1.31	1.35	1.35
16750.0	6.97	7.00	0.03	7.06	6.46	16750.0	1.31	1.35	1.33
17000.0	7.12	6.90	0.23	6.95	7.23	17000.0	1.27	1.29	1.29
17250.0	6.97	6.71	0.26	6.82	8.72	17250.0	1.21	1.26	1.24
17500.0	6.69	6.57	0.12	6.68	8.47	17500.0	1.14	1.18	1.18
17750.0	6.56	6.51	0.04	6.62	7.72	17750.0	1.08	1.13	1.13
18000.0	6.61	6.53	0.08	6.60	7.34	18000.0	1.05	1.08	1.08
18250.0	6.69	6.54	0.15	6.62	8.08	18250.0	1.13	1.06	1.09
18500.0	6.61	6.53	0.09	6.73	9.37	18500.0	1.24	1.11	1.15
18750.0	6.47	6.54	0.07	6.80	9.70	18750.0	1.32	1.17	1.22
19000.0	6.54	6.74	0.20	6.94	9.22	19000.0	1.39	1.20	1.27
19250.0	6.73	6.91	0.18	7.20	8.68	19250.0	1.48	1.29	1.34
19500.0	6.99	7.01	0.02	7.49	9.26	19500.0	1.59	1.31	1.39
19750.0	7.13	7.03	0.09	7.71	10.32	19750.0	1.64	1.31	1.40
20000.0	7.21	7.23	0.02	7.80	12.12	20000.0	1.58	1.29	1.39


¹Total Loss = Insertion Loss + 6dB Splitter Loss

2 Way-0° Resistive Power Splitter/Combiner ZFRSC-ED13066

Typical Performance Curves



Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L
JJJ245	.75 (19.05)	1.00 (25.40)	.58 (14.73)	.38 (9.65)	.29 (7.37)	.35 (8.89)	1.39 (35.31)	1.32 (33.53)	.10 (2.54)	.10 (2.54)	.595 (15.11)

CASE#	M	N	P	Q	WT. GRAM
JJJ245	1.190 (30.23)	.23 (5.84)	.995 (25.27)	.106 (2.69)	22.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Mounting bracket available upon request. Add suffix B to part number.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I