

Coaxial High Pass Filter

ZHFG-K2750+

50Ω 2900 to 16000 MHz



Generic photo used for illustration purposes only
CASE STYLE: UK3042

The Big Deal

- Good Power Handling, 4 W
- Temperature Stable
- Broadband Connectorized Package
- Good Rejection, 40 dB Typ.

Product Overview

ZHFG-K2750+ is a 50Ω high pass filter built in broadband connectorized package. Covering 2900-16000 MHz bandwidth, these units offer good matching within the passband and good rejection in stopband. ZHFG-K2750+ offer low insertion loss, and good power handling capability. It handles up to 4W RF input power and provides a wide operating temperature range from -55°C to 125°C.

Key Features

Feature	Advantages
Low Passband Insertion Loss	Suitable for high performance applications.
4W Power Handling	Supports a range of system power requirements.
Connectorized Package	The connectorized package is easy to interface with other devices and well suited for test setups.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



High Pass Filter

50Ω 2900 to 16000 MHz

ZHFG-K2750+



Features

- Temperature Stable
- Good Power Handling, 4 W

Generic photo used for illustration purposes only

CASE STYLE: UK3042
Connectors Model
2.92mm-F ZHFG-K2750+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Applications

- Transmitters / Receivers
- Test and Measurements
- Military Applications
- Telecommunications and Broadband Wireless Systems
- 5G Sub 6 GHz
- WiFi 6E and X-band Radar

Functional Schematic



Electrical Specifications at 25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Stopband	Rejection	DC-F1	DC - 1000	30	40	-	dB
		F1-F2	1000 - 2000	30	37	-	dB
	Freq. Cut-Off	F3*	2750	-	3.0	-	dB
Passband	Insertion Loss	F4-F5	2900 - 3100	-	2.0	-	dB
		F5-F6	3100 - 3500	-	1.5	2.5	dB
		F6-F7	3500 - 14000	-	1.4	2.2	dB
		F7-F8	14000 - 16000	-	1.6	-	dB
	Return Loss	F4-F8	2900 - 16000	-	12	-	dB

In Applications where DC voltage is present at either input or output ports, DC blocks are required.

* Typically, a $\pm 5\%$ frequency deviation from the stated value may occur on a unit-to-unit basis.

Maximum Ratings





Operating Temperature	-55°C to 125°C
Storage Temperature	-55°C to 125°C
RF Power Input*	4W max. @ 25°C

*Passband rating, derate linearly to 0.7W at 125°C ambient
Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
10	73.22	0.15
250	51.75	0.40
500	46.08	0.51
1000	40.66	0.57
1500	37.54	0.52
2000	44.08	0.59
2100	41.78	0.67
2200	30.48	0.81
2320	21.31	1.13
2500	10.54	2.66
2700	3.48	10.18
2750	2.78	13.75
2900	1.85	30.76
3100	1.47	29.97
3500	1.19	21.26
5000	0.88	44.00
8000	0.86	26.03
10000	1.06	14.99
14000	1.29	13.89
16000	1.47	16.96

Typical Frequency Response



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Coaxial Connections

PORT - 1	2.92mm-Female
PORT - 2	2.92mm-Female

Outline Drawing



Outline Dimensions (inch mm)

A	B	C	D	E	F
.68	.60	.39	.200	.10	.400
17.1	15.2	10.0	5.08	2.5	10.16
G	H	J	K		Wt.
.24	.070	.22	.30		grams
6.0	1.78	5.5	7.6		24

Note: Please refer to case style drawing for details

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp






Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
10	76.84	73.22	82.16	0.10	0.15	0.20	0.11	0.15	0.22
20	72.45	73.68	72.61	0.12	0.17	0.23	0.13	0.19	0.25
80	61.10	61.13	61.05	0.18	0.25	0.34	0.20	0.27	0.37
100	59.18	59.25	59.21	0.20	0.27	0.36	0.22	0.29	0.39
150	55.86	55.86	55.97	0.24	0.32	0.42	0.26	0.34	0.45
200	53.50	53.52	53.62	0.28	0.36	0.47	0.30	0.38	0.49
250	51.71	51.75	51.80	0.31	0.40	0.51	0.32	0.41	0.53
300	50.20	50.22	50.26	0.34	0.43	0.54	0.35	0.44	0.56
350	48.93	48.97	49.01	0.36	0.46	0.58	0.37	0.47	0.59
400	47.83	47.90	47.94	0.37	0.48	0.60	0.38	0.49	0.62
450	46.89	46.95	47.03	0.39	0.50	0.63	0.39	0.50	0.63
500	46.04	46.08	46.19	0.40	0.51	0.64	0.40	0.52	0.65
600	44.59	44.63	44.74	0.42	0.54	0.67	0.42	0.54	0.68
700	43.37	43.45	43.55	0.43	0.56	0.69	0.43	0.55	0.69
800	42.34	42.38	42.48	0.44	0.57	0.70	0.44	0.56	0.69
900	41.42	41.48	41.57	0.45	0.57	0.71	0.44	0.57	0.70
1000	40.60	40.66	40.74	0.44	0.57	0.70	0.44	0.56	0.69
1100	39.86	39.90	39.99	0.44	0.56	0.69	0.43	0.55	0.68
1200	39.17	39.21	39.30	0.43	0.56	0.68	0.42	0.54	0.67
1300	38.55	38.58	38.66	0.42	0.55	0.67	0.42	0.53	0.65
1400	37.97	38.01	38.09	0.41	0.54	0.65	0.41	0.52	0.64
1500	37.49	37.54	37.62	0.40	0.52	0.64	0.40	0.51	0.63
1600	37.13	37.20	37.31	0.39	0.52	0.63	0.39	0.51	0.62
1700	37.01	37.13	37.31	0.39	0.52	0.63	0.39	0.51	0.63
1800	37.35	37.59	37.91	0.39	0.52	0.65	0.40	0.52	0.64
1900	38.67	39.20	39.88	0.41	0.55	0.67	0.42	0.54	0.68
2000	42.76	44.08	45.31	0.44	0.59	0.73	0.45	0.59	0.74
2100	45.27	41.78	38.42	0.50	0.67	0.84	0.52	0.68	0.85
2200	32.32	30.48	28.51	0.61	0.81	1.02	0.63	0.82	1.04
2320	22.61	21.31	19.82	0.87	1.13	1.45	0.90	1.16	1.49
2500	11.44	10.54	9.55	2.06	2.66	3.49	2.13	2.75	3.62
2700	3.57	3.48	3.44	8.51	10.18	12.31	8.80	10.56	12.84
2750	2.72	2.78	2.87	11.82	13.75	16.14	12.27	14.32	16.87
2900	1.66	1.85	2.06	27.74	30.76	32.29	28.87	30.02	28.65
2960	1.49	1.70	1.91	44.46	43.74	33.12	34.07	31.51	28.25
3000	1.42	1.62	1.83	41.14	37.28	30.67	32.37	30.45	27.50
3060	1.33	1.52	1.73	33.61	31.92	27.62	31.08	29.62	26.52
3100	1.28	1.47	1.68	31.82	29.97	26.12	31.00	29.17	25.82
3160	1.21	1.41	1.61	29.96	27.72	24.31	31.39	28.44	24.72
3200	1.18	1.37	1.57	28.82	26.45	23.32	31.20	27.67	23.98
3260	1.13	1.32	1.52	27.23	24.88	22.12	29.90	26.26	22.86
3300	1.10	1.29	1.49	26.24	24.00	21.48	28.69	25.32	22.23
3360	1.07	1.26	1.44	24.92	22.89	20.72	26.87	24.01	21.38
3400	1.05	1.23	1.42	24.17	22.29	20.32	25.81	23.25	20.90
3460	1.02	1.20	1.39	23.26	21.59	19.91	24.48	22.32	20.35
3500	1.00	1.19	1.37	22.79	21.26	19.71	23.74	21.81	20.04
3560	0.98	1.16	1.34	22.22	20.88	19.55	22.81	21.19	19.71
3600	0.96	1.15	1.32	21.95	20.72	19.52	22.33	20.88	19.55
3660	0.94	1.12	1.30	21.67	20.59	19.56	21.78	20.55	19.42
3700	0.93	1.11	1.28	21.58	20.58	19.66	21.50	20.37	19.38
4000	0.86	1.03	1.18	22.43	21.84	21.65	21.09	20.46	20.16
5000	0.72	0.88	1.01	40.45	44.00	38.12	32.31	32.73	32.43
6000	0.68	0.84	0.96	34.74	31.59	28.96	27.66	25.69	24.16
7000	0.68	0.84	0.96	42.05	41.94	36.88	25.13	24.26	24.02
8000	0.68	0.86	0.97	27.03	26.03	27.86	25.41	24.73	26.29
10000	0.86	1.06	1.22	15.08	14.99	14.46	14.88	14.81	14.38
12000	0.98	1.21	1.38	13.65	13.86	13.55	14.07	14.29	14.00
14000	1.01	1.29	1.46	14.15	13.89	14.09	13.72	13.37	13.65
15000	1.00	1.27	1.45	16.16	16.80	17.66	16.32	17.10	18.65
16000	1.12	1.47	1.78	17.93	16.96	15.33	23.17	21.10	18.22

Typical Performance Data


FREQ.	GROUP DELAY		
(MHz)	(nsec)		
	@-55°C	@+25°C	@+125°C
2900	0.84	0.81	0.78
3100	0.64	0.62	0.61
3300	0.53	0.52	0.51
3500	0.46	0.46	0.45
3700	0.41	0.41	0.40
4000	0.37	0.37	0.37
4300	0.34	0.33	0.33
4600	0.31	0.31	0.31
4900	0.29	0.29	0.29
5200	0.28	0.27	0.28
5500	0.26	0.26	0.26
5800	0.25	0.25	0.25
6100	0.25	0.24	0.25
6400	0.24	0.24	0.24
6700	0.23	0.23	0.23
7000	0.23	0.23	0.23
7300	0.22	0.22	0.23
7600	0.22	0.22	0.22
7900	0.22	0.22	0.22
8200	0.22	0.22	0.22
8500	0.21	0.21	0.22
8800	0.21	0.21	0.22
9100	0.21	0.21	0.21
9400	0.21	0.21	0.21
9700	0.21	0.21	0.21
10000	0.21	0.21	0.21
10300	0.21	0.21	0.21
10600	0.20	0.21	0.21
10900	0.20	0.20	0.21
11200	0.20	0.20	0.21
11500	0.20	0.20	0.21
11800	0.20	0.20	0.21
12100	0.20	0.20	0.21
12400	0.20	0.20	0.21
12700	0.21	0.21	0.21
13000	0.21	0.21	0.21
13500	0.21	0.21	0.21
14000	0.21	0.21	0.21
14500	0.21	0.21	0.22
15000	0.22	0.22	0.22
16000	0.23	0.24	0.24

Typical Performance Curves



Outline Dimensions

UK3042



CASE#	A	B	C	D	E	F
UK3042	.68 (17.1)	.60 (15.2)	.39 (10.0)	.200 (5.08)	.10 (2.5)	.400 (10.16)

CASE#	G	H	J	K	WT.GRAMS
UK3042	.24 (6.0)	.070 (1.78)	.22 (5.5)	.30 (7.6)	24

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .050$; 3 Pl. $\pm .015$

Notes:

- Case material: Brass alloy.
- Case Finish:
 - Case & Cover of the units –Gold plating.
- Refer to the individual model data sheet for the type of connectors available.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet