

Power Splitter/Combiner

ZFSC-4-1W+

4 Way-0° 50Ω 10 to 500 MHz


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1W max.
Internal Dissipation	0.250W max.
Permanent damage may occur if any of these limits are exceeded.	

Coaxial Connections

SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3
PORT 4	4

Outline Drawing



Outline Dimensions (inch mm)

A	B	C	D	E	F	G	H
1.25	1.25	.75	.63	.38	.61	--	.80
31.75	31.75	19.05	16.00	9.65	15.49	--	20.32

J	K	L	M	N	P	Q	wt
.80	.76	.125	1.688	2.18	.75	.07	grams
20.32	19.30	3.18	42.88	55.37	19.05	1.78	85.0

Features

- wideband, 10 to 500 MHz
- good isolation, 23 dB typ.
- rugged shielded case
- good VSWR, 1.15:1

Applications

- VHF/UHF
- radio communication



Generic photo used for illustration purposes only

CASE STYLE: G15

Connectors	Model
BNC	ZFSC-4-1W-BNC+
SMA	ZFSC-4-1W-S+
BRACKET (OPTION "B")	

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications




FREQ. RANGE (MHz)	ISOLATION (dB)						INSERTION LOSS (dB) ABOVE 6.0 dB						PHASE UNBALANCE (Degrees)			AMPLITUDE UNBALANCE (dB)		
	L		M		U		L		M		U		L	M	U	L	M	U
	f _L -f _U	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Max.	Typ.	Max.	Typ.	Max.	Max.	Max.	Max.	Max.	Max.
10-500	23	20	23	20	23	20	0.6	1.5	0.6	1.5	0.6	1.5	4	8	8	0.2	0.3	0.4

L = low range [f_L to 10 f_L] M = mid range [10 f_L to f_U/2] U = upper range [f_U/2 to f_U]

Typical Performance Data

Freq. (MHz)	Total Loss ¹ (dB)				Amp. Unbal. (dB)	Isolation (dB)			Phase Unbal. (deg.)	VSWR				
	S-1	S-2	S-3	S-4		1-2	1-4	3-4		S	1	2	3	4
10	6.36	6.35	6.35	6.35	0.01	42.49	31.51	42.51	0.07	1.11	1.04	1.04	1.04	1.04
50	6.36	6.36	6.36	6.36	0.01	42.13	31.71	42.28	0.28	1.11	1.02	1.02	1.03	1.03
70	6.39	6.38	6.39	6.38	0.01	41.32	31.80	41.74	0.38	1.11	1.02	1.02	1.03	1.02
100	6.40	6.40	6.40	6.39	0.00	40.14	31.90	40.81	0.54	1.11	1.02	1.03	1.03	1.03
130	6.42	6.40	6.41	6.41	0.01	38.97	31.90	39.89	0.68	1.11	1.03	1.03	1.03	1.03
150	6.43	6.42	6.42	6.43	0.01	38.33	31.88	39.37	0.78	1.11	1.03	1.03	1.03	1.03
180	6.45	6.43	6.43	6.44	0.02	37.56	31.84	38.69	0.92	1.11	1.03	1.04	1.04	1.04
200	6.47	6.45	6.45	6.47	0.02	37.18	31.81	38.39	1.05	1.11	1.04	1.04	1.04	1.04
230	6.48	6.45	6.46	6.48	0.03	36.66	31.66	37.95	1.16	1.12	1.04	1.05	1.05	1.04
250	6.50	6.46	6.46	6.48	0.04	36.50	31.61	37.84	1.25	1.12	1.04	1.06	1.06	1.05
310	6.53	6.47	6.46	6.52	0.07	36.39	31.33	37.92	1.52	1.13	1.05	1.07	1.08	1.06
350	6.55	6.48	6.48	6.53	0.07	36.90	31.27	38.63	1.74	1.13	1.06	1.08	1.09	1.06
410	6.59	6.49	6.48	6.57	0.12	38.42	30.99	39.94	1.88	1.13	1.07	1.11	1.12	1.07
450	6.67	6.56	6.53	6.63	0.13	39.87	30.96	40.10	2.05	1.13	1.08	1.12	1.13	1.08
500	6.70	6.54	6.52	6.66	0.18	39.29	30.72	37.36	2.17	1.14	1.09	1.14	1.16	1.09

1. Total Loss = Insertion Loss + 6dB splitter loss.



electrical schematic



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



4 Way-0° Power Splitter/Combiner

ZFSC-4-1W+

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)				AMP. UNBAL. (dB)	ISOLATION (dB)			PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)				
	S-1	S-2	S-3	S-4		1-2	1-4	3-4			S	1	2	3	4
10.0	6.36	6.35	6.35	6.35	0.01	42.49	31.51	42.51	0.07	10.0	1.11	1.04	1.04	1.04	1.04
18.0	6.35	6.34	6.34	6.35	0.01	42.71	31.57	42.70	0.12	18.0	1.11	1.03	1.03	1.03	1.03
26.0	6.35	6.35	6.35	6.35	0.00	42.74	31.57	42.63	0.13	26.0	1.11	1.03	1.03	1.03	1.03
34.0	6.35	6.35	6.35	6.35	0.01	42.54	31.60	42.59	0.17	34.0	1.11	1.03	1.03	1.03	1.03
42.0	6.36	6.35	6.35	6.35	0.01	42.38	31.67	42.45	0.23	42.0	1.11	1.02	1.03	1.03	1.03
50.0	6.36	6.36	6.36	6.36	0.01	42.13	31.71	42.28	0.28	50.0	1.11	1.02	1.02	1.03	1.03
60.0	6.38	6.37	6.37	6.38	0.01	41.74	31.75	42.09	0.34	60.0	1.11	1.02	1.02	1.03	1.02
70.0	6.39	6.38	6.39	6.38	0.01	41.32	31.80	41.74	0.38	70.0	1.11	1.02	1.02	1.03	1.02
80.0	6.40	6.39	6.39	6.39	0.01	40.95	31.84	41.45	0.42	80.0	1.11	1.02	1.02	1.03	1.02
90.0	6.40	6.38	6.40	6.39	0.01	40.56	31.87	41.12	0.50	90.0	1.11	1.02	1.02	1.03	1.03
100.0	6.40	6.40	6.40	6.39	0.00	40.14	31.90	40.81	0.54	100.0	1.11	1.02	1.03	1.03	1.03
110.0	6.40	6.40	6.39	6.41	0.01	39.76	31.90	40.49	0.58	110.0	1.11	1.02	1.03	1.03	1.03
120.0	6.41	6.40	6.41	6.41	0.01	39.34	31.90	40.19	0.63	120.0	1.11	1.03	1.03	1.03	1.03
130.0	6.42	6.40	6.41	6.41	0.01	38.97	31.90	39.89	0.68	130.0	1.11	1.03	1.03	1.03	1.03
140.0	6.43	6.42	6.42	6.43	0.01	38.67	31.89	39.58	0.72	140.0	1.11	1.03	1.03	1.03	1.03
150.0	6.43	6.42	6.42	6.43	0.01	38.33	31.88	39.37	0.78	150.0	1.11	1.03	1.03	1.03	1.03
160.0	6.44	6.42	6.43	6.43	0.02	38.07	31.88	39.04	0.84	160.0	1.11	1.03	1.03	1.04	1.03
170.0	6.44	6.42	6.42	6.43	0.02	37.77	31.85	38.89	0.85	170.0	1.11	1.03	1.04	1.04	1.03
180.0	6.45	6.43	6.43	6.44	0.02	37.56	31.84	38.69	0.92	180.0	1.11	1.03	1.04	1.04	1.04
190.0	6.46	6.44	6.45	6.46	0.02	37.37	31.83	38.50	0.98	190.0	1.11	1.03	1.04	1.04	1.04
200.0	6.47	6.45	6.45	6.47	0.02	37.18	31.81	38.39	1.05	200.0	1.11	1.04	1.04	1.04	1.04
210.0	6.47	6.45	6.45	6.47	0.03	36.92	31.73	38.15	1.09	210.0	1.12	1.04	1.05	1.05	1.04
220.0	6.47	6.44	6.44	6.46	0.03	36.82	31.67	38.03	1.07	220.0	1.12	1.04	1.05	1.05	1.04
230.0	6.48	6.45	6.46	6.48	0.03	36.66	31.66	37.95	1.16	230.0	1.12	1.04	1.05	1.05	1.04
240.0	6.51	6.47	6.46	6.50	0.04	36.55	31.64	37.90	1.23	240.0	1.12	1.04	1.05	1.06	1.05
250.0	6.50	6.46	6.46	6.48	0.04	36.50	31.61	37.84	1.25	250.0	1.12	1.04	1.06	1.06	1.05
270.0	6.50	6.46	6.46	6.49	0.04	36.38	31.55	37.80	1.38	270.0	1.12	1.05	1.06	1.06	1.05
290.0	6.57	6.52	6.51	6.56	0.05	36.37	31.51	37.87	1.40	290.0	1.12	1.05	1.07	1.07	1.05
310.0	6.53	6.47	6.46	6.52	0.07	36.39	31.33	37.92	1.52	310.0	1.13	1.05	1.07	1.08	1.06
330.0	6.56	6.48	6.48	6.54	0.08	36.58	31.29	38.14	1.62	330.0	1.13	1.06	1.08	1.08	1.06
350.0	6.55	6.48	6.48	6.53	0.07	36.90	31.27	38.63	1.74	350.0	1.13	1.06	1.08	1.09	1.06
370.0	6.62	6.55	6.54	6.61	0.08	37.34	31.22	39.04	1.74	370.0	1.13	1.06	1.09	1.10	1.07
390.0	6.62	6.54	6.53	6.61	0.09	37.84	31.09	39.47	1.85	390.0	1.13	1.07	1.10	1.11	1.07
410.0	6.59	6.49	6.48	6.57	0.12	38.42	30.99	39.94	1.88	410.0	1.13	1.07	1.11	1.12	1.07
430.0	6.64	6.53	6.51	6.61	0.12	39.23	30.99	40.27	2.06	430.0	1.13	1.08	1.11	1.12	1.08
450.0	6.67	6.56	6.53	6.63	0.13	39.87	30.96	40.10	2.05	450.0	1.13	1.08	1.12	1.13	1.08
460.0	6.71	6.59	6.57	6.67	0.14	40.08	30.91	39.76	2.05	460.0	1.13	1.08	1.13	1.14	1.08
470.0	6.71	6.60	6.57	6.69	0.14	40.10	30.86	39.33	2.10	470.0	1.14	1.08	1.13	1.14	1.08
480.0	6.70	6.56	6.53	6.65	0.16	40.03	30.77	38.75	2.04	480.0	1.14	1.09	1.13	1.15	1.09
490.0	6.68	6.54	6.52	6.65	0.16	39.77	30.75	38.09	2.10	490.0	1.14	1.09	1.14	1.15	1.09
500.0	6.70	6.54	6.52	6.66	0.18	39.29	30.72	37.36	2.17	500.0	1.14	1.09	1.14	1.16	1.09

¹ Total Loss = Insertion Loss+ 6dB Splitter Loss

REV. X2
ZFSC-4-1W+
100721
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661








The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



4 Way-0° Power Splitter/Combiner

ZFSC-4-1W+

Typical Performance Curves




REV. X2
ZFSC-4-1W+
100721
Page 1 of 1



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Outline Dimensions



CASE #	A	B	C	D	E	F	G	H	J	K	L
G15	1.25 (31.75)	1.25 (31.75)	.75 (19.05)	.63 (16.00)	.38 (9.65)	.61 (15.49)	--	.80 (20.32)	.80 (20.32)	.76 (19.30)	.125 (3.18)

CASE #	M	N	P	Q	WT. GRAM
G15	1.688 (42.88)	2.18 (55.37)	.75 (19.05)	.07 (1.78)	85.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Mounting bracket available on request. Add suffix B to part number.
- For Bracket version, option "B" dimension "K" changes from .76 to .90 inches when connectors are type TNC.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I