



COAXIAL HIGH IP3

Low Noise Amplifier

ZHL-3010+

50Ω Medium High Power 50 to 1000 MHz SMA Female

FEATURES

- Wideband, 50 to 1000 MHz
- Low Noise, 5.5 dB Typ.
- High IP3, +46 dBm Typ.
- Very High IP2, +68 to +83 dBm Typ.
- Protected by US Patent 6,943,629



Generic photo used for illustration purposes only

APPLICATIONS

- VHF/UHF
- Cellular
- Test Equipment
- Instrumentation
- Laboratory

Model No.	ZHL-3010+
Case Style	S32
Connectors	SMA female

+RoHS Compliant
 The +Suffix identifies RoHS Compliance.
 See our website for methodologies and qualifications

ELECTRICAL SPECIFICATIONS

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Units
Frequency Range		50		1000	MHz
Noise Figure	50-1000		5.5		dB
Gain	50-1000	30			dB
Gain Flatness	50-1000			±1.0	dB
Output Power at 1 dB Compression	50-1000	+26			dBm
Output Third Order Intercept Point	50-1000		+46		dBm
Input VSWR	50-1000			2.5	:1
Output VSWR	50-1000			2.0	:1
DC Supply Voltage			+12		V
Supply Current				1.0	A

Open load is not recommended, may cause damage.
 With no load, derate max input power by 20 dB.

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-20 °C to +65 °C
Storage Temperature	-55 °C to +100 °C
DC Voltage	+13 V max.
RF Input Power (No Damage)	-3 dBm

Permanent damage may occur if any of these limits are exceeded.

REV. D
 ECO-017949
 ZHL-3010+
 MCL NY
 260305






COAXIAL HIGH IP3

Low Noise Amplifier


ZHL-3010+

50Ω Medium High Power 50 to 1000 MHz SMA Female

OUTLINE DRAWING



MOUNTING INFORMATION FOR MODELS WITHOUT HEATSINK



OUTLINE DIMENSIONS (Inch/mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt	
3.75	2.00	1.80	.19	3.375	.19	1.625	.144	.50	.40	.50	1.30	.10	.38	3.00	.30	2.60	.80	grams	
95.25	50.80	45.72	4.83	85.73	4.83	41.28	3.66	12.70	10.16	12.70	33.02	2.54	9.65	76.20	7.62	66.04	20.32	220.0	
																		wt. w/o heat sink	150



COAXIAL HIGH IP3






Low Noise Amplifier

ZHL-3010+

50Ω Medium High Power 50 to 1000 MHz SMA Female

TYPICAL PERFORMANCE DATA/CURVES

FREQUENCY (MHz)	GAIN (dB)	DIRECTIVITY (dB)	VSWR (:1)		NOISE FIGURE (dB)	P _{OUT} at 1 dB COMPR. (dBm)
	+12 V	+12 V	IN	OUT	+12 V	+12 V
50.0	36.37	16.10	1.78	1.28	5.14	29.62
155.6	36.23	15.10	2.12	1.77	5.19	30.12
261.1	36.00	15.80	2.19	1.81	5.40	30.67
366.7	36.09	16.50	2.04	1.44	5.44	31.55
472.2	36.21	16.40	1.94	1.07	5.46	30.87
577.8	36.00	15.30	1.91	1.15	5.40	30.76
683.3	35.30	18.20	1.74	1.18	5.30	30.08
788.9	35.60	18.60	1.88	1.01	5.24	30.18
894.4	35.48	17.40	2.08	1.27	5.33	29.93
1000.0	35.29	20.20	2.04	1.56	5.43	28.74



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Low Noise Amplifier

ZHL-3010+

Typical Performance Data

FREQUENCY (MHz)	GAIN (dB) 12V	DIRECTIVITY (dB) 12V	VSWR IN (:1) 12V	VSWR OUT (:1) 12V	NOISE FIGURE (dB) 12V	Pout at 1dB Comp. (dBm) 12V
50.0	36.37	16.12	1.78	1.28	5.14	29.62
155.6	36.23	15.05	2.12	1.77	5.19	30.12
261.1	36.00	15.76	2.19	1.81	5.40	30.67
366.7	36.09	16.47	2.04	1.44	5.44	31.55
472.2	36.21	16.41	1.94	1.07	5.46	30.87
577.8	36.00	15.29	1.91	1.15	5.40	30.76
683.3	35.30	18.17	1.74	1.18	5.30	30.08
788.9	35.60	18.58	1.88	1.01	5.24	30.18
894.4	35.48	17.36	2.08	1.27	5.33	29.93
1000.0	35.29	20.20	2.04	1.56	5.43	28.74

REV. X1
ZHL-3010+
060914
Page 1 of 1








IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves



Outline Dimensions



MOUNTING INFORMATION FOR MODELS WITHOUT HEATSINK



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
S32	3.75 (95.25)	2.00 (50.80)	1.80 (45.72)	.19 (4.83)	3.375 (85.73)	.19 (4.83)	1.625 (41.28)	.144 (3.66)	.50 (12.70)	.40 (10.16)	.50 (12.70)	1.30 (33.02)	.10 (2.54)

CASE#	P	Q	R	S	T	WT. GRAMS	WT. WITHOUT HEATSINK GRAMS
S32	.38 (9.65)	3.00 (76.20)	.30 (7.62)	2.60 (66.04)	.80 (20.32)	220.0	150.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Heat sink finish: Black anodize.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-20° to 65° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Stabilization Bake	(non-operating) 125°C, 24 hours	- - -
Burn-in at Elevated Temp.	(DC on) 160 hours at 85° C	MIL-STD-202, Method 108
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, except 100°C