



Mini-Circuits

(LTCC) COAXIAL

High Pass Filter

ZHFW-K9000+

50 Ω

10 to 19.5 GHz 2.92mm Female

KEY FEATURES

- Low Insertion Loss, 1.7 dB Typ.
- Return Loss, 11 dB Typ.
- Stopband Rejection, 42 dB Typ.
- Broadband Connectorized Package.
- Power Handling: 2.5 Watts

APPLICATIONS

- X Band Satellite
- Cellular Backhaul
- X Band Radar
- Test and Measurement


PRODUCT OVERVIEW

ZHFW-K9000+ is a 50 Ω high pass filter built in broad band connectorized package. Covering 10-19.5 GHz bandwidth, these units offer good matching within the passband and good rejection in stopband. ZHFW-K9000+ offer low insertion loss, and excellent power handling capability. It handles up to 2.5 W RF input power and provides a wide operating temperature range from -55°C to 125°C.



Generic photo used for illustration purposes only

FUNCTIONAL DIAGRAM

ELECTRICAL SPECIFICATIONS^{1,2} AT +25°C

Parameter		F#	Frequency (GHz)	Min.	Typ.	Max.	Units
Passband	Insertion Loss	F3-F4	10 - 11.5	—	2.4	—	dB
		F4-F5	11.5 - 17	—	1.7	2.3	
		F5-F6	17 - 19.5	—	1.7	—	
	Return Loss	F3-F4	10 - 11.5	—	12	—	dB
		F4-F5	11.5 - 17	—	13	—	
		F5-F6	17 - 19.5	—	11	—	
Stopband	Rejection	DC-F1	DC - 6	32	42	—	dB
		F1-F2	6 - 7.2	23	37	—	
	Freq. Cut-Off ³	Fc	9.1	—	3	—	dB

1. This filter is bi-directional, RF1 and RF2 ports may be interchanged, see S-Parameters for actual performance.

2. This component should not be used as a DC-block. In applications where DC voltage and/or current is present at either the input or output ports, external DC blocking capacitors are required.

3. Typical variation $\pm 5\%$.


ABSOLUTE MAXIMUM RATINGS⁴

Parameter	Ratings
Operating Temperature	-55°C to +125°C
Storage Temperature	-55°C to +125°C
Input Power ⁵	2.5 W @ +25°C

4. Permanent damage may occur if any of these limits are exceeded.

5. Power rating applies only to signals within the passband. Power rating above +25°C operating temperature decreases linearly to 0.6 W at +125°C.

TYPICAL FREQUENCY RESPONSE



Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR
ECO-027003
ZHFW-K9000+
EDU5170
URJ
250919

PAGE 1 OF 4



(LTCC) COAXIAL

High Pass Filter






ZHFW-K9000+

Mini-Circuits

50 Ω

10 to 19.5 GHz 2.92mm Female

TYPICAL PERFORMANCE GRAPHS





(LTCC) COAXIAL

High Pass Filter

ZHFW-K9000+

Mini-Circuits


50 Ω

10 to 19.5 GHz 2.92mm Female

CONNECTOR DESCRIPTION

Function	Marking on Unit	Connector
RF1 ¹	1	2.92mm Female
RF2 ¹	2	2.92mm Female

CASE STYLE DRAWING



Unit weight: 24grams

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm$.050"; 3 Pl. $\pm$.015"

PRODUCT MARKING*: ZHFW-K9000+

*Marking may contain other features or characters for internal lot control.



(LTCC) COAXIAL

High Pass Filter

ZHFW-K9000+

50Ω 10 to 19.5 GHz 2.92mm Female

ADDITIONAL INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance Data & Graphs	Data
	Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
Case Style	UK3042
RoHS Status	Compliant
Environmental Ratings	ENV124

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Coaxial High Pass Filter

ZHFW-K9000+






Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
10	77.89	73.20	73.65	0.07	0.11	0.15	0.09	0.14	0.18
100	71.33	70.03	71.11	0.33	0.45	0.58	0.37	0.47	0.60
500	57.31	57.35	57.35	0.37	0.50	0.64	0.41	0.53	0.66
1000	51.56	51.53	51.70	0.37	0.51	0.63	0.42	0.54	0.67
1500	48.32	48.34	48.47	0.35	0.49	0.60	0.39	0.51	0.61
2000	46.10	46.13	46.29	0.32	0.46	0.55	0.34	0.46	0.55
2500	44.62	44.66	44.73	0.29	0.42	0.50	0.31	0.42	0.49
3000	43.56	43.64	43.68	0.26	0.39	0.47	0.28	0.38	0.45
3500	42.99	43.06	43.20	0.26	0.39	0.47	0.28	0.39	0.45
4000	42.84	42.97	43.13	0.28	0.43	0.51	0.31	0.42	0.49
5000	44.40	44.73	45.01	0.44	0.62	0.74	0.47	0.61	0.72
5500	46.82	47.35	47.77	0.56	0.76	0.91	0.58	0.75	0.88
5800	49.59	50.44	51.29	0.62	0.84	1.00	0.65	0.83	0.98
6000	52.91	54.15	55.63	0.67	0.90	1.06	0.70	0.88	1.04
6200	59.27	61.32	61.21	0.71	0.95	1.12	0.74	0.94	1.10
6400	59.84	56.75	53.65	0.75	1.00	1.18	0.78	0.99	1.16
6600	50.81	48.99	47.14	0.78	1.04	1.22	0.81	1.04	1.21
6800	45.12	43.89	42.46	0.79	1.06	1.25	0.83	1.06	1.24
7000	40.84	39.80	38.53	0.82	1.09	1.28	0.86	1.09	1.27
7200	37.17	36.18	34.98	0.87	1.15	1.36	0.90	1.14	1.33
7425	33.32	32.37	31.17	0.95	1.24	1.48	0.95	1.21	1.42
7500	32.07	31.13	29.92	0.97	1.28	1.52	0.97	1.24	1.46
7950	24.65	23.62	22.25	1.24	1.61	1.99	1.17	1.49	1.81
8475	15.44	14.26	12.69	2.35	3.16	4.36	2.04	2.70	3.68
8975	6.53	5.74	4.89	9.27	12.45	17.85	7.36	9.40	12.08
9000	6.15	5.43	4.64	10.04	13.43	19.25	7.89	9.98	12.63
9100	4.83	4.33	3.86	13.75	18.20	25.22	10.18	12.29	14.54
10000	1.68	1.92	2.09	23.30	26.90	39.02	20.67	22.06	24.95
10500	1.41	1.67	1.87	22.46	20.36	17.99	20.81	19.68	18.17
11000	1.37	1.65	1.87	14.37	14.05	13.49	14.67	14.41	14.02
11500	1.42	1.69	1.89	12.15	12.23	12.23	12.72	12.75	12.81
12000	1.42	1.67	1.85	11.70	11.98	12.18	12.35	12.54	12.79
12500	1.36	1.61	1.78	11.83	12.19	12.32	12.49	12.79	13.02
13000	1.31	1.56	1.74	12.03	12.36	12.30	12.69	13.05	13.09
13500	1.27	1.52	1.72	12.40	12.60	12.44	13.10	13.39	13.25
14000	1.21	1.48	1.67	13.22	13.32	13.24	13.98	14.18	14.06
14500	1.13	1.41	1.59	14.79	14.81	15.00	15.75	15.82	15.92
14800	1.07	1.35	1.53	16.31	16.32	16.76	17.41	17.44	17.78
15000	1.03	1.31	1.49	17.61	17.66	18.25	18.84	18.85	19.38
15200	1.00	1.28	1.45	19.23	19.38	20.16	20.63	20.65	21.39
15400	0.96	1.24	1.42	21.34	21.60	22.62	22.97	22.99	23.96
15600	0.94	1.22	1.40	23.68	24.31	25.47	25.71	25.80	26.77
15800	0.92	1.20	1.39	25.86	26.86	27.58	28.21	28.12	28.30
16000	0.91	1.20	1.38	26.11	26.88	26.78	27.99	27.51	26.93
16200	0.91	1.20	1.39	24.23	24.41	24.24	25.32	24.68	24.25
16400	0.92	1.21	1.41	21.85	21.77	21.80	22.68	22.08	21.93
16600	0.93	1.24	1.43	19.83	19.66	19.82	20.48	19.93	19.97
16800	0.96	1.27	1.47	18.29	18.04	18.32	18.76	18.19	18.34
17000	0.99	1.30	1.50	17.01	16.75	17.12	17.32	16.77	16.98
17200	1.02	1.34	1.54	15.93	15.70	16.11	16.10	15.60	15.83
17400	1.05	1.38	1.58	15.05	14.87	15.30	15.06	14.62	14.85
17600	1.09	1.42	1.61	14.38	14.20	14.66	14.20	13.81	14.01
17800	1.12	1.45	1.65	13.84	13.68	14.14	13.51	13.14	13.31
18000	1.15	1.49	1.69	13.34	13.25	13.69	12.88	12.55	12.70
18200	1.18	1.52	1.72	12.97	12.92	13.35	12.36	12.09	12.22
18400	1.21	1.54	1.74	12.66	12.66	13.09	11.92	11.72	11.84
18600	1.23	1.56	1.76	12.43	12.47	12.88	11.59	11.44	11.55
19000	1.27	1.59	1.80	12.08	12.26	12.59	11.12	11.13	11.22
19200	1.28	1.60	1.81	12.01	12.24	12.58	11.00	11.07	11.20
19500	1.29	1.61	1.81	11.99	12.28	12.60	10.98	11.18	11.35

Typical Performance Data


FREQ.	GROUP DELAY		
(MHz)	(nsec)		
	@-55°C	@+25°C	@+125°C
10000	0.35	0.34	0.34
10250	0.33	0.32	0.32
10500	0.31	0.31	0.30
10750	0.30	0.29	0.29
11000	0.28	0.28	0.27
11250	0.27	0.27	0.26
11500	0.26	0.26	0.26
11750	0.25	0.25	0.25
12000	0.25	0.25	0.25
12250	0.24	0.24	0.24
12500	0.24	0.24	0.24
12750	0.23	0.23	0.23
13000	0.23	0.23	0.23
13250	0.23	0.23	0.22
13500	0.22	0.22	0.22
13750	0.22	0.22	0.22
14000	0.22	0.22	0.22
14250	0.22	0.21	0.22
14500	0.21	0.21	0.21
14750	0.21	0.21	0.21
15000	0.21	0.21	0.21
15250	0.21	0.21	0.21
15500	0.21	0.21	0.21
15750	0.21	0.21	0.21
16000	0.21	0.21	0.21
16250	0.21	0.21	0.21
16500	0.21	0.21	0.21
16750	0.20	0.20	0.20
17000	0.20	0.20	0.20
17250	0.20	0.20	0.20
17500	0.20	0.20	0.20
17750	0.20	0.20	0.20
18000	0.20	0.20	0.20
18250	0.20	0.20	0.20
18500	0.20	0.20	0.20
18750	0.20	0.20	0.20
19000	0.20	0.20	0.20
19250	0.20	0.20	0.20
19300	0.20	0.20	0.20
19500	0.20	0.20	0.20

Typical Performance Curves



Outline Dimensions

UK3042



CASE#	A	B	C	D	E	F
UK3042	.68 (17.1)	.60 (15.2)	.39 (10.0)	.200 (5.08)	.10 (2.5)	.400 (10.16)

CASE#	G	H	J	K	WT.GRAMS
UK3042	.24 (6.0)	.070 (1.78)	.22 (5.5)	.30 (7.6)	24

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .050$; 3 Pl. $\pm .015$

Notes:

- Case material: Brass alloy.
- Case Finish:
 - Case & Cover of the units –Gold plating.
- Refer to the individual model data sheet for the type of connectors available.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet