

Coaxial

Low Noise Amplifier

ZHL-0812MLN

50Ω


800 to 1200 MHz

Features

- very low noise figure, 1.6 dB max.
- wideband, 800 to 1200 MHz
- high dynamic range

Applications

- UHF
- cellular
- PCS/GSM



Case Style: FJ893

Connectors	Model	Price	Qty.
SMA	ZHL-0812MLN	Contact Sales Dept.	

NON-CATALOG

Electrical Specifications


Parameter	Frequency (MHz)	Min.	Typ.	Max.	Units
Frequency Range		800		1200	MHz
Noise Figure	800-1200	—	—	1.6	dB
Gain	800-1200	28	—	—	dB
Gain Flatness	800-1200	—	—	±1.0	dB
Output Power at 1dB compression	800-1200	—	+20	—	dBm
Output third order intercept point	800-1200	—	+33	—	dBm
Input VSWR	800-1200	—	—	2.5	:1
Output VSWR	800-1200	—	—	2.5	:1
DC Supply Voltage		—	15	—	V
Supply Current		—	—	300	mA

Noise Figure specified at room temperature, increases to 2.3 dB max. at +65°C

Open load is not recommended, potentially can cause damage.

With no load derate max input power by 20 dB

Outline Drawing



Maximum Ratings

Parameter	Ratings
Operating Temperature	-20°C to 65°C
Storage Temperature	-55°C to 100°C
DC Voltage	17V
Input RF Power (no damage)	0 dBm

Permanent damage may occur if any of these limits are exceeded.

Outline Dimensions (inch mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt
3.75	2.00	1.80	.19	3.375	.19	1.625	.144	.50	.40	.50	1.30	.10	.38	3.00	.30	2.60	.80	grams
95.25	50.80	45.72	4.83	85.73	4.83	41.28	3.66	12.70	10.16	12.70	33.02	2.54	9.65	76.20	7.62	66.04	20.32	220.0



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine www.minicircuits.com Provides ACTUAL Data Instantly at minicircuits.com






Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp.

For detailed performance specs
& shopping online see web site

REV. C
M134858
ZHL-0812MLN
111205
Page 1 of 2

NON-CATALOG

FREQUENCY (MHz)	GAIN (dB)			DIRECTIVITY (dB)			VSWR (:1)		NOISE FIGURE (dB)	POUT at 1 dB COMPR. (dBm)
	12V	15V	16V	12V	15V	16V	IN	OUT		
800.00	32.01	32.53	32.51	36.23	36.79	45.05	1.57	1.80	1.32	22.16
844.44	31.87	32.39	32.38	31.70	34.82	34.73	1.52	1.77	1.35	22.37
888.88	31.91	32.39	32.36	46.06	40.30	39.61	1.51	1.74	1.40	21.95
933.33	31.60	32.10	32.08	32.05	35.42	31.82	1.48	1.72	1.43	22.82
977.77	31.70	32.15	32.11	32.61	33.50	30.62	1.41	1.69	1.44	22.51
1022.22	31.46	31.93	31.90	30.83	34.90	32.15	1.31	1.60	1.40	23.21
1066.66	31.51	31.94	31.90	31.87	33.51	33.80	1.22	1.62	1.36	23.24
1111.11	31.30	31.72	31.68	32.34	32.94	34.17	1.22	1.59	1.33	23.22
1155.55	31.13	31.55	31.50	34.00	33.17	33.74	1.38	1.56	1.33	23.53
1200.00	30.90	31.27	32.20	33.22	31.39	31.70	1.64	1.53	1.36	23.83



Low Noise Amplifier

ZHL-0812MLN

Typical Performance Data

FREQUENCY (MHz)	GAIN (dB)			DIRECTIVITY (dB)			VSWR IN (:1) 15V	VSWR OUT (:1) 15V	NOISE FIGURE (dB) 15V	Pout at 1dB Comp. (dBm) 15V
	12V	15V	16V	12V	15V	16V				
800.0	32.01	32.53	32.51	36.23	36.79	45.95	1.57	1.80	1.36	22.16
844.4	31.87	32.39	32.38	31.70	34.82	34.73	1.52	1.77	1.40	22.37
888.9	31.91	32.39	32.36	46.06	40.30	39.61	1.51	1.74	1.44	21.95
933.3	31.60	32.10	32.08	32.65	35.42	31.92	1.48	1.72	1.42	22.82
977.8	31.70	32.15	32.11	32.61	33.50	30.62	1.41	1.69	1.39	22.51
1022.2	31.46	31.93	31.90	30.83	34.90	32.15	1.31	1.66	1.35	23.21
1066.7	31.51	31.94	31.90	31.67	33.51	33.80	1.22	1.62	1.33	23.24
1111.1	31.30	31.72	31.68	32.34	32.94	34.17	1.22	1.59	1.32	23.22
1155.6	31.13	31.55	31.50	34.00	33.17	33.74	1.38	1.56	1.39	23.53
1200.0	30.90	31.27	32.20	33.22	31.39	31.70	1.64	1.53	1.46	23.83

REV. X1

ZHL-0812MLN

060914

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661








The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Low Noise Amplifier

ZHL-0812MLN

Typical Performance Curves



REV. X1
ZHL-0812MLN
060914
Page 1 of 1




Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions



MOUNTING INFORMATION FOR MODELS WITHOUT HEATSINK



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
S32	3.75 (95.25)	2.00 (50.80)	1.80 (45.72)	.19 (4.83)	3.375 (85.73)	.19 (4.83)	1.625 (41.28)	.144 (3.66)	.50 (12.70)	.40 (10.16)	.50 (12.70)	1.30 (33.02)	.10 (2.54)

CASE#	P	Q	R	S	T	WT. GRAMS	WT. WITHOUT HEATSINK GRAMS
S32	.38 (9.65)	3.00 (76.20)	.30 (7.62)	2.60 (66.04)	.80 (20.32)	220.0	150.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Heat sink finish: Black anodize.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-20° to 65° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Stabilization Bake	(non-operating) 125°C, 24 hours	- - -
Burn-in at Elevated Temp.	(DC on) 160 hours at 85° C	MIL-STD-202, Method 108
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, except 100°C