

Amplifier**ZHL-ED12883/1****Important Note**

This model has been designed, built and tested in our engineering department. Performance data represents model capability.
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

**CASE STYLE : S32**

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	10		550	MHz
Gain		11		dB
Output Power @1 dB compr.		29.00		dB
Noise Figure		4.0		dB
IP3		46.0		dBm
VSWR	IN	1.77		(:1)
	OUT	1.40		(:1)
DC Power	Voltage	12.0		V
	Current	525.0		mA

MAXIMUM RATINGS	
Operating Temperature	-20°C to 85°C
Storage Temperature	-55°C to 100°C

High Power Amplifier

ZHL-ED12883/1







Typical Performance Data

FREQUENCY (MHz)	GAIN (dB) 12V	DIRECTIVITY (dB) 12V	VSWR IN (:1) 12V	VSWR OUT (:1) 12V	NOISE FIGURE (dB) 12V	Pout at 1dB Comp. (dBm) 12V	Output IP3 (dBm) 12V
10.0	11.11	5.30	1.76	1.93	10.29	29.02	47.22
50.0	11.36	5.55	1.33	1.60	3.52	28.97	45.85
100.0	11.35	5.61	1.17	1.38	3.06	29.14	46.11
125.0	11.34	5.66	1.15	1.25	3.10	29.46	48.24
150.0	11.31	5.74	1.22	1.14	3.11	29.61	45.37
175.0	11.24	5.88	1.35	1.12	3.10	29.94	47.25
200.0	11.14	6.10	1.51	1.21	3.20	30.09	47.51
225.0	11.01	6.39	1.68	1.33	3.31	30.26	47.78
250.0	10.87	6.69	1.86	1.46	3.42	30.27	47.43
300.0	10.58	7.31	2.16	1.67	3.64	30.18	47.43
325.0	10.44	7.60	2.25	1.73	3.72	30.09	47.73
350.0	10.40	7.71	2.30	1.74	3.80	30.22	48.16
400.0	10.23	8.06	2.26	1.64	4.02	29.77	47.67
450.0	10.26	8.04	2.14	1.41	4.19	29.26	45.91
500.0	10.21	8.22	2.06	1.13	4.37	28.82	46.29
550.0	10.00	8.66	2.18	1.27	4.53	28.61	45.89
600.0	9.47	9.70	2.50	1.67	4.64	17.86	44.33
650.0	8.97	10.76	2.83	2.10	4.76	17.31	46.16
700.0	8.31	11.98	2.99	2.45	4.81	18.69	45.44
750.0	8.04	12.64	2.90	2.63	4.93	16.77	43.70


High Power Amplifier

Typical Performance Curves


ZHL-ED12883/1



Outline Dimensions



MOUNTING INFORMATION FOR MODELS WITHOUT HEATSINK



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
S32	3.75 (95.25)	2.00 (50.80)	1.80 (45.72)	.19 (4.83)	3.375 (85.73)	.19 (4.83)	1.625 (41.28)	.144 (3.66)	.50 (12.70)	.40 (10.16)	.50 (12.70)	1.30 (33.02)	.10 (2.54)

CASE#	P	Q	R	S	T	WT. GRAMS	WT. WITHOUT HEATSINK GRAMS
S32	.38 (9.65)	3.00 (76.20)	.30 (7.62)	2.60 (66.04)	.80 (20.32)	220.0	150.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Heat sink finish: Black anodize.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-20° to 65° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Stabilization Bake	(non-operating) 125°C, 24 hours	- - -
Burn-in at Elevated Temp.	(DC on) 160 hours at 85° C	MIL-STD-202, Method 108
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, except 100°C