



Mini-Circuits®

COAXIAL

High Power Amplifier


ZHL-1000-3W+
ZHL-1000-3WX+**50Ω 3W 500 to 1000 MHz**

FEATURES

- High Power, 3 Watt
- Wideband, 500 to 1000 MHz
- High Power Output, +35dBm Min.
- High IP3, +45 dBm typ.
- High Gain, 43 dB typ.
- Protected by US Patent, 6,943,629

APPLICATIONS

- VHF
- Cellular
- Instrumentation
- Laboratory



Generic photo used for illustration purposes only

Model No.	ZHL-1000-3W+	ZHL-1000-3WX+ [▲]
Case Style	DDD131	
Connectors	SMA	

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Min.	Typ.	Max.	Units
Frequency Range	500	—	1000	MHz
Gain	38	—	—	dB
Gain Flatness ¹	—	—	±1.2	dB
Output Power at 1dB compression	+33.5	+36	—	dBm
Noise Figure	—	3.5	—	dB
Output third order intercept point	—	+45	—	dBm
Input VSWR	—	2.0	—	:1
Output VSWR	—	2.5	—	:1
DC Supply Voltage	—	24	—	V
Supply Current	—	—	2.25	A

[▲] Heat sink not included. Alternative heat sinking and heat removal must be provided by the user to limit maximum base-plate temperature to 75°C, in order to ensure proper performance. For reference, this requires thermal resistance of user's external heat sink to be 0.8°C/W max.

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-20°C to +65°C
Storage Temperature	-55°C to +100°C
Base Plate Temperature	+75°C
DC Voltage	+25V
Input RF Power (no damage)	0 dBm

Permanent damage may occur if any of these limits are exceeded.

Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. L
ECO-023957
EDR-11977
MCIL
ZHL-1000-3W+
250206
PAGE 1 OF 3



Mini-Circuits


COAXIAL

High Power Amplifier


ZHL-1000-3W+
ZHL-1000-3WX+

50Ω 3W 500 to 1000 MHz

OUTLINE DRAWING



MOUNTING INFORMATION FOR MODELS WITHOUT HEATSINK



OUTLINE DIMENSIONS (Inch/mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt
7.00	3.25	3.13	.25	6.500	.38	2.500	.156	.88	.43	.62	1.00	2.63	.125	.50	6.00	2.23	8.35	grams*
177.80	82.55	79.50	6.35	165.10	9.65	63.50	3.96	22.35	10.92	15.75	25.40	66.80	3.18	12.70	152.40	56.64	212.09	1780

*510 grams without heatsink



Mini-Circuits

COAXIAL


High Power Amplifier

ZHL-1000-3W+
ZHL-1000-3WX+


50Ω 3W 500 to 1000 MHz

TYPICAL PERFORMANCE CHARTS


Gain vs. Frequency




Isolation vs. Frequency




Return Loss vs. Frequency




Output Power @ 1dB Compression vs. Frequency



IP3 vs. Frequency



Noise Figure vs. Frequency



NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Coaxial High Power Amplifier

ZHL-1000-3W+

Typical Performance Data

FREQ. (MHz)	GAIN (dB)			DIRECTIVITY 24V	VSWR (:1)		NOISE FIGURE (dB) 24V	POUT @ 1 dB COMPRESSION (dBm) 24V	OUTPUT IP3 (dBm) 24V
	23V	24V	25V		IN 24V	OUT 24V			
300	44.10	44.04	44.00	32.58	1.53	4.24	3.60	31.60	47.04
350	44.45	44.42	44.40	37.32	1.57	2.78	3.61	33.99	48.36
400	44.12	44.13	44.13	33.32	1.66	1.90	3.71	35.86	47.83
450	43.69	43.74	43.77	37.94	1.70	1.39	3.64	37.36	47.62
500	43.44	43.51	43.57	33.21	1.64	1.22	3.60	37.59	47.32
550	43.44	43.53	43.60	39.42	1.53	1.32	3.63	37.59	47.36
600	43.64	43.73	43.81	35.50	1.30	1.52	3.63	37.77	47.29
650	43.49	43.57	43.66	34.29	1.21	1.63	3.57	37.75	46.09
700	43.86	43.93	44.01	34.55	1.30	1.74	3.61	37.08	45.12
750	44.17	44.23	44.31	44.04	1.34	1.77	3.53	36.75	44.66
800	44.48	44.54	44.62	38.17	1.31	1.77	3.46	36.78	44.74
850	44.65	44.70	44.77	52.63	1.30	1.77	3.50	36.31	45.06
900	44.73	44.78	44.84	45.00	1.34	1.81	3.53	36.72	44.83
950	44.86	44.91	44.98	53.07	1.33	1.86	3.53	36.50	44.91
1000	44.89	44.95	45.04	42.88	1.19	1.88	3.55	36.24	44.26









P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS


REV. OR
 ZHL-1000-3W+
 11/9/2018
 Page 1 of 1

Typical Performance Curves



Outline Dimensions

DDD131



MOUNTING INFORMATION FOR MODELS WITHOUT HEATSINK

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
DDD131	7.00 (177.80)	3.25 (82.55)	3.13 (79.50)	.25 (6.35)	6.500 (165.10)	.38 (9.65)	2.500 (63.50)	.156 (3.96)	.88 (22.35)	.43 (10.92)	.62 (15.75)	1.00 (25.40)	2.63 (66.68)

CASE#	P	Q	R	S	T	WT. GRAMS	WT. WITHOUT HEATSINK GRAMS
DDD131	.125 (3.18)	.50 (12.70)	6.00 (152.40)	2.23 (56.64)	8.35 (212.09)	1780	510

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Heatsink finish: Black anodize if supplied with heatsink.
- Refer to the individual model data sheet for the type of connectors available.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified