



COAXIAL

Medium High Power Amplifier

ZHL-1042J+ ZHL-1042JX+


50Ω 10 to 4200 MHz SMA Female

FEATURES

- Wideband, 10 to 4200 MHz
- High Output IP3, +35 dBm Typ.
- Low Noise, 6 dB Min.

APPLICATIONS

- Communication Systems
- Laboratory



Generic photo used for illustration purposes only

Model No.	ZHL-1042J+	ZHL-1042JX+▲
Case Style	NN92	
Connectors	SMA female	

+RoHS Compliant
 The +Suffix identifies RoHS Compliance.
 See our website for methodologies and qualifications

ELECTRICAL SPECIFICATIONS AT +25 °C

Parameter	Condition (MHz)	ZHL-1042J+ ZHL-1042JX+▲			Units
		Min.	Typ.	Max.	
Frequency Range		10		4200	MHz
Gain	10-4200	24	27	32	dB
Gain Flatness	10-4200		±1.2	±1.7	dB
Output Power at 1 dB Compression	10-4200	+20	+22		dBm
Output Power at 3 dB Compression	10-4200	+21	+23		dBm
Noise Figure	10-4200		6.0		dB
Output Third Order Intercept Point	10-4200		+35		dBm
Input VSWR	10-4200			2.5	:1
Output VSWR	10-4200			2.5	:1
DC Supply Voltage			+15		V
Supply Current				0.330	A

Open load is not recommended, potentially can cause damage.
With no load, derate max. input power by 20 dB.

▲ Heat sink not included. Alternative heat sinking and heat removal must be provided by the user to limit maximum base-plate temperature to +65 °C, in order to ensure proper performance. For reference, this requires thermal resistance of user's external heat sink to be 2.2°C/W max.

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-20 °C to +65 °C
Storage Temperature	-55 °C to +100 °C
DC Voltage	+20 V
Input RF Power (No Damage)	+10 dBm

Permanent damage may occur if any of these limits are exceeded.





COAXIAL


Medium High Power Amplifier

ZHL-1042J+ ZHL-1042JX+


Mini-Circuits

50Ω 10 to 4200 MHz SMA Female

OUTLINE DRAWING FOR MODELS WITH HEATSINK



MOUNTING INFORMATION FOR MODELS WITHOUT HEATSINK



OUTLINE DIMENSIONS (Inch/mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	wt
3.66	3.25	2.13	.25	3.16	.38	2.50	.156	.72	.64	.74	1.78	2.30	.125	.50	2.66	1.13	grams*
92.96	82.55	54.10	6.35	80.26	9.65	63.50	3.96	18.29	16.26	18.80	45.21	58.42	3.18	12.70	67.56	28.7	500.0







*362 grams without heatsink





TYPICAL PERFORMANCE DATA/CURVES

FREQUENCY (MHz)	GAIN (dB)	DIRECTIVITY (dB)	VSWR (:1)		P _{out} at 1 dB COMPR. (dBm)	NOISE FIGURE (dB)	OIP3 (dBm)
	+15 V	+15 V	+15 V		+15 V	+15 V	+15 V
			IN	OUT			
10	27.79	29.01	2.29	2.11	23.20	5.21	33.56
300	28.09	18.28	1.56	1.67	23.35	4.10	38.81
600	27.78	18.55	1.65	1.38	22.89	4.11	40.42
900	27.83	18.03	1.62	1.12	22.78	4.15	42.12
1200	28.19	16.76	1.49	1.19	23.51	4.27	45.58
1500	28.50	15.16	1.45	1.52	24.25	4.35	49.14
1800	28.22	14.69	1.46	1.84	24.02	4.53	46.70
2100	27.95	14.64	1.37	1.94	24.20	4.60	44.94
2400	27.58	14.89	1.38	1.77	24.62	4.72	48.99
2700	27.21	15.26	1.55	1.51	24.31	4.79	47.16
3000	26.86	15.57	1.59	1.48	24.21	4.83	43.89
3300	26.61	15.50	1.36	1.61	24.24	4.96	42.27
3600	26.79	15.54	1.03	1.59	24.03	4.96	41.05
3900	26.67	16.18	1.28	1.39	23.59	4.97	39.79
4200	26.56	17.35	1.21	1.28	22.48	5.01	38.07



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Amplifier






ZHL-1042J+

Typical Performance Data


FREQ. (MHz)	GAIN (dB)			DIRECTIVITY (dB)			VSWR (:1)		NOISE FIGURE (dB) 15V	POUT @ 1 dB COMPRESSION (dBm) 15V
	12V	15V	16V	12V	15V	16V	IN 15V	OUT 15V		
10.0	27.55	28.68	28.68	33.40	32.60	33.80	1.60	1.57	19.14	22.32
21.4	28.01	29.08	29.09	30.70	19.80	26.40	1.56	1.83	17.99	23.20
67.0	27.31	28.36	28.37	28.30	27.70	27.50	1.57	1.84	13.37	22.82
209.9	27.41	28.43	28.44	32.30	29.80	34.40	1.52	1.78	7.36	22.75
258.5	26.30	27.16	27.18	29.70	23.10	24.80	1.65	1.10	5.34	21.04
657.2	27.06	28.06	28.06	29.80	23.00	30.50	1.24	1.43	5.90	21.80
1514.1	27.81	28.70	28.71	29.50	29.10	27.40	1.53	1.62	5.28	20.96
1836.4	27.53	28.29	28.28	30.00	26.70	27.70	1.88	1.47	5.40	21.14
2158.7	26.69	27.44	27.44	25.50	26.20	27.90	1.94	1.29	5.39	20.59
2373.6	26.44	27.26	27.27	25.00	26.00	28.50	1.83	1.20	5.30	20.84
2910.8	26.45	27.38	27.41	23.90	28.10	23.20	1.48	1.12	5.41	20.61
3233.1	26.74	27.60	27.60	23.50	31.50	25.70	1.45	1.34	5.43	20.72
3555.4	26.87	27.63	27.64	28.60	25.90	25.80	1.17	1.64	5.43	20.61
3877.7	27.26	28.14	28.15	22.20	20.80	22.20	1.31	1.75	5.55	21.22
4200.0	27.17	28.06	28.08	21.90	18.30	21.20	1.46	1.66	5.58	20.82




Typical Performance Curves



Outline Dimensions



MOUNTING INFORMATION FOR MODELS WITHOUT HEATSINK



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
NN92	3.66 (92.96)	3.25 (82.55)	2.13 (54.10)	.25 (6.35)	3.16 (80.26)	.38 (9.65)	2.50 (63.50)	.156 (3.96)	.72 (18.29)	.64 (16.26)	.74 (18.80)	1.78 (45.21)	2.30 (58.42)

CASE#	P	Q	R	S	WT. GRAMS	WT. WITHOUT HEATSINK GRAMS
NN92	.125 (3.18)	.50 (12.70)	2.66 (67.56)	1.13 (28.58)	500.0	362.0

Dimensions are in inches (mm). Tolerances: 2 Pl. + .03; 3 Pl. + .015

Notes:

- Case material: Aluminum alloy.
- Case and mounting bracket finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Heat sink finish: Black anodize.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-20° to 65° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Stabilization Bake	(non-operating) 125°C, 24 hours	- - -
Burn-in at Elevated Temp.	(DC on) 160 hours at 85° C	MIL-STD-202, Method 108
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, except 100°C