



COAXIAL

Medium Power Amplifier

ZHL-10M1G01W0+
ZHL-10M1G01W0X+

50Ω 10 to 1000 MHz Broadband 1 W SMA Female

KEY FEATURES

- Broadband, 10 to 1000 MHz
- High Gain, 22 dB Typ.
- High P1dB, +31 dBm, Typ.
- High OIP3, +46 dBm Typ.




Generic photo used for illustration purposes only

APPLICATIONS

- Communication Systems
- R&D, Production, and Test Systems
- Test & Measurement Equipment
- General Laboratory Applications

FUNCTIONAL DIAGRAM



PRODUCT OVERVIEW

Mini-Circuits' ZHL-10M1G01W0(X)+ is a medium power broadband amplifier providing more than 1 W of output power with a typical small signal gain of 22 dB over the 10 to 1000 MHz frequency band. The amplifier uses state-of-the-art semiconductor technology and can be used in a wide range of applications. A single supply voltage ensures ease of operation. The amplifier is made with a rugged aluminum housing and can be supplied with or without a heatsink.

ELECTRICAL SPECIFICATIONS AT $T_{MOUNTING\ BASE} = +25\ ^\circ C$, $V_{DC} = +24\ V$

Parameter	Symbol	Condition	Min.	Typ.	Max.	Units
Frequency Range	f		10		1000	MHz
Small Signal Gain	G_{SS}	$P_{OUT} = -25\ dBm$	16	22	24	dB
Small Signal Gain Flatness	$G_{SS-FLAT}$	$P_{OUT} = -25\ dBm$		± 0.2	± 1.4	dB
Output Power at 1 dB Compression	P_{1dB}	$P_{OUT-REF} = +15\ dBm$	+29	+31		dBm
Output Power at 3 dB Compression	P_{3dB}	$P_{OUT-REF} = +15\ dBm$	+30	+32		dBm
Noise Figure	NF			9		dB
Output Third Order Intercept Point	OIP3	$P_{OUT} = +20\ dBm/ tone$		+46		dBm
Input Return Loss	I-RL	$P_{OUT} = -25\ dBm$	9.5	24		dB
Output Return Loss	O-RL	$P_{OUT} = -25\ dBm$	9	16		dB
DC Supply Voltage	V_{DC}		+20	+24	+25	V
Supply Current	I_{DC}	Without fan at P_{3dB} With fan at P_{3dB}		0.5 0.9	0.6 1.0	A





COAXIAL


Medium Power Amplifier

ZHL-10M1G01W0+
ZHL-10M1G01W0X+


50Ω 10 to 1000 MHz Broadband 1 W SMA Female

TYPICAL PERFORMANCE DATA AT $T_{MOUNTINGBASE} = +25\text{ }^{\circ}\text{C}$, $V_{DC} = +24\text{ V}$, 50Ω


Small Signal Gain vs. Frequency




Return Loss vs. Frequency




Output Power at 1dB Compression vs. Frequency




Output Power at 3dB Compression vs. Frequency



Noise Figure vs. Frequency



Output Third Order Intercept Point vs. Frequency





COAXIAL

Medium Power Amplifier

ZHL-10M1G01W0+
ZHL-10M1G01W0X+

50Ω 10 to 1000 MHz Broadband 1 W SMA Female

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings	
Operating Temperature	ZHL-10M1G01W0+	T _{AMBIENT} : -20 °C to +60 °C
	ZHL-10M1G01W0X+	T _{MOUNTING BASE} : -20 °C to +85 °C
Storage Temperature	-55 °C to +100 °C	
No damage with an open or short at P _{OUT} = +28 dBm CW		
RF Input Power (No Damage)	+15 dBm	
DC Operating Voltage	+25 V	
Total Power Dissipation (Without Fan at P3dB)	15 W	
Total Power Dissipation (With Fan at P3dB)	25 W	

Permanent damage may occur if any of these limits are exceeded.

DETERMINING MAXIMUM THERMAL RESISTANCE OF USERS' EXTERNAL HEAT SINK

$\text{MAXIMUM THERMAL RESISTANCE} = \frac{\text{MAXIMUM OPERATING CASE TEMP} - \text{MAXIMUM USER AMBIENT TEMP}}{\text{POWER DISSIPATION}}$
<p>Example:</p> <p>MAXIMUM MOUNTING BASE TEMP = +85 °C (CHECK MAXIMUM RATINGS TABLE FOR THIS VALUE) MAXIMUM USER AMBIENT TEMP = +60 °C (USER DEFINED) POWER DISSIPATION = 12 WATTS (CHECK MAXIMUM RATINGS TABLE FOR THIS VALUE) THEN MAXIMUM ALLOWABLE THERMAL RESISTANCE = 2.1 °C/W</p>





COAXIAL

Medium Power Amplifier

ZHL-10M1G01W0+
ZHL-10M1G01W0X+


Mini-Circuits

50Ω 10 to 1000 MHz Broadband 1 W SMA Female


COAXIAL CONNECTIONS

IN (RF-IN)	SMA female
OUT (RF-OUT)	SMA female

CASE STYLE DRAWING WITH HEATSINK (ZHL-10M1G01W0+)



CASE STYLE DRAWING WITHOUT HEATSINK (ZHL-10M1G01W0X+)



Weight: 440 grams Weight without heatsink: 325 grams Dimensions are in inches [mm].
Tolerances: 2 Pl.±03; 3 Pl. ±.015 Inch

OUTLINE DIMENSIONS (Inch mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt
4.75	2.00	2.12	.19	4.375	.23	1.540	.144	.58	.34	.50	1.50	1.00	.12	.38	4.00	.30	2.60	grams*
120.65	50.80	53.85	4.83	111.13	5.84	39.12	3.66	14.73	8.64	12.70	38.10	25.40	3.05	9.65	101.60	7.62	66.04	440.0

*325 grams without heatsink





COAXIAL

Medium Power Amplifier

ZHL-10M1G01W0+
ZHL-10M1G01W0X+

50Ω 10 to 1000 MHz Broadband 1 W SMA Female

ADDITIONAL INFORMATION IS AVAILABLE ON OUR DASHBOARD.

Performance Data & Graphs	Table
	Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
RoHS Status	Compliant
Environmental Ratings	ENV23T15

ORDERING INFORMATION

Model No. Links	ZHL-10M1G01W0+	ZHL-10M1G01W0X+
Option	With Heatsink	Without Heatsink
Case Style	T34	
Connector	IN (SMA female) / OUT (SMA female)	

NOTES







- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html






Typical Performance Data

Frequency (MHz)	Gain	Isolation	Return Loss (dB)		P _{OUT} @ 1dB Compression	P _{OUT} @ 3dB Compression	P _{OUT} @ Saturation	OIP3	Noise Figure
	(dB)	(dB)	IN	OUT	(dBm)	(dBm)	(dBm)	(dBm)	(dB)
	24V	24V	24V	24V	24V	24V	24V	24V	24V
10	22.39	51.29	31.18	11.60	29.85	30.61	31.04	47.69	9.27
20	22.28	51.36	31.79	11.18	30.01	30.89	31.43	46.83	8.86
40	22.31	51.12	32.25	11.14	30.30	31.11	31.46	47.82	8.84
60	22.32	51.28	32.23	11.19	30.41	31.15	31.47	47.29	8.83
80	22.33	51.10	32.07	11.29	30.45	31.18	31.42	47.41	8.82
100	22.35	50.88	31.70	11.42	30.51	31.23	31.46	47.51	8.86
120	22.36	51.20	31.30	11.58	30.52	31.24	31.41	47.15	8.85
140	22.36	50.98	30.90	11.77	30.55	31.24	31.49	47.00	8.82
160	22.38	50.77	30.49	11.99	30.52	31.19	31.43	46.54	8.82
180	22.40	50.92	29.92	12.25	30.54	31.19	31.45	46.60	8.83
200	22.42	50.49	29.45	12.55	30.58	31.22	31.45	46.86	8.83
220	22.44	50.95	28.98	12.87	30.67	31.30	31.39	47.05	8.83
240	22.46	50.82	28.47	13.24	30.74	31.36	31.39	46.71	8.81
260	22.48	50.43	27.86	13.63	30.76	31.37	31.32	46.57	8.84
280	22.51	50.52	27.42	14.05	30.86	31.46	31.38	46.55	8.83
300	22.53	50.92	26.86	14.51	30.90	31.46	31.43	46.34	8.81
320	22.54	50.72	26.30	15.00	30.89	31.41	31.47	46.01	8.84
340	22.57	50.27	25.76	15.54	30.92	31.42	31.53	45.90	8.84
360	22.58	50.61	25.27	16.11	30.96	31.44	31.53	45.78	8.83
380	22.60	50.31	24.78	16.67	31.02	31.48	31.54	45.73	8.84
400	22.59	50.93	24.37	17.39	31.08	31.52	31.50	45.79	8.85
420	22.60	50.53	23.86	17.80	31.13	31.57	31.54	45.79	8.85
440	22.59	49.99	23.48	18.36	31.19	31.61	31.59	45.74	8.84
460	22.56	50.21	23.07	18.68	31.24	31.67	31.69	45.57	8.82
480	22.54	50.08	22.62	18.82	31.29	31.71	31.79	45.55	8.86
500	22.56	50.08	22.23	18.81	31.32	31.77	31.79	45.54	8.85
520	22.58	50.10	21.91	18.92	31.37	31.85	31.96	45.58	8.88
540	22.61	50.32	21.60	19.04	31.43	31.94	32.03	45.56	8.86
560	22.62	50.23	21.31	19.10	31.49	32.02	32.06	45.62	8.83
580	22.63	50.12	21.07	19.13	31.54	32.07	32.07	45.60	8.84
600	22.63	49.89	20.80	19.02	31.57	32.10	32.11	45.42	8.86
620	22.63	49.54	20.57	18.88	31.59	32.10	32.11	45.35	8.90
640	22.63	50.13	20.37	18.70	31.61	32.11	32.13	45.19	8.87
660	22.62	50.19	20.26	18.47	31.62	32.10	32.16	45.20	8.87
680	22.61	49.95	20.06	18.30	31.62	32.09	32.14	45.22	8.91
700	22.60	49.89	19.97	18.15	31.61	32.07	32.10	45.26	8.92
720	22.58	49.91	19.91	17.94	31.60	32.01	32.03	45.12	8.89
740	22.57	50.01	19.83	17.79	31.56	31.94	32.00	45.02	8.89
760	22.54	49.63	19.82	17.69	31.54	31.88	31.96	44.99	8.90
780	22.51	49.90	19.82	17.59	31.52	31.85	31.92	44.96	8.91
800	22.48	49.74	19.81	17.50	31.51	31.83	31.93	45.02	8.89
820	22.45	50.13	19.88	17.35	31.49	31.80	31.89	45.11	8.88
840	22.42	49.94	19.95	17.11	31.47	31.77	31.87	45.13	8.92
860	22.40	49.63	20.05	16.79	31.45	31.73	31.80	45.14	8.95
880	22.40	49.89	20.21	16.46	31.43	31.68	31.76	45.14	8.93
900	22.41	49.91	20.35	16.14	31.41	31.63	31.71	45.13	8.91
920	22.40	49.59	20.59	15.85	31.39	31.59	31.64	44.93	8.92
940	22.39	49.72	20.86	15.63	31.36	31.56	31.60	44.80	8.91
960	22.39	49.81	21.13	15.39	31.32	31.52	31.55	44.66	8.91
980	22.36	49.56	21.45	15.19	31.30	31.49	31.57	44.64	8.94
1000	22.35	49.36	21.78	14.99	31.25	31.45	31.52	45.08	8.91


Typical Performance Curves




Typical Performance Curves



Outline Dimensions



MOUNTING INFORMATION FOR MODELS WITHOUT HEATSINK



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
T34	4.75 (120.65)	2.00 (50.80)	2.12 (53.85)	.19 (4.83)	4.375 (111.13)	.23 (5.84)	1.540 (39.12)	.144 (3.66)	.58 (14.73)	.34 (8.64)	.50 (12.70)	1.50 (38.10)	1.00 (25.40)

CASE#	P	Q	R	S	T	WT. GRAMS	WT. WITHOUT HEATSINK GRAMS
T34	.12 (3.05)	.38 (9.65)	4.00 (101.60)	.30 (7.62)	2.60 (66.04)	440.0	325.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish and mounting bracket finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Heat sink finish: Black anodize.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-20° to 60°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Stabilization Bake	(non-operating) 125°C, 24 hours	- - -
Burn-in at Elevated Temp.	(DC on) 160 hours at 85° C	MIL-STD-202, Method 108
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, except 100°C