



COAXIAL

# Medium High Power Amplifier

**ZHL-1W-63-S+**  
**ZHL-1W-63X-S+**

50Ω 1W 600 to 6000 MHz

## THE BIG DEAL

- Wideband, 600 to 6000 MHz
- High Gain, 35 dB typ.
- High OIP3, +35 dBm typ.



Generic photo used for illustration purposes only

<b>Model No.</b>	ZHL-1W-63-S+	ZHL-1W-63X-S+▲
<b>Case Style</b>	U2847	
<b>Connectors</b>	SMA	

## APPLICATIONS

- Communication Systems
- Cellular
- Instrumentation
- Laboratory

**+RoHS Compliant**  
 The +Suffix identifies RoHS Compliance.  
 See our website for methodologies and qualifications

## PRODUCT OVERVIEW

Mini-Circuits' ZHL-1W-63-S+ is class AB a medium-power connectorized amplifier with GaN output transistor supporting a wide range of applications from 600 to 6000 MHz, such as test instrumentation, SatCom, and mobile communications systems, including those operating in the new telecom Band 71 allocation (617 to 698 MHz). This model provides +30 dBm output power at saturation. The amplifier operates on a 15V DC supply and comes housed in compact aluminum alloy case (7.00 x 3.25 x 1.12") with SMA connectors, built-in bracket for mounting, and an optional heat sink for efficient cooling.

## KEY FEATURES

Feature	Advantages
Wideband, usable from 500 to 6100 MHz	One amplifier supports a broad range of system and test lab applications. Extended bandwidth down to 600 MHz supports new telecom Band 71 allocation (617 to 698 MHz)
High Gain, 35 dB	Reduces the number of gain stages, lowering component count and overall system cost.
Medium Output Power, +30 dBm	Supports a wide range of power requirements.
High OIP3, +35 dBm	Provides highly linear performance with excellent sensitivity and two-tone spur-free dynamic range.

REV. B  
 ECO-018143  
 ZHL-1W-63-S+  
 MCL NY  
 231012





COAXIAL

# Medium High Power Amplifier

ZHL-1W-63-S+  
ZHL-1W-63X-S+

Mini-Circuits

50Ω 1W 600 to 6000 MHz

## ELECTRICAL SPECIFICATIONS AT 25°C

Parameter	Condition (MHz)	ZHL-1W-63-S+ ZHL-1W-63X-S+▲			Units
		Min.	Typ.	Max.	
Frequency Range		600	–	6000	MHz
Gain	600-6000	29	35	46	dB
Gain Flatness	600-6000	–	±3.5	–	dB
Output Power at 3 dB Compression	600-6000	–	+28	–	dBm
Output Power at Saturation	600-6000	+28	+30	–	dBm
Noise Figure	600-6000	–	12	–	dB
Output third order intercept point	600-6000	–	+35	–	dBm
Input VSWR	600-6000	–	2.5	–	:1
Output VSWR	600-6000	–	3.5	–	:1
DC Supply Voltage		–	+15	–	V
Supply Current		–	1.0	1.5	A

▲ Heat sink not included. Alternative heat sinking and heat removal must be provided by the user to limit maximum base-plate temperature to 85°C, in order to ensure proper performance. For reference, this requires thermal resistance of user's external heat sink to be 1.1°C/W max.

## ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	0°C to +60°C
Storage Temperature	-55°C to +100°C
DC Voltage	+20V
Input RF Power (no damage) at load	+5 dBm
Input RF power at OPEN / SHORT	-18 dBm

Permanent damage may occur if any of these limits are exceeded.





COAXIAL


# Medium High Power Amplifier

ZHL-1W-63-S+  
ZHL-1W-63X-S+

Mini-Circuits

50Ω 1W 600 to 6000 MHz

## OUTLINE DRAWING



Weight: 650 grams  
950 grams with heatsink





COAXIAL

# Medium High Power Amplifier







ZHL-1W-63-S+  
ZHL-1W-63X-S+

Mini-Circuits

50Ω 1W 600 to 6000 MHz

### TYPICAL PERFORMANCE DATA/CURVES

FREQUENCY (MHz)	GAIN (dB)	DIRECTIVITY (dB)	VSWR (:1)		NOISE FIGURE (dB)	POUT at 3dB COMPR. (dBm)	POUT at SATURATION (dBm)	OIP3 (dBm)
	15V	15V	IN	OUT	15V	15V	15V	15V
600	36.57	52.82	2.48	2.00	12.44	30.53	30.57	44.35
1000	37.54	44.33	1.82	1.34	10.20	31.71	31.98	45.58
1500	38.76	50.02	1.51	1.26	9.96	32.16	32.51	44.57
2000	37.92	46.44	1.44	1.51	10.28	31.38	31.79	43.89
2500	37.67	45.18	1.30	1.61	9.88	30.78	31.02	42.76
3000	37.74	47.90	1.41	1.48	9.62	30.85	30.95	42.98
3500	37.42	52.42	1.65	1.35	10.45	30.65	31.00	42.74
4000	36.61	51.04	1.31	1.48	11.49	30.44	30.87	42.82
4500	36.17	50.00	1.33	1.69	11.35	29.76	30.34	41.77
5000	35.85	44.03	1.27	1.63	11.01	29.70	30.36	41.11
5500	35.71	54.64	1.35	1.45	10.99	29.86	30.45	41.10
6000	35.26	43.38	1.47	1.17	11.38	29.69	30.10	41.27



#### NOTES







- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)



## Typical Performance Data

FREQUENCY (MHz)	GAIN (dB) 15V	DIRECTIVITY (dB) 15V	VSWR (:1)		NOISE FIGURE (dB) 15V	Pout at 3dB COMPRESSION (dBm) 15V	Pout at SATURATION (dBm) 15V	OUTPUT IP3 (dBm) 15V
			IN 15V	OUT 15V				
500	34.39	51.20	2.87	2.60	13.86	29.51	29.81	43.60
550	35.75	52.48	2.67	2.21	13.01	29.97	30.17	44.21
600	36.57	52.82	2.48	2.00	12.44	30.53	30.57	44.35
650	37.27	55.30	2.28	1.85	12.13	30.75	31.02	44.56
700	37.82	55.70	2.09	1.73	11.70	30.97	31.14	44.29
750	38.12	50.19	1.95	1.64	11.27	31.14	31.49	44.43
800	38.16	49.86	1.87	1.56	10.97	31.15	31.47	44.72
850	38.02	57.13	1.85	1.49	10.78	31.56	31.82	45.02
900	37.82	46.83	1.84	1.43	10.59	31.58	31.76	44.96
950	37.65	50.84	1.83	1.38	10.34	31.76	32.02	45.11
1000	37.54	44.33	1.82	1.34	10.20	31.71	31.98	45.58
1100	37.57	52.28	1.75	1.26	9.99	31.89	32.27	45.06
1200	37.88	46.64	1.67	1.22	9.91	32.21	32.46	44.99
1300	38.27	45.14	1.58	1.20	9.82	32.25	32.60	44.83
1400	38.60	54.71	1.52	1.22	9.85	32.27	32.56	44.64
1500	38.76	50.02	1.51	1.26	9.96	32.16	32.51	44.57
1600	38.73	46.36	1.51	1.31	10.00	32.20	32.44	44.35
1700	38.56	46.85	1.51	1.36	10.19	31.85	32.43	44.33
1800	38.36	47.83	1.50	1.41	10.17	31.88	32.22	44.27
1900	38.11	54.36	1.47	1.48	10.15	31.62	32.01	44.11
2000	37.92	46.44	1.44	1.51	10.28	31.38	31.79	43.89
2100	37.68	45.81	1.39	1.56	10.19	31.05	31.54	43.46
2200	37.69	43.03	1.34	1.56	10.08	31.01	31.43	43.15
2300	37.74	48.59	1.29	1.58	10.11	30.68	31.24	42.91
2400	37.71	55.25	1.27	1.60	10.08	30.63	31.11	42.72
2500	37.67	45.18	1.30	1.61	9.88	30.78	31.02	42.76
2600	37.59	45.03	1.35	1.63	9.84	30.44	30.97	42.80
2700	37.36	50.79	1.38	1.64	9.84	30.64	31.07	42.98
2800	37.38	51.72	1.40	1.56	9.53	30.67	31.03	43.15
2900	37.54	53.31	1.40	1.52	9.65	30.50	30.89	43.12
3000	37.74	47.90	1.41	1.48	9.62	30.85	30.95	42.98
3100	37.93	49.73	1.45	1.43	9.58	30.77	30.98	42.89
3200	38.04	49.50	1.53	1.39	9.86	30.93	30.99	42.83
3300	37.98	54.93	1.61	1.36	10.08	30.83	30.98	42.73
3400	37.75	52.32	1.66	1.34	10.13	30.78	31.14	42.79
3500	37.42	52.42	1.65	1.35	10.45	30.65	31.00	42.74
3600	37.09	53.37	1.58	1.37	10.69	30.69	31.08	42.90
3700	36.84	46.89	1.49	1.39	10.92	30.67	30.99	43.03
3800	36.72	46.11	1.40	1.41	11.18	30.71	30.90	42.98
3900	36.71	45.33	1.34	1.44	11.35	30.45	30.86	42.83
4000	36.61	51.04	1.31	1.48	11.49	30.44	30.87	42.82
4100	36.31	44.32	1.30	1.52	11.50	30.53	30.82	42.61
4200	36.53	50.00	1.32	1.55	11.44	30.31	30.81	42.49
4300	36.48	48.85	1.33	1.59	11.49	30.21	30.71	42.34
4400	36.36	47.34	1.33	1.65	11.37	30.10	30.45	41.94
4500	36.17	50.00	1.33	1.69	11.35	29.76	30.34	41.77
4600	35.99	48.14	1.31	1.68	11.35	29.58	30.26	41.45
4700	35.80	51.91	1.28	1.66	11.27	29.80	30.27	41.36
4800	35.58	47.11	1.23	1.66	11.38	29.56	30.29	40.98
4900	35.62	52.47	1.25	1.66	11.12	29.58	30.29	41.01
5000	35.85	44.03	1.27	1.63	11.01	29.70	30.36	41.11
5100	36.11	51.90	1.31	1.52	10.92	29.56	30.12	40.90
5200	36.18	53.07	1.35	1.51	10.85	29.59	30.23	41.00
5300	36.18	52.68	1.37	1.47	10.77	29.56	30.27	40.83
5400	35.99	48.18	1.38	1.45	10.82	29.69	30.24	40.85
5500	35.71	54.64	1.35	1.45	10.99	29.86	30.45	41.10
5600	35.49	42.79	1.32	1.32	11.03	29.78	30.35	41.25
5700	35.66	43.54	1.33	1.15	11.30	29.86	30.33	41.33
5800	35.75	40.80	1.38	1.05	11.16	29.98	30.35	41.39
5900	35.63	39.54	1.43	1.14	11.39	29.75	30.31	41.46
6000	35.26	43.38	1.47	1.17	11.38	29.69	30.10	41.27
6100	34.70	45.35	1.52	1.34	11.53	29.38	29.88	40.91

## Typical Performance Curves




# Case Style

# U

## Outline Dimensions

## U2847



Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .03$ ; 3 Pl.  $\pm .015$

### Notes:

- Case material: Aluminum alloy.
- Case finish and mounting bracket finish:  
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.  
For Non-RoHS Case Styles: Yellow hexavalent chrome based conversion coating.  
Due to transition from non-RoHS to RoHS, models will be supplied with either case style finish until the non-RoHS case inventory is depleted.
- Heat sink finish: Black anodize.
- Weight: 650 grams No HTSK  
950 grams W/HTSK

**Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-20° to 45°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Stabilization Bake	(non-operating) 125°C, 24 hours	- - -
Burn-in at Elevated Temp.	(DC on) 160 hours at 60° C base plate Temperature	MIL-STD-202, Method 108
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, except 100°C