



COAXIAL

High Power Amplifier


ZHL-20W-83-S+ ZHL-20W-83X-S+

Mini-Circuits

50Ω 20W 4000 to 8000 MHz

THE BIG DEAL

- Saturated Power, 20W typ.
- Wide Bandwidth, 4000 to 8000 MHz
- High Gain, 56 dB typ.
- Self-protected from overheating, reverse polarity and DC shorting/unshorting



Generic photo used for illustration purposes only

Model No.	ZHL-20W-83-S+	ZHL-20W-83X-S+▲
Case Style	CP2548-2	
Connectors	IN-SMA, OUT-SMA	

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

APPLICATIONS

- High Power Test Sets
- Burn-in Setups
- Communications
- Radar

PRODUCT OVERVIEW

The ZHL-20W-83-S+ is a Class AB, high-power amplifier providing 20W saturated power over the 4000 to 8000 MHz band, ideal for a variety of high-power test setups as well as applications including communications, radar and more. The ruggedly-designed amplifier provides unconditional stability and built-in self-protection against reverse polarity and overheating. The amplifier's output stage is further protected in the event of a fault condition, allowing high power operation for up to 2 minutes into an OPEN or SHORT up to 15W output power. Housed in a rugged aluminum alloy case measuring 4.3 x 6.7 x 1.4", the unit features SMA connectors and optional heat sink and fan attachment for cooling.

KEY FEATURES

Feature	Advantages
Wideband, usable from 4000 to 8000 MHz	Suitable for a broad range of high-power, wideband applications, including test setups, communications and defense applications.
High Gain, 56 dB typ.	Enables signal amplification to 20W output without the need for multiple gain stages.
Built-in self-protection	In instances of potentially-damaging overheating within the housing an automatic sensing feature signals the unit to power down.
Unconditional Stability	Provides reliable performance independent of input and load conditions.
Ruggedness	Able to operate into an open and short for 2 minutes at 15W output power.

REV. B
ECO-017840
ZHL-20W-83-S+
MCL NY
230616





COAXIAL

High Power Amplifier

ZHL-20W-83-S+
ZHL-20W-83X-S+

Mini-Circuits

ELECTRICAL SPECIFICATIONS AT T_(HEATSINK MOUNTING SURFACE)=25°C

Parameter	ZHL-20W-83-S+ ZHL-20W-83X-S+ [▲]			Units
	Min.	Typ.	Max.	
Frequency Range	4000		8000	MHz
Gain ¹	44.5	56	60.5	dB
Gain Flatness ¹		3.2	5.5	dB
Output Power at 1dB compression ⁴	34.5	39		dBm
Output Power at Saturation ⁴	41.5	44		dBm
Noise Figure		11		dB
Output third order intercept point ²	39.5	50		dBm
Input VSWR ¹		1.6		:1
Output VSWR ¹		1.7		:1
DC Supply Voltage ³	+26	+28	+29	V
Supply Current		4	8	A

1. Small signal input power -50 dBm typ.
2. Two tones, 35 dBm/tone, 1 MHz spacing.
3. Typical spec is recommended operating voltage.
4. Power measured of fundamental tone only. Does not include power contribution of harmonic signals.

[▲] Heat sink not included. Alternative heat sinking and heat removal must be provided by the user to limit maximum base-plate temperature to 80°C, in order to ensure proper performance.

ABSOLUTE MAXIMUM RATINGS⁵

Parameter	Ratings
Operating Heatsink Mounting Surface Temperature	0°C to +80°C
Storage Temperature	-55°C to +100°C
DC Voltage	+29V
Input RF Power (no damage)	+5 dBm ⁶

5. Specifications apply to CW signals only permanent damage may occur if any of these limits are exceeded.
6. Into 50 ohm load






COAXIAL


High Power Amplifier

ZHL-20W-83-S+ ZHL-20W-83X-S+

OUTLINE DRAWING FOR MODELS WITH HEATSINK



MOUNTING INFORMATION OF MODEL WITHOUT HEATSINK



OUTLINE DIMENSIONS (Inch mm)

A	B	C	D	E	F	G	H	J	K	L	wt
7.25	4.33	4.58	6.69	1.38	3.36	--	--	.62	3.34	.71	grams*
184.15	110.0	116.33	170	35.05	85.34	--	--	15.75	84.84	18.03	2041






*880 grams without heatsink





TYPICAL PERFORMANCE DATA/CURVES

Frequency (MHz)	Gain (dB)	VSWR (:1)		POUT at 1 dB (dBm)	PSAT (dBm)	NOISE FIGURE (dB)	IP3
		IN	OUT				
4000	57.0	1.38	1.32	39.99	43.96	10.26	51.29
4500	57.8	1.56	1.74	38.83	44.73	10.10	50.07
5000	57.3	1.21	1.52	38.61	43.99	10.10	50.02
5500	54.9	1.52	1.86	39.35	43.98	10.38	51.33
6000	57.5	1.45	1.52	38.05	44.21	10.63	48.46
6500	53.9	1.84	1.51	39.33	44.01	10.74	49.81
7000	55.2	1.74	1.57	40.83	44.06	11.24	50.89
7500	55.90	1.83	1.89	39.48	44.43	10.99	48.69
8000	52.38	1.48	1.74	41.86	43.99	11.51	51.72









- NOTES**
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Typical Performance Data


FREQUENCY (MHz)	GAIN (dB) 28V	DIRECTIVITY (dB) 28V	VSWR (:1)		NOISE FIGURE (dB) 28V	Pout @ 1 dB COMPRESSION (dBm) 28V	Pout @ SATURATION (dBm) 28V	OUTPUT IP3 (dBm) 28V
			IN 28V	OUT 28V				
4000	56.96	30.91	1.38	1.32	9.61	39.99	43.96	51.29
4100	56.97	29.63	1.45	1.39	9.51	40.03	44.45	51.28
4200	56.93	31.97	1.51	1.50	9.64	39.35	44.28	50.63
4300	57.12	29.80	1.54	1.48	9.53	38.70	44.35	50.06
4400	57.74	31.31	1.56	1.51	9.61	38.77	44.62	50.13
4500	57.82	30.61	1.56	1.74	9.75	38.83	44.73	50.07
4600	57.84	35.16	1.54	1.83	9.48	38.54	44.67	50.11
4700	57.67	31.38	1.51	1.80	9.53	38.36	44.46	49.88
4800	57.69	32.31	1.45	1.60	9.49	37.90	44.03	49.37
4900	57.68	29.51	1.34	1.44	9.42	38.30	44.15	49.72
5000	57.35	29.68	1.21	1.52	9.48	38.61	43.99	50.02
5100	56.97	31.00	1.15	1.80	9.54	38.49	44.05	50.17
5200	56.43	30.30	1.24	1.95	9.50	38.52	44.18	50.30
5300	55.50	31.53	1.36	1.89	9.56	38.48	44.10	50.24
5400	55.15	33.45	1.47	1.85	9.56	38.67	43.94	50.66
5500	54.88	30.45	1.52	1.86	9.79	39.35	43.98	51.33
5600	54.63	31.52	1.50	1.81	9.84	39.89	44.15	51.71
5700	54.83	34.31	1.43	1.69	10.11	39.90	44.30	51.35
5800	56.06	36.33	1.39	1.59	9.86	39.16	44.42	50.41
5900	56.86	30.61	1.38	1.58	10.15	38.47	44.38	49.25
6000	57.52	31.18	1.45	1.52	10.08	38.05	44.21	48.46
6100	57.18	31.20	1.53	1.48	10.17	37.71	43.90	47.75
6200	56.64	32.39	1.62	1.54	10.26	37.14	43.63	47.42
6300	55.77	32.85	1.70	1.48	10.18	37.25	43.58	47.65
6400	54.87	34.37	1.78	1.45	10.58	38.15	43.79	48.51
6500	53.89	33.92	1.84	1.51	10.51	39.33	44.01	49.81
6600	53.00	37.38	1.89	1.55	10.54	40.14	43.97	51.20
6700	52.81	36.18	1.85	1.51	10.70	40.86	44.09	52.59
6800	53.34	30.35	1.75	1.52	10.57	41.20	44.16	52.13
6900	54.05	30.39	1.71	1.54	10.61	41.49	44.33	52.04
7000	55.17	31.20	1.74	1.57	10.79	40.83	44.06	50.89
7100	55.33	30.87	1.85	1.70	10.78	40.36	43.97	50.03
7200	55.41	33.01	1.94	1.84	10.78	39.58	43.77	48.53
7300	56.04	34.92	1.98	1.89	10.75	38.69	43.72	47.31
7400	56.49	32.05	1.94	1.91	10.79	38.72	44.08	47.23
7500	55.90	29.16	1.83	1.89	10.68	39.48	44.43	48.69
7600	55.72	32.58	1.63	2.08	10.70	40.01	44.46	49.09
7700	55.68	30.20	1.45	2.20	10.83	40.81	44.38	49.86
7800	55.54	29.78	1.39	1.97	10.68	40.92	44.15	49.91
7900	54.55	28.76	1.39	1.55	10.79	41.69	44.09	50.56
8000	52.38	31.73	1.48	1.74	10.94	41.86	43.99	51.72

Typical Performance Curves




Outline Dimensions

CP2548-2



MOUNTING INFORMATION OF MODEL WITHOUT HEATSINK



CASE#	A	B	C	D	E	F	G	H	J	K	L	WT. GRAMS	WT. WITHOUT HEATSINK GRAMS
CP2548-2	7.25 (184.15)	4.33 (110.0)	4.58 (116.33)	6.69 (170.0)	1.38 (35.05)	3.36 (85.34)	--	--	.62 (15.65)	3.34 (84.80)	.71 (18.00)	2041	880

Dimensions are in inches (mm). Tolerances: 2 Pl. ±.03; 3 Pl. ±.015

Notes:

- Case material: Aluminum alloy
- Finish:
For RoHS Case Styles: Clear Chemical conversion coating, non-chrome or trivalent chrome based.
- Heat sink finish: Black anodize.
- Refer to the individual model data sheet for the type of connectors available.
- Recommended screws for mounting model without heat sink on 3/32" thick sheet: #6-32, 1.50" Length.
- Shape of connector flange may vary.

Mini-Circuits
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	0° to 80° C	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Stabilization Bake	(non-operating) 125°C, 24 hours	---
Burn-in at Elevated Temp.	(DC on) 160 hours at 60° C base plate Temperature	MIL-STD-202, Method 108
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A, except 100°C