

Power Splitter/Combiner 12 Way-0°

ZN12PD-ED14746/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE: 99-01-1708

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		200		4000 MHz
Isolation	200-2000 MHz		22	
	2000-4000 MHz		24	
Insertion Loss	200-2000 MHz		1.2	
	2000-4000 MHz		2.6	
Phase Unbalance	200-2000 MHz		8.0	
	2000-4000 MHz		15.0	
Amplitude Unbalance	200-2000 MHz		0.4	
	2000-4000 MHz		0.9	
VSWR	SUM Port		1.50	
	OUT Ports		1.25	

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

COAXIAL CONNECTIONS	
SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3
PORT 4	4
PORT 5	5
PORT 6	6
PORT 7	7
PORT 8	8
PORT 9	9
PORT 10	10
PORT 11	11
PORT 12	12

electrical schematic








Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB) S-1	AMP. UNBAL. (dB)	ISOLATION (dB)		PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)	
			1-2	3-4			S	12
200.0	11.03	0.23	8.47	9.85	1.12	200.0	1.14	1.21
250.0	11.05	0.24	10.99	11.16	1.46	250.0	1.06	1.14
300.0	11.14	0.25	13.53	11.47	1.56	300.0	1.28	1.10
350.0	11.41	0.26	16.60	12.21	1.68	350.0	1.67	1.11
400.0	11.53	0.26	19.53	13.97	1.89	400.0	1.79	1.10
450.0	11.38	0.27	22.10	17.57	2.09	450.0	1.53	1.09
500.0	11.29	0.25	23.33	24.45	2.25	500.0	1.33	1.06
550.0	11.36	0.24	23.93	41.59	2.41	550.0	1.41	1.01
600.0	11.39	0.24	27.94	31.81	2.66	600.0	1.44	1.10
650.0	11.42	0.25	34.09	24.37	2.99	650.0	1.47	1.19
700.0	11.48	0.27	25.25	20.62	3.32	700.0	1.52	1.23
750.0	11.40	0.28	22.38	19.73	3.55	750.0	1.37	1.21
800.0	11.33	0.30	22.08	21.20	3.58	800.0	1.15	1.17
850.0	11.60	0.40	21.86	22.70	3.73	850.0	1.34	1.14
900.0	11.66	0.27	22.12	23.58	3.36	900.0	1.59	1.08
950.0	11.59	0.21	24.17	24.99	3.68	950.0	1.44	1.03
1000.0	11.46	0.20	29.50	29.24	4.18	1000.0	1.11	1.06
1100.0	11.54	0.24	47.03	41.44	4.97	1100.0	1.28	1.08
1200.0	11.73	0.23	28.20	27.70	5.55	1200.0	1.50	1.14
1300.0	11.65	0.27	29.77	23.28	5.50	1300.0	1.32	1.09
1400.0	11.87	0.25	32.48	27.22	5.46	1400.0	1.52	1.14
1500.0	11.91	0.43	28.93	32.82	7.07	1500.0	1.40	1.15
1550.0	11.87	0.14	32.30	36.29	7.21	1550.0	1.30	1.14
1600.0	11.75	0.30	41.09	36.02	8.03	1600.0	1.21	1.13
1700.0	11.79	0.27	31.18	30.84	7.90	1700.0	1.21	1.12
1800.0	11.75	0.35	36.63	30.79	8.95	1800.0	1.14	1.04
1900.0	11.89	0.48	26.88	24.46	8.20	1900.0	1.40	1.05
2000.0	11.93	0.36	23.01	21.33	8.53	2000.0	1.07	1.13
2100.0	12.18	0.37	22.08	20.53	10.33	2100.0	1.64	1.20
2200.0	11.97	0.40	28.07	25.59	9.89	2200.0	1.17	1.13
2300.0	12.06	0.26	29.32	30.09	10.15	2300.0	1.09	1.08
2400.0	12.13	0.37	28.32	28.91	12.48	2400.0	1.06	1.07
2500.0	12.16	0.46	23.56	21.60	12.90	2500.0	1.24	1.09
2600.0	12.27	0.43	23.30	20.54	14.35	2600.0	1.25	1.07
2700.0	12.41	0.68	21.84	21.17	15.24	2700.0	1.51	1.13
2800.0	12.53	0.76	21.26	20.24	14.54	2800.0	1.61	1.22
2900.0	12.31	0.86	27.32	27.03	14.08	2900.0	1.35	1.22
3000.0	12.30	0.87	29.34	29.32	13.12	3000.0	1.29	1.09
3100.0	12.37	0.69	26.10	24.73	13.84	3100.0	1.19	1.06
3200.0	12.41	0.91	25.85	24.39	14.67	3200.0	1.41	1.09
3300.0	12.41	0.96	33.06	25.89	13.38	3300.0	1.27	1.23
3400.0	12.47	0.84	35.32	31.85	13.54	3400.0	1.14	1.25
3500.0	12.47	0.81	30.22	28.67	12.50	3500.0	1.10	1.10
3600.0	12.79	0.55	23.28	22.55	10.89	3600.0	1.28	1.07
3700.0	13.03	0.51	25.15	23.93	12.37	3700.0	1.15	1.10
3800.0	13.05	0.75	34.30	27.63	13.54	3800.0	1.15	1.25
3900.0	13.37	1.00	27.49	24.12	14.01	3900.0	1.23	1.37
4000.0	13.39	1.03	26.59	25.77	15.94	4000.0	1.08	1.33

¹Total Loss = Insertion Loss + 10.8dB Splitter Loss

Typical Performance Curves





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I