

Coaxial Frequency Mixer

Level 17 (LO Power +17 dBm) 3700 to 8000 MHz

Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA

Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

LO	1
RF	2
IF	3

Outline Drawing



Outline Dimensions (inch)

A	B	C	D	E	F	G	H
1.00	.75	.58	.50	.29	.38	.140	--
25.40	19.05	14.73	12.70	7.37	9.65	3.56	--
J	K	L	M	N	P	wt	
.687	--	.32	.13	.10	.16	grams	
17.45	--	8.13	3.30	2.54	4.06	25.0	

Features

- wide frequency range, 3700 to 8000 MHz
- low conversion loss, 5.8 dB typ.
- high L-R isolation, 40 dB typ.

Applications

- SATCOM
- instrumentation
- defense & federal communications
- SHF

ZMX-8GH



Generic photo used for illustration purposes only

CASE STYLE: BU413

Connectors	Model
SMA	ZMX-8GH

Electrical Specifications


FREQUENCY (MHz)		CONVERSION LOSS (dB)			LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)	
LO/RF	IF	$f_L - f_U$	$\bar{X}$	σ	Total Range Max.	Typ.	Min.	Typ.	Min.
3700-8000	DC-2000		5.8	0.30	8.5	40	20	18	8

1 dB COMP: +14 dBm typ.

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +17dBm	LO +17dBm	LO +17dBm	LO +17dBm	LO +17dBm
3700.00	3730.00	4.92	33.44	12.23	5.02	1.98
3886.79	3916.79	4.99	31.47	12.75	5.42	1.90
4000.00	4030.00	5.03	32.33	13.05	5.47	2.04
4260.38	4290.38	4.94	41.36	14.54	5.55	2.28
4509.43	4539.43	4.87	35.93	14.36	6.15	2.32
4758.49	4788.49	4.82	34.53	15.93	5.69	2.46
5000.00	4970.00	4.34	40.09	17.09	5.09	2.46
5256.60	5226.60	4.34	40.85	17.27	3.30	2.51
5505.66	5475.66	4.30	38.82	18.71	2.15	2.32
5754.72	5724.72	4.42	40.06	18.33	1.77	2.56
6000.00	5970.00	5.20	36.23	18.33	1.74	2.61
6439.62	6409.62	4.38	33.53	17.51	1.73	2.28
6688.68	6658.68	4.17	31.56	17.45	1.64	1.87
7000.00	6970.00	4.42	29.88	17.86	1.59	1.81
7240.00	7210.00	4.51	27.35	17.67	1.55	2.13
7493.33	7463.33	4.39	24.88	17.03	1.40	1.76
7683.33	7653.33	4.71	22.85	16.56	1.25	1.27
7746.67	7716.67	4.97	22.55	17.30	1.13	1.29
7810.00	7780.00	5.05	22.39	17.74	1.10	1.27
8000.00	7970.00	4.96	22.56	21.24	1.08	1.28

Electrical Schematic









Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A
M151107
ZMX-8GH
DJ/TD/CP/AM
200430
Page 1 of 2



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Frequency Mixer

ZMX-8GH

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=30MHz (dB)			RF (IN) (MHz)	LO (MHz)	IP3 INPUT (dBm)			RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=+14dBm (dB)		
		@LO (dBm)					@LO (dBm)					@LO (dBm)		
		+14	+17	+20			+14	+17	+20			+14	+17	+20
1560.1	1590.1	21.70	10.22	10.20	1560.1	1590.1	10.23	22.56	22.58	1560.1	1590.1	-7.77	2.10	2.16
1813.6	1843.6	11.76	8.98	7.20	1813.6	1843.6	20.27	26.21	24.87	1813.6	1843.6	-0.16	0.94	1.13
2067.1	2097.1	10.88	8.23	7.06	2067.1	2097.1	16.36	26.05	25.97	2067.1	2097.1	-0.48	0.71	1.11
2320.6	2350.6	8.58	7.00	6.47	2320.6	2350.6	24.17	24.38	24.49	2320.6	2350.6	0.74	0.97	1.04
2574.1	2604.1	7.22	5.96	5.53	2574.1	2604.1	24.10	23.40	23.65	2574.1	2604.1	1.16	1.31	1.18
2827.6	2857.6	6.17	5.60	5.38	2827.6	2857.6	23.40	25.76	25.43	2827.6	2857.6	1.49	1.22	1.08
3081.1	3111.1	5.72	5.35	5.21	3081.1	3111.1	25.10	25.81	26.56	3081.1	3111.1	1.28	0.97	0.93
3334.6	3364.6	5.66	5.33	5.19	3334.6	3364.6	24.50	25.42	25.75	3334.6	3364.6	0.99	0.72	0.70
3588.1	3618.1	5.83	5.53	5.38	3588.1	3618.1	24.70	25.36	24.91	3588.1	3618.1	0.87	0.64	0.62
3841.6	3871.6	5.64	5.32	5.21	3841.6	3871.6	23.14	24.67	24.31	3841.6	3871.6	0.96	0.70	0.71
4095.1	4125.1	5.94	5.50	5.32	4095.1	4125.1	20.96	24.72	25.62	4095.1	4125.1	0.80	0.54	0.54
4348.6	4378.6	5.93	5.38	5.21	4348.6	4378.6	21.37	23.13	25.41	4348.6	4378.6	0.84	0.62	0.57
4602.1	4632.1	6.05	5.43	5.17	4602.1	4632.1	23.17	21.53	23.24	4602.1	4632.1	0.83	0.57	0.50
4855.6	4885.6	5.81	5.28	5.04	4855.6	4885.6	22.84	22.02	22.82	4855.6	4885.6	1.00	0.65	0.53
5109.1	5139.1	5.66	5.08	4.83	5109.1	5139.1	21.97	21.84	21.59	5109.1	5139.1	1.26	0.76	0.52
5362.6	5392.6	5.70	5.11	4.82	5362.6	5392.6	20.76	22.05	21.62	5362.6	5392.6	1.19	0.67	0.53
5616.1	5646.1	5.62	4.93	4.71	5616.1	5646.1	19.52	21.94	22.24	5616.1	5646.1	1.41	0.74	0.52
5869.6	5899.6	6.23	5.50	5.19	5869.6	5899.6	21.39	25.19	24.42	5869.6	5899.6	0.97	0.55	0.44
6123.1	6153.1	6.26	5.32	4.99	6123.1	6153.1	18.94	22.92	23.24	6123.1	6153.1	1.23	0.80	0.67
6376.6	6406.6	6.16	5.20	4.93	6376.6	6406.6	18.83	23.26	24.04	6376.6	6406.6	1.33	0.88	0.79
6630.1	6660.1	6.03	4.96	4.73	6630.1	6660.1	17.37	23.05	24.10	6630.1	6660.1	1.48	1.04	0.97
6909.0	6939.0	5.50	4.76	4.62	6909.0	6939.0	18.63	23.82	24.62	6909.0	6939.0	1.47	0.95	1.00
7162.4	7192.4	5.97	4.98	4.79	7162.4	7192.4	19.32	24.15	25.04	7162.4	7192.4	1.19	0.79	0.87
7441.3	7471.3	5.89	5.16	5.00	7441.3	7471.3	21.07	24.26	24.88	7441.3	7471.3	1.12	0.70	0.83
7694.8	7724.8	5.78	5.31	5.22	7694.8	7724.8	21.39	24.29	25.06	7694.8	7724.8	1.17	0.73	0.86
7973.6	8003.6	5.52	5.21	5.19	7973.6	8003.6	21.88	24.41	24.64	7973.6	8003.6	1.04	0.77	0.94
8227.1	8257.1	5.45	5.16	5.12	8227.1	8257.1	22.92	25.33	25.46	8227.1	8257.1	1.10	0.79	0.96
8506.0	8536.0	5.42	5.18	5.14	8506.0	8536.0	23.27	25.37	25.44	8506.0	8536.0	1.19	0.81	0.92
8759.5	8789.5	5.58	5.30	5.22	8759.5	8789.5	22.84	25.21	25.69	8759.5	8789.5	1.23	0.83	0.95
9038.4	9068.4	5.86	5.58	5.42	9038.4	9068.4	22.19	24.92	25.85	9038.4	9068.4	1.13	0.78	0.99
9291.8	9321.8	6.33	6.01	5.85	9291.8	9321.8	21.58	24.28	26.41	9291.8	9321.8	1.22	0.64	0.85
9570.7	9600.7	6.46	6.04	5.91	9570.7	9600.7	20.18	22.75	25.31	9570.7	9600.7	1.63	0.62	0.78
9824.2	9854.2	7.37	6.14	5.97	9824.2	9854.2	17.40	21.36	23.95	9824.2	9854.2	1.64	0.81	0.67
10103.0	10133.0	15.20	6.90	6.29	10103.0	10133.0	9.09	20.74	22.98	10103.0	10133.0	-5.08	1.13	0.54
10356.5	10386.5	30.91	11.65	7.05	10356.5	10386.5	1.17	16.07	22.54	10356.5	10386.5	-18.31	-1.81	0.56
10635.4	10665.4	34.37	14.37	7.23	10635.4	10665.4	0.24	11.62	22.43	10635.4	10665.4	-21.87	-4.02	0.58
10888.9	10918.9	27.24	10.14	7.48	10888.9	10918.9	3.42	21.28	24.78	10888.9	10918.9	-15.21	-0.78	0.35
11167.8	11197.8	33.01	11.20	8.68	11167.8	11197.8	0.99	18.93	23.78	11167.8	11197.8	-20.85	-1.68	-0.26
11421.3	11451.3	37.33	12.40	9.63	11421.3	11451.3	-0.38	17.73	21.73	11421.3	11451.3	-23.95	-2.36	-0.68
11700.1	11730.1	36.01	13.95	10.62	11700.1	11730.1	0.33	19.87	21.94	11700.1	11730.1	-21.28	-1.99	0.00



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350186, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4861



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=5850MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=3690MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=8010.1MHz (dB)
		@LO (dBm)			@LO (dBm)			@LO (dBm)
		+17			+17			+17
2149.9	3700.1	5.33	10.1	3700.1	5.79	2910.0	5100.1	10.74
2029.9	3820.1	5.10	90.1	3780.1	5.51	2830.0	5180.1	9.62
1909.9	3940.1	4.99	170.1	3860.1	5.54	2750.0	5260.1	8.55
1809.9	4040.1	4.97	250.1	3940.1	5.58	2670.0	5340.1	7.72
1689.9	4160.1	5.20	330.1	4020.1	5.62	2590.0	5420.1	7.38
1589.9	4260.1	5.22	410.1	4100.1	5.63	2510.0	5500.1	7.36
1469.9	4380.1	5.19	490.1	4180.1	5.79	2430.0	5580.1	7.23
1369.9	4480.1	5.07	570.1	4260.1	5.83	2350.0	5660.1	7.14
1249.9	4600.1	5.08	650.1	4340.1	5.86	2270.0	5740.1	7.18
1149.9	4700.1	4.99	730.1	4420.1	5.98	2190.0	5820.1	7.02
1030.0	4820.0	4.91	810.1	4500.1	6.16	2110.0	5900.1	6.77
930.0	4920.0	4.93	890.1	4580.1	6.26	2030.0	5980.1	6.65
810.0	5040.0	4.97	970.1	4660.1	6.38	1950.0	6060.1	6.60
710.0	5140.0	4.95	1050.1	4740.1	6.42	1870.0	6140.1	6.44
590.0	5260.0	4.93	1130.1	4820.1	6.58	1790.0	6220.1	6.24
490.0	5360.0	4.95	1210.1	4900.1	6.60	1710.0	6300.1	6.18
370.0	5480.0	4.93	1290.1	4980.1	6.49	1630.0	6380.1	6.18
270.0	5580.0	4.95	1370.1	5060.1	6.57	1550.0	6460.1	6.23
150.0	5700.0	5.05	1450.1	5140.1	6.78	1470.0	6540.1	6.17
50.0	5800.0	5.24	1510.1	5200.1	6.84	1410.0	6600.1	5.90
70.0	5920.0	5.44	1590.1	5280.1	7.10	1330.0	6680.1	5.89
170.0	6020.0	5.57	1650.1	5340.1	7.34	1270.0	6740.1	5.90
290.0	6140.0	5.51	1730.1	5420.1	7.46	1190.0	6820.1	5.75
390.0	6240.0	5.48	1790.1	5480.1	7.60	1130.0	6880.1	5.82
510.0	6360.0	5.57	1870.1	5560.1	7.97	1050.0	6960.1	5.68
610.0	6460.0	5.67	1930.1	5620.1	7.98	990.0	7020.1	5.63
730.0	6580.0	5.85	2010.1	5700.1	8.21	910.0	7100.1	5.72
830.0	6680.0	5.98	2070.1	5760.1	8.47	850.0	7160.1	5.62
950.0	6800.0	6.13	2150.1	5840.1	8.59	770.0	7240.1	5.57
1050.0	6900.0	6.22	2210.1	5900.1	8.65	710.0	7300.1	5.53
1170.1	7020.1	6.36	2290.1	5980.1	8.79	630.0	7380.1	5.48
1270.1	7120.1	6.35	2350.1	6040.1	8.95	570.0	7440.1	5.39
1390.1	7240.1	6.47	2430.1	6120.1	9.07	490.0	7520.1	5.39
1490.1	7340.1	6.46	2490.1	6180.1	9.12	430.0	7580.1	5.31
1610.1	7460.1	6.51	2570.1	6260.1	9.26	350.0	7660.1	5.34
1710.1	7560.1	6.57	2630.1	6320.1	9.48	290.0	7720.1	5.26
1830.1	7680.1	6.47	2710.1	6400.1	9.72	210.0	7800.1	5.29
1930.1	7780.1	6.50	2770.1	6460.1	10.18	150.0	7860.1	5.26
2050.1	7900.1	6.65	2850.1	6540.1	10.71	70.0	7940.1	5.30
2150.1	8000.1	6.70	2910.1	6600.1	11.26	10.0	8000.1	5.59

Frequency Mixer

ZMX-8GH

Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)		
	+14	+17	+20	+14	+17	+20
1590.1	24.82	25.34	25.43	7.11	12.49	12.76
1843.6	36.15	33.19	30.11	6.96	9.04	12.95
2097.1	36.19	28.76	28.37	7.10	8.48	10.48
2350.6	27.40	25.62	26.19	6.97	7.79	9.07
2604.1	26.36	26.04	26.16	6.42	7.31	8.13
2857.6	29.82	29.21	28.77	7.39	8.49	9.27
3111.1	33.28	31.33	30.48	9.37	10.09	10.38
3364.6	34.65	33.13	31.70	11.31	11.64	10.96
3618.1	35.25	34.15	32.90	13.51	13.00	12.02
3871.6	34.93	34.58	33.88	15.63	14.21	13.12
4125.1	42.84	40.10	37.09	17.44	15.11	13.82
4378.6	38.93	40.63	38.26	18.04	15.95	14.36
4632.1	37.89	38.04	38.05	18.90	16.99	15.24
4885.6	39.90	38.53	37.63	19.30	17.55	16.02
5139.1	40.08	42.18	40.79	19.47	17.96	16.57
5392.6	37.86	40.85	41.51	19.46	18.38	17.10
5646.1	36.73	41.10	42.47	19.58	19.04	17.85
5899.6	33.24	36.03	39.92	19.24	18.96	18.20
6153.1	31.53	34.53	38.02	19.22	19.26	18.56
6406.6	30.84	33.88	37.47	19.46	19.55	19.27
6660.1	28.92	32.24	35.97	19.27	19.51	19.62
6939.0	28.05	31.44	35.62	19.04	19.69	19.82
7192.5	26.72	30.23	36.10	19.55	20.14	20.49
7471.3	26.52	29.68	33.77	19.22	20.07	20.45
7724.8	26.44	28.92	32.43	20.91	21.61	22.03
8003.6	25.75	27.97	30.12	24.93	25.56	26.24
8257.2	25.09	26.93	28.21	27.59	29.17	30.35
8536.0	24.26	25.61	26.47	29.27	31.59	33.93
8789.5	23.38	24.71	25.54	30.32	32.89	35.41
9068.4	22.04	23.55	24.50	31.40	33.42	34.87
9321.8	20.21	21.89	22.86	32.29	33.30	33.62
9600.7	19.07	20.87	21.97	33.24	32.73	32.05
9854.2	17.82	19.72	21.10	32.29	31.07	30.27
10133.1	16.53	17.57	19.20	28.82	28.29	27.81
10386.5	15.20	15.71	16.92	25.24	25.13	25.06
10665.4	14.34	14.91	16.16	22.89	23.05	23.17
10918.9	16.31	17.04	17.87	24.18	24.52	24.88
11197.8	20.44	20.63	21.15	28.50	28.71	28.88
11451.3	23.24	23.70	24.32	33.95	34.14	33.35
11730.1	26.68	29.33	30.39	41.30	37.47	33.79

RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB)		
		@LO (dBm)		
		+14	+17	+20
1560.1	1590.1	13.38	11.87	11.86
1813.6	1843.6	12.73	10.92	10.11
2067.1	2097.1	15.26	12.40	11.12
2320.6	2350.6	16.47	14.96	14.43
2574.1	2604.1	18.05	19.61	19.90
2827.6	2857.6	24.30	25.38	25.82
3081.1	3111.1	26.95	26.59	26.26
3334.6	3364.6	27.48	27.05	26.52
3588.1	3618.1	27.18	27.03	26.75
3841.6	3871.6	27.69	27.74	27.75
4095.1	4125.1	29.12	29.15	29.07
4348.6	4378.6	30.04	30.43	30.68
4602.1	4632.1	31.01	31.34	31.80
4855.6	4885.6	32.62	32.81	33.19
5109.1	5139.1	34.33	34.61	35.09
5362.6	5392.6	35.18	35.35	35.67
5616.1	5646.1	36.57	36.52	36.35
5869.6	5899.6	37.24	37.17	37.01
6123.1	6153.1	36.11	35.46	35.01
6376.6	6406.6	35.71	34.96	34.47
6630.1	6660.1	34.16	33.27	32.69
6909.0	6939.0	30.93	30.32	29.86
7162.4	7192.4	28.72	28.32	27.94
7441.3	7471.3	26.30	26.21	26.02
7694.8	7724.8	24.40	24.48	24.44
7973.6	8003.6	25.13	25.35	25.48
8227.1	8257.1	27.33	27.63	27.78
8506.0	8536.0	30.05	30.25	30.53
8759.5	8789.5	32.81	33.00	33.25
9038.4	9068.4	35.85	35.98	36.32
9291.8	9321.8	39.14	39.28	39.36
9570.7	9600.7	43.30	42.86	42.66
9824.2	9854.2	45.74	44.75	44.02
10103.0	10133.0	41.25	41.57	41.25
10356.5	10386.5	36.23	36.78	37.33
10635.4	10665.4	32.77	33.66	34.44
10888.9	10918.9	32.78	34.61	35.79
11167.8	11197.8	33.52	35.97	37.39
11421.3	11451.3	31.09	32.74	33.51
11700.1	11730.1	23.69	24.93	25.73

Frequency Mixer

ZMX-8GH

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	RF VSWR (:1)			LO (MHz)	LO VSWR (:1)			IF (OUT) (MHz)	IF VSWR @LO=8000MHz (:1)		
		@LO (dBm)				@LO (dBm)				@LO (dBm)		
		+14	+17	+20		+14	+17	+20		+14	+17	+20
1560.1	1590.1	15.39	5.19	5.09	1590.1	9.90	3.18	3.20	10.1	1.46	1.22	1.08
1813.6	1843.6	7.56	5.58	4.09	1843.6	7.66	4.17	3.14	90.1	1.46	1.22	1.08
2067.1	2097.1	7.08	4.80	3.82	2097.1	5.13	3.00	2.80	170.1	1.43	1.20	1.07
2320.6	2350.6	5.41	4.06	3.50	2350.6	3.19	2.32	2.50	250.1	1.42	1.20	1.09
2574.1	2604.1	5.07	4.05	3.50	2604.1	2.74	2.14	2.30	330.1	1.47	1.26	1.14
2827.6	2857.6	4.08	3.50	3.18	2857.6	2.14	1.85	2.29	410.1	1.48	1.26	1.15
3081.1	3111.1	3.95	3.43	3.15	3111.1	1.54	1.57	2.16	490.1	1.46	1.25	1.16
3334.6	3364.6	3.94	3.42	3.05	3364.6	1.20	1.55	2.24	570.1	1.43	1.25	1.20
3588.1	3618.1	3.86	3.40	3.05	3618.1	1.08	1.53	2.23	650.1	1.48	1.33	1.29
3841.6	3871.6	3.90	3.34	2.94	3871.6	1.31	1.66	2.37	730.1	1.53	1.40	1.37
4095.1	4125.1	3.84	3.23	2.78	4125.1	1.58	1.71	2.26	810.1	1.60	1.47	1.44
4348.6	4378.6	4.03	3.20	2.74	4378.6	1.92	1.91	2.40	890.1	1.66	1.53	1.48
4602.1	4632.1	4.11	3.20	2.60	4632.1	2.16	2.04	2.39	970.1	1.67	1.53	1.49
4855.6	4885.6	3.88	3.11	2.48	4885.6	2.44	2.17	2.47	1050.1	1.69	1.57	1.54
5109.1	5139.1	3.69	2.95	2.28	5139.1	2.90	2.34	2.47	1130.1	1.76	1.66	1.64
5362.6	5392.6	3.38	2.70	2.08	5392.6	3.30	2.48	2.59	1210.1	1.95	1.84	1.81
5616.1	5646.1	3.31	2.51	1.92	5646.1	3.86	2.52	2.43	1290.1	2.09	1.95	1.89
5869.6	5899.6	3.10	2.50	2.02	5899.6	4.16	2.57	2.39	1370.1	2.13	1.96	1.89
6123.1	6153.1	3.21	2.50	2.02	6153.1	4.72	2.60	2.26	1450.1	2.13	1.97	1.89
6376.6	6406.6	2.95	2.29	1.97	6406.6	4.77	2.54	2.11	1530.1	2.21	2.04	1.95
6630.1	6660.1	2.65	1.91	1.63	6660.1	5.49	2.54	1.90	1610.1	2.39	2.17	2.06
6909.0	6939.0	2.20	1.67	1.42	6939.0	5.16	2.37	1.67	1690.1	2.52	2.26	2.12
7162.4	7192.4	1.97	1.45	1.26	7192.5	5.03	2.16	1.39	1770.1	2.57	2.30	2.15
7441.3	7471.3	1.76	1.39	1.20	7471.3	4.14	1.83	1.11	1850.1	2.69	2.38	2.19
7694.8	7724.8	1.56	1.32	1.21	7724.8	2.99	1.50	1.14	1930.1	2.77	2.41	2.20
7973.6	8003.6	1.63	1.44	1.35	8003.6	2.30	1.32	1.42	2010.1	2.75	2.37	2.14
8227.1	8257.1	1.63	1.52	1.49	8257.2	1.75	1.30	1.74	2090.1	2.69	2.31	2.07
8506.0	8536.0	1.82	1.73	1.69	8536.0	1.28	1.46	2.07	2170.1	2.72	2.33	2.09
8759.5	8789.5	2.02	1.92	1.90	8789.5	1.17	1.80	2.57	2250.1	2.79	2.39	2.15
9038.4	9068.4	2.44	2.34	2.30	9068.4	1.66	2.30	3.15	2310.1	2.74	2.37	2.15
9291.8	9321.8	2.73	2.64	2.61	9321.8	2.38	2.82	3.59	2390.1	2.74	2.43	2.25
9570.7	9600.7	3.31	3.14	3.09	9600.7	3.65	3.76	4.44	2450.1	2.78	2.54	2.42
9824.2	9854.2	4.02	3.40	3.29	9854.2	5.47	4.80	5.16	2530.1	2.87	2.74	2.69
10103.0	10133.0	8.86	4.35	3.87	10133.1	5.97	5.17	4.92	2590.1	2.95	2.90	2.92
10356.5	10386.5	10.43	5.66	3.78	10386.5	4.27	4.24	3.99	2670.1	3.17	3.27	3.40
10635.4	10665.4	10.02	6.46	3.77	10665.4	2.60	2.65	2.66	2730.1	3.50	3.74	3.97
10888.9	10918.9	7.50	4.54	3.45	10918.9	4.05	3.83	3.54	2810.1	4.03	4.47	4.83
11167.8	11197.8	10.37	5.66	4.59	11197.8	9.18	8.05	6.81	2870.1	4.21	4.72	5.13
11421.3	11451.3	6.86	4.44	3.81	11451.3	16.11	13.70	11.17	2950.1	5.02	5.74	6.30
11700.1	11730.1	2.83	2.52	2.39	11730.1	18.50	15.26	11.61	3010.1	6.01	6.86	7.50

Harmonics Tables

RF HARMONICS ORDER	(-dBm)	(-dBc)										
	0	-	-	+4	50	12	42	---	---	---	---	---
	1	-	33	+0	56	37	39	51	---	---	---	---
	2	64	67	59	48	54	71	52	76	---	---	---
	3	>90	78	72	>84	58	>84	75	>84	75	---	---
	4	>90	>84	>84	>84	>84	>84	>84	>84	>84	>84	---
	5	---	---	>84	>84	>84	>84	>84	>84	>84	>84	---
	6	---	---	---	>84	>84	>84	>84	>84	>84	>84	>84
	7	---	---	---	---	>84	>84	>84	>84	>84	>84	>84
	8	---	---	---	---	---	>84	>84	>84	>84	>84	>84
	9	---	---	---	---	---	---	>84	>84	>84	>84	>84
	10	---	---	---	---	---	---	---	>84	>84	>84	>84
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions:

RF IN: 5850 MHz; -1.00 dBm.

LO IN: 5880 MHz; +17.00 dBm

IF OUT: 30 MHz; -6.28 dBm

RF HARMONICS ORDER	(-dBm)	(-dBc)										
	0	-	-	5	57	24	51	---	---	---	---	---
	1	-	33	+0	55	37	42	62	---	---	---	---
	2	45	57	53	37	47	61	46	72	---	---	---
	3	63	59	55	71	37	74	65	62	64	---	---
	4	84	75	73	80	65	62	63	79	64	77	---
	5	---	---	93	80	77	>94	66	93	73	>94	73
	6	---	---	---	>94	87	90	79	81	77	90	75
	7	---	---	---	---	>94	>94	93	>94	71	>94	86
	8	---	---	---	---	---	>94	93	>94	92	90	92
	9	---	---	---	---	---	---	>94	>94	>94	>94	82
	10	---	---	---	---	---	---	---	>94	>94	>94	>94
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions:

RF IN: 5850 MHz; 9.00 dBm.

LO IN: 5880 MHz; +17.00 dBm

IF OUT: 30 MHz; 3.59 dBm


Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.

2. + entry denotes harmonics are in (dBc) above IF OUTPUT.


3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

Typical Performance Curves


Conversion Loss @ IF=30MHz




Conversion Loss vs. LO @ RF=5850MHz




Conversion Loss vs. IF @ RF=5850MHz




Conversion Loss vs. IF @ RF=3690MHz




Conversion Loss vs. IF @ RF=8010.1MHz



IP3 Input




Compression @ RF IN=+14dBm




Typical Performance Curves


LO-RF Isolation




LO-IF Isolation




RF-IF Isolation




RF VSWR



LO VSWR



IF VSWR



Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	+4	50	12	42	---	---	---	---	---	---
1	-	33	+0	56	37	39	51	---	---	---	---	---
2	64	67	59	48	54	71	52	76	---	---	---	---
3	>90	78	72	>84	58	>84	75	>84	75	---	---	---
4	>90	>84	>84	>84	>84	>84	>84	>84	>84	>84	---	---
5	---	---	>84	>84	>84	>84	>84	>84	>84	>84	>84	---
6	---	---	---	>84	>84	>84	>84	>84	>84	>84	>84	>84
7	---	---	---	---	>84	>84	>84	>84	>84	>84	>84	>84
8	---	---	---	---	---	>84	>84	>84	>84	>84	>84	>84
9	---	---	---	---	---	---	>84	>84	>84	>84	>84	>84
10	---	---	---	---	---	---	---	>84	>84	>84	>84	>84
RF CAL	0	1	2	3	4	5	6	7	8	9	10	

LO HARMONICS ORDER

Test conditions: RF IN: 5850 MHz; -1.00 dBm.
LO IN: 5880 MHz; +17.00 dBm
IF OUT: 30 MHz; -6.28 dBm

RF HARMONICS ORDER


	(-dBm)	(-dBc)										
0	-	-	5	57	24	51	---	---	---	---	---	---
1	-	33	+0	55	37	42	62	---	---	---	---	---
2	45	57	53	37	47	61	46	72	---	---	---	---
3	63	59	55	71	37	74	65	62	64	---	---	---
4	84	75	73	80	65	62	63	79	64	77	---	---
5	---	---	93	80	77	>94	66	93	73	>94	73	---
6	---	---	---	>94	87	90	79	81	77	90	75	90
7	---	---	---	---	>94	>94	93	>94	71	>94	86	89
8	---	---	---	---	---	>94	93	>94	92	90	92	>94
9	---	---	---	---	---	---	>94	>94	>94	>94	82	>94
10	---	---	---	---	---	---	---	>94	>94	>94	>94	>94
RF CAL	0	1	2	3	4	5	6	7	8	9	10	

LO HARMONICS ORDER

Test conditions: RF IN: 5850 MHz; 9.00 dBm.
LO IN: 5880 MHz; +17.00 dBm
IF OUT: 30 MHz; 3.59 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
BU413	1.00 (25.40)	.75 (19.05)	.58 (14.73)	.50 (12.70)	.29 (7.37)	.38 (9.65)	.140 (3.56)	--	.687 (17.45)	--	.32 (8.13)	.13 (3.30)	.10 (2.54)

CASE#	P	WT. GRAMS
BU413	.16 (4.06)	25

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.



INTERNET <http://www.minicircuits.com>
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I