

Coaxial Frequency Mixer

Level 23 (LO Power +23 dBm) 5 to 500 MHz

ZMY-1+


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	350mW
IF Current	40mA
Permanent damage may occur if any of these limits are exceeded.	

Coaxial Connections

LO	1
RF	3
IF	2

Outline Drawing



Outline Dimensions (inch)

A	B	C	D	E	F	G	H
1.50	1.13	1.00	.50	.155	2.345	.138	.987
38.10	28.70	25.40	12.70	3.94	59.56	3.51	25.07
J	K	L	M	N	P	S	wt
2.50	.10	.31	.75	1.19	.66	.150	grams
63.50	2.54	7.87	19.05	30.23	16.76	3.81	40.0

Features

- low conversion loss, 6.62 dB typ.
- high isolation, 40 dB typ. L-R & L-I
- wideband, 5 to 500 MHz

Applications

- VHF/UHF
- instrumentation



Generic photo used for illustration purposes only

CASE STYLE: M21

Connectors	Model
SMA	ZMY-1+
BRACKET (OPTION "BR")	

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications

FREQUENCY (MHz)		CONVERSION LOSS (dB)				LO-RF ISOLATION (dB)						LO-IF ISOLATION (dB)					
LO/RF	IF	Mid-Band m		Total Range Max.		L		M		U		L		M		U	
f_L - f_U		$\bar{X}$	σ	Max.	Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.
5-500	DC-500	6.62	0.10	7.5	8.5	55	45	40	30	30	25	55	45	40	30	30	20


1 dB COMP.: +15 dBm typ.

L = low range [f_L to $10 f_L$] M = mid range [$10 f_L$ to $f_U/2$] U = upper range [$f_U/2$ to f_U]
m = mid band [$2 f_L$ to $f_U/2$]

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +23dBm	LO +23dBm	LO +23dBm	LO +23dBm	LO +23dBm
5.00	35.00	6.52	57.02	82.02	1.29	2.50
10.00	40.00	6.40	56.72	82.32	1.14	2.37
20.00	50.00	6.40	54.48	81.28	1.06	2.33
35.94	65.94	6.43	51.51	75.99	1.05	2.31
50.00	80.00	6.40	48.82	72.57	1.07	2.37
82.35	52.35	6.39	45.62	62.91	1.08	2.20
100.00	70.00	6.36	44.05	58.66	1.10	2.25
144.22	114.22	6.53	41.60	53.71	1.12	2.11
175.16	145.16	6.68	40.04	51.38	1.14	2.25
200.00	170.00	6.69	39.45	50.73	1.16	2.06
221.57	191.57	6.52	36.41	46.45	1.18	2.17
252.50	222.50	6.52	36.33	47.23	1.20	2.04
283.44	253.44	6.64	36.36	47.98	1.22	2.10
314.38	284.38	6.74	36.35	46.73	1.24	1.96
345.32	315.32	6.62	33.85	44.99	1.26	2.04
376.26	346.26	6.50	30.50	41.75	1.29	1.96
407.19	377.19	6.43	32.89	42.28	1.31	1.95
438.13	408.13	6.50	33.81	42.66	1.35	1.90
469.07	439.07	6.81	33.63	41.41	1.38	1.87
500.00	470.00	6.62	34.24	40.42	1.44	1.83

Electrical Schematic









Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. D
M170832
ZMY-1+
DJ/TD/CP/AM
200806



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Frequency Mixer

ZMY-1+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=30MHz (dB)		
		@LO (dBm)		
		+20	+23	+26
5.0	35.0	6.50	6.52	6.53
10.0	40.0	6.60	6.40	6.48
20.1	50.1	5.64	5.52	5.46
30.1	60.1	5.67	5.54	5.48
40.1	70.1	5.69	5.54	5.49
50.1	80.1	5.65	5.53	5.50
60.1	90.1	5.63	5.54	5.51
80.1	110.1	5.66	5.57	5.55
100.1	130.1	5.67	5.60	5.57
120.1	150.1	5.68	5.61	5.58
140.1	170.1	5.70	5.65	5.62
160.1	190.1	5.70	5.64	5.61
180.1	210.1	5.72	5.67	5.64
200.1	230.1	5.76	5.69	5.66
220.1	250.1	5.79	5.72	5.69
240.1	270.1	5.82	5.75	5.71
260.1	290.1	5.89	5.80	5.75
280.1	310.1	5.91	5.84	5.79
300.1	330.1	5.89	5.83	5.80
320.1	350.1	5.92	5.86	5.85
350.1	380.1	6.08	5.96	5.91
380.1	410.1	6.20	6.06	5.94
410.1	440.1	6.37	6.19	6.03
440.1	470.1	6.47	6.22	6.04
470.1	500.1	6.35	6.11	5.96
500.1	530.1	6.39	6.09	5.92
530.1	560.1	6.57	6.24	6.05
560.1	590.1	7.08	6.57	6.34
590.1	620.1	7.39	6.63	6.33
620.1	650.1	7.67	6.94	6.57
650.1	680.1	8.62	7.90	7.30
690.1	720.1	8.44	7.92	7.40
730.1	760.1	8.09	7.77	7.54
810.1	840.1	8.30	8.10	7.90
850.1	880.1	8.40	8.15	7.98
890.1	920.1	8.60	8.30	8.12
930.1	960.1	8.80	8.55	8.40
970.1	1000.1	9.46	9.11	8.86
1010.1	1040.1	10.51	10.05	9.69
1050.1	1080.1	11.85	11.28	10.69

RF (IN) (MHz)	LO (MHz)	IP3 INPUT (dBm)		
		@LO (dBm)		
		+20	+23	+26
10.1	40.1	26.95	26.61	34.09
20.1	50.1	25.12	32.82	27.31
30.1	60.1	25.12	32.54	28.50
40.1	70.1	26.50	26.40	29.08
50.1	80.1	27.57	27.39	29.22
60.1	90.1	25.37	27.97	28.90
80.1	110.1	24.28	27.36	28.18
100.1	130.1	25.74	27.06	27.64
120.1	150.1	25.45	26.70	27.38
140.1	170.1	25.78	26.17	26.89
160.1	190.1	24.74	25.40	26.89
180.1	210.1	24.76	25.73	27.23
200.1	230.1	23.31	24.44	26.59
220.1	250.1	24.65	25.20	26.35
240.1	270.1	25.58	26.50	28.60
260.1	290.1	22.63	24.21	26.98
280.1	310.1	22.70	23.36	25.18
300.1	330.1	23.61	24.49	26.84
320.1	350.1	24.32	25.67	28.50
350.1	380.1	21.75	24.36	27.00
380.1	410.1	17.95	20.48	24.38
410.1	440.1	18.27	19.45	22.03
440.1	470.1	20.01	21.93	24.19
470.1	500.1	23.13	26.20	30.13
500.1	530.1	25.56	29.49	39.10
530.1	560.1	26.74	30.04	32.88
560.1	590.1	26.59	35.14	42.27
590.1	620.1	21.16	31.00	32.66
620.1	650.1	20.19	26.34	29.75
650.1	680.1	19.71	21.44	24.54
690.1	720.1	20.04	21.60	29.25
730.1	760.1	24.02	26.76	27.62
770.1	800.1	24.62	29.29	32.32
810.1	840.1	26.39	34.47	33.29
850.1	880.1	25.50	27.81	31.80
890.1	920.1	25.77	26.75	27.85
930.1	960.1	27.51	28.82	30.01
970.1	1000.1	24.81	26.81	29.82
1010.1	1040.1	20.78	23.04	22.24
1050.1	1080.1	17.98	22.47	19.95

RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=+15dBm (dB)		
		@LO (dBm)		
		+20	+23	+26
10.1	40.1	0.45	0.30	0.16
20.1	50.1	0.51	0.34	0.19
30.1	60.1	0.55	0.38	0.21
40.1	70.1	0.53	0.35	0.17
50.1	80.1	0.49	0.29	0.12
60.1	90.1	0.42	0.22	0.08
80.1	110.1	0.39	0.19	0.06
100.1	130.1	0.41	0.21	0.08
120.1	150.1	0.41	0.24	0.13
140.1	170.1	0.38	0.24	0.13
160.1	190.1	0.34	0.22	0.12
180.1	210.1	0.28	0.16	0.07
200.1	230.1	0.29	0.19	0.10
220.1	250.1	0.32	0.22	0.15
240.1	270.1	0.35	0.24	0.15
260.1	290.1	0.36	0.26	0.16
280.1	310.1	0.37	0.26	0.14
300.1	330.1	0.51	0.34	0.18
320.1	350.1	0.72	0.48	0.31
350.1	380.1	0.96	0.69	0.44
380.1	410.1	1.08	0.81	0.51
410.1	440.1	1.18	0.93	0.63
440.1	470.1	1.33	1.17	0.91
470.1	500.1	1.22	1.05	0.81
500.1	530.1	1.27	1.08	0.88
530.1	560.1	1.44	1.22	1.01
560.1	590.1	1.29	1.14	0.93
590.1	620.1	0.98	1.11	0.90
620.1	650.1	0.74	0.93	0.77
650.1	680.1	0.43	0.67	0.75
690.1	720.1	0.39	0.56	0.61
730.1	760.1	0.71	0.73	0.54
770.1	800.1	0.68	0.62	0.35
810.1	840.1	0.61	0.51	0.38
850.1	880.1	0.68	0.61	0.51
890.1	920.1	0.59	0.44	0.40
930.1	960.1	0.58	0.33	0.49
970.1	1000.1	0.71	0.33	0.52
1010.1	1040.1	0.96	0.48	0.58
1050.1	1080.1	0.94	0.60	0.51

REV. X2

ZMY-1+

100818

Page 1 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



Frequency Mixer

ZMY-1+

Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=250.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=10.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=500.1MHz (dB)
		@LO (dBm)			@LO (dBm)			@LO (dBm)
		+23			+23			+23
0.5	249.6	5.80	0.5	10.6	5.58	0.5	499.6	6.18
1.0	249.1	5.72	0.8	10.9	5.53	0.8	499.4	6.11
1.5	248.6	5.71	1.0	11.1	5.51	1.0	499.1	6.09
2.0	248.1	5.70	2.0	12.1	5.49	2.0	498.1	6.10
2.5	247.6	5.70	3.0	13.1	5.49	3.0	497.1	6.10
3.0	247.1	5.69	4.0	14.1	5.50	4.0	496.1	6.11
4.0	246.1	5.69	5.0	15.1	5.50	5.0	495.1	6.12
5.0	245.1	5.70	6.0	16.1	5.50	6.0	494.1	6.13
6.0	244.1	5.70	8.0	18.1	5.50	8.0	492.1	6.14
8.0	242.1	5.69	10.0	20.1	5.51	10.0	490.1	6.17
10.0	240.1	5.69	15.0	25.1	5.52	15.0	485.1	6.24
15.0	235.1	5.71	20.0	30.1	5.53	20.0	480.1	6.30
20.0	230.1	5.70	25.0	35.1	5.55	25.0	475.1	6.34
25.0	225.1	5.70	30.0	40.1	5.55	30.0	470.1	6.38
30.0	220.1	5.71	35.0	45.1	5.55	35.0	465.1	6.45
35.0	215.1	5.72	40.0	50.1	5.52	40.0	460.1	6.50
40.0	210.1	5.70	45.0	55.1	5.50	45.0	455.1	6.54
45.0	205.1	5.72	50.0	60.1	5.54	50.0	450.1	6.55
50.0	200.1	5.74	70.0	80.1	5.52	70.0	430.1	6.52
55.0	195.1	5.75	90.0	100.1	5.53	90.0	410.1	6.43
60.0	190.1	5.74	110.0	120.1	5.55	110.0	390.1	6.35
65.0	185.1	5.74	130.0	140.1	5.58	130.0	370.1	6.27
70.0	180.1	5.75	150.0	160.1	5.57	150.0	350.1	6.32
80.0	170.1	5.75	170.0	180.1	5.60	170.0	330.1	6.38
90.0	160.1	5.76	190.0	200.1	5.61	190.0	310.1	6.50
100.0	150.1	5.77	210.0	220.1	5.60	210.0	290.1	6.44
110.0	140.1	5.78	230.0	240.1	5.66	230.0	270.1	6.46
120.0	130.1	5.77	250.0	260.1	5.66	250.0	250.1	6.28
130.0	120.1	5.75	270.0	280.1	5.70	270.0	230.1	6.48
140.0	110.1	5.76	290.0	300.1	5.72	290.0	210.1	6.50
150.0	100.1	5.77	310.0	320.1	5.72	310.0	190.1	6.50
160.0	90.1	5.77	330.0	340.1	5.74	330.0	170.1	6.54
170.0	80.1	5.76	350.0	360.1	5.72	350.0	150.1	6.53
180.0	70.1	5.75	370.0	380.1	5.75	370.0	130.1	6.52
190.0	60.1	5.76	390.0	400.1	5.76	390.0	110.1	6.49
200.0	50.1	5.77	410.0	420.1	5.71	410.0	90.1	6.47
210.0	40.1	5.82	430.0	440.1	5.77	430.0	70.1	6.46
220.0	30.1	5.86	450.0	460.1	5.74	450.0	50.1	6.44
230.0	20.1	5.89	470.0	480.1	5.73	470.0	30.1	6.52
240.0	10.1	5.93	490.0	500.1	5.70	490.0	10.1	6.54

REV. X2
ZMY-1+
100818
Page 2 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



Frequency Mixer

ZMY-1+

Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)		
	+20	+23	+26	+20	+23	+26
5.0	61.85	57.02	53.70	79.05	82.02	86.00
10.0	60.36	56.72	53.82	79.25	82.32	86.00
20.1	77.12	77.40	83.55	66.09	65.11	58.40
30.1	74.00	74.22	80.80	64.92	64.16	58.60
40.1	72.01	72.07	77.47	62.98	63.52	57.90
50.1	70.45	70.64	73.52	61.98	59.85	57.43
60.1	68.79	68.97	71.28	59.17	57.44	56.61
80.1	68.19	68.21	66.55	53.20	55.19	54.72
100.1	67.07	67.10	64.58	51.25	53.50	52.90
120.1	67.22	66.90	63.35	49.41	51.65	51.59
140.1	64.03	63.79	65.62	48.02	50.41	50.91
160.1	63.29	62.98	62.21	47.35	49.27	49.80
180.1	63.35	63.07	60.17	45.58	47.31	47.55
200.1	61.19	61.02	59.61	44.67	45.95	45.44
220.1	65.32	64.97	58.86	43.99	44.71	43.79
240.1	63.07	62.94	59.87	41.67	43.06	43.29
260.1	64.10	63.71	56.72	41.90	42.66	42.35
280.1	78.04	73.63	54.92	39.60	40.51	40.54
300.1	60.08	59.64	56.39	39.81	40.04	38.83
320.1	57.09	56.78	63.96	37.74	37.70	36.68
350.1	54.22	54.18	47.00	35.85	35.62	35.21
380.1	58.13	58.41	51.64	35.15	34.52	34.13
410.1	53.94	54.28	61.42	34.03	33.27	31.50
440.1	50.54	52.13	44.08	32.65	31.90	30.41
470.1	52.89	54.13	43.32	30.71	29.70	29.32
500.1	45.57	47.79	47.95	27.77	26.97	26.65
530.1	44.93	45.56	41.03	25.36	24.34	23.90
560.1	47.31	42.72	40.94	25.18	24.01	24.09
590.1	44.69	42.71	43.58	25.51	23.80	23.26
620.1	41.70	37.43	37.50	24.24	21.79	20.91
650.1	44.77	37.30	37.51	23.07	20.26	19.24
690.1	43.92	37.72	38.76	24.11	21.93	20.87
730.1	39.42	33.93	31.55	20.43	18.30	17.81
810.1	35.55	31.20	29.24	17.16	15.58	16.02
850.1	32.71	28.09	26.93	13.34	12.22	13.04
890.1	32.87	28.57	28.24	13.87	12.89	14.14
930.1	31.94	27.43	25.86	13.58	12.66	13.92
970.1	29.40	25.38	24.12	11.23	10.24	11.65
1010.1	30.04	26.98	24.97	13.33	12.27	13.68
1050.1	27.79	25.26	23.14	11.85	10.84	12.30

RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB)		
		@LO (dBm)		
		+20	+23	+26
10.1	40.1	34.65	32.88	30.61
20.1	50.1	33.51	31.73	29.00
30.1	60.1	33.26	31.59	29.32
40.1	70.1	32.87	31.67	31.04
50.1	80.1	32.32	31.70	31.73
60.1	90.1	31.77	31.29	31.62
80.1	110.1	30.87	30.44	30.58
100.1	130.1	29.93	29.53	29.16
120.1	150.1	28.92	28.47	27.01
140.1	170.1	28.61	28.61	28.05
160.1	190.1	28.51	28.61	28.82
180.1	210.1	28.35	28.53	28.82
200.1	230.1	28.20	28.32	28.36
220.1	250.1	28.11	28.14	27.64
240.1	270.1	28.62	28.72	28.57
260.1	290.1	28.50	28.78	29.14
280.1	310.1	29.11	29.45	29.88
300.1	330.1	29.37	30.08	30.72
320.1	350.1	29.72	30.60	31.20
350.1	380.1	28.71	29.85	30.78
380.1	410.1	27.71	28.78	29.07
410.1	440.1	25.98	26.86	28.32
440.1	470.1	24.83	25.12	25.88
470.1	500.1	24.61	24.79	24.76
500.1	530.1	23.76	24.05	24.45
530.1	560.1	23.44	23.86	24.85
560.1	590.1	24.00	24.00	23.97
590.1	620.1	24.46	24.33	24.08
620.1	650.1	24.65	25.22	25.24
650.1	680.1	24.15	23.87	23.28
690.1	720.1	23.45	23.39	23.05
730.1	760.1	23.08	22.33	21.62
770.1	800.1	22.75	22.16	21.51
810.1	840.1	22.21	21.94	21.70
850.1	880.1	21.40	21.00	20.55
890.1	920.1	20.84	20.49	20.17
930.1	960.1	19.94	19.47	19.01
970.1	1000.1	19.53	19.31	19.08
1010.1	1040.1	17.84	17.61	17.13
1050.1	1080.1	17.43	17.54	17.49

REV. X2

ZMY-1+

100818

Page 3 of 5

Frequency Mixer

ZMY-1+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	RF VSWR (:1)			LO (MHz)	LO VSWR (:1)				IF (OUT) (MHz)	IF VSWR @LO=500.1MHz (:1)		
		@LO (dBm)				@LO (dBm)					@LO (dBm)		
		+20	+23	+26		+20	+23	+26	+20		+23	+26	
5.0	35.0	1.26	1.29	1.34	5.0	1.88	2.50	3.19	0.5	1.32	1.31	1.33	
10.0	40.0	1.12	1.14	1.19	10.0	1.80	2.37	2.55	0.8	1.22	1.13	1.11	
20.1	50.1	1.16	1.07	1.02	20.1	1.49	2.09	2.67	1.0	1.29	1.16	1.09	
30.1	60.1	1.16	1.07	1.01	30.1	1.43	1.91	2.21	2.0	1.39	1.25	1.16	
40.1	70.1	1.16	1.05	1.01	40.1	1.41	1.84	2.08	3.0	1.38	1.24	1.15	
50.1	80.1	1.11	1.04	1.02	50.1	1.41	1.87	2.16	4.0	1.36	1.22	1.13	
60.1	90.1	1.09	1.04	1.04	60.1	1.48	2.01	2.40	5.0	1.34	1.20	1.12	
80.1	110.1	1.10	1.05	1.05	80.1	1.59	2.38	3.34	6.0	1.32	1.19	1.11	
100.1	130.1	1.09	1.06	1.06	100.1	1.54	2.27	3.13	8.0	1.31	1.17	1.09	
120.1	150.1	1.10	1.07	1.07	120.1	1.43	1.90	2.16	10.0	1.30	1.17	1.09	
140.1	170.1	1.10	1.08	1.08	140.1	1.42	1.85	2.15	15.0	1.30	1.17	1.09	
160.1	190.1	1.09	1.08	1.09	160.1	1.54	2.15	2.77	20.0	1.31	1.17	1.09	
180.1	210.1	1.09	1.08	1.09	180.1	1.62	2.39	3.38	25.0	1.31	1.18	1.09	
200.1	230.1	1.09	1.08	1.09	200.1	1.52	2.10	2.52	30.0	1.32	1.18	1.10	
220.1	250.1	1.09	1.08	1.09	220.1	1.46	1.89	2.13	35.0	1.33	1.19	1.10	
240.1	270.1	1.09	1.08	1.10	240.1	1.53	2.01	2.36	40.0	1.33	1.19	1.11	
260.1	290.1	1.08	1.08	1.09	260.1	1.70	2.42	3.37	45.0	1.34	1.20	1.12	
280.1	310.1	1.06	1.06	1.08	280.1	1.70	2.40	3.06	50.0	1.35	1.20	1.12	
300.1	330.1	1.05	1.07	1.09	300.1	1.60	2.08	2.32	70.0	1.37	1.23	1.15	
320.1	350.1	1.04	1.06	1.08	320.1	1.57	2.00	2.31	90.0	1.38	1.24	1.17	
350.1	380.1	1.03	1.00	1.02	350.1	1.80	2.51	3.42	110.0	1.40	1.27	1.19	
380.1	410.1	1.09	1.06	1.04	380.1	1.78	2.35	2.71	130.0	1.43	1.29	1.22	
410.1	440.1	1.18	1.15	1.12	410.1	1.70	2.13	2.46	150.0	1.45	1.31	1.24	
440.1	470.1	1.26	1.23	1.21	440.1	1.94	2.61	3.42	170.0	1.48	1.34	1.27	
470.1	500.1	1.33	1.30	1.28	470.1	1.92	2.48	2.88	190.0	1.50	1.36	1.29	
500.1	530.1	1.48	1.44	1.40	500.1	1.82	2.27	2.63	210.0	1.52	1.38	1.30	
530.1	560.1	1.51	1.47	1.44	530.1	2.02	2.63	3.34	230.0	1.55	1.40	1.32	
560.1	590.1	1.76	1.70	1.66	560.1	2.10	2.67	3.09	250.0	1.57	1.42	1.33	
590.1	620.1	1.80	1.72	1.69	590.1	2.02	2.49	2.84	270.0	1.60	1.44	1.35	
620.1	650.1	2.01	1.93	1.89	620.1	2.21	2.75	3.29	290.0	1.61	1.45	1.36	
650.1	680.1	2.24	2.15	2.10	650.1	2.36	2.94	3.37	310.0	1.62	1.46	1.36	
690.1	720.1	2.31	2.28	2.22	690.1	2.28	2.75	3.08	330.0	1.64	1.47	1.36	
730.1	760.1	2.62	2.61	2.57	730.1	2.48	3.04	3.53	350.0	1.66	1.48	1.37	
810.1	840.1	3.67	3.59	3.51	810.1	2.42	2.86	3.25	370.0	1.66	1.48	1.37	
850.1	880.1	4.07	3.95	3.89	850.1	2.82	3.47	4.01	390.0	1.66	1.48	1.36	
890.1	920.1	4.87	4.69	4.54	890.1	2.33	2.69	2.97	410.0	1.66	1.48	1.36	
930.1	960.1	5.95	5.70	5.56	930.1	2.95	3.56	4.01	430.0	1.66	1.47	1.35	
970.1	1000.1	7.60	7.34	7.14	970.1	2.47	2.81	3.01	450.0	1.67	1.48	1.35	
1010.1	1040.1	8.27	8.05	7.87	1010.1	2.92	3.33	3.55	470.0	1.67	1.48	1.35	
1050.1	1080.1	10.02	9.79	9.90	1050.1	2.89	3.31	3.67	490.0	1.65	1.46	1.33	

REV. X2

ZMY-1+

100818

Page 4 of 5

Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	12	27	14	30	17	38	25	32	25	38
1	-	27	+0	32	11	36	23	41	29	47	41	47
2	98	70	49	66	49	66	51	66	62	74	62	74
3	109	76	60	79	60	82	60	78	68	86	69	85
4	>123	95	87	98	85	95	85	94	86	100	94	103
5	>122	112	99	103	95	102	94	103	94	103	103	111
6	>124	>123	115	>118	105	116	105	114	104	113	108	120
7	>123	>124	>122	>124	>121	118	>122	>121	>122	>120	>123	>123
8	>123	>122	>122	>125	>122	>123	117	>122	119	>122	118	>124
9	>123	>121	>123	>123	>124	>122	>123	>123	>120	>123	>121	>122
10	>123	>122	>121	>123	>124	>123	>123	>123	>122	>122	>122	>121
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 250.1 MHz; .02.00 dBm.
LO IN: 280.01 MHz; +23.00 dBm
IF OUT: 29.91 MHz; -5.65 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	21	36	26	41	28	50	37	43	37	50
1	-	27	+0	32	11	37	24	43	30	48	40	51
2	85	68	43	66	43	64	44	59	56	65	53	60
3	98	59	48	66	46	67	45	60	54	63	62	72
4	118	81	63	85	62	77	61	73	63	80	74	82
5	>122	75	66	72	61	73	59	72	57	70	62	73
6	>123	88	84	82	86	80	77	82	74	90	76	91
7	>124	91	83	88	74	99	74	100	77	103	86	98
8	123	115	93	106	91	94	84	89	87	89	90	91
9	>124	108	101	106	95	114	84	97	81	95	81	98
10	123	108	109	111	109	110	104	105	95	112	94	106
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 250.1 MHz; 10.00 dBm.
LO IN: 280.01 MHz; +23.00 dBm
IF OUT: 29.91 MHz; 4.37 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2
ZMY-1+
100818

Page 5 of 5




Frequency Mixer


ZMY-1+

Typical Performance Curves


Conversion Loss @ IF=30MHz




Conversion Loss vs. IF @ RF=250.1MHz




Conversion Loss vs. IF @ RF=10.1MHz




Conversion Loss vs. IF @ RF=500.1MHz



IP3 Input



Compression @ RF IN=+15dBm



REV. X2

ZMY-1+

100818

Page 1 of 3

Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see




Frequency Mixer


ZMY-1+

Typical Performance Curves


LO-RF Isolation




LO-IF Isolation




RF-IF Isolation




RF VSWR



LO VSWR



IF VSWR



REV. X2

ZMY-1+

100818

Page 2 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	12	27	14	30	17	38	25	32	25	38
1	-	27	+0	32	11	36	23	41	29	47	41	47
2	98	70	49	66	49	66	51	66	62	74	62	74
3	109	76	60	79	60	82	60	78	68	86	69	85
4	>123	95	87	98	85	95	85	94	86	100	94	103
5	>122	112	99	103	95	102	94	103	94	103	103	111
6	>124	>123	115	>118	105	116	105	114	104	113	108	120
7	>123	>124	>122	>124	>121	118	>122	>121	>122	>120	>123	>123
8	>123	>122	>122	>125	>122	>123	117	>122	119	>122	118	>124
9	>123	>121	>123	>123	>124	>122	>123	>123	>120	>123	>121	>122
10	>123	>122	>121	>123	>124	>123	>123	>123	>122	>122	>122	>121
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions:

RF IN: 250.1 MHz; .02.00 dBm.

LO IN: 280.01 MHz; +23.00 dBm

IF OUT: 29.91 MHz; -5.65 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	21	36	26	41	28	50	37	43	37	50
1	-	27	+0	32	11	37	24	43	30	48	40	51
2	85	68	43	66	43	64	44	59	56	65	53	60
3	98	59	48	66	46	67	45	60	54	63	62	72
4	118	81	63	85	62	77	61	73	63	80	74	82
5	>122	75	66	72	61	73	59	72	57	70	62	73
6	>123	88	84	82	86	80	77	82	74	90	76	91
7	>124	91	83	88	74	99	74	100	77	103	86	98
8	123	115	93	106	91	94	84	89	87	89	90	91
9	>124	108	101	106	95	114	84	97	81	95	81	98
10	123	108	109	111	109	110	104	105	95	112	94	106
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions:

RF IN: 250.1 MHz; 10.00 dBm.

LO IN: 280.01 MHz; +23.00 dBm

IF OUT: 29.91 MHz; 4.37 dBm

Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.

2. + entry denotes harmonics are in (dBc) above IF OUTPUT.

3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2

ZMY-1+

100818

Page 3 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see





Outline Dimensions

M21

M22

M23



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
M21	1.50 (38.10)	1.13 (28.70)	1.00 (25.40)	.50 (12.70)	.155 (3.94)	2.345 (59.56)	.138 (3.51)	.987 (25.07)	2.50 (63.50)	.10 (2.54)	.31 (7.87)	.75 (19.05)	1.19 (30.23)
M22	2.25 (57.15)	1.38 (35.05)	1.24 (31.50)		.150 (3.81)	3.100 (78.74)		1.238 (31.45)	3.25 (82.55)		.40 (10.16)	1.15 (29.21)	1.86 (47.24)
M23	2.25 (57.15)	1.38 (35.05)	1.24 (31.50)		.150 (3.81)	3.100 (78.74)		1.238 (31.45)	3.25 (82.55)		.63 (16.00)	1.06 (26.92)	1.63 (41.40)

CASE#	P	Q	R	S	WT. GRAMS
M21	.66 (16.76)	--	--	.150 (3.81)	40.0
M22	.64 (16.26)	--	--		74.0
M23	.69 (17.53)	--	--		70.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
 - For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
 - For Non-RoHS Case Styles: Yellow hexavalent chrome based conversion coating.

Due to transition from non-RoHS to RoHS, models will be supplied with either case style finish until the non-RoHS case inventory is depleted.
- Mounting bracket available on request. For bracket mounted on connector end add suffix B to part number and add \$5.00 to unit cost. For bracket mounted on the rear, add suffix BR to part number and add \$1.50 to unit cost.



INTERNET <http://www.minicircuits.com>
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
 Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
 Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I