

Power Splitter/Combiner

2 Way-0° 50Ω 600 to 2200 MHz


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	10W max.
Internal Dissipation	0.25W max.
DC Current	800 mA (400mA for each port)
Permanent damage may occur if any of these limits are exceeded.	

Coaxial Connections

SUM PORT	S
PORT 1	1
PORT 2	2

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F
2.88	2.00	.53	.125	2.750	1.000
73.15	50.80	13.46	3.18	69.85	25.40
G	H	J	K	L	wt
.125	.56	.24	1.66	.65	grams
3.18	14.22	6.10	42.16	16.51	100

Features

- low insertion loss, 0.3 dB typ.
- good isolation, 22 dB typ.
- very good input VSWR, 1.2:1 typ.
- excellent output VSWR, 1.15:1 typ.

Applications

- cellular
- GPS
- PCS
- GSM
- WCDMA
- DCS
- PDC




Electrical Specifications

FREQ. RANGE (MHz)	ISOLATION (dB)		INSERTION LOSS (dB) ABOVE 3.0 dB		PHASE UNBALANCE (Degrees)	AMPLITUDE UNBALANCE (dB)	VSWR (:1)			
f _L -f _U	Typ.	Min.	Typ.	Max.	Max.	Max.	S		OUT	
							Typ.	Max.	Typ.	Max.
600-725	18	14	0.2	0.5	2	0.2	1.25	1.6	1.15	1.3
725-2050	22	16	0.3	0.7	3	0.3	1.2	1.6	1.15	1.3
2050-2200	20	15	0.3	0.8	3	0.4	1.2	1.6	1.1	1.3


Typical Performance Data

Frequency (MHz)	Total Loss ¹ (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
600.00	3.26	3.30	0.04	16.55	0.01	1.35	1.19	1.19
650.00	3.24	3.29	0.05	17.91	0.04	1.31	1.17	1.17
700.00	3.24	3.29	0.04	19.26	0.03	1.28	1.15	1.16
725.00	3.24	3.29	0.05	19.92	0.02	1.27	1.15	1.15
750.00	3.24	3.29	0.05	20.57	0.01	1.26	1.14	1.14
775.00	3.25	3.29	0.04	21.21	0.05	1.25	1.13	1.14
800.00	3.24	3.29	0.05	21.86	0.03	1.24	1.12	1.13
1000.00	3.24	3.30	0.06	27.59	0.02	1.16	1.06	1.08
1200.00	3.26	3.31	0.05	41.07	0.05	1.11	1.10	1.09
1400.00	3.30	3.35	0.05	28.51	0.07	1.19	1.16	1.12
1600.00	3.36	3.42	0.06	23.11	0.08	1.31	1.17	1.14
1800.00	3.39	3.46	0.07	21.72	0.17	1.34	1.12	1.12
2000.00	3.38	3.45	0.08	22.20	0.21	1.23	1.09	1.10
2050.00	3.37	3.45	0.08	21.66	0.21	1.20	1.09	1.10
2200.00	3.40	3.48	0.09	17.69	0.22	1.24	1.13	1.14

1. Total Loss = Insertion Loss + 3dB splitter loss.



electrical schematic



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



ZN2PD1-222-S+



Generic photo used for illustration purposes only

CASE STYLE: AB762

Connectors	Model
SMA	ZN2PD1-222-S+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

2 Way-90° Power Splitter/Combiner

ZN2PD1-222+

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	ISOLATION (dB)	PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
250.0	3.46	3.49	0.04	7.91	0.16	250.0	1.77	1.46	1.47
300.0	3.41	3.46	0.05	9.05	0.10	300.0	1.70	1.39	1.40
350.0	3.38	3.42	0.04	10.22	0.08	350.0	1.63	1.34	1.34
400.0	3.34	3.38	0.05	11.40	0.07	400.0	1.56	1.29	1.29
450.0	3.31	3.35	0.04	12.63	0.06	450.0	1.50	1.26	1.26
500.0	3.28	3.33	0.04	13.90	0.04	500.0	1.44	1.23	1.23
550.0	3.26	3.31	0.04	15.20	0.03	550.0	1.39	1.21	1.21
600.0	3.26	3.30	0.04	16.55	0.01	600.0	1.35	1.19	1.19
625.0	3.26	3.29	0.04	17.24	0.08	625.0	1.33	1.18	1.18
650.0	3.24	3.29	0.05	17.91	0.04	650.0	1.31	1.17	1.17
675.0	3.24	3.29	0.05	18.59	0.03	675.0	1.30	1.16	1.17
700.0	3.24	3.29	0.04	19.26	0.03	700.0	1.28	1.15	1.16
725.0	3.24	3.29	0.05	19.92	0.02	725.0	1.27	1.15	1.15
750.0	3.24	3.29	0.05	20.57	0.01	750.0	1.26	1.14	1.14
775.0	3.25	3.29	0.04	21.21	0.05	775.0	1.25	1.13	1.14
800.0	3.24	3.29	0.05	21.86	0.03	800.0	1.24	1.12	1.13
850.0	3.24	3.29	0.05	23.14	0.01	850.0	1.22	1.10	1.12
900.0	3.25	3.29	0.05	24.43	0.01	900.0	1.20	1.08	1.10
1000.0	3.24	3.30	0.06	27.59	0.02	1000.0	1.16	1.06	1.08
1100.0	3.24	3.30	0.06	32.36	0.01	1100.0	1.13	1.06	1.08
1200.0	3.26	3.31	0.05	41.07	0.05	1200.0	1.11	1.10	1.09
1300.0	3.27	3.33	0.05	34.52	0.07	1300.0	1.14	1.14	1.11
1400.0	3.30	3.35	0.05	28.51	0.07	1400.0	1.19	1.16	1.12
1500.0	3.34	3.39	0.05	25.14	0.08	1500.0	1.26	1.18	1.14
1600.0	3.36	3.42	0.06	23.11	0.08	1600.0	1.31	1.17	1.14
1700.0	3.38	3.45	0.07	22.00	0.10	1700.0	1.34	1.15	1.14
1800.0	3.39	3.46	0.07	21.72	0.17	1800.0	1.34	1.12	1.12
1900.0	3.39	3.46	0.07	22.07	0.19	1900.0	1.30	1.10	1.11
2000.0	3.38	3.45	0.08	22.20	0.21	2000.0	1.23	1.09	1.10
2050.0	3.37	3.45	0.08	21.66	0.21	2050.0	1.20	1.09	1.10
2100.0	3.37	3.45	0.08	20.61	0.20	2100.0	1.19	1.10	1.11
2150.0	3.38	3.47	0.09	19.20	0.22	2150.0	1.20	1.11	1.12
2200.0	3.40	3.48	0.09	17.69	0.22	2200.0	1.24	1.13	1.14
2300.0	3.45	3.55	0.10	14.89	0.23	2300.0	1.35	1.19	1.19
2400.0	3.54	3.64	0.10	12.70	0.31	2400.0	1.50	1.31	1.31
2500.0	3.65	3.75	0.10	11.14	0.34	2500.0	1.65	1.51	1.51
2600.0	3.75	3.87	0.11	9.99	0.47	2600.0	1.80	1.83	1.82
2625.0	3.79	3.89	0.10	9.73	0.50	2625.0	1.83	1.93	1.92
2650.0	3.81	3.92	0.10	9.47	0.51	2650.0	1.85	2.03	2.02
2675.0	3.83	3.94	0.11	9.21	0.51	2675.0	1.88	2.15	2.14
2700.0	3.85	3.96	0.11	8.93	0.57	2700.0	1.90	2.28	2.27






¹ Total Loss = Insertion Loss+ 3dB Splitter Loss

REV. X2
ZN2PD1-222+
100627
Page 1 of 1

2 Way-90° Power Splitter/Combiner

ZN2PD1-222+

Typical Performance Curves



REV. X2
ZN2PD1-222+
100627
Page 1 of 1




The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see

Mini-Circuits®

RF/MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



Outline Dimensions



CASE #	A	B	C	D	E	F	G	H	J	K	L	WT. GRAM
AB762	2.88 (73.15)	2.00 (50.80)	.53 (13.46)	.125 (3.18)	2.750 (69.85)	1.000 (25.40)	.125 (3.18)	.56 (14.22)	.24 (6.10)	1.66 (42.16)	.65 (16.51)	100

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I