

3 Way-0° 50Ω 1800 to 6200 MHz


Maximum Ratings

Operating Temperature	-55 °C to +100 °C
Storage Temperature	-55 °C to +100 °C
Power Input (as a splitter)	10 W max.
Internal Dissipation	0.6 W max.
DC Current	750 mA (250 mA for each port)


Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3

Outline Drawing**Outline Dimensions (inch/mm)**


A	B	C	D	E	F	G
2.25	2.30	.63	.125	2.125	—	.125
57.15	58.42	16.00	3.18	53.98	—	3.18
H	J	K	L	M	wt	
1.13	.31	.500	.125	2.175	grams	
28.70	7.87	12.70	3.18	55.25	94	

Electrical Schematic**Features**

- wideband, 1800 to 6200 MHz
- low insertion loss, 0.9 dB typ.
- low phase unbalance, 3.0 deg. typ.
- good isolation, 22 dB typ.
- DC Pass from sum port to all output ports

Applications

- PCS/UMTS
- LTE
- WIMAX
- WiFi
- bluetooth



CASE STYLE: UU181

Connectors Model

SMA ZN3PD-622W-S+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at +25 °C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		1800		6200	MHz
Insertion Loss Above 4.8 dB	1800-6200	—	1.0	1.5	
	2300-6000	—	0.8	1.2	dB
Isolation	1800-6200	15	20	—	
	2300-6000	16	22	—	dB
Phase Unbalance	1800-6000	—	3	7	Degree
Amplitude Unbalance	1800-6200	—	0.6	0.9	dB
VSWR (Port S)	1800-6200	—	1.4	—	:1
VSWR (Port 1-3)	1800-6200	—	1.3	—	:1

Notes






A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

ZN3PD-622W-S+

Typical Performance Graphs



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



3 Way-0° Power Splitter/Combiner

ZN3PD-622W-S+

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹			AMP. UNBAL. (dB)	ISOLATION			PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR			
	S-1	(dB) S-2	S-3		(dB) 1-2	1-3	2-3			(:1) S	1	2	3
1800	5.33	4.81	5.30	0.52	33.54	17.78	33.76	1.83	1800	1.25	1.28	1.14	1.26
1900	5.40	4.87	5.37	0.53	28.76	18.45	28.69	1.75	1900	1.33	1.29	1.12	1.28
2000	5.49	4.95	5.46	0.53	26.23	19.07	26.02	1.69	2000	1.40	1.30	1.11	1.28
2050	5.53	4.99	5.50	0.54	25.37	19.37	25.11	1.66	2050	1.43	1.29	1.11	1.28
2100	5.56	5.02	5.54	0.54	24.72	19.66	24.40	1.62	2100	1.46	1.29	1.11	1.28
2150	5.58	5.03	5.56	0.55	24.24	19.98	23.88	1.56	2150	1.48	1.28	1.11	1.27
2200	5.58	5.03	5.56	0.55	23.90	20.30	23.49	1.49	2200	1.50	1.27	1.11	1.26
2250	5.57	5.02	5.55	0.55	23.73	20.65	23.28	1.41	2250	1.51	1.26	1.10	1.24
2300	5.55	5.01	5.53	0.54	23.68	20.98	23.17	1.35	2300	1.51	1.24	1.10	1.23
2350	5.53	4.99	5.50	0.54	23.77	21.32	23.20	1.27	2350	1.49	1.21	1.09	1.20
2400	5.51	4.97	5.48	0.53	23.91	21.66	23.29	1.22	2400	1.47	1.19	1.08	1.18
2450	5.48	4.95	5.45	0.53	24.18	22.01	23.49	1.18	2450	1.44	1.16	1.07	1.15
2500	5.45	4.93	5.42	0.52	24.56	22.37	23.81	1.15	2500	1.40	1.14	1.07	1.13
2550	5.42	4.91	5.39	0.51	25.00	22.70	24.17	1.19	2550	1.36	1.11	1.06	1.10
2600	5.40	4.89	5.37	0.51	25.60	23.08	24.69	1.21	2600	1.31	1.08	1.06	1.07
2700	5.36	4.87	5.32	0.49	27.04	23.80	25.93	1.26	2700	1.22	1.03	1.09	1.02
2800	5.34	4.86	5.29	0.48	28.90	24.59	27.56	1.33	2800	1.13	1.07	1.13	1.06
2900	5.33	4.86	5.28	0.47	30.74	25.40	29.27	1.37	2900	1.07	1.13	1.17	1.12
3000	5.34	4.88	5.29	0.47	31.30	26.23	30.21	1.46	3000	1.11	1.19	1.22	1.18
3100	5.37	4.91	5.31	0.46	30.02	27.03	29.54	1.51	3100	1.19	1.26	1.26	1.24
3200	5.40	4.95	5.34	0.44	27.95	27.75	27.79	1.56	3200	1.26	1.31	1.29	1.29
3300	5.42	4.99	5.38	0.43	26.12	28.29	26.03	1.58	3300	1.32	1.35	1.32	1.33
3400	5.45	5.02	5.40	0.42	24.64	28.58	24.53	1.60	3400	1.36	1.37	1.32	1.35
3500	5.46	5.05	5.42	0.42	23.57	28.62	23.39	1.58	3500	1.38	1.37	1.32	1.36
3600	5.47	5.06	5.43	0.42	22.79	28.43	22.54	1.60	3600	1.37	1.36	1.30	1.35
3700	5.47	5.06	5.45	0.41	22.31	28.05	22.01	1.62	3700	1.34	1.33	1.27	1.33
3800	5.47	5.06	5.45	0.41	22.07	27.57	21.70	1.70	3800	1.30	1.29	1.25	1.29
3900	5.47	5.06	5.45	0.41	22.10	26.97	21.64	1.87	3900	1.26	1.24	1.22	1.24
4000	5.47	5.06	5.43	0.41	22.50	26.29	21.91	2.00	4000	1.22	1.19	1.22	1.19
4100	5.47	5.06	5.41	0.42	23.27	25.74	22.55	2.02	4100	1.20	1.13	1.23	1.14
4200	5.49	5.07	5.43	0.42	24.48	25.31	23.60	2.05	4200	1.21	1.09	1.25	1.11
4300	5.53	5.11	5.47	0.42	26.14	25.02	25.07	2.10	4300	1.23	1.08	1.29	1.09
4400	5.59	5.16	5.52	0.42	28.38	24.78	27.10	2.20	4400	1.28	1.10	1.31	1.09
4500	5.63	5.21	5.56	0.42	30.99	24.51	29.78	2.30	4500	1.33	1.12	1.34	1.12
4600	5.65	5.24	5.57	0.41	32.38	24.37	32.62	2.39	4600	1.38	1.14	1.35	1.14
4700	5.63	5.24	5.56	0.39	30.23	24.35	31.98	2.45	4700	1.40	1.16	1.35	1.15
4800	5.61	5.24	5.53	0.37	27.13	24.44	28.62	2.50	4800	1.39	1.17	1.31	1.16
4900	5.59	5.22	5.51	0.37	24.60	24.63	25.62	2.53	4900	1.37	1.17	1.26	1.16
5000	5.58	5.22	5.50	0.36	22.65	24.85	23.33	2.60	5000	1.35	1.16	1.19	1.15
5100	5.58	5.23	5.50	0.35	21.22	25.15	21.65	2.62	5100	1.35	1.14	1.13	1.13
5200	5.58	5.24	5.50	0.34	20.20	25.47	20.42	2.70	5200	1.35	1.11	1.07	1.11
5300	5.59	5.27	5.50	0.32	19.50	25.67	19.51	2.74	5300	1.36	1.10	1.02	1.09
5400	5.61	5.29	5.51	0.32	19.09	25.72	18.91	2.75	5400	1.37	1.10	1.05	1.09
5500	5.63	5.33	5.53	0.30	18.93	25.43	18.54	2.79	5500	1.39	1.11	1.11	1.10
5550	5.64	5.34	5.54	0.30	18.96	25.22	18.47	2.83	5550	1.39	1.12	1.14	1.11
5600	5.64	5.35	5.54	0.29	19.07	24.89	18.48	2.85	5600	1.39	1.14	1.16	1.12
5650	5.66	5.36	5.56	0.30	19.21	24.53	18.52	2.90	5650	1.39	1.15	1.19	1.14
5700	5.67	5.37	5.57	0.30	19.40	24.07	18.60	2.91	5700	1.38	1.17	1.20	1.16
5750	5.68	5.38	5.58	0.30	19.62	23.61	18.70	2.97	5750	1.37	1.19	1.21	1.17
5800	5.68	5.38	5.59	0.30	19.95	23.06	18.91	3.01	5800	1.35	1.20	1.22	1.19
5850	5.69	5.38	5.60	0.31	20.26	22.48	19.11	3.04	5850	1.34	1.24	1.21	1.21
5900	5.69	5.39	5.60	0.31	20.63	21.88	19.34	3.09	5900	1.31	1.24	1.20	1.23
5950	5.70	5.38	5.61	0.32	20.97	21.25	19.58	3.18	5950	1.29	1.27	1.19	1.26
6000	5.71	5.38	5.62	0.33	21.34	20.61	19.85	3.21	6000	1.27	1.30	1.18	1.29
6050	5.73	5.39	5.64	0.34	21.59	19.96	20.03	3.28	6050	1.26	1.31	1.16	1.32
6100	5.75	5.39	5.66	0.36	21.76	19.33	20.18	3.35	6100	1.26	1.34	1.14	1.35
6150	5.77	5.40	5.69	0.37	21.73	18.68	20.22	3.46	6150	1.27	1.37	1.12	1.38
6200	5.81	5.42	5.73	0.39	21.53	18.07	20.13	3.51	6200	1.30	1.40	1.09	1.42

¹Total Loss = Insertion Loss + 4.8dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site www.minicircuits.com








The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. OR
ZN3PD-622W-S+
1/18/2019
Page 1 of 1

Typical Performance Curves





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I