

Wideband, DC Pass Directional Coupler

ZUDC6-0283-S+

50Ω 6 dB Up to 50 W 2 to 8 GHz

The Big Deal

- Wideband, 2 to 8 GHz
- Power Handling up to 50 W



CASE STYLE: HT2446-1

Product Overview

The Mini-Circuits ZUDC6-0283-S+ wideband directional coupler offers exceptional performance operating over 2 to 8 GHz. This coupler has excellent coupling flatness, good directivity, and power handling. It is ideal for lab testing applications as well as for power monitoring over wide bands, among other applications.

Key Features

| Feature | Advantages |
|--|---|
| Wide bandwidth | With a bandwidth spanning 2 to 8 GHz, ZUDC6-0283-S+ coupler is ideal for most lab testing applications, avoiding the need to switch components for different frequency bands. |
| Excellent Directivity • 27 dB typ. up to 8 GHz | High directivity allows sampling of input powers with minimal detrimental effects due to output mismatches. |
| Excellent Return Loss (In & Out) • 22 dB typ. up to 8 GHz | Good return loss over 2 to 8 GHz minimizes undesired reflections and resulting amplitude ripple. |

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits website at www.minicircuits.com/MCLStore/terms.jsp



Wideband, DC Pass Directional Coupler

50Ω 6 dB Up to 50 W 2 to 8 GHz

ZUDC6-0283-S+

Maximum Ratings


| | |
|-----------------------|-------------------|
| Operating Temperature | -55 °C to +85 °C |
| Storage Temperature | -55 °C to +100 °C |
| Supplied Termination* | 1 W |
| DC Current | 1 A |

Permanent damage may occur if any of these limits are exceeded
* up to +25 °C, derates linearly to 325 mW at +100 °C.

Coaxial Connections

| | |
|----------------------------|-----|
| INPUT | IN |
| OUTPUT | OUT |
| COUPLED | CPL |
| TERMINATION (50Ω) INCLUDED | — |


Outline Drawing



Weight: 28 grams;

Dimensions are in inches (mm). Tolerances: 2 PL±.03; 3 PL ± .015

Electrical Schematic



Features

- Wide frequency range, 2 to 8 GHz
- Good coupling flatness, ±0.6 dB typ.
- Excellent directivity, 27 dB typ. up to 8 GHz
- Excellent return loss, 22 dB typ. up to 8 GHz
- DC current pass through input to output

Applications

- mobile
- fixed satellite
- lab use
- WiFi
- radar



Generic photo used for illustration purposes only
CASE STYLE: HT2446-1

| | |
|------------|---------------|
| Connectors | Model |
| SMA Female | ZUDC6-0283-S+ |

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at +25 °C

| Parameter | Frequency (GHz) | Min. | Typ. | Max. | Units |
|--------------------------------------|-----------------|------|---------|-------|-------|
| Operating Frequency | | 2 | | 8 | GHz |
| Coupling | 2-8 | - | 6.5±1.0 | - | dB |
| Coupling Flatness (±) | 2-8 | - | ±0.6 | ±1.25 | dB |
| Mainline Loss ¹ | 2-8 | - | 1.3 | 2.2 | dB |
| Directivity | 2-8 | 18 | 29 | - | dB |
| Return Loss (In & Out) | 2-8 | 19 | 30 | - | dB |
| Return Loss (Coupling) | 2-8 | 19 | 30 | - | dB |
| Input Power (In to Out) ² | 2-8 | - | - | 50 | W |
| Input Power (Out to In) | 2-8 | - | - | 3 | W |



1. Mainline loss includes coupling loss

2. Up to +25 °C, derates linearly to 5 W at +100 °C.

Typical Performance Data

| Frequency (MHz) | Mainline Loss ¹ (dB) | | Coupling (dB) In-Cpl | Directivity (dB) | Return Loss (dB) | | |
|-----------------|---------------------------------|--|----------------------|------------------|------------------|-------|-------|
| | In-Out | | | | In | Out | Cpl |
| 2000 | 1.30 | | 6.45 | 27.22 | 32.11 | 29.49 | 28.01 |
| 2500 | 1.14 | | 7.19 | 28.98 | 23.97 | 21.91 | 23.50 |
| 3000 | 1.23 | | 6.95 | 29.49 | 22.65 | 22.11 | 24.82 |
| 3500 | 1.38 | | 6.42 | 27.78 | 26.55 | 26.44 | 32.59 |
| 4000 | 1.33 | | 6.60 | 28.30 | 38.56 | 36.54 | 32.63 |
| 4500 | 1.17 | | 7.33 | 30.36 | 29.51 | 31.26 | 29.17 |
| 5000 | 1.16 | | 7.44 | 30.94 | 28.45 | 30.13 | 34.15 |
| 5500 | 1.33 | | 6.80 | 32.07 | 33.20 | 34.16 | 32.64 |
| 6000 | 1.43 | | 6.53 | 32.66 | 36.27 | 33.67 | 34.77 |
| 6500 | 1.32 | | 6.99 | 28.08 | 32.42 | 32.79 | 31.90 |
| 7000 | 1.19 | | 7.60 | 28.62 | 29.73 | 29.94 | 26.88 |
| 8000 | 1.45 | | 6.70 | 27.83 | 36.44 | 33.04 | 34.37 |

1. Mainline loss includes coupling loss



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A
ECO-016429
ZUDC6-0283-S+
MCL NY
260417
Page 2 of 2

Typical Performance Data





| FREQUENCY (MHz) | INSERTION LOSS ⁽¹⁾ (dB) | COUPLING (dB) | DIRECTIVITY (dB) | RETURN LOSS | | |
|--------------------|---------------------------------------|------------------|---------------------|-------------|-------------|-------|
| | | | | IN | OUT (dB) | CPL |
| 2000 | 1.30 | 6.45 | 27.22 | 32.11 | 29.49 | 28.01 |
| 2100 | 1.25 | 6.64 | 27.64 | 30.00 | 28.23 | 26.45 |
| 2200 | 1.21 | 6.82 | 27.90 | 27.80 | 25.96 | 25.30 |
| 2300 | 1.17 | 6.98 | 28.25 | 26.18 | 24.21 | 24.44 |
| 2400 | 1.15 | 7.11 | 28.54 | 24.86 | 22.90 | 23.83 |
| 2500 | 1.14 | 7.19 | 28.98 | 23.97 | 21.91 | 23.50 |
| 2600 | 1.14 | 7.23 | 29.28 | 23.22 | 21.39 | 23.34 |
| 2700 | 1.15 | 7.21 | 29.70 | 22.77 | 21.18 | 23.41 |
| 2800 | 1.17 | 7.15 | 30.17 | 22.46 | 21.25 | 23.64 |
| 2900 | 1.20 | 7.06 | 30.15 | 22.46 | 21.55 | 24.10 |
| 3000 | 1.23 | 6.95 | 29.49 | 22.65 | 22.11 | 24.82 |
| 3100 | 1.27 | 6.82 | 28.93 | 23.01 | 22.85 | 25.77 |
| 3200 | 1.30 | 6.69 | 28.38 | 23.59 | 23.63 | 27.14 |
| 3300 | 1.34 | 6.58 | 28.07 | 24.31 | 24.52 | 28.91 |
| 3400 | 1.36 | 6.48 | 27.94 | 25.29 | 25.48 | 30.84 |
| 3500 | 1.38 | 6.42 | 27.78 | 26.55 | 26.44 | 32.59 |
| 3600 | 1.39 | 6.38 | 27.73 | 28.18 | 27.65 | 33.93 |
| 3700 | 1.39 | 6.39 | 27.79 | 30.17 | 29.04 | 34.48 |
| 3800 | 1.38 | 6.42 | 27.91 | 32.94 | 30.95 | 35.26 |
| 4000 | 1.33 | 6.60 | 28.30 | 38.56 | 36.54 | 32.63 |
| 4200 | 1.27 | 6.88 | 29.04 | 37.32 | 37.21 | 30.25 |
| 4400 | 1.20 | 7.19 | 29.94 | 30.84 | 33.13 | 29.23 |
| 4600 | 1.15 | 7.44 | 30.66 | 28.62 | 29.88 | 29.56 |
| 4800 | 1.13 | 7.53 | 30.86 | 27.96 | 28.99 | 31.47 |
| 5000 | 1.16 | 7.44 | 30.94 | 28.45 | 30.13 | 34.15 |
| 5200 | 1.22 | 7.21 | 31.08 | 29.89 | 32.32 | 34.56 |
| 5400 | 1.30 | 6.93 | 31.72 | 32.04 | 32.91 | 33.41 |
| 5600 | 1.37 | 6.69 | 32.60 | 33.88 | 34.74 | 32.33 |
| 5800 | 1.42 | 6.55 | 33.01 | 36.19 | 33.81 | 32.94 |
| 6000 | 1.43 | 6.53 | 32.66 | 36.27 | 33.67 | 34.77 |
| 6200 | 1.40 | 6.64 | 30.73 | 34.74 | 33.56 | 34.82 |
| 6400 | 1.35 | 6.86 | 28.76 | 33.05 | 34.44 | 33.13 |
| 6600 | 1.28 | 7.14 | 27.54 | 31.62 | 31.96 | 30.46 |
| 6800 | 1.23 | 7.42 | 26.99 | 30.46 | 30.63 | 28.03 |
| 7000 | 1.19 | 7.60 | 28.62 | 29.73 | 29.94 | 26.88 |
| 7200 | 1.20 | 7.61 | 26.47 | 29.43 | 30.55 | 26.79 |
| 7400 | 1.24 | 7.45 | 25.09 | 29.77 | 32.80 | 27.95 |
| 7600 | 1.31 | 7.19 | 25.40 | 31.00 | 32.49 | 30.50 |
| 7800 | 1.38 | 6.91 | 27.07 | 33.57 | 32.21 | 35.94 |
| 8000 | 1.45 | 6.70 | 27.83 | 36.44 | 33.04 | 34.37 |


⁽¹⁾Mainline loss includes coupling loss

Directional Coupler

Typical Performance Curves

ZUDC6-0283-S+





Weight: 28 grams;

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

1. Case Material: Aluminum Alloy
2. Case Finish: Blue Painting, Pantone 286

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|-----------------------|---------------------------------------|---|
| Operating Temperature | -55° to +85 °C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C Ambient Environment | Individual Model Data Sheet |
| Thermal Shock | -55° to 100°C, 100 cycles | MIL-STD-202, Method 107, Condition A-3, except +100°C |