Engineering Development Model

Frequency Mixer ZX05-ED12902/4

Level 10 (LO Power + 10 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : FL905

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		**Min.**	**Typ.**	**Max.**	**Units**
Frequency	**LO** (f_L to f_U)	750		6000	MHz
	RF (f_L to f_U)	750		6000	MHz
	IF	10		1500	MHz
Conversion Loss	**Total Range**		6.9		dB
LO-RF Isolation			28		dB
LO-IF Isolation			21		dB
Input IP3			+14		dBm
1 dB Compression			+3		dBm

MAXIMUM RATINGS	
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C

COAXIAL CONNECTIONS	
LO	2
RF	3
IF	1

Electrical Schematics



Frequency Mixer ZX05-ED12902/4

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=30MHz (dB) @LO (dBm)		
		+7	+10	+13
550.0	580.0	19.19	12.50	8.87
750.0	780.0	7.31	6.60	6.29
950.0	980.0	6.81	6.27	5.85
1150.0	1180.0	6.41	6.28	6.18
1350.0	1380.0	6.26	6.21	6.25
1550.0	1580.0	6.17	6.02	5.98
1750.0	1780.0	6.45	6.27	6.21
1950.0	1980.0	6.62	6.49	6.43
2150.0	2180.0	6.51	6.36	6.29
2350.0	2380.0	6.11	5.93	5.85
2550.0	2580.0	6.51	6.08	5.82
2750.0	2780.0	5.56	5.32	5.21
2950.0	2980.0	5.09	5.00	5.02
3150.0	3180.0	5.27	5.30	5.38
3350.0	3380.0	5.53	5.53	5.59
3550.0	3580.0	6.07	5.94	5.91
3730.0	3760.0	6.61	6.42	6.38
3910.0	3940.0	7.45	7.11	6.91
4010.0	4040.0	7.50	7.22	7.10
4090.0	4120.0	7.72	7.36	7.25
4190.0	4220.0	8.11	7.63	7.46
4270.0	4300.0	8.05	7.56	7.42
4370.0	4400.0	8.73	7.83	7.59
4520.0	4550.0	7.82	6.95	6.79
4640.0	4670.0	8.10	7.16	6.98
4780.0	4810.0	8.00	7.25	7.33
4900.0	4930.0	7.97	7.30	7.29
5040.0	5070.0	8.29	7.63	7.57
5160.0	5190.0	8.54	7.96	7.89
5300.0	5330.0	8.28	8.02	8.08
5420.0	5450.0	8.36	8.04	8.00
5560.0	5590.0	8.55	8.26	8.15
5680.0	5710.0	8.14	7.94	7.90
5820.0	5850.0	7.83	7.65	7.62
5940.0	5970.0	8.61	8.22	8.05
6080.0	6110.0	8.20	7.81	7.62
6200.0	6230.0	7.89	7.55	7.32
6340.0	6370.0	8.16	7.87	7.64
6460.0	6490.0	9.40	9.02	8.78
6600.0	6630.0	14.98	12.80	12.11

RF (IN) (MHz)	LO (MHz)	IP3 INPUT (dBm) @LO (dBm)		
		+7	+10	+13
550.0	580.0	-4.69	1.33	11.39
750.0	780.0	5.24	13.31	14.53
950.0	980.0	6.35	7.94	9.60
1150.0	1180.0	8.94	9.04	9.42
1350.0	1380.0	11.85	11.61	13.01
1550.0	1580.0	14.71	13.50	16.22
1750.0	1780.0	14.26	15.40	19.95
1950.0	1980.0	18.69	18.52	18.78
2150.0	2180.0	14.48	14.86	15.31
2350.0	2380.0	10.21	11.61	12.54
2550.0	2580.0	7.65	8.63	9.91
2750.0	2780.0	5.21	6.07	7.31
2950.0	2980.0	11.89	12.65	12.76
3150.0	3180.0	14.24	15.51	16.19
3350.0	3380.0	17.19	18.84	18.91
3550.0	3580.0	14.90	14.82	15.88
3730.0	3760.0	16.81	15.55	15.21
3910.0	3940.0	14.29	15.12	15.86
4010.0	4040.0	15.23	16.31	16.17
4090.0	4120.0	16.13	18.63	17.08
4190.0	4220.0	15.09	17.38	17.41
4270.0	4300.0	15.46	18.76	19.11
4370.0	4400.0	19.68	20.22	19.84
4520.0	4550.0	11.58	11.89	11.46
4640.0	4670.0	12.83	11.34	11.19
4780.0	4810.0	14.48	12.21	10.30
4900.0	4930.0	13.87	13.33	12.63
5040.0	5070.0	18.34	14.27	14.78
5160.0	5190.0	17.21	15.09	15.72
5300.0	5330.0	13.13	15.48	14.43
5420.0	5450.0	16.26	16.37	16.22
5560.0	5590.0	17.00	16.92	15.17
5680.0	5710.0	15.06	17.73	17.29
5820.0	5850.0	16.58	15.48	16.10
5940.0	5970.0	15.08	14.11	14.34
6080.0	6110.0	12.03	11.55	11.78
6200.0	6230.0	11.57	10.93	11.17
6340.0	6370.0	13.18	12.82	12.12
6460.0	6490.0	12.69	14.75	14.71
6600.0	6630.0	9.76	11.60	13.95

RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=+3dBm (dB) @LO (dBm)		
		+7	+10	+13
550.0	580.0	-4.17	-0.23	1.02
750.0	780.0	3.42	2.71	2.23
950.0	980.0	2.75	2.65	2.58
1150.0	1180.0	2.04	1.69	1.39
1350.0	1380.0	1.13	0.87	0.73
1550.0	1580.0	0.90	0.70	0.56
1750.0	1780.0	0.98	0.70	0.50
1950.0	1980.0	0.90	0.69	0.52
2150.0	2180.0	1.09	0.85	0.66
2350.0	2380.0	1.38	1.14	0.94
2550.0	2580.0	1.76	1.58	1.38
2750.0	2780.0	2.26	1.97	1.77
2950.0	2980.0	1.78	1.46	1.31
3150.0	3180.0	1.09	0.77	0.65
3350.0	3380.0	1.48	1.09	0.84
3550.0	3580.0	1.51	1.15	0.91
3730.0	3760.0	1.16	0.89	0.71
3910.0	3940.0	1.06	0.87	0.77
4010.0	4040.0	0.93	0.76	0.70
4090.0	4120.0	0.79	0.60	0.50
4190.0	4220.0	0.81	0.60	0.47
4270.0	4300.0	0.84	0.61	0.46
4370.0	4400.0	0.93	0.70	0.56
4520.0	4550.0	1.48	1.14	1.03
4640.0	4670.0	1.57	1.19	1.01
4780.0	4810.0	1.38	1.15	1.07
4900.0	4930.0	1.07	0.81	0.73
5040.0	5070.0	0.86	0.62	0.55
5160.0	5190.0	0.70	0.49	0.44
5300.0	5330.0	0.78	0.49	0.43
5420.0	5450.0	0.58	0.43	0.42
5560.0	5590.0	0.46	0.35	0.31
5680.0	5710.0	0.57	0.40	0.35
5820.0	5850.0	0.59	0.44	0.37
5940.0	5970.0	0.73	0.66	0.60
6080.0	6110.0	1.00	0.91	0.88
6200.0	6230.0	1.17	1.04	1.00
6340.0	6370.0	1.25	1.03	0.96
6460.0	6490.0	1.20	0.83	0.75
6600.0	6630.0	0.73	0.84	0.58

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=3010.1MHz (dB)
		@LO (dBm)
		+10
1550.1	1460.0	10.80
1510.1	1500.0	9.60
1470.1	1540.0	8.86
1430.1	1580.0	8.52
1390.1	1620.0	8.25
1350.1	1660.0	8.09
1310.1	1700.0	7.72
1270.1	1740.0	7.42
1230.1	1780.0	7.56
1190.1	1820.0	8.01
1150.1	1860.0	8.15
1110.1	1900.0	8.11
1070.1	1940.0	8.05
1030.1	1980.0	8.02
990.1	2020.0	7.96
950.1	2060.0	7.63
910.1	2100.0	7.42
870.1	2140.0	7.12
830.1	2180.0	6.75
790.1	2220.0	6.59
750.1	2260.0	6.44
710.1	2300.0	6.52
670.1	2340.0	6.53
630.1	2380.0	6.54
590.1	2420.0	6.09
550.1	2460.0	5.82
510.1	2500.0	5.55
470.1	2540.0	5.35
430.1	2580.0	5.25
390.1	2620.0	5.30
350.1	2660.0	5.22
310.1	2700.0	5.19
270.1	2740.0	5.13
230.1	2780.0	5.19
190.1	2820.0	5.28
150.1	2860.0	5.28
110.1	2900.0	5.19
70.1	2940.0	5.15
30.1	2980.0	5.07
10.1	3000.0	5.50

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=739.9MHz (dB)
		@LO (dBm)
		+10
10.1	750.0	7.15
50.1	790.0	6.61
90.1	830.0	6.52
130.1	870.0	6.48
170.1	910.0	6.49
210.1	950.0	6.61
250.1	990.0	6.57
290.1	1030.0	6.44
330.1	1070.0	6.28
370.1	1110.0	6.27
410.1	1150.0	6.31
450.1	1190.0	6.25
490.1	1230.0	6.17
530.1	1270.0	6.15
570.1	1310.0	6.19
610.1	1350.0	6.15
650.1	1390.0	6.20
690.1	1430.0	6.19
730.1	1470.0	6.31
770.1	1510.0	6.45
810.1	1550.0	6.47
850.1	1590.0	6.50
890.1	1630.0	6.74
930.1	1670.0	6.95
970.1	1710.0	7.08
1010.1	1750.0	7.09
1050.1	1790.0	6.97
1090.1	1830.0	7.24
1130.1	1870.0	7.40
1170.1	1910.0	7.56
1210.1	1950.0	7.62
1250.1	1990.0	7.82
1290.1	2030.0	7.98
1330.1	2070.0	8.09
1370.1	2110.0	8.24
1410.1	2150.0	8.47
1450.1	2190.0	8.64
1490.1	2230.0	9.04
1530.1	2270.0	9.49
1590.1	2330.0	10.59

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=6010.1MHz (dB)
		@LO (dBm)
		+10
1510.1	4500.0	12.60
1470.1	4540.0	12.09
1430.1	4580.0	11.81
1390.1	4620.0	11.43
1350.1	4660.0	11.16
1310.1	4700.0	11.12
1270.1	4740.0	10.77
1230.1	4780.0	10.57
1190.1	4820.0	10.21
1150.1	4860.0	9.78
1110.1	4900.0	9.45
1070.1	4940.0	9.00
1030.1	4980.0	8.63
990.1	5020.0	8.33
950.1	5060.0	7.96
910.1	5100.0	7.94
870.1	5140.0	7.68
830.1	5180.0	7.62
790.1	5220.0	7.52
750.1	5260.0	7.34
710.1	5300.0	7.35
670.1	5340.0	7.14
630.1	5380.0	7.04
590.1	5420.0	6.93
550.1	5460.0	6.91
510.1	5500.0	6.98
470.1	5540.0	6.86
430.1	5580.0	6.78
390.1	5620.0	6.89
350.1	5660.0	6.92
310.1	5700.0	7.04
270.1	5740.0	7.25
230.1	5780.0	7.51
190.1	5820.0	7.81
150.1	5860.0	8.00
130.1	5880.0	8.10
90.1	5920.0	8.11
70.1	5940.0	8.04
30.1	5980.0	8.00
10.1	6000.0	8.36

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB) @LO (dBm)			LO-IF ISOLATION (dB) @LO (dBm)		
	+7	+10	+13	+7	+10	+13
580.0	63.45	61.39	57.89	28.88	29.02	29.15
780.0	41.56	40.63	40.44	24.70	26.74	28.99
980.0	40.40	41.01	41.50	26.69	29.00	31.11
1180.0	41.05	40.43	39.67	30.66	32.25	32.44
1380.0	35.15	33.80	32.71	34.02	35.24	35.38
1580.0	33.73	32.61	31.73	29.06	30.36	31.29
1780.0	35.56	34.34	33.22	21.21	21.45	21.31
1980.0	34.56	33.58	32.83	13.04	13.91	14.39
2180.0	34.91	33.62	32.74	11.63	13.04	14.15
2380.0	32.27	30.75	29.52	14.31	16.03	17.69
2580.0	31.12	29.87	29.25	17.19	18.76	20.20
2780.0	29.16	27.24	25.56	19.24	19.71	19.79
2980.0	29.15	26.63	25.11	21.25	20.40	19.94
3180.0	26.71	25.38	24.20	24.41	23.57	22.91
3380.0	27.34	26.20	25.58	22.76	22.56	22.42
3580.0	26.33	25.60	25.13	22.35	22.66	23.06
3760.0	26.10	25.39	24.62	18.77	19.30	19.74
3940.0	26.79	26.15	25.21	19.36	20.00	20.67
4040.0	27.32	26.37	25.27	18.35	19.41	20.46
4120.0	27.12	26.29	25.18	16.71	17.76	18.88
4220.0	26.99	25.98	24.63	15.77	16.77	17.92
4300.0	27.83	26.32	24.62	15.51	16.49	17.61
4400.0	29.46	27.18	25.08	15.03	15.82	16.76
4550.0	28.75	26.19	23.87	15.37	15.61	15.63
4670.0	28.87	26.27	23.15	17.25	16.86	15.46
4810.0	29.10	26.50	22.98	23.17	20.55	17.38
4930.0	28.98	26.37	23.38	38.13	31.88	27.43
5070.0	28.02	25.78	23.52	30.61	31.97	32.72
5190.0	27.04	25.32	23.76	26.74	27.04	26.72
5330.0	25.81	24.93	24.14	24.70	24.32	23.79
5450.0	24.79	24.49	24.12	23.32	22.66	22.00
5590.0	24.27	24.36	24.22	21.96	21.12	20.48
5710.0	24.14	24.54	24.72	21.17	20.19	19.74
5850.0	23.40	24.23	24.50	19.71	19.17	18.62
5970.0	22.69	23.76	24.70	18.72	18.20	18.07
6110.0	21.45	22.59	23.67	18.27	18.02	18.10
6230.0	21.12	22.47	23.50	18.04	18.30	18.37
6370.0	22.28	23.88	25.14	18.39	19.09	19.52
6490.0	24.64	26.57	28.27	18.50	19.69	20.47
6630.0	29.01	29.94	31.33	17.62	18.74	19.14

RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB) @LO (dBm)		
		+7	+10	+13
550.0	580.0	28.19	24.87	20.29
750.0	780.0	15.77	14.32	13.73
950.0	980.0	13.04	12.49	12.14
1150.0	1180.0	19.12	18.82	18.59
1350.0	1380.0	25.03	25.52	25.81
1550.0	1580.0	27.10	27.10	26.93
1750.0	1780.0	26.91	26.76	26.66
1950.0	1980.0	34.07	33.90	33.78
2150.0	2180.0	38.73	38.67	38.80
2350.0	2380.0	39.43	39.65	39.88
2550.0	2580.0	35.36	35.39	35.77
2750.0	2780.0	28.79	28.56	28.48
2950.0	2980.0	26.35	26.47	26.85
3150.0	3180.0	23.48	23.15	23.13
3350.0	3380.0	28.25	27.43	26.63
3550.0	3580.0	20.01	19.82	19.70
3730.0	3760.0	22.13	21.38	21.07
3910.0	3940.0	30.07	29.81	30.35
4010.0	4040.0	39.05	37.74	35.98
4090.0	4120.0	28.93	27.45	26.62
4190.0	4220.0	24.96	23.27	22.25
4270.0	4300.0	23.66	21.67	20.76
4370.0	4400.0	27.85	26.80	26.85
4520.0	4550.0	28.12	27.53	26.68
4640.0	4670.0	27.25	25.93	24.68
4780.0	4810.0	27.86	25.14	23.31
4900.0	4930.0	24.46	23.14	22.15
5040.0	5070.0	23.06	23.60	23.76
5160.0	5190.0	24.58	25.25	25.68
5300.0	5330.0	27.45	28.29	28.93
5420.0	5450.0	30.17	30.94	31.60
5560.0	5590.0	32.40	33.31	34.02
5680.0	5710.0	34.31	35.22	35.52
5820.0	5850.0	33.90	34.52	34.77
5940.0	5970.0	29.66	29.74	29.64
6080.0	6110.0	25.98	25.61	25.13
6200.0	6230.0	24.19	23.69	22.91
6340.0	6370.0	22.52	22.03	21.33
6460.0	6490.0	21.60	21.29	20.97
6600.0	6630.0	21.78	21.32	21.62

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	RF VSWR (:1) @LO (dBm)		
		+7	+10	+13
550.0	580.0	10.89	6.81	4.82
750.0	780.0	2.37	2.25	2.19
950.0	980.0	2.13	1.96	1.82
1150.0	1180.0	3.15	3.12	3.07
1350.0	1380.0	3.19	3.08	3.05
1550.0	1580.0	2.95	2.71	2.48
1750.0	1780.0	3.05	2.74	2.55
1950.0	1980.0	3.18	3.01	2.89
2150.0	2180.0	3.08	2.89	2.75
2350.0	2380.0	2.59	2.39	2.24
2550.0	2580.0	2.82	2.60	2.44
2750.0	2780.0	1.90	1.70	1.52
2950.0	2980.0	1.34	1.34	1.35
3150.0	3180.0	1.60	1.67	1.73
3350.0	3380.0	1.54	1.51	1.51
3550.0	3580.0	2.26	2.13	2.06
3730.0	3760.0	3.09	2.88	2.74
3910.0	3940.0	3.85	3.56	3.33
4010.0	4040.0	4.03	3.74	3.53
4090.0	4120.0	4.10	3.74	3.46
4190.0	4220.0	4.42	3.98	3.67
4270.0	4300.0	4.16	3.69	3.37
4370.0	4400.0	4.66	4.01	3.69
4520.0	4550.0	3.05	2.67	2.47
4640.0	4670.0	2.98	2.60	2.36
4780.0	4810.0	3.13	2.73	2.51
4900.0	4930.0	3.24	2.86	2.67
5040.0	5070.0	3.62	3.25	3.08
5160.0	5190.0	4.04	3.67	3.52
5300.0	5330.0	4.36	3.96	3.84
5420.0	5450.0	4.47	4.05	3.78
5560.0	5590.0	4.45	4.09	3.74
5680.0	5710.0	4.19	3.84	3.56
5820.0	5850.0	3.45	3.14	2.88
5940.0	5970.0	3.79	3.52	3.28
6080.0	6110.0	2.92	2.73	2.55
6200.0	6230.0	2.10	1.99	1.84
6340.0	6370.0	1.74	1.68	1.61
6460.0	6490.0	2.28	2.24	2.19
6600.0	6630.0	4.02	3.83	3.76

LO (MHz)	LO VSWR (:1) @LO (dBm)		
	+7	+10	+13
580.0	36.97	34.75	28.03
780.0	10.19	8.35	8.64
980.0	3.07	3.85	4.80
1180.0	1.46	2.01	2.62
1380.0	1.08	1.40	1.86
1580.0	1.67	2.01	2.53
1780.0	2.07	2.62	3.31
1980.0	1.92	2.61	3.39
2180.0	1.90	2.48	3.17
2380.0	2.08	2.40	2.90
2580.0	1.98	2.03	2.35
2780.0	1.64	1.52	1.76
2980.0	1.43	1.15	1.45
3180.0	1.18	1.24	1.65
3380.0	1.17	1.56	2.05
3580.0	1.63	1.98	2.48
3760.0	2.12	2.37	2.82
3940.0	2.77	2.73	3.03
4040.0	3.26	2.95	3.11
4120.0	3.72	3.13	3.11
4220.0	4.20	3.26	3.04
4300.0	4.68	3.29	2.86
4400.0	5.72	3.67	2.86
4550.0	6.28	3.95	2.78
4670.0	6.73	4.29	2.88
4810.0	6.91	4.27	2.87
4930.0	6.76	4.00	2.72
5070.0	5.95	3.73	2.90
5190.0	5.19	3.56	3.16
5330.0	4.17	3.40	3.43
5450.0	3.43	3.25	3.56
5590.0	2.94	3.06	3.44
5710.0	2.63	2.90	3.30
5850.0	2.15	2.52	2.93
5970.0	1.94	2.27	2.62
6110.0	1.90	2.19	2.48
6230.0	2.11	2.39	2.66
6370.0	2.71	3.03	3.31
6490.0	3.37	3.71	3.99
6630.0	3.02	3.17	3.28

IF (OUT) (MHz)	IF VSWR @LO=6000MHz (:1) @LO (dBm)		
	+7	+10	+13
10.0	1.57	1.95	2.29
50.0	1.60	1.98	2.33
90.0	1.57	1.92	2.24
130.0	1.60	1.92	2.22
170.0	1.60	1.87	2.13
210.0	1.61	1.83	2.05
250.0	1.62	1.80	2.00
290.0	1.63	1.75	1.91
330.0	1.67	1.75	1.89
370.0	1.66	1.69	1.80
410.0	1.72	1.71	1.78
450.0	1.70	1.65	1.69
490.0	1.74	1.64	1.64
530.0	1.70	1.57	1.54
570.0	1.69	1.49	1.42
610.0	1.67	1.43	1.31
650.0	1.68	1.40	1.22
690.0	1.88	1.60	1.43
730.0	2.32	2.04	1.88
770.0	3.12	2.77	2.54
810.0	3.81	3.34	3.02
850.0	4.19	3.65	3.29
890.0	4.30	3.75	3.36
930.0	4.18	3.66	3.30
970.0	4.15	3.65	3.31
1010.0	4.03	3.57	3.24
1050.0	3.98	3.55	3.26
1090.0	3.95	3.55	3.29
1130.0	3.97	3.63	3.42
1170.0	4.10	3.81	3.64
1210.0	4.20	3.96	3.84
1250.0	4.41	4.27	4.22
1290.0	4.67	4.61	4.64
1330.0	5.10	5.16	5.28
1370.0	5.68	5.87	6.11
1390.0	6.01	6.28	6.56
1430.0	6.86	7.31	7.70
1450.0	7.34	7.87	8.31
1490.0	8.39	9.04	9.58
1510.0	8.90	9.63	10.13

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Harmonics Tables

RF HARMONICS ORDER	(-dBm)	(-dBc)										
0	-	-	4	4	12	36	19	36	32	---	---	---
1	-	18	+0	22	12	31	41	57	46	46	---	---
2	90	63	52	60	69	64	64	>72	64	67	65	---
3	>90	>72	66	>72	67	>72	66	>72	>72	>72	>72	>72
4	>90	>72	>72	>72	>72	>72	>72	>72	>72	>72	>72	>72
5	>90	>72	>72	>72	>72	>72	>72	>72	>72	>72	>72	>72
6	>90	>72	>72	>72	>72	>72	>72	>72	>72	>72	>72	>72
7	>90	>72	>72	>72	>72	>72	>72	>72	>72	>72	>72	>72
8	---	---	>72	>72	>72	>72	>72	>72	>72	>72	>72	>72
9	---	---	---	>72	>72	>72	>72	>72	>72	>72	>72	>72
10	---	---	---	---	>72	>72	>72	>72	>72	>72	>72	>72
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 3375 MHz; -12.00 dBm.
LO IN: 3405 MHz; +10.00 dBm
IF OUT: 30 MHz; -17.76 dBm

RF HARMONICS ORDER	(-dBm)	(-dBc)										
0	-	-	6	15	22	48	30	49	45	---	---	---
1	-	17	+0	22	12	32	41	56	48	47	---	---
2	70	51	40	49	64	53	56	70	55	58	56	---
3	>90	62	45	55	44	52	44	60	70	70	65	70
4	>90	>82	71	66	70	61	65	65	77	>82	77	75
5	>90	75	>82	>82	70	75	68	>82	72	82	>82	>82
6	>90	>82	>82	>82	>82	>82	>82	77	82	>82	>82	>82
7	>90	>82	>82	>82	>82	>82	>82	>82	>82	>82	>82	>82
8	---	---	>82	>82	>82	>82	>82	>82	>82	>82	>82	>82
9	---	---	---	>82	>82	>82	>82	>82	>82	>82	>82	>82
10	---	---	---	---	>82	>82	>82	>82	>82	>82	>82	>82
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 3375 MHz; -2.00 dBm.
LO IN: 3405 MHz; +10.00 dBm
IF OUT: 30 MHz; -7.85 dBm

Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Typical Performance Curves

Conversion Loss @ IF=30MHz



Conversion Loss vs. IF @ RF=3010.1MHz



Conversion Loss vs. IF @ RF=739.9MHz



Conversion Loss vs. IF@ RF=6010.1MHz



IP3 Input



Compression @ RF IN=+3dBm



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Typical Performance Curves

LO-RF Isolation



LO-IF Isolation



RF-IF Isolation



RF VSWR



LO VSWR



IF VSWR



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Harmonics Tables

RF HARMONICS ORDER	(-dBm)	(-dBc)										
0	-	-	4	4	12	36	19	36	32	---	---	---
1	-	18	+0	22	12	31	41	57	46	46	---	---
2	90	63	52	60	69	64	64	>72	64	67	65	---
3	>90	>72	66	>72	67	>72	66	>72	>72	>72	>72	>72
4	>90	>72	>72	>72	>72	>72	>72	>72	>72	>72	>72	>72
5	>90	>72	>72	>72	>72	>72	>72	>72	>72	>72	>72	>72
6	>90	>72	>72	>72	>72	>72	>72	>72	>72	>72	>72	>72
7	>90	>72	>72	>72	>72	>72	>72	>72	>72	>72	>72	>72
8	---	---	>72	>72	>72	>72	>72	>72	>72	>72	>72	>72
9	---	---	---	>72	>72	>72	>72	>72	>72	>72	>72	>72
10	---	---	---	---	>72	>72	>72	>72	>72	>72	>72	>72
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 3375 MHz; -12.00 dBm.
LO IN: 3405 MHz; +10.00 dBm
IF OUT: 30 MHz; -17.76 dBm

RF HARMONICS ORDER	(-dBm)	(-dBc)										
0	-	-	6	15	22	48	30	49	45	---	---	---
1	-	17	+0	22	12	32	41	56	48	47	---	---
2	70	51	40	49	64	53	56	70	55	58	56	---
3	>90	62	45	55	44	52	44	60	70	70	65	70
4	>90	>82	71	66	70	61	65	65	77	>82	77	75
5	>90	75	>82	>82	70	75	68	>82	72	82	>82	>82
6	>90	>82	>82	>82	>82	>82	>82	77	82	>82	>82	>82
7	>90	>82	>82	>82	>82	>82	>82	>82	>82	>82	>82	>82
8	---	---	>82	>82	>82	>82	>82	>82	>82	>82	>82	>82
9	---	---	---	>82	>82	>82	>82	>82	>82	>82	>82	>82
10	---	---	---	---	>82	>82	>82	>82	>82	>82	>82	>82
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 3375 MHz; -2.00 dBm.
LO IN: 3405 MHz; +10.00 dBm
IF OUT: 30 MHz; -7.85 dBm

Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Case Style FL

FL905

Outline Dimensions



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N	WT, GRAM
FL905	.74 (18.80)	.90 (22.86)	.54 (13.72)	.50 (12.70)	.04 (1.02)	.16 (4.06)	.29 (7.37)	.37 (9.40)	- -	.122 (3.10)	.496 (12.60)	.106 (2.69)	.122 (3.10)	20.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .03; 3Pl. ± .015.
Tolerance on hole size and interaxes dimensions to be ±.005.

Notes:

1. Case material: Brass.
2. Case finish: Nickel plate.

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.

Mini-Circuits

Environmental Specifications **ENV28T5**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I

This document and its contents are the property of Mini-Circuits.