Coaxial

Power Splitter/Combiner

ZX10-4-24-S+

4 Way-0° 50Ω 1675 to 2350 MHz

Generic photo used for illustration purposes only

CASE STYLE: GR1026

Connectors	Model
SMA	ZX10-4-24-S+

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	2.5W max.*
Power Input (as a combiner)	0.125W max.

*maximum VSWR at output 1.2:1

Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3
PORT 4	4

Features

- low insertion loss, 0.9 dB typ.
- high isolation, 20 dB typ.
- rigid unibody construction
- gold plated connectors; nickel plated body
- low cost
- small size
- protected by US patent 6,790,049

Applications

- PCS/DCS
- antenna arrays
- signal distribution
- test bench

Outline Drawing



Outline Dimensions (inch / mm)

A	B	C	D	E	F	G	H
2.04	.60	.75	.50	.10	.17	.25	.25
51.82	15.24	19.05	12.70	2.54	4.32	6.35	6.35

J	K	L	M	N			wt
.50	.11	1.820	.106	.12			grams
12.70	2.79	46.23	2.69	3.05			60.0

Electrical Specifications (T_{AMB}=25°C)

FREQ. RANGE (MHz)	ISOLATION (dB)		INSERTION LOSS (dB) ABOVE 6 dB		PHASE UNBALANCE (Deg.)	AMPLITUDE UNBALANCE (dB)	INPUT VSWR (:1)	OUTPUT VSWR (:1)
f_L-f_U	Typ.	Min.	Typ.	Max.	Max.	Max.	Typ.	Typ.
1675-2350	**20**	**17**	**0.9**	**1.1**	**5.0**	**0.7**	**1.18**	**1.3**
1775-2200	25	20	0.9	1.1	5.0	0.7	1.18	1.3

Typical Performance Data

Freq. (MHz)	Total Loss[1] (dB)				Amp. Unbal. (dB)	Isolation (dB)			Phase Unbal. (deg.)	VSWR S	VSWR 1	VSWR 2	VSWR 3	VSWR 4
	S-1	S-2	S-3	S-4		1-2	2-3	3-4						
1675.00	6.39	6.69	6.34	6.28	0.41	21.22	25.68	21.32	0.58	1.12	1.14	1.19	1.13	1.18
1700.00	6.39	6.70	6.34	6.28	0.42	22.15	26.12	22.32	0.45	1.11	1.14	1.19	1.12	1.18
1750.00	6.39	6.71	6.35	6.28	0.44	24.28	27.06	24.59	0.43	1.09	1.14	1.20	1.13	1.18
1800.00	6.40	6.73	6.36	6.28	0.45	27.02	28.12	27.60	0.39	1.08	1.15	1.20	1.13	1.18
1850.00	6.41	6.74	6.37	6.27	0.47	30.96	29.32	32.08	0.63	1.07	1.16	1.20	1.13	1.18
1900.00	6.44	6.75	6.39	6.28	0.47	37.87	30.73	40.30	0.89	1.07	1.16	1.21	1.13	1.19
1950.00	6.45	6.76	6.41	6.27	0.48	45.62	32.44	39.41	1.17	1.07	1.17	1.22	1.14	1.20
2000.00	6.49	6.76	6.43	6.28	0.49	34.59	34.61	32.00	1.51	1.08	1.19	1.23	1.15	1.21
2050.00	6.51	6.77	6.45	6.28	0.49	29.72	37.55	28.05	1.82	1.09	1.20	1.24	1.15	1.22
2100.00	6.55	6.77	6.47	6.29	0.48	26.72	42.00	25.45	1.97	1.09	1.21	1.25	1.16	1.23
2150.00	6.59	6.76	6.50	6.29	0.47	24.64	48.00	23.57	2.21	1.09	1.24	1.26	1.19	1.24
2200.00	6.63	6.76	6.52	6.29	0.46	23.01	43.74	22.06	2.45	1.08	1.26	1.28	1.20	1.26
2250.00	6.68	6.74	6.55	6.30	0.44	21.68	38.14	20.85	2.76	1.07	1.28	1.28	1.22	1.27
2300.00	6.72	6.73	6.56	6.30	0.43	20.57	34.39	19.84	2.93	1.05	1.29	1.30	1.23	1.29
2350.00	6.78	6.72	6.60	6.30	0.48	19.56	31.63	18.93	2.96	1.05	1.31	1.31	1.25	1.30

1. Total Loss = Insertion Loss + 6dB splitter loss.

ZX10-4-24-S+
TOTAL LOSS



ZX10-4-24-S+
ISOLATION



ZX10-4-24-S+
VSWR



electrical schematic

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

4 Way-0° Power Splitter/Combiner ZX10-4-24+

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS[1] (dB)				AMP. UNBAL. (dB)	ISOLATION (dB)			PHASE UNBAL. (deg.)
	S-1	S-2	S-3	S-4		1-2	2-3	3-4	
1675	6.40	6.69	6.35	6.33	0.36	19.72	23.64	20.21	0.97
1685	6.40	6.69	6.35	6.33	0.36	20.02	23.76	20.53	0.96
1695	6.40	6.69	6.36	6.33	0.36	20.32	23.90	20.86	0.96
1705	6.40	6.69	6.36	6.33	0.37	20.63	24.03	21.21	0.98
1715	6.40	6.70	6.36	6.32	0.37	20.95	24.17	21.56	0.98
1725	6.40	6.70	6.36	6.32	0.38	21.27	24.32	21.92	0.96
1735	6.40	6.70	6.36	6.32	0.38	21.60	24.47	22.28	0.95
1745	6.40	6.71	6.37	6.32	0.38	21.94	24.62	22.67	0.95
1755	6.40	6.71	6.37	6.32	0.39	22.29	24.78	23.07	0.94
1765	6.40	6.71	6.37	6.32	0.39	22.66	24.93	23.49	0.94
1775	6.41	6.72	6.38	6.32	0.39	23.03	25.09	23.92	0.91
1780	6.41	6.72	6.38	6.33	0.39	23.22	25.17	24.15	0.91
1785	6.41	6.72	6.38	6.32	0.40	23.42	25.26	24.37	0.90
1790	6.41	6.72	6.38	6.32	0.40	23.62	25.35	24.60	0.88
1795	6.41	6.72	6.38	6.33	0.40	23.82	25.43	24.84	0.87
1800	6.41	6.72	6.39	6.32	0.40	24.02	25.52	25.08	0.88
1820	6.42	6.73	6.39	6.33	0.40	24.88	25.88	26.10	0.83
1840	6.42	6.74	6.40	6.33	0.41	25.79	26.25	27.23	0.78
1860	6.43	6.75	6.41	6.33	0.42	26.78	26.65	28.47	0.79
1880	6.44	6.75	6.42	6.34	0.42	27.84	27.08	29.82	0.83
1900	6.44	6.76	6.43	6.34	0.42	28.95	27.53	31.31	0.95
1930	6.46	6.77	6.44	6.34	0.43	30.81	28.20	33.83	1.07
1960	6.47	6.78	6.45	6.34	0.43	32.54	28.98	35.88	1.21
1990	6.49	6.78	6.47	6.35	0.44	33.85	29.89	36.30	1.34
2020	6.51	6.79	6.48	6.35	0.44	34.09	30.85	34.66	1.51
2050	6.52	6.79	6.50	6.35	0.44	33.19	32.00	32.53	1.65
2080	6.54	6.80	6.51	6.36	0.44	31.86	33.35	30.65	1.79
2110	6.56	6.80	6.53	6.36	0.44	30.36	34.85	29.00	1.97
2140	6.58	6.80	6.54	6.36	0.44	29.07	36.87	27.70	2.14
2170	6.60	6.81	6.56	6.37	0.44	27.92	39.52	26.60	2.28
2200	6.62	6.80	6.57	6.37	0.44	26.89	43.01	25.64	2.40
2215	6.64	6.80	6.58	6.37	0.43	26.43	45.02	25.22	2.48
2230	6.65	6.80	6.59	6.37	0.43	26.00	46.90	24.83	2.55
2245	6.66	6.80	6.59	6.37	0.43	25.57	47.58	24.44	2.61
2260	6.67	6.80	6.60	6.37	0.43	25.14	46.41	24.06	2.71
2275	6.68	6.79	6.61	6.37	0.42	24.73	44.28	23.70	2.77
2290	6.69	6.79	6.61	6.37	0.42	24.36	42.10	23.38	2.83
2305	6.70	6.78	6.62	6.37	0.42	24.00	40.21	23.07	2.90
2320	6.71	6.78	6.62	6.37	0.41	23.64	38.59	22.76	2.92
2335	6.72	6.78	6.63	6.37	0.41	23.30	37.15	22.47	2.95
2350	6.73	6.77	6.63	6.37	0.40	22.96	35.89	22.19	3.00

FREQ. (MHz)	VSWR (:1)					
	S	1	2	3	4
1675	1.06	1.11	1.15	1.11	1.14
1685	1.05	1.11	1.15	1.11	1.14
1695	1.05	1.12	1.15	1.11	1.14
1705	1.04	1.12	1.16	1.11	1.15
1715	1.03	1.12	1.16	1.11	1.15
1725	1.03	1.12	1.16	1.11	1.15
1735	1.02	1.12	1.16	1.11	1.15
1745	1.02	1.12	1.16	1.11	1.15
1755	1.02	1.12	1.16	1.11	1.15
1765	1.03	1.12	1.16	1.11	1.15
1775	1.03	1.12	1.16	1.11	1.15
1780	1.04	1.12	1.17	1.11	1.15
1785	1.04	1.13	1.17	1.11	1.15
1790	1.04	1.13	1.17	1.11	1.15
1795	1.04	1.13	1.17	1.11	1.16
1800	1.05	1.13	1.17	1.11	1.16
1820	1.06	1.13	1.17	1.11	1.16
1840	1.07	1.13	1.17	1.12	1.16
1860	1.09	1.14	1.17	1.12	1.16
1880	1.10	1.14	1.18	1.12	1.16
1900	1.11	1.15	1.18	1.13	1.17
1930	1.13	1.15	1.19	1.13	1.18
1960	1.15	1.16	1.20	1.14	1.18
1990	1.16	1.17	1.21	1.15	1.19
2020	1.17	1.18	1.21	1.16	1.20
2050	1.18	1.19	1.22	1.17	1.21
2080	1.19	1.20	1.23	1.18	1.22
2110	1.20	1.21	1.24	1.20	1.23
2140	1.21	1.23	1.25	1.21	1.24
2170	1.21	1.24	1.26	1.22	1.25
2200	1.21	1.25	1.26	1.23	1.26
2215	1.21	1.26	1.26	1.24	1.26
2230	1.20	1.26	1.27	1.25	1.27
2245	1.20	1.27	1.28	1.26	1.28
2260	1.20	1.28	1.28	1.26	1.28
2275	1.19	1.28	1.28	1.27	1.29
2290	1.18	1.28	1.28	1.27	1.29
2305	1.18	1.29	1.29	1.28	1.29
2320	1.17	1.29	1.30	1.28	1.30
2335	1.17	1.30	1.30	1.29	1.31
2350	1.16	1.31	1.30	1.30	1.31

[1] Total Loss = Insertion Loss+ 6dB Splitter Loss

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

4 Way-0° Power Splitter/Combiner ZX10-4-24+

Typical Performance Curves

Total Loss



Isolation



Amplitude Unbalance



Phase Unbalance



VSWR



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Case Style GR

GR1026

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	WT. GRAM
GR1026	2.04 (51.82)	.60 (15.24)	.75 (19.05)	.50 (12.70)	.10 (2.54)	.17 (4.32)	.25 (6.35)	.25 (6.35)	.50 (12.70)	.11 (2.79)	1.820 (46.23)	.106 (2.69)	.12 (3.05)	60.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .03; 3Pl. ± .015.
Tolerance on hole size and interaxes dimensions to be ±.005.

Notes:
1. Case material: Brass.
2. Case finish: Nickel plate.

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document nd its contents are the property of Mini-Circuits

Mini-Circuits

Environmental Specifications **ENV28T5**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I

This document and its contents are the property of Mini-Circuits.