

Coaxial Directional Coupler

50Ω 5 to 1200 MHz


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Permanent damage may occur if any of these limits are exceeded.	

Coaxial Connections

INPUT	1
OUTPUT	2
COUPLED	3

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
.74	.90	.54	.50	.04	.16	.29
18.80	22.86	13.72	12.70	1.02	4.06	7.37
H	J	K	L	M	N	wt
.37	--	.122	.496	.106	.122	grams
9.40	--	3.10	12.60	2.69	3.10	20.0

Features

- very flat coupling
- very broad, multi-octave
- all welded construction
- protected by U.S. Patents 6,140,887 & 6,784,521 & 6,790,049

Applications

- VHF/UHF
- communications receivers & transmitters
- cellular
- instrumentation

Directional Coupler Electrical Specifications ($T_{AMB} = 25^{\circ}C$)




FREQ. (MHz)	COUPLING (dB)		MAINLINE LOSS ¹ (dB)						DIRECTIVITY (dB)						VSWR (:1)	POWER INPUT, W					
			L			M			U			L				M			U		
			Typ.	Max.	Flatness	Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Min.	Typ.		Min.	Typ.	Min.	Typ.	Max.	Max.
f _L -f _U	Nom.	Flatness	Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Max.	L	MU	Max.		
5-1200	13.0±0.5	±0.3	06	0.9	0.7	1.1	0.9	1.5	21	18	19	15	15	10	1.15	0.5	1.0				

L = low range [f_L to $10 f_L$] M = mid range [$10 f_L$ to $f_U/2$] U = upper range [$f_U/2$ to f_U]


1. Mainline loss includes theoretical power loss at coupled port.

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out		Coupling (dB) In-Cpl	Directivity (dB)		Return Loss (dB) In Out		Cpl
5.00	0.67		12.93	21.86	22.28	30.20		24.37
10.00	0.63		12.92	21.79	22.90	33.04		24.96
50.00	0.64		12.94	21.62	23.33	35.18		25.41
100.00	0.65		12.97	21.36	23.44	34.61		25.60
200.00	0.67		13.00	20.75	23.69	32.95		25.93
400.00	0.72		13.06	19.10	24.38	30.15		26.19
500.00	0.75		13.10	18.21	24.74	29.05		25.88
800.00	0.90		13.20	15.71	24.52	27.13		24.26
1000.00	1.05		13.22	14.27	23.46	26.43		23.13
1200.00	1.19		13.34	12.99	21.92	25.81		22.53



Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) THAT ROUTES DC FROM RF PORTS TO GROUND.


Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

ZX30-13-4-S+



Generic photo used for illustration purposes only

CASE STYLE: FL905

Connectors Model
SMA ZX30-13-4-S+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

REV. L
M171494
ED-10213A/3
ZX30-13-4-S+
WZ/TD/CP/AM
200814
Page 1 of 1

Directional Coupler

ZX30-13-4+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	OUT	CPL
5.0	0.61	12.85	21.51	22.96	32.14	24.94
10.0	0.60	12.84	21.53	23.33	34.70	25.46
15.0	0.60	12.84	21.52	23.47	35.43	25.60
20.0	0.61	12.85	21.50	23.49	35.68	25.66
50.0	0.62	12.89	21.36	23.55	35.32	25.86
80.0	0.63	12.90	21.21	23.58	34.12	25.93
100.0	0.63	12.90	21.03	23.60	33.29	25.95
125.0	0.65	12.92	20.84	23.60	32.48	26.00
150.0	0.65	12.92	20.63	23.58	31.78	26.13
200.0	0.65	12.94	20.12	23.40	30.01	26.30
250.0	0.68	12.99	19.59	23.26	28.64	26.45
275.0	0.68	13.00	19.30	23.11	28.04	26.50
300.0	0.69	12.99	19.01	22.94	27.54	26.47
325.0	0.69	13.01	18.74	22.87	27.12	26.45
350.0	0.71	13.01	18.47	22.83	26.74	26.45
375.0	0.71	13.03	18.18	22.75	26.32	26.41
400.0	0.73	13.06	17.86	22.61	25.88	26.36
450.0	0.75	13.08	17.31	22.40	25.16	26.18
475.0	0.76	13.10	17.00	22.42	24.91	26.02
500.0	0.77	13.09	16.76	22.35	24.73	25.82
525.0	0.78	13.12	16.46	22.18	24.50	25.64
550.0	0.79	13.13	16.18	22.01	24.20	25.56
575.0	0.79	13.14	15.91	21.97	23.91	25.44
600.0	0.82	13.15	15.64	21.98	23.81	25.19
625.0	0.83	13.16	15.38	21.96	23.78	24.88
650.0	0.83	13.18	15.11	21.80	23.62	24.62
675.0	0.83	13.18	14.84	21.66	23.39	24.45
700.0	0.87	13.19	14.61	21.65	23.25	24.23
725.0	0.88	13.23	14.35	21.72	23.28	23.92
750.0	0.86	13.25	14.12	21.71	23.25	23.64
775.0	0.88	13.23	13.89	21.63	23.09	23.45
800.0	0.92	13.25	13.64	21.53	22.87	23.24
825.0	0.93	13.28	13.41	21.49	22.86	22.91
850.0	0.91	13.32	13.18	21.56	22.94	22.55
875.0	0.93	13.30	12.97	21.65	22.93	22.31
900.0	0.97	13.31	12.77	21.62	22.75	22.12
925.0	0.98	13.34	12.55	21.53	22.68	21.87
950.0	0.98	13.35	12.35	21.46	22.77	21.52
975.0	0.99	13.37	12.17	21.53	22.83	21.19
1000.0	1.00	13.37	11.97	21.65	22.77	21.00

REV. X1
ZX30-13-4+
060718
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661







The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Directional Coupler

ZX30-13-4+

Typical Performance Curves




REV. X1
ZX30-13-4+
060718
Page 1 of 1



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Outline Dimensions



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N	WT, GRAM
FL905	.74 (18.80)	.90 (22.86)	.54 (13.72)	.50 (12.70)	.04 (1.02)	.16 (4.06)	.29 (7.37)	.37 (9.40)	- -	.122 (3.10)	.496 (12.60)	.106 (2.69)	.122 (3.10)	20.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$.

Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Notes:

1. Case material: Brass.
2. Case finish: Nickel plate.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I