

Coaxial

Bandpass Filter

ZX75BP-1135-S+

50Ω

900 to 1370 MHz

The Big Deal

- Low insertion loss of typical 0.6 dB
- Good matching and good out of band rejection
- Connectorized package
- High power handling, 10 W



Generic photo used for illustration purposes only
CASE STYLE: HY1239

Product Overview

ZX75BP-1135-S+ is a low loss band pass filter in a rugged connectorized package covering 900-1370 MHz. The high power handling capability of this filter finds it application in high power transmitters. The filter also offers lower passband insertion loss and good stopband rejection until 5600 MHz. In addition, it has repeatable performance across lots and consistent performance across temperature.

Key Features

Feature	Advantages
Low insertion loss	Lower insertion loss result in better SNR in receiver front end and better power delivery to antenna in transmitter.
Good matching and good out of band rejection	This filter has good matching, which enables maximum power transform and better out of band rejection results in wide spur free band.
Connectorized package	Connectorized package is easy to interface with other devices and well suited for test setups.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Bandpass Filter

50Ω 900 to 1370 MHz

ZX75BP-1135-S+



Generic photo used for illustration purposes only


Features

- Low insertion loss of typical 0.6 dB
- Good matching and good out of band rejection
- Connectorized package


Applications

- Defence / Military
- L-Band applications
- Radio astronomy
- Wireless medical telemetry

Functional Schematic







Typical Frequency Response



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR
M174540
ZX75BP-1135-S+
EDU3594
URJ
190711
Page 2 of 3

Electrical Specifications at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Center Frequency	-	-	1135	-	MHz
	Insertion Loss	F1-F2	-	0.6	1.2	dB
	VSWR	F1-F2	-	1.35	1.5	:1
Stop Band, Lower	Insertion Loss	DC-F3	40	45	-	dB
	VSWR	DC-F3	-	28	-	:1
Stop Band, Upper	Insertion Loss	F4-F5	40	50	-	dB
	VSWR	F4-F6	-	40	-	dB
		F4-F6	-	28	-	:1

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	10 W max. @ 25°C

RF power derate linearly to 5 W @ 85°C
 Permanent damage may occur if any of these limits are exceeded.


Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	90.92	434.30	900	1.66
105	50.27	1737.18	930	1.58
380	47.04	347.44	960	1.52
500	50.91	157.93	990	1.46
550	30.79	115.81	1020	1.42
595	20.96	72.39	1050	1.40
700	3.19	4.43	1080	1.39
900	0.33	1.05	1110	1.38
1135	0.35	1.10	1135	1.39
1370	0.50	1.14	1170	1.40
1500	3.02	3.94	1200	1.42
1700	20.85	30.49	1230	1.43
1800	30.82	37.77	1260	1.46
2000	70.72	52.65	1290	1.50
2500	55.52	78.97	1320	1.56
2800	65.71	69.49	1330	1.59
3000	55.68	59.91	1340	1.62
4000	62.36	45.72	1350	1.66
5000	51.08	38.61	1360	1.70
5600	40.11	44.55	1370	1.74

Coaxial Connections

PORT - 1	SMA-FEMALE
PORT - 2	SMA-FEMALE

Outline Drawing



Outline Dimensions (inch mm)

A	B	C	D	E	F	G
1.20	.75	.46	1.18	.04	.17	1.00
30.48	19.05	11.68	29.97	1.02	4.32	25.40
H	J	K	L	M	N	Wt.
.50	.35	.18	.21	1.88	.106	grams
12.70	8.89	4.57	5.28	47.75	2.69	35.0

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Coaxial Band Pass Filter

ZX75BP-1135-S+






Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
1	87.65	90.92	89.01	0.04	0.04	0.04	0.04	0.04	0.04
10	69.49	69.33	69.57	0.00	0.00	0.00	0.00	0.00	0.00
100	50.67	50.60	50.49	0.00	0.00	0.01	0.01	0.02	0.02
200	48.29	48.28	48.21	0.00	0.01	0.02	0.06	0.08	0.09
300	66.54	66.89	67.16	0.01	0.03	0.04	0.16	0.18	0.19
380	47.04	47.04	47.06	0.03	0.05	0.06	0.20	0.23	0.25
500	51.54	50.91	50.34	0.08	0.11	0.12	0.19	0.23	0.25
550	30.93	30.79	30.63	0.12	0.15	0.17	0.18	0.22	0.25
595	21.06	20.96	20.85	0.20	0.24	0.26	0.23	0.28	0.31
700	3.21	3.19	3.17	3.78	3.99	4.13	3.80	4.02	4.17
820	0.36	0.42	0.46	19.15	19.31	19.18	18.50	18.66	18.59
850	0.32	0.38	0.42	20.53	20.87	20.81	19.47	19.78	19.78
900	0.27	0.33	0.37	30.94	31.70	32.78	27.22	27.59	28.23
920	0.26	0.32	0.36	33.96	33.96	35.98	30.84	30.79	32.16
940	0.26	0.33	0.36	27.47	27.61	27.88	27.72	27.78	28.25
960	0.27	0.33	0.37	23.67	23.92	23.95	24.07	24.30	24.41
1000	0.29	0.35	0.39	20.19	20.48	20.44	20.35	20.63	20.65
1100	0.29	0.36	0.40	22.04	22.16	22.12	21.30	21.49	21.60
1120	0.29	0.35	0.39	24.13	24.27	24.27	22.98	23.21	23.44
1135	0.28	0.35	0.39	26.39	26.63	26.73	24.72	25.07	25.48
1200	0.29	0.36	0.41	28.67	29.01	30.00	27.85	28.15	29.40
1300	0.38	0.46	0.51	18.91	19.14	19.33	19.07	19.30	19.51
1370	0.41	0.50	0.56	23.06	23.53	23.56	24.43	25.44	26.11
1500	2.78	3.02	3.22	4.58	4.51	4.41	4.62	4.51	4.38
1600	10.92	11.24	11.49	0.93	1.00	1.04	0.74	0.79	0.81
1700	20.58	20.85	21.07	0.49	0.57	0.62	0.24	0.30	0.34
1800	30.53	30.82	31.05	0.38	0.46	0.51	0.13	0.20	0.24
2000	70.57	70.72	69.55	0.24	0.33	0.39	0.08	0.15	0.19
2500	55.36	55.52	55.73	0.12	0.22	0.29	0.04	0.12	0.17
2800	65.08	65.71	65.74	0.15	0.25	0.32	0.04	0.12	0.18
2900	67.90	64.11	62.21	0.18	0.29	0.36	0.04	0.12	0.18
3000	54.57	55.68	56.13	0.19	0.29	0.36	0.04	0.13	0.18
3100	60.86	60.94	61.17	0.19	0.29	0.35	0.04	0.13	0.19
3200	63.27	63.60	63.70	0.20	0.30	0.36	0.04	0.13	0.19
3300	66.09	66.65	66.62	0.22	0.32	0.38	0.05	0.14	0.20
3400	62.90	63.06	63.58	0.24	0.34	0.39	0.05	0.14	0.20
3500	64.03	64.73	64.80	0.25	0.35	0.40	0.05	0.14	0.20
3600	64.64	64.75	65.07	0.26	0.36	0.42	0.06	0.15	0.21
3700	64.40	64.47	64.69	0.26	0.36	0.42	0.06	0.15	0.21
3800	63.68	64.17	64.33	0.27	0.37	0.43	0.07	0.16	0.22
3900	63.12	63.29	63.32	0.27	0.38	0.44	0.08	0.17	0.23
4000	62.24	62.36	62.42	0.26	0.38	0.45	0.08	0.17	0.22
4100	61.34	61.62	61.38	0.26	0.38	0.45	0.09	0.18	0.24
4200	60.35	60.44	60.48	0.25	0.38	0.46	0.09	0.18	0.24
4300	59.32	59.42	59.41	0.25	0.38	0.46	0.09	0.18	0.24
4400	58.06	58.41	58.32	0.24	0.38	0.46	0.10	0.19	0.24
4500	57.10	57.22	57.14	0.24	0.38	0.48	0.11	0.20	0.25
4600	56.02	55.92	56.06	0.23	0.38	0.48	0.10	0.19	0.25
4700	54.79	54.88	54.86	0.23	0.38	0.49	0.11	0.20	0.25
4800	53.61	53.61	53.69	0.24	0.39	0.50	0.11	0.21	0.26
4900	52.38	52.44	52.43	0.26	0.42	0.54	0.11	0.20	0.25
5000	51.01	51.08	51.07	0.30	0.45	0.57	0.12	0.21	0.26
5100	49.46	49.52	49.59	0.29	0.44	0.56	0.12	0.21	0.26
5200	47.92	48.00	48.02	0.23	0.39	0.51	0.13	0.22	0.27
5300	46.35	46.31	46.33	0.21	0.37	0.50	0.13	0.22	0.26
5400	44.50	44.48	44.49	0.21	0.38	0.50	0.13	0.23	0.27
5450	43.57	43.53	43.48	0.20	0.37	0.50	0.14	0.23	0.27
5500	42.49	42.48	42.44	0.20	0.37	0.50	0.14	0.23	0.28
5550	41.40	41.37	41.29	0.21	0.38	0.51	0.14	0.24	0.28
5600	40.13	40.11	40.10	0.21	0.39	0.52	0.15	0.24	0.28

Typical Performance Data

FREQ.	GROUP DELAY		
(MHz)	(nsec)		
	@-40°C	@+25°C	@+85°C
900	1.67	1.66	1.65
910	1.64	1.63	1.63
920	1.62	1.61	1.60
930	1.59	1.58	1.58
940	1.57	1.56	1.55
950	1.55	1.54	1.53
960	1.53	1.52	1.51
970	1.51	1.50	1.49
980	1.49	1.48	1.47
990	1.47	1.46	1.46
1000	1.46	1.45	1.44
1010	1.44	1.44	1.43
1020	1.43	1.42	1.42
1030	1.42	1.41	1.41
1040	1.41	1.41	1.40
1050	1.41	1.40	1.39
1060	1.40	1.39	1.39
1070	1.40	1.39	1.39
1080	1.40	1.39	1.38
1090	1.39	1.38	1.38
1100	1.39	1.38	1.38
1110	1.39	1.38	1.38
1120	1.40	1.39	1.39
1135	1.40	1.39	1.39
1140	1.40	1.40	1.39
1150	1.40	1.40	1.39
1160	1.40	1.40	1.39
1170	1.41	1.40	1.39
1180	1.41	1.41	1.40
1190	1.42	1.41	1.41
1200	1.42	1.42	1.41
1210	1.43	1.42	1.42
1220	1.43	1.43	1.42
1230	1.44	1.43	1.43
1240	1.45	1.44	1.44
1250	1.46	1.45	1.45
1260	1.47	1.46	1.46
1270	1.48	1.47	1.47
1280	1.49	1.48	1.48
1300	1.52	1.52	1.52
1370	1.74	1.74	1.75

Typical Performance Curves




Case Style

HY

Outline Dimensions

HY1239



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N	WT GRAMS
HY1239	1.20 (30.48)	.75 (19.05)	.46 (11.68)	1.18 (29.97)	.04 (1.02)	.17 (4.32)	1.00 (25.40)	.50 (12.70)	.35 (8.89)	.18 (4.57)	.21 (5.28)	1.88 (47.75)	.106 (2.69)	35.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$
Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Note:

1. Case material: Brass
2. Case finish: Nickel plate



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 40°C, 96 hours; Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11ms half-sine, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition A