

Coaxial Low Pass Filter

ZX75LP-340-S+

50Ω

DC to 340 MHz

The Big Deal

- High rejection
- Low Insertion loss, 1 dB typical in passband
- Fast roll-off
- Good VSWR
- Connectorized package



Generic photo used for illustration purposes only
CASE STYLE: KE1467

Product Overview

ZX75LP-340-S+ is a 50Ω low pass filter built in a connectorized package. Covering DC-340 MHz bandwidth, these units offer good matching within the passband and high rejection in stopband. This will find its applications in receivers and transmitters to suppress spurious emission and harmonics. In addition it has repeatable performance across production lots and consistent performance across temperature.

Key Features

Feature	Advantages
Low passband insertion loss	Suitable for high performance application
Fast roll-off	Provides very good adjacent band rejection
Connectorized package	The connectorized package is easy to interface with other devices and well suited for test setups
Good VSWR	Provides good interface when used with other devices.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Low Pass Filter

50Ω

DC to 340 MHz

ZX75LP-340-S+



Generic photo used for illustration purposes only

CASE STYLE: KE1467

Connectors	Model
SMA-MF	ZX75LP-340-S+

Features

- High rejection
- Low Insertion loss
- Fast roll-off
- Good VSWR
- Connectorized package

Applications

- Satellite
- Wireless communications
- Receivers / Transmitters

Electrical Specifications at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Insertion Loss	DC-F1	—	1.0	2.2	dB
	Freq. Cut-Off	F2	—	3.0	—	dB
	VSWR	DC-F1	—	1.4	1.8	:1
Stop Band	Rejection Loss	F3-F4	20	31	—	dB
	VSWR	F3-F4	—	35	—	:1

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W max.

Permanent damage may occur if any of these limits are exceeded.


Functional Schematic



Typical Performance Data at 25°C





Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
1	0.05	1.01	1	2.19
50	0.15	1.07	10	2.14
100	0.21	1.06	25	2.11
200	0.37	1.08	50	2.12
340	1.10	1.36	100	2.19
365	3.10	3.16	110	2.20
380	6.05	6.42	120	2.22
400	11.38	14.62	130	2.25
440	22.46	32.18	140	2.29
475	31.38	41.37	175	2.41
500	37.44	45.72	180	2.44
550	48.93	52.65	200	2.54
600	59.10	59.91	220	2.67
650	69.09	64.35	240	2.84
700	73.06	69.49	250	2.94
750	75.09	72.39	260	3.05
800	72.64	75.53	280	3.30
1000	73.50	78.97	300	3.67
1500	67.41	72.39	320	4.27
2000	37.29	41.37	340	5.28

Typical Frequency Response



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.C
 ECO-004400
 ZX75LP-340-S+
 EDR10364U
 URJ
 201007
 Page 2 of 3

Coaxial Connections

INPUT	SMA-Male
OUTPUT	SMA-Female

Outline Drawing



Outline Dimensions (inch)

A	B	C	D	E	F	G
.74	.75	.46	1.18	.04	.362	.21
18.80	19.05	11.68	29.97	1.02	9.19	5.33
H	J	K	L	M		Wt.
.362	1.00	.37	.18	.11		grams
9.19	25.40	9.40	4.57	2.79		24.4

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp






Typical Performance Data

FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
0.5	0.04	0.05	0.06	46.87	44.13	42.66	46.95	44.25	42.72
1	0.04	0.06	0.07	46.69	44.01	42.56	46.76	44.08	42.59
10	0.05	0.08	0.08	40.29	38.51	37.65	40.53	38.71	37.79
50	0.12	0.14	0.16	31.06	30.03	29.38	31.49	30.37	29.72
100	0.18	0.22	0.23	28.84	30.56	31.23	29.43	31.46	32.55
120	0.20	0.24	0.26	30.30	33.41	34.60	31.04	35.29	37.87
140	0.21	0.26	0.29	34.34	36.79	34.66	35.67	40.65	37.11
160	0.24	0.30	0.32	39.50	33.91	30.71	42.54	35.05	31.30
180	0.27	0.33	0.37	32.24	30.08	28.21	32.54	30.39	28.41
200	0.30	0.37	0.41	27.73	28.23	27.61	27.80	28.38	27.68
220	0.33	0.40	0.45	25.98	28.38	29.25	26.06	28.55	29.35
240	0.37	0.45	0.50	26.88	31.77	36.01	27.04	32.09	36.72
280	0.46	0.57	0.64	36.78	30.20	26.56	36.34	30.17	26.58
300	0.55	0.67	0.75	26.81	25.55	23.76	27.16	25.85	24.04
320	0.65	0.79	0.88	26.80	27.50	26.76	29.51	31.48	30.64
340	0.88	1.09	1.22	19.76	18.30	17.36	21.54	19.51	18.43
342	0.93	1.15	1.29	18.27	16.93	16.05	19.59	17.90	16.90
344	0.99	1.23	1.38	16.83	15.64	14.81	17.86	16.41	15.50
346	1.05	1.31	1.47	15.49	14.44	13.66	16.33	15.06	14.22
348	1.14	1.40	1.58	14.24	13.30	12.58	14.92	13.81	13.04
350	1.23	1.51	1.70	13.07	12.22	11.56	13.62	12.66	11.95
360	2.01	2.37	2.64	8.18	7.78	7.37	8.45	8.01	7.57
365	2.61	3.01	3.32	6.36	6.11	5.81	6.57	6.29	5.97
370	3.40	3.83	4.17	4.88	4.76	4.55	5.06	4.91	4.68
375	4.36	4.80	5.17	3.73	3.70	3.57	3.88	3.82	3.68
380	5.49	5.92	6.31	2.85	2.88	2.81	2.98	2.99	2.90
390	8.09	8.51	8.88	1.70	1.81	1.80	1.81	1.89	1.88
400	10.94	11.31	11.64	1.08	1.20	1.23	1.17	1.27	1.29
410	13.84	14.16	14.45	0.74	0.86	0.91	0.81	0.91	0.96
420	16.67	16.96	17.22	0.55	0.66	0.71	0.61	0.71	0.76
430	19.42	19.68	19.92	0.42	0.53	0.59	0.47	0.58	0.63
440	22.09	22.34	22.57	0.35	0.45	0.50	0.39	0.49	0.54
450	24.73	25.00	25.17	0.29	0.38	0.44	0.33	0.42	0.47
460	27.36	27.60	27.78	0.25	0.34	0.39	0.29	0.38	0.43
470	29.92	30.18	30.33	0.21	0.30	0.35	0.24	0.33	0.38
475	31.18	31.42	31.59	0.20	0.29	0.34	0.23	0.31	0.36
480	32.42	32.68	32.83	0.19	0.28	0.33	0.21	0.30	0.35
485	33.68	33.91	34.06	0.18	0.26	0.32	0.21	0.28	0.34
490	34.88	35.14	35.29	0.17	0.25	0.31	0.19	0.27	0.32
495	36.10	36.34	36.49	0.17	0.25	0.30	0.18	0.27	0.32
500	37.31	37.56	37.70	0.16	0.24	0.29	0.17	0.26	0.31
550	49.30	49.59	49.89	0.07	0.16	0.21	0.10	0.18	0.22
600	61.59	61.86	62.44	0.05	0.13	0.18	0.05	0.13	0.18
650	73.70	73.02	72.29	0.03	0.12	0.17	0.03	0.12	0.17
700	80.99	81.53	79.66	0.02	0.12	0.17	0.02	0.10	0.15
750	79.15	77.15	80.64	0.02	0.12	0.17	0.02	0.10	0.16
800	75.83	77.90	76.32	0.04	0.14	0.19	0.01	0.10	0.16
850	77.26	75.20	76.03	0.03	0.14	0.21	0.01	0.11	0.17
900	73.01	73.07	73.77	0.06	0.17	0.24	0.02	0.13	0.19
1000	72.95	71.46	72.59	0.10	0.21	0.28	0.05	0.15	0.22
1100	72.43	72.03	71.92	0.15	0.27	0.34	0.07	0.20	0.26
1200	69.38	70.08	69.43	0.21	0.33	0.40	0.12	0.23	0.31
1300	67.67	67.63	68.91	0.27	0.39	0.46	0.16	0.28	0.36
1400	67.03	67.34	67.50	0.33	0.45	0.54	0.21	0.34	0.42
1500	66.63	67.27	67.57	0.38	0.52	0.60	0.26	0.39	0.47
1600	67.37	68.30	68.84	0.44	0.58	0.68	0.32	0.45	0.53
1700	73.79	74.68	74.79	0.50	0.64	0.73	0.37	0.51	0.59
1800	69.74	69.86	68.48	0.54	0.68	0.78	0.43	0.57	0.64
1900	53.99	54.17	53.83	0.56	0.71	0.82	0.49	0.63	0.71
2000	40.44	40.12	39.62	0.60	0.76	0.87	0.62	0.78	0.90


Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(ns)		
	@-40°C	@+25°C	@+85°C
0.5	2.20	2.08	2.11
1	2.20	2.11	2.12
10	2.13	2.15	2.14
11	2.11	2.14	2.14
12	2.12	2.14	2.14
13	2.11	2.12	2.13
14	2.11	2.11	2.12
15	2.12	2.12	2.13
16	2.10	2.13	2.13
17	2.12	2.13	2.13
18	2.08	2.10	2.11
19	2.10	2.09	2.10
20	2.11	2.10	2.11
25	2.11	2.10	2.12
30	2.11	2.12	2.12
35	2.11	2.11	2.13
40	2.12	2.10	2.11
45	2.10	2.13	2.12
50	2.13	2.11	2.13
60	2.14	2.14	2.15
70	2.12	2.12	2.13
80	2.15	2.15	2.15
90	2.17	2.16	2.17
100	2.18	2.18	2.18
110	2.19	2.19	2.20
120	2.22	2.22	2.21
130	2.26	2.25	2.26
140	2.28	2.30	2.30
145	2.30	2.31	2.30
150	2.32	2.33	2.31
160	2.37	2.35	2.35
170	2.40	2.39	2.39
180	2.44	2.43	2.43
190	2.48	2.49	2.49
200	2.53	2.54	2.55
210	2.60	2.60	2.60
220	2.66	2.67	2.68
230	2.75	2.75	2.74
240	2.83	2.84	2.85
250	2.91	2.94	2.93
255	2.99	2.99	3.00
260	3.03	3.05	3.06
265	3.09	3.09	3.11
270	3.16	3.17	3.18
275	3.22	3.22	3.23
280	3.29	3.31	3.29
285	3.37	3.38	3.39
290	3.45	3.47	3.47
295	3.54	3.56	3.56
300	3.66	3.67	3.68
305	3.74	3.75	3.77
310	3.87	3.90	3.91
315	4.02	4.04	4.08
320	4.21	4.24	4.28
340	5.21	5.24	5.30

Typical Performance Curves



Outline Dimensions



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M
KE1467	.74 (18.80)	.75 (19.05)	.46 (11.68)	1.18 (29.97)	.04 (1.02)	.362 (9.19)	.21 (5.33)	.362 (9.19)	1.00 (25.40)	.37 (9.40)	.18 (4.57)	.11 (2.79)

CASE #.	WT. GRAM
KE1467	24.4

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Note:

1. Case material: Brass
2. Case finish: Gold
3. Cover: Nickel plated.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I