

Coaxial Power Splitter/Combiner

4 Way-0° 50Ω 800 to 1125 MHz

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	2.5W max.*
Power Input (as a combiner)	0.125W max.


*maximum VSWR at output 1.2:1

Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3
PORT 4	4

Outline Drawing



Outline Dimensions (inch mm)

A	B	C	D	E	F	G	H
2.04	.60	.75	.50	.10	.17	.25	.25
51.82	15.24	19.05	12.70	2.54	4.32	6.35	6.35
J	K	L	M	N			wt
.50	.11	1.820	.106	.12			grams
12.70	2.79	46.23	2.69	3.05			60.0

Features

- low insertion loss, 0.6 dB typ.
- high isolation, 20 dB typ.
- rigid unibody construction
- gold plated connectors; nickel plated body
- low cost
- small size
- protected by US patent 6,790,049

Applications

- cellular/ISM
- antenna arrays
- signal distribution
- test bench




Electrical Specifications (T_{AMB}=25°C)

FREQ. RANGE (MHz)	ISOLATION (dB)		INSERTION LOSS (dB) ABOVE 6 dB		PHASE UNBALANCE (Deg.)	AMPLITUDE UNBALANCE (dB)	INPUT VSWR (:1)	OUTPUT VSWR (:1)
f _L -f _H	Typ.	Min.	Typ.	Max.	Max.	Max.	Typ.	Typ.
800-1125	20	15	0.6	1.3	3.0	0.7	1.2	1.2
875-1050	24	18	0.6	1.0	3.0	0.7	1.2	1.2

Typical Performance Data

Freq. (MHz)	Total Loss ¹ (dB)				Amp. Unbal. (dB)	Isolation (dB)			Phase Unbal. (deg.)	VSWR S	VSWR 1	VSWR 2	VSWR 3	VSWR 4
	S-1	S-2	S-3	S-4		1-2	2-3	3-4						
800.00	6.66	6.63	6.46	6.46	0.21	17.74	25.02	17.42	0.75	1.35	1.13	1.14	1.11	1.14
850.00	6.65	6.62	6.43	6.41	0.24	21.03	27.87	20.56	0.94	1.25	1.14	1.16	1.13	1.15
875.00	6.63	6.61	6.41	6.38	0.26	23.27	29.78	22.65	1.05	1.21	1.15	1.17	1.13	1.16
900.00	6.65	6.64	6.42	6.38	0.27	26.35	32.31	25.44	1.16	1.18	1.16	1.18	1.14	1.16
925.00	6.65	6.64	6.42	6.37	0.28	31.09	35.93	29.50	1.25	1.15	1.16	1.19	1.15	1.17
950.00	6.64	6.63	6.40	6.35	0.29	41.92	42.34	37.29	1.36	1.13	1.17	1.20	1.15	1.18
975.00	6.66	6.67	6.43	6.36	0.31	37.73	55.86	44.16	1.48	1.12	1.18	1.20	1.16	1.18
1000.00	6.68	6.70	6.44	6.36	0.33	29.65	40.26	31.78	1.59	1.12	1.18	1.21	1.17	1.19
1025.00	6.67	6.69	6.44	6.35	0.35	25.50	34.70	26.87	1.68	1.12	1.19	1.22	1.17	1.19
1050.00	6.69	6.72	6.45	6.35	0.37	22.72	31.30	23.78	1.79	1.13	1.19	1.22	1.18	1.20
1075.00	6.73	6.77	6.49	6.38	0.39	20.66	28.87	21.54	1.90	1.15	1.20	1.23	1.18	1.21
1100.00	6.73	6.78	6.50	6.37	0.40	18.95	26.93	19.74	1.97	1.16	1.20	1.24	1.19	1.21
1125.00	6.73	6.79	6.50	6.36	0.42	17.53	25.33	18.25	2.08	1.19	1.21	1.24	1.20	1.22

1. Total Loss = Insertion Loss + 6dB splitter loss.



electrical schematic



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. C
M151107
ZX10-4-11
ED-10988/1
AD/RC/CP/AM
151019

ZX10-4-11+
ZX10-4-11



CASE STYLE: GR1026

Connectors	Model
SMA	ZX10-4-11-S(+)

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

4 Way-0° Power Splitter/Combiner

ZX10-4-11

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)				AMP. UNBAL. (dB)	ISOLATION (dB)			PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)				
	S-1	S-2	S-3	S-4		1-2	2-3	3-4			S	1	2	3	4
800.0	6.67	6.69	6.50	6.54	0.19	17.08	23.88	16.91	1.59	800.0	1.38	1.11	1.12	1.09	1.11
815.0	6.66	6.68	6.48	6.52	0.19	17.88	24.49	17.71	1.58	815.0	1.35	1.11	1.13	1.09	1.11
830.0	6.65	6.67	6.47	6.50	0.20	18.75	25.15	18.60	1.56	830.0	1.32	1.12	1.13	1.09	1.11
845.0	6.65	6.67	6.46	6.48	0.21	19.73	25.88	19.58	1.55	845.0	1.28	1.12	1.14	1.09	1.11
860.0	6.64	6.66	6.45	6.47	0.22	20.82	26.70	20.69	1.54	860.0	1.25	1.12	1.14	1.10	1.12
875.0	6.64	6.66	6.44	6.46	0.22	22.08	27.61	21.97	1.51	875.0	1.23	1.13	1.14	1.10	1.12
880.0	6.64	6.66	6.44	6.45	0.22	22.54	27.94	22.43	1.51	880.0	1.22	1.13	1.15	1.10	1.12
885.0	6.64	6.66	6.43	6.45	0.22	23.02	28.28	22.93	1.50	885.0	1.21	1.13	1.15	1.10	1.12
890.0	6.64	6.66	6.43	6.45	0.23	23.54	28.63	23.45	1.49	890.0	1.20	1.13	1.15	1.10	1.12
895.0	6.63	6.66	6.43	6.44	0.23	24.09	29.00	24.01	1.48	895.0	1.19	1.13	1.15	1.10	1.12
900.0	6.64	6.66	6.43	6.44	0.23	24.68	29.38	24.61	1.48	900.0	1.18	1.13	1.15	1.10	1.12
905.0	6.63	6.66	6.43	6.44	0.23	25.31	29.79	25.25	1.48	905.0	1.18	1.13	1.15	1.10	1.12
910.0	6.63	6.66	6.43	6.43	0.24	25.98	30.22	25.94	1.48	910.0	1.17	1.13	1.15	1.10	1.12
915.0	6.64	6.66	6.43	6.43	0.23	26.72	30.67	26.69	1.47	915.0	1.16	1.13	1.15	1.10	1.12
920.0	6.64	6.66	6.42	6.43	0.24	27.52	31.16	27.50	1.47	920.0	1.15	1.14	1.16	1.10	1.12
925.0	6.64	6.66	6.43	6.43	0.24	28.41	31.67	28.41	1.45	925.0	1.15	1.14	1.16	1.10	1.12
930.0	6.64	6.67	6.42	6.43	0.24	29.40	32.23	29.42	1.46	930.0	1.14	1.14	1.16	1.10	1.12
935.0	6.64	6.67	6.42	6.42	0.24	30.50	32.82	30.54	1.45	935.0	1.13	1.14	1.16	1.10	1.12
940.0	6.64	6.67	6.43	6.42	0.25	31.77	33.46	31.86	1.44	940.0	1.12	1.14	1.16	1.10	1.12
945.0	6.64	6.67	6.42	6.42	0.25	33.24	34.15	33.38	1.43	945.0	1.12	1.14	1.16	1.10	1.13
950.0	6.64	6.67	6.42	6.42	0.25	35.03	34.89	35.23	1.44	950.0	1.11	1.14	1.17	1.11	1.13
960.0	6.64	6.68	6.43	6.42	0.26	40.28	36.63	40.77	1.45	960.0	1.10	1.14	1.17	1.11	1.13
970.0	6.64	6.68	6.43	6.42	0.27	53.55	38.84	55.96	1.43	970.0	1.09	1.14	1.17	1.11	1.13
980.0	6.65	6.69	6.43	6.42	0.27	43.55	41.82	42.66	1.43	980.0	1.08	1.15	1.17	1.11	1.12
990.0	6.65	6.70	6.43	6.41	0.28	36.72	46.22	36.23	1.43	990.0	1.07	1.15	1.17	1.11	1.13
1000.0	6.65	6.71	6.43	6.42	0.29	32.93	53.24	32.57	1.44	1000.0	1.06	1.15	1.17	1.11	1.13
1010.0	6.65	6.71	6.44	6.42	0.29	30.31	50.88	30.03	1.44	1010.0	1.05	1.15	1.18	1.11	1.13
1020.0	6.66	6.72	6.44	6.42	0.30	28.31	44.52	28.06	1.43	1020.0	1.05	1.15	1.18	1.11	1.13
1030.0	6.66	6.73	6.45	6.42	0.31	26.69	40.68	26.47	1.43	1030.0	1.04	1.15	1.18	1.11	1.13
1040.0	6.67	6.74	6.45	6.42	0.31	25.32	37.95	25.13	1.43	1040.0	1.04	1.15	1.19	1.11	1.13
1050.0	6.67	6.74	6.46	6.43	0.32	24.14	35.88	23.97	1.42	1050.0	1.04	1.16	1.19	1.11	1.13
1056.0	6.67	6.75	6.46	6.43	0.32	23.50	34.84	23.34	1.44	1056.0	1.04	1.16	1.19	1.11	1.13
1062.0	6.68	6.76	6.47	6.43	0.32	22.91	33.91	22.76	1.42	1062.0	1.04	1.16	1.19	1.11	1.13
1068.0	6.68	6.76	6.47	6.43	0.33	22.36	33.05	22.22	1.44	1068.0	1.05	1.16	1.19	1.11	1.13
1074.0	6.68	6.77	6.48	6.43	0.33	21.84	32.28	21.70	1.42	1074.0	1.05	1.16	1.19	1.12	1.13
1080.0	6.68	6.77	6.48	6.44	0.33	21.35	31.56	21.22	1.41	1080.0	1.05	1.16	1.19	1.12	1.13
1089.0	6.69	6.78	6.49	6.44	0.34	20.67	30.58	20.55	1.42	1089.0	1.06	1.16	1.19	1.12	1.14
1098.0	6.69	6.79	6.49	6.44	0.34	20.04	29.70	19.93	1.43	1098.0	1.06	1.16	1.20	1.12	1.14
1107.0	6.70	6.80	6.50	6.45	0.35	19.46	28.90	19.36	1.44	1107.0	1.07	1.17	1.20	1.12	1.14
1116.0	6.70	6.81	6.51	6.45	0.35	18.91	28.16	18.82	1.44	1116.0	1.07	1.17	1.20	1.12	1.14
1125.0	6.71	6.81	6.52	6.46	0.36	18.40	27.48	18.31	1.42	1125.0	1.08	1.17	1.21	1.12	1.15

¹ Total Loss = Insertion Loss + 6dB Splitter Loss

REV. X2
ZX10-4-11
100627
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



4 Way-0° Power Splitter/Combiner

ZX10-4-11

Typical Performance Curves




REV. X2
ZX10-4-11
100627
Page 1 of 1



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	WT. GRAM
GR1026	2.04 (51.82)	.60 (15.24)	.75 (19.05)	.50 (12.70)	.10 (2.54)	.17 (4.32)	.25 (6.35)	.25 (6.35)	.50 (12.70)	.11 (2.79)	1.820 (46.23)	.106 (2.69)	.12 (3.05)	60.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$.

Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Notes:

1. Case material: Brass.
2. Case finish: Nickel plate.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I