

ZHL-100W-52-S+, ZHL-100W-52X-S+

AN-60-096

The model ZHL-100W-52X+ is a high power (up to 100W) connectorized wide band amplifier. It was redesigned because of EOL of the output transistor. Case style BT1165 is not changed.

## COMPARISON PERFORMANCE TABLES: $T_{AMB}=25^{\circ}C$

FREQUENCY (MHz)	GAIN (dB)		DIRECTIVITY (dB)		VSWR (:1)			
	24 V		24 V		IN		OUT	
	NEW	OLD	NEW	OLD	NEW	OLD	NEW	OLD
50	52.57	49.67	32.85	15.37	1.50	1.37	1.93	1.43
100	52.74	49.92	32.83	15.38	1.17	1.29	1.92	1.76
150	52.49	50.03	32.69	16.57	1.12	1.40	1.77	2.12
200	52.19	49.85	36.43	21.66	1.37	1.56	1.57	2.15
250	52.32	49.51	37.30	19.22	1.55	1.59	1.44	1.95
300	52.82	49.16	39.05	22.96	1.72	1.45	1.37	2.18
350	53.35	49.25	36.58	20.65	1.89	1.27	1.43	2.85
400	53.54	49.85	38.35	21.22	2.12	1.24	1.62	4.09
450	53.21	50.13	42.19	19.82	2.25	1.60	2.59	3.92
500	52.88	49.78	42.22	19.50	2.07	1.70	3.51	2.83

Table 1 GAIN, DIRECTIVITY, VSWR vs FREQUENCY


- a. Suitability within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.

FREQUENCY (MHz)	NOISE FIGURE (dB)		Pout at 1 dB COMPR. (dBm) 24 V		Pout at 3 dB COMPR. (dBm) 24 V		OIP3 (dBm) 24 V	
	24 V		24 V		24 V		24 V	
	NEW	OLD	NEW	OLD	NEW	OLD	NEW	OLD
50	4.31	4.58	48.11	48.28	49.39	48.87	60.14	61.24
100	4.03	4.10	48.46	49.07	49.42	49.72	59.75	61.94
150	4.05	4.11	49.16	49.18	49.90	49.85	60.53	60.85
200	4.19	4.01	49.36	48.65	49.97	49.55	61.26	59.28
250	4.44	4.12	49.22	47.92	49.79	48.62	60.54	57.44
300	4.66	4.28	48.70	47.66	49.50	48.58	60.44	56.73
350	4.86	4.29	48.33	47.58	49.30	48.56	59.69	56.38
400	4.98	4.39	48.21	47.13	49.40	48.15	58.94	56.26
450	5.05	4.41	47.69	47.22	49.02	48.35	58.46	56.74
500	5.13	4.50	47.72	47.61	49.15	48.45	57.83	56.81

Table 2 NOISE FIGURE, OUTPUT POWER at COMPRESSION, OIP3 vs FREQUENCY


- a. Suitability within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.

COMPARISON PERFORMANCE GRAPHS:  $T_{AMB}=25^{\circ}C$




Graph 1 GAIN vs FREQUENCY

- a. Suitability within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.




Graph 2 DIRECTIVITY vs FREQUENCY

- a. Suitability within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.




Graph 3 VSWR IN vs FREQUENCY

- a. Suitability within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.




Graph 4 VSWR OUT vs FREQUENCY

- a. Suitability within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.




Graph 5 NOISE FIGURE vs FREQUENCY

- a. Suitability within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.




Graph 6 OUTPUT POWER at 1 dB COMPRESSION vs FREQUENCY

- a. Suitability within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.



Graph 7 OUTPUT POWER at 3 dB COMPRESSION vs FREQUENCY

- a. Suitability within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.



Graph 8 OIP3 vs FREQUENCY

## CONCLUSION

1. The performance of the redesign model is slightly different from the performance of the original model:
  - Gain is 2 dB higher or 52 dB typ.
  - P1dB and P3dB are 0.5 dB higher
  - OIP3 is about 1 dB higher.
2. The new design may replace the original catalog model.

- a. Suitability within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.

## IMPORTANT NOTICE

© 2015 Mini-Circuits

This document is provided as an accommodation to Mini-Circuits customers in connection with Mini-Circuits parts only. In that regard, this document is for informational and guideline purposes only. Mini-Circuits assumes no responsibility for errors or omissions in this document or for any information contained herein.

Mini-Circuits may change this document or the Mini-Circuits parts referenced herein (collectively, the "Materials") from time to time, without notice. Mini-Circuits makes no commitment to update or correct any of the Materials, and Mini-Circuits shall have no responsibility whatsoever on account of any updates or corrections to the Materials or Mini-Circuits' failure to do so.

Mini-Circuits customers are solely responsible for the products, systems, and applications in which Mini-Circuits parts are incorporated or used. In that regard, customers are responsible for consulting with their own engineers and other appropriate professionals who are familiar with the specific products and systems into which Mini-Circuits' parts are to be incorporated or used so that the proper selection, installation/integration, use and safeguards are made. Accordingly, Mini-Circuits assumes no liability therefor.

In addition, your use of this document and the information contained herein is subject to Mini-Circuits' standard terms of use, which are available at Mini-Circuits' website at [www.minicircuits.com/homepage/terms\\_of\\_use.html](http://www.minicircuits.com/homepage/terms_of_use.html).

Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation: (i) by Mini-Circuits of such third-party's products, services, processes, or other information; or (ii) by any such third-party of Mini-Circuits or its products, services, processes, or other information.

- a. Suitability within a particular system must be determined by and is solely the responsibility of the customer based on, among other things, electrical performance criteria, stimulus conditions, application, compatibility with other components and environmental conditions and stresses.