

Coaxial Amplifier

ZX60-ED12843/2

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : GC957

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	.5		4000	MHz
Gain		19.4		dB
Output Power @ 1dB Compression		17.3		dBm
Noise Figure		5.4		dB
IP3		33		dBm
VSWR	IN	1.20		(:1)
	OUT	2.00		(:1)
DC Power	Voltage	5		V
	Current		110	mA

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Input Power	13dBm

High Power Amplifier

ZX60-ED12843/2







Typical Performance Data

FREQUENCY (MHz)	GAIN (dB) 24V	DIRECTIVITY (dB) 24V	VSWR IN (:1) 24V	VSWR OUT (:1) 24V	Pout at 1dB Comp. (dBm) 24V	FREQUENCY (MHz)	NOISE FIGURE (dB) 24V	Output IP3 (dBm) 24V
0.5	22.79	9.50	1.22	1.52	17.42	10.0	5.45	32.33
1.0	23.01	8.94	1.13	1.27	17.73	50.0	5.36	32.27
10.0	23.25	8.24	1.08	1.04	18.10	100.0	5.41	32.09
100.0	23.06	8.45	1.08	1.09	17.76	200.0	5.35	31.68
300.0	23.03	8.06	1.16	1.13	17.68	300.0	5.53	31.95
500.0	23.11	7.18	1.21	1.36	18.32	400.0	5.56	33.11
700.0	22.62	7.18	1.23	1.60	18.40	500.0	5.57	33.27
800.0	22.32	7.27	1.23	1.71	18.39	600.0	5.52	33.13
805.0	22.31	7.25	1.23	1.72	18.39	700.0	5.47	33.00
1000.0	21.69	7.39	1.24	1.90	18.37	800.0	5.43	32.71
1200.0	21.04	7.52	1.25	2.06	18.48	1000.0	5.42	32.51
1400.0	20.40	7.67	1.26	2.19	18.44	1100.0	5.43	32.46
1600.0	19.79	7.77	1.26	2.28	18.52	1200.0	5.41	32.44
1800.0	19.20	7.87	1.27	2.36	18.55	1300.0	5.41	32.55
2000.0	18.66	7.95	1.27	2.41	18.59	1400.0	5.42	32.63
2200.0	18.15	7.99	1.27	2.44	18.70	1500.0	5.39	31.84
2400.0	17.66	8.05	1.28	2.45	18.50	1600.0	5.40	32.55
2600.0	17.20	8.11	1.27	2.46	18.67	1700.0	5.40	31.75
2800.0	16.75	8.22	1.27	2.45	18.81	1800.0	5.44	32.37
3000.0	16.29	8.35	1.26	2.39	18.98	2000.0	5.47	32.07
3200.0	15.88	8.49	1.26	2.44	18.92	2200.0	5.50	32.04
3400.0	15.47	8.62	1.25	2.45	18.55	2400.0	5.56	32.38
3600.0	15.07	8.84	1.25	2.48	18.12	2600.0	5.56	31.92
3800.0	14.69	9.03	1.25	2.53	17.80	2800.0	5.62	31.73
4000.0	14.35	9.14	1.28	2.63	17.45	3000.0	5.70	31.24

High Power Amplifier

Typical Performance Curves

ZX60-ED12843/2




Case Style

Outline Dimensions

GC

GC957



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N
GC957	.74 (18.80)	.75 (19.15)	.46 (11.61)	1.18 (30.07)	.04 (1.02)	.17 (4.32)	.45 (11.40)	.59 (14.86)	.33 (8.31)	.21 (5.44)	.22 (5.59)	.14 (3.56)	1.00 (25.4)

CASE #.	P	Q	R	WT GRAMS
GC957	.37 (9.40)	.18 (4.57)	.106 (2.69)	23.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$
Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Note:

1. Case material: Brass
2. Case finish: Nickel plate

Mini-Circuits®

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Case Temperature	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Stabilization Bake	(non-operating) 125°C, 24 hours	- - -
Burn-in at Elevated Temp.	(DC on) 160 hours at 85° C	MIL-STD-202, Method 108
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, except 100°C