



CASE STYLE: GC957

The Big Deal

- Industry Leading High IP3, 46 dBm typ.
- Output Power at 1 dB Compression, +23 dBm
- Wideband, 500 to 1200 MHz

Product Overview

The ZX60-H122+ (RoHS compliant) uses Mini-Circuits' high dynamic MMIC technology and optimization circuits to provide industry leading linearity over a focused frequency range. Housed in a rugged, cost effective unibody chassis, this amplifier supports a wide variety of applications requiring moderate power output, low distortion and 50 ohm matched input/output ports.

Key Features

Feature	Advantages
Extreme High IP3 vs. Current 46.2 dBm typical at 900 MHz versus DC Power consumption of 145mA	The ZX60-H122+ offers industry leading IP3 performance relative to power consumption. The combination of the design and E-PHEMT provides enhanced linearity as evidence in the IP3. This feature makes this amplifier ideal for use in: • driver amplifiers for complex waveform upconverter paths • drivers in linearized transmit systems • secondary amplifiers in ultra high dynamic range receivers
Optimized Frequency Range	Covering primary wireless communication bands: cellular and LTE
Low Noise Figure, 2.5 dB typ.	A unique feature of the ZX60-H122+ is the combination of low noise figure performance with the high dynamic range, differentiating this amplifier from the competition.
Unconditionally Stable	Capable to operate to a wide range of source and load impedances.
Very Small Size, 0.75" x 0.75"	The unique unibody size and construction enable the ZX60-H122+ to be used in extremely compact connected applications.

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Ultra High IP3

Wideband Amplifier

ZX60-H122+

50Ω

500 to 1200 MHz

Features

- Ultra High IP3, +46.2 dBm typ. at 0.9 GHz
- Gain, 14.9 dB typ. at 0.9 GHz
- High Pout, P1dB, +22.8 dBm typ. at 0.9 GHz
- Low noise figure, 2.5 dB typ. at 0.9 GHz

Applications

- LTE
- Buffer amplifier
- Test equipment
- High dynamic range lab driver amps



Generic photo used for illustration purposes only

CASE STYLE: GC957

Connectors	Model
SMA	ZX60-H122+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C and 5.5V unless noted

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency Range		0.5		1.2	GHz
Gain	0.5		15.6		dB
	0.7		15.3		
	0.9	13.4	14.9	16.4	
	1.2		14.2		
Input Return Loss	0.5		18.4		dB
	0.7		16.9		
	0.9		14.4		
	1.2		11.2		
Output Return Loss	0.5		16.6		dB
	0.7		13.6		
	0.9		11.4		
	1.2		8.9		
Output IP3	0.5		41.9		dBm
	0.7		45.2		
	0.9	41.0	46.2		
	1.2		40.6		
Output Power @ 1 dB compression	0.5		22.3		dBm
	0.7		22.4		
	0.9		22.8		
	1.2		23.0		
Noise Figure	0.5		2.3		dB
	0.7		2.4		
	0.9		2.5		
	1.2		2.5		
Directivity (Isolation-Gain)	0.5 - 1.2		6		dB
DC Voltage		5.5	—	7.0	V
DC Current		110	145	180	mA

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com


REV. B
ECO-000670
ED-14675
ZX60-H122+
CW/TH/CP
191118
Page 2 of 4

Maximum Ratings

Parameter	Ratings
Operating Temperature	-40°C to 85°C Case
Storage Temperature	-55°C to 100°C
DC Voltage	7 V
Input RF Power (no damage)	24 dBm
Power Consumption	1.25 W

Permanent damage may occur if any of these limits are exceeded.

Outline Drawing



NOTE: When soldering the DC connections, caution must be used to avoid overheating the DC terminal. See Application Note. [AN-40-010](#).

Outline Dimensions (inch/mm)







A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	wt
.74	.75	.46	1.18	.04	.17	.45	.59	.33	.21	.22	.14	1.00	.37	.18	.106	grams
18.80	19.1	11.68	30.0	1.02	4.32	11.4	14.99	8.38	5.33	5.59	3.56	25.40	9.40	4.57	2.69	23.0

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



FREQUENCY (MHz)	GAIN (dB)	DIRECTIVITY (dB)	VSWR (:1)		POUT at 1dB COMPR. (dBm)	NOISE FIGURE (dB)	OUTPUT IP3 (dBm)
			IN	OUT			
500.00	15.58	5.44	1.21	1.34	22.3	2.3	41.9
550.00	15.53	5.45	1.22	1.37	22.0	2.3	41.3
600.00	15.46	5.53	1.23	1.41	22.1	2.4	42.2
650.00	15.39	5.64	1.25	1.46	22.4	2.4	44.2
700.00	15.31	5.74	1.28	1.50	22.4	2.4	45.2
725.00	15.26	5.82	1.29	1.52	22.6	2.4	46.1
750.00	15.20	5.89	1.31	1.54	22.7	2.4	46.5
800.00	15.09	6.03	1.34	1.58	22.8	2.4	46.7
850.00	14.99	6.16	1.38	1.63	22.8	2.5	46.7
900.00	14.91	6.22	1.42	1.68	22.8	2.5	46.2
950.00	14.83	6.31	1.45	1.74	23.2	2.5	42.7
1000.00	14.72	6.43	1.49	1.80	23.3	2.5	41.4
1050.00	14.62	6.54	1.53	1.86	23.3	2.5	42.4
1100.00	14.49	6.70	1.58	1.92	23.3	2.5	41.6
1150.00	14.36	6.85	1.63	1.98	23.1	2.5	40.3
1200.00	14.22	7.02	1.68	2.06	23.0	2.5	40.6



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data

NOTE: Use PDF Bookmarks to view DATA at required conditions

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.50V, Id = 147.39mA @ Temperature = 25degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
200.0	16.12	21.32	13.76	17.75	1.14	0.71	39.59	21.79	2.23
250.0	16.09	21.19	15.84	19.83	1.14	0.71	39.39	21.74	2.25
300.0	16.06	21.24	17.57	20.57	1.15	0.72	40.46	22.12	2.24
350.0	16.00	21.22	18.68	20.05	1.15	0.72	40.49	22.09	2.20
400.0	15.95	21.15	19.32	19.01	1.15	0.71	41.39	22.13	2.28
450.0	15.88	21.22	19.61	17.82	1.16	0.71	41.05	22.13	2.25
500.0	15.79	21.23	19.30	16.62	1.16	0.71	41.83	22.49	2.22
525.0	15.76	21.20	19.29	16.21	1.16	0.71	41.18	22.29	2.27
550.0	15.74	21.19	19.14	15.84	1.16	0.71	41.69	22.12	2.27
575.0	15.70	21.21	18.92	15.38	1.16	0.71	43.58	22.46	2.36
600.0	15.67	21.19	18.61	14.96	1.16	0.70	42.28	22.28	2.36
625.0	15.62	21.22	18.33	14.58	1.17	0.71	42.58	22.37	2.35
650.0	15.58	21.26	18.07	14.22	1.17	0.71	44.22	22.60	2.37
675.0	15.54	21.25	17.78	13.88	1.17	0.70	45.48	22.56	2.32
700.0	15.49	21.26	17.36	13.59	1.17	0.70	45.31	22.60	2.36
725.0	15.43	21.26	17.03	13.29	1.18	0.70	46.76	22.71	2.32
750.0	15.37	21.29	16.62	13.04	1.18	0.71	46.32	22.90	2.29
775.0	15.31	21.30	16.25	12.79	1.18	0.71	49.78	22.79	2.38
800.0	15.26	21.32	15.85	12.52	1.19	0.71	47.71	23.00	2.40
825.0	15.21	21.34	15.49	12.23	1.19	0.71	48.55	22.93	2.32
850.0	15.17	21.37	15.17	11.92	1.19	0.71	47.54	22.98	2.41
875.0	15.13	21.31	14.88	11.64	1.18	0.70	45.16	23.10	2.41
900.0	15.09	21.34	14.57	11.36	1.19	0.70	47.33	23.05	2.42
925.0	15.04	21.33	14.28	11.11	1.18	0.70	44.43	23.20	2.41
950.0	15.00	21.35	14.00	10.88	1.19	0.70	42.69	23.41	2.44
975.0	14.94	21.34	13.73	10.63	1.19	0.69	45.64	23.13	2.42
1000.0	14.88	21.39	13.43	10.43	1.19	0.69	41.92	23.53	2.43
1025.0	14.83	21.39	13.17	10.21	1.19	0.69	42.65	23.56	2.39
1050.0	14.77	21.38	12.90	10.02	1.19	0.69	42.73	23.54	2.40
1075.0	14.71	21.37	12.61	9.83	1.19	0.69	42.98	23.51	2.47
1100.0	14.65	21.41	12.34	9.62	1.19	0.69	41.26	23.49	2.45
1125.0	14.59	21.40	12.05	9.43	1.19	0.68	41.93	23.32	2.41
1150.0	14.52	21.43	11.78	9.25	1.20	0.68	40.42	23.33	2.51
1175.0	14.45	21.43	11.51	9.05	1.20	0.68	41.47	23.27	2.51
1200.0	14.38	21.46	11.22	8.85	1.20	0.68	41.11	23.22	2.54
1300.0	14.07	21.52	10.10	8.10	1.20	0.67	39.62	22.97	2.52
1400.0	13.74	21.70	9.01	7.34	1.21	0.66	39.68	22.63	2.64
1500.0	13.36	21.87	7.97	6.58	1.22	0.65	38.92	22.18	2.59

Wideband Amplifier

ZX60-H122+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.50V, Id = 150.08mA @ Temperature = -45degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
200.0	15.49	20.71	14.79	15.51	1.14	0.69	36.56	21.90	1.85
250.0	15.44	20.60	17.63	16.24	1.15	0.69	36.23	21.86	1.86
300.0	15.41	20.61	20.33	16.53	1.15	0.69	37.47	22.18	1.85
350.0	15.36	20.68	23.04	16.51	1.16	0.69	36.92	22.17	1.85
400.0	15.33	20.63	25.77	16.34	1.16	0.69	37.63	22.20	1.90
450.0	15.28	20.65	27.95	16.05	1.17	0.69	37.51	22.23	1.87
500.0	15.21	20.62	27.95	15.68	1.17	0.69	37.92	22.57	1.90
525.0	15.18	20.64	27.89	15.50	1.17	0.69	37.71	22.44	1.92
550.0	15.18	20.61	27.28	15.48	1.17	0.69	37.55	22.26	1.92
575.0	15.15	20.59	26.57	15.31	1.17	0.69	38.70	22.51	1.91
600.0	15.13	20.61	25.62	15.18	1.17	0.69	38.11	22.35	1.94
625.0	15.10	20.61	24.85	15.01	1.17	0.69	38.44	22.43	1.99
650.0	15.08	20.64	24.12	14.85	1.18	0.69	39.66	22.61	1.97
675.0	15.05	20.62	23.34	14.65	1.18	0.69	39.79	22.58	1.95
700.0	15.02	20.65	22.55	14.51	1.18	0.69	39.80	22.61	2.00
725.0	14.97	20.69	21.94	14.34	1.19	0.70	39.92	22.73	1.98
750.0	14.93	20.67	21.20	14.19	1.19	0.70	41.47	22.88	1.95
775.0	14.88	20.69	20.58	14.07	1.19	0.70	40.93	22.79	2.01
800.0	14.83	20.68	19.87	13.94	1.19	0.70	41.91	22.96	1.98
825.0	14.79	20.72	19.32	13.71	1.20	0.70	41.36	22.91	1.95
850.0	14.76	20.70	18.85	13.47	1.20	0.70	41.97	22.96	2.02
875.0	14.75	20.70	18.38	13.19	1.20	0.70	42.96	23.05	2.04
900.0	14.72	20.68	18.01	12.89	1.19	0.70	42.41	23.02	2.04
925.0	14.69	20.68	17.61	12.63	1.19	0.69	44.10	23.16	1.99
950.0	14.66	20.70	17.23	12.38	1.19	0.69	48.77	23.31	2.01
975.0	14.62	20.67	16.82	12.11	1.19	0.69	43.03	23.13	2.01
1000.0	14.57	20.71	16.39	11.90	1.20	0.69	47.04	23.39	1.98
1025.0	14.54	20.71	15.98	11.66	1.20	0.69	47.29	23.49	1.99
1050.0	14.49	20.71	15.61	11.42	1.20	0.69	45.52	23.45	2.01
1075.0	14.44	20.77	15.21	11.22	1.20	0.69	50.46	23.40	2.02
1100.0	14.39	20.75	14.84	10.96	1.20	0.68	48.37	23.35	1.99
1125.0	14.34	20.76	14.43	10.71	1.20	0.68	49.22	23.21	1.99
1150.0	14.28	20.77	14.08	10.49	1.20	0.68	43.99	23.13	2.00
1175.0	14.22	20.82	13.72	10.25	1.21	0.68	46.59	23.13	2.07
1200.0	14.17	20.86	13.38	9.99	1.21	0.68	45.46	23.07	2.03
1300.0	13.89	20.95	12.01	9.00	1.22	0.67	42.65	22.74	2.15
1400.0	13.56	21.09	10.64	7.97	1.22	0.65	41.62	22.39	2.21
1500.0	13.17	21.33	9.29	6.92	1.23	0.63	40.59	21.93	2.16

Wideband Amplifier

ZX60-H122+

Typical Performance Data

Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)









TEST CONDITIONS: Vd = 5.50V, Id = 148.59mA @ Temperature = 85degC

FREQ	Gain	Isolation	Input Return Loss	Output Return Loss	Stability		IP-3 Output	1dB Comp. Output	Noise Figure
(MHz)	(dB)	(dB)	(dB)	(dB)	K	Measure	(dBm)	(dBm)	(dB)
200.0	16.45	21.64	12.86	19.12	1.14	0.72	41.21	21.66	2.52
250.0	16.43	21.58	14.54	23.25	1.14	0.73	41.31	21.60	2.51
300.0	16.40	21.55	15.64	24.87	1.15	0.73	43.01	22.00	2.48
350.0	16.34	21.51	16.25	22.73	1.15	0.73	42.57	21.97	2.51
400.0	16.28	21.55	16.50	20.26	1.15	0.73	43.44	22.01	2.59
450.0	16.20	21.55	16.52	18.17	1.15	0.72	43.44	22.01	2.56
500.0	16.10	21.59	16.31	16.59	1.16	0.73	45.22	22.33	2.51
525.0	16.06	21.56	16.29	16.01	1.16	0.72	44.80	22.12	2.60
550.0	16.03	21.53	16.17	15.48	1.15	0.72	44.38	21.98	2.54
575.0	15.99	21.52	16.09	14.90	1.15	0.71	48.93	22.36	2.60
600.0	15.94	21.58	15.91	14.38	1.16	0.71	46.68	22.17	2.57
625.0	15.89	21.58	15.74	13.93	1.16	0.71	47.28	22.26	2.65
650.0	15.84	21.61	15.55	13.50	1.16	0.71	48.50	22.50	2.65
675.0	15.79	21.64	15.35	13.11	1.17	0.71	51.34	22.47	2.61
700.0	15.73	21.60	15.08	12.76	1.16	0.71	51.71	22.51	2.68
725.0	15.66	21.65	14.82	12.45	1.17	0.71	46.95	22.63	2.66
750.0	15.59	21.69	14.53	12.14	1.18	0.71	44.47	22.82	2.66
775.0	15.53	21.65	14.25	11.85	1.17	0.71	45.19	22.70	2.71
800.0	15.47	21.70	13.93	11.56	1.18	0.71	43.88	22.91	2.68
825.0	15.42	21.71	13.67	11.27	1.18	0.71	44.28	22.83	2.63
850.0	15.36	21.67	13.40	10.98	1.17	0.70	44.85	22.90	2.71
875.0	15.31	21.68	13.14	10.72	1.18	0.70	42.71	23.02	2.72
900.0	15.26	21.67	12.89	10.45	1.17	0.70	43.18	22.95	2.72
925.0	15.20	21.71	12.66	10.23	1.18	0.70	42.47	23.09	2.69
950.0	15.15	21.71	12.43	10.01	1.18	0.70	41.10	23.28	2.71
975.0	15.08	21.72	12.21	9.78	1.18	0.69	42.90	23.01	2.71
1000.0	15.02	21.71	11.96	9.59	1.18	0.69	40.26	23.39	2.73
1025.0	14.96	21.74	11.75	9.40	1.18	0.69	41.34	23.40	2.68
1050.0	14.90	21.75	11.53	9.22	1.18	0.69	41.02	23.37	2.73
1075.0	14.83	21.75	11.31	9.05	1.18	0.69	41.23	23.33	2.72
1100.0	14.76	21.74	11.10	8.88	1.18	0.68	40.18	23.30	2.67
1125.0	14.69	21.79	10.85	8.69	1.18	0.68	40.62	23.11	2.70
1150.0	14.61	21.76	10.64	8.54	1.18	0.68	39.39	23.12	2.73
1175.0	14.54	21.78	10.41	8.36	1.19	0.68	39.72	23.04	2.82
1200.0	14.47	21.84	10.16	8.20	1.19	0.68	39.90	22.97	2.78
1300.0	14.14	21.94	9.18	7.56	1.20	0.67	38.90	22.69	2.87
1400.0	13.79	22.04	8.20	6.92	1.20	0.66	38.61	22.36	2.97
1500.0	13.42	22.13	7.29	6.30	1.20	0.65	37.96	21.92	2.92

Wideband Amplifier

ZX60-H122+

Typical Performance Curves



Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED

minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 • (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS


REV. X1
ZX60-H122+
2/22/2012
Page 1 of 1

Case Style

Outline Dimensions

GC

GC957



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N
GC957	.74 (18.80)	.75 (19.15)	.46 (11.61)	1.18 (30.07)	.04 (1.02)	.17 (4.32)	.45 (11.40)	.59 (14.86)	.33 (8.31)	.21 (5.44)	.22 (5.59)	.14 (3.56)	1.00 (25.4)

CASE #.	P	Q	R	WT GRAMS
GC957	.37 (9.40)	.18 (4.57)	.106 (2.69)	23.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$
Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Note:

1. Case material: Brass
2. Case finish: Nickel plate

Mini-Circuits®

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Case Temperature	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Stabilization Bake	(non-operating) 125°C, 24 hours	- - -
Burn-in at Elevated Temp.	(DC on) 160 hours at 85° C	MIL-STD-202, Method 108
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, except 100°C