

50Ω 9 to 15 MHz

Operating Temperature -40°C to 85°C

Storage Temperature	-55°C to 100°C
---------------------	----------------

RF Power Input 0.25 W at 25°C

Permanent damage may occur if any of these limits are exceeded.

Features

- High Rejection
- Sharp Insertion Loss roll off
- Shielded case


Applications

- High rejection applications
- Image rejection
- IF signal processing
- Receivers / Transmitters
- Test Lab

SMA Connectors		Model	Case
INPUT	OUTPUT		
FEMALE	FEMALE	ZX75-12-S+	HY1239
MALE	FEMALE	ZX75-12M-S+	HY1238

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Outline Dimensions (inch)

A	B	C	D	E	F	
1.20	.75	.46	1.18	.04	.17	
30.48	19.05	11.68	29.97	1.02	4.32	
G	H	J	K	L	M	wt.
1.00	.50	.35	.18	.106	1.88	grams
25.40	12.70	8.89	4.57	2.69	47.75	35.0


Note:

* M dimension is 2.05 inch (52.07 mm) for HY1238 Case Style.


Bandpass Filter Electrical Specifications (T_{AMB} = 25°C)

CENTER FREQ. (MHz) Fc	PASSBAND (MHz) (Loss < 3.5dB) F1 - F2	STOPBANDS (MHz)				VSWR (:1)		
		Loss > 20dB		Loss > 40dB		Passband		Stopband
		F3	F4	F5	F6	Typ.	Max.	Typ.
12	9 - 15	7.5	18	7	20 - 3000	1.5	2.2	30

Typical Frequency Response





Functional Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
0.3	100.39	1737.18
7.0	53.30	62.05
7.5	36.73	35.46
8.0	14.55	9.74
8.2	5.51	2.37
8.5	3.45	2.36
9.0	1.85	1.22
11.0	1.31	1.40
12.0	1.26	1.37
13.0	1.59	1.77
15.0	2.09	1.75
15.7	4.10	2.81
16.0	6.58	4.66
16.6	15.51	11.77
18.0	37.07	30.49
20.0	60.12	59.91
100.0	94.22	248.17
1000.0	67.12	23.49
3000.0	59.03	6.19



Notes

Notes

A. Features and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Technical specifications and performance data contained in this specification document are based on Mini-Circuits' currently established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MC/Store/Terms.jsp

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.3	100.39	0.01
7.0	53.30	0.28
7.5	36.73	0.49
8.0	14.55	1.79
8.2	5.51	7.81
8.5	3.45	7.87
9.0	1.85	20.08
11.0	1.31	15.62
12.0	1.26	16.04
13.0	1.59	11.12
15.0	2.09	11.31
15.7	4.10	6.46
16.0	6.58	3.79
16.6	15.51	1.48
18.0	37.07	0.57
20.0	60.12	0.29
100.0	94.22	0.07
1000.0	67.12	0.74
3000.0	59.03	2.83

REV. X1
ZX75-12+
080928
Page 1 of 1





IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



Patent Pending The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Typical Performance Curves



REV. X1

ZX75-12+

080928

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Case Style

HY

Outline Dimensions

HY1239



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N	WT GRAMS
HY1239	1.20 (30.48)	.75 (19.05)	.46 (11.68)	1.18 (29.97)	.04 (1.02)	.17 (4.32)	1.00 (25.40)	.50 (12.70)	.35 (8.89)	.18 (4.57)	.21 (5.28)	1.88 (47.75)	.106 (2.69)	35.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$
Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Note:

1. Case material: Brass
2. Case finish: Nickel plate



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I