


Outline Dimensions



| CASE# | A | B | C | D | E | F | G | H | J | K | L | M | N | WT. GRAM |
|--------|-----------------|----------------|----------------|----------------|---------------|---------------|---------------|---------------|----------------|---------------|-----------------|----------------|---------------|----------|
| GW1052 | 1.04 (26.42) | .60 (15.24) | .75 (19.05) | .50 (12.70) | .10 (2.54) | .17 (4.32) | .25 (6.35) | .25 (6.35) | .50 (12.70) | .11 (2.79) | .820 (20.83) | .106 (2.69) | .12 (3.05) | 21.0 |

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$.
Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Notes:

1. Case material: Brass.
2. Case finish: Nickel plate.