


Outline Dimensions

HF1485-1



CASE #	A	B	C	D	E	F	G	H	J	K	L	M
HF1485-1	.44 (11.18)	.74 (18.80)	.19 (4.83)	.200 (5.08)	.07 (1.78)	.140 (3.56)	.110 (2.79)	.060 (1.52)	.200 (5.08)	.480 (12.19)	.100 (2.54)	.065 (1.65)

CASE #	N	WT. GRAMS
HF1485-1	.080 (2.03)	3.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm 0.015''$; 3 Pl. $\pm 0.01''$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
 - For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RFIIF MICROWAVE COMPONENTS