


Outline Dimensions

JC0603C-3



Suggested Layout,
Tolerance to be within ± 0.002

CASE #	A	B	C	D	E	F	G	H	J	K	L
JC0603C-3	.063 (1.60)	.032 (.80)	.024 (.60)	.026 (.65)	.012 (.30)	.012 (.30)	.006 (.15)	.087 (2.20)	.055 (1.40)	.012 (.30)	.020 (.50)

CASE #	M*	N	P	Q	WT. GRAMS
JC0603C-3	.012 (.30)	.047 (1.20)	.020 (.50)	.016 (.40)	.005

Dimensions are in inches (mm). Tolerances: 3 Pl. $\pm .004$

Notes:

- Open style, ceramic base.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
- Line width should be designed to match 50 OHMS characteristic impedance, depending on PCB material & thickness.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS