



## Outline Dimensions

JC0603C-4



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAMS
JC0603C-4	.063 (1.60)	.032 (0.80)	.022 (0.55)	.012 (0.30)	.008 (0.20)	.006 (0.15)	.008 (0.20)	.020 (0.50)	.020 (0.50)	.010 (0.25)	.022 (0.55)	.053 (1.35)	.005

Dimensions are in inches (mm). Tolerances: 3 Pl.  $\pm .004$

### Notes:

- Open style, ceramic base.
- Termination finish:  
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
- Line width should be designed to match 50 OHMS characteristic impedance, depending on PCB material & thickness.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS