

# Coaxial-Ceramic Resonator Filters and Multiplexers

50Ω

DC to 6 GHz

## The Big Deal

- Low insertion loss with excellent power handling
- Passbands up to 6 GHz
- Fractional bandwidth from <1 to 25%
- Excellent temperature stability
- Rugged construction to handle demanding environmental conditions



## Product Overview

Mini-Circuits' *Coaxial-Ceramic Resonator filters* offer low insertion loss in very small form factors, using ceramic material with high dielectric constant and superior Q factor. Bandpass and bandstop filters, diplexer and multiplexer designs can be constructed using this technology. Low insertion loss combined with excellent power handling makes these filters well suited for transmitter and receiver signal chains. Advanced filter design and construction can achieve stopband width greater than 3x the center frequency.

All our coaxial-ceramic resonator filters are built with rugged construction, qualified to withstand multiple demanding reflow cycles. Custom integrated assembly with LNA greatly simplifying system integration. They can be realized in small form factors with high-quality, precise machining for applications where size is critical. Excellent repeatability across units is achieved through precise tuning and process control.

## Key Features

| Feature                  | Advantages                                                                                                                                                                            |
|--------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Low insertion loss       | Low signal loss results in better SNR in signal chain                                                                                                                                 |
| Fast roll-off            | Higher selectivity results in better adjacent channel rejection and dynamic range                                                                                                     |
| Wide stop band           | Wide spur-free stopband results in better receiver sensitivity                                                                                                                        |
| Excellent power handling | Well suited for transmitter applications                                                                                                                                              |
| Rugged Construction      | These filter assemblies have been qualified over a wide range of thermal, mechanical and environmental conditions including withstanding the stress of extensive solder reflow cycles |
| Small Size               | Very well suited for high performance applications where size is a constraint.                                                                                                        |
| Temperature stability    | Very minimal change in electrical performance across temperature makes these filters suitable for a wide range of operating conditions.                                               |

### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Bandpass Filter

50Ω 790 to 890 MHz

**ZX75BP-840-S+**



Generic photo used for illustration purposes only

CASE STYLE: HY1238

| Connectors | Model         |
|------------|---------------|
| SMA-MF     | ZX75BP-840-S+ |


## Features

- Low insertion loss
- High selectivity
- High power handling
- Connectorized package


## Applications

- Traffic collision avoidance system (TCAS)
- Aeronautical radio navigation
- Fixed satellite
- Radio astronomy
- Radar and navigation system

## Functional Schematic



## Typical Frequency Response



## Electrical Specifications at 25°C

| Parameter        | F#               | Frequency (MHz) | Min. | Typ. | Max. | Unit |
|------------------|------------------|-----------------|------|------|------|------|
| Pass Band        | Center Frequency | -               | -    | 840  | -    | MHz  |
|                  | Insertion Loss   | F1-F2           | -    | 1.0  | 2    | dB   |
|                  | VSWR             | F1-F2           | -    | 1.3  | -    | :1   |
| Stop Band, Lower | Insertion Loss   | DC-F3           | 20   | 30   | -    | dB   |
|                  | VSWR             | DC-F3           | -    | 20   | -    | :1   |
| Stop Band, Upper | Insertion Loss   | F4-F5           | 20   | 30   | -    | dB   |
|                  | VSWR             | F4-F5           | -    | 20   | -    | :1   |

## Maximum Ratings

|                       |                |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C  |
| Storage Temperature   | -55°C to 100°C |
| RF Power Input*       | 5 W max.       |





\* Passband rating, derate linearly to 3.5W at 85°C ambient.  
Permanent damage may occur if any of these limits are exceeded.

## Typical Performance Data at 25°C

| Frequency (MHz) | Insertion Loss (dB) | VSWR (:1) | Frequency (MHz) | Group Delay (nsec) |
|-----------------|---------------------|-----------|-----------------|--------------------|
| 1               | 97.61               | 4229.18   | 790             | 6.64               |
| 500             | 55.57               | 106.11    | 795             | 6.34               |
| 665             | 34.65               | 72.01     | 800             | 6.11               |
| 677             | 30.86               | 66.79     | 805             | 5.92               |
| 707             | 20.78               | 46.78     | 810             | 5.76               |
| 732             | 11.20               | 18.81     | 815             | 5.61               |
| 755             | 3.10                | 3.48      | 820             | 5.48               |
| 785             | 0.83                | 1.05      | 825             | 5.37               |
| 790             | 0.80                | 1.04      | 830             | 5.28               |
| 840             | 0.71                | 1.20      | 835             | 5.21               |
| 890             | 0.68                | 1.06      | 840             | 5.14               |
| 900             | 0.71                | 1.09      | 845             | 5.10               |
| 940             | 3.00                | 3.85      | 850             | 5.08               |
| 970             | 9.89                | 18.08     | 855             | 5.07               |
| 990             | 14.87               | 34.88     | 860             | 5.06               |
| 1014            | 20.34               | 52.32     | 865             | 5.07               |
| 1065            | 30.76               | 70.19     | 870             | 5.09               |
| 1070            | 31.77               | 70.60     | 875             | 5.11               |
| 1400            | 43.17               | 86.94     | 880             | 5.15               |
| 1650            | 45.40               | 86.82     | 890             | 5.29               |

## +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



## Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)




[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B  
ECO-004071  
ZX75BP-840-S+  
EDU2756  
URJ  
201123  
Page 2 of 3

Coaxial Connections

|        |            |
|--------|------------|
| INPUT  | SMA-MALE   |
| OUTPUT | SMA-FEMALE |

Outline Drawing



Outline Dimensions ( <sup>inch</sup>/<sub>mm</sub> )

|       |       |       |       |       |      |       |
|-------|-------|-------|-------|-------|------|-------|
| A     | B     | C     | D     | E     | F    | G     |
| 1.20  | .75   | .46   | 1.18  | .04   | .17  | 1.00  |
| 30.48 | 19.05 | 11.68 | 29.97 | 1.02  | 4.32 | 25.40 |
| H     | J     | K     | L     | M     | N    | Wt.   |
| .50   | .35   | .18   | .21   | 2.05  | .106 | grams |
| 12.70 | 8.89  | 4.57  | 5.28  | 52.07 | 2.69 | 35.0  |

Note: Please refer to case style drawing for details

Notes  
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)







## Typical Performance Data


| FREQ. | INSERTION LOSS |        |        | INPUT RETURN LOSS |        |        | OUTPUT RETURN LOSS |        |        |
|-------|----------------|--------|--------|-------------------|--------|--------|--------------------|--------|--------|
| (MHz) | (dB)           |        |        | (dB)              |        |        | (dB)               |        |        |
|       | @-40°C         | @+25°C | @+85°C | @-40°C            | @+25°C | @+85°C | @-40°C             | @+25°C | @+85°C |
| 1     | 123.09         | 97.61  | 102.00 | 0.01              | 0.00   | 0.01   | 0.01               | 0.01   | 0.01   |
| 10    | 99.62          | 117.62 | 100.54 | 0.00              | 0.00   | 0.00   | 0.00               | 0.01   | 0.01   |
| 50    | 106.09         | 110.49 | 94.67  | 0.01              | 0.01   | 0.01   | 0.02               | 0.03   | 0.03   |
| 100   | 82.99          | 84.54  | 84.31  | 0.00              | 0.02   | 0.02   | 0.04               | 0.06   | 0.07   |
| 150   | 74.29          | 74.72  | 74.47  | 0.01              | 0.03   | 0.03   | 0.08               | 0.12   | 0.14   |
| 200   | 68.55          | 68.66  | 68.49  | 0.02              | 0.05   | 0.05   | 0.16               | 0.20   | 0.22   |
| 225   | 65.86          | 66.13  | 66.08  | 0.03              | 0.06   | 0.06   | 0.20               | 0.24   | 0.27   |
| 250   | 63.86          | 64.23  | 64.24  | 0.04              | 0.07   | 0.07   | 0.24               | 0.28   | 0.31   |
| 275   | 62.51          | 62.69  | 62.61  | 0.04              | 0.08   | 0.08   | 0.27               | 0.32   | 0.35   |
| 300   | 61.00          | 61.01  | 61.36  | 0.05              | 0.09   | 0.09   | 0.29               | 0.35   | 0.38   |
| 325   | 59.74          | 59.83  | 60.10  | 0.06              | 0.10   | 0.10   | 0.32               | 0.38   | 0.42   |
| 350   | 58.62          | 58.75  | 58.86  | 0.07              | 0.11   | 0.11   | 0.35               | 0.42   | 0.46   |
| 375   | 57.81          | 57.90  | 58.00  | 0.07              | 0.12   | 0.13   | 0.36               | 0.44   | 0.48   |
| 400   | 57.06          | 57.01  | 57.13  | 0.08              | 0.13   | 0.14   | 0.38               | 0.46   | 0.51   |
| 500   | 55.55          | 55.57  | 55.66  | 0.11              | 0.16   | 0.18   | 0.42               | 0.51   | 0.56   |
| 600   | 61.03          | 60.66  | 59.21  | 0.13              | 0.19   | 0.21   | 0.41               | 0.51   | 0.57   |
| 665   | 34.79          | 34.65  | 34.05  | 0.17              | 0.24   | 0.26   | 0.39               | 0.50   | 0.55   |
| 680   | 30.03          | 29.90  | 29.29  | 0.19              | 0.27   | 0.29   | 0.39               | 0.50   | 0.55   |
| 708   | 20.57          | 20.42  | 19.75  | 0.28              | 0.38   | 0.42   | 0.44               | 0.56   | 0.63   |
| 730   | 12.14          | 12.00  | 11.29  | 0.67              | 0.83   | 0.96   | 0.80               | 0.97   | 1.11   |
| 740   | 8.10           | 8.01   | 7.34   | 1.34              | 1.56   | 1.86   | 1.47               | 1.69   | 1.98   |
| 750   | 4.45           | 4.46   | 3.96   | 3.07              | 3.43   | 4.12   | 3.23               | 3.57   | 4.21   |
| 755   | 3.03           | 3.10   | 2.74   | 4.70              | 5.14   | 6.15   | 4.91               | 5.32   | 6.23   |
| 760   | 2.00           | 2.12   | 1.91   | 7.04              | 7.58   | 9.01   | 7.35               | 7.83   | 9.06   |
| 790   | 0.63           | 0.80   | 0.86   | 33.90             | 34.04  | 27.79  | 31.35              | 30.17  | 23.68  |
| 800   | 0.59           | 0.75   | 0.82   | 38.05             | 35.66  | 26.47  | 32.25              | 31.17  | 25.00  |
| 840   | 0.57           | 0.71   | 0.77   | 20.45             | 20.92  | 20.89  | 21.41              | 22.14  | 22.90  |
| 860   | 0.53           | 0.68   | 0.74   | 24.19             | 24.78  | 25.00  | 23.87              | 24.32  | 25.03  |
| 890   | 0.53           | 0.68   | 0.75   | 32.93             | 31.43  | 31.47  | 27.92              | 26.34  | 25.94  |
| 900   | 0.55           | 0.71   | 0.79   | 27.87             | 26.88  | 26.20  | 24.24              | 23.04  | 22.44  |
| 915   | 0.71           | 0.89   | 0.98   | 16.30             | 15.95  | 15.51  | 15.59              | 15.08  | 14.64  |
| 925   | 1.10           | 1.31   | 1.42   | 10.32             | 10.19  | 10.00  | 10.28              | 10.07  | 9.87   |
| 940   | 2.76           | 3.00   | 3.12   | 4.57              | 4.62   | 4.63   | 4.85               | 4.89   | 4.92   |
| 970   | 9.71           | 9.89   | 9.90   | 0.85              | 0.96   | 1.02   | 1.26               | 1.42   | 1.53   |
| 1015  | 20.47          | 20.56  | 20.45  | 0.24              | 0.33   | 0.36   | 0.65               | 0.81   | 0.90   |
| 1070  | 31.73          | 31.77  | 31.62  | 0.17              | 0.25   | 0.27   | 0.55               | 0.71   | 0.80   |
| 1100  | 38.16          | 38.14  | 38.02  | 0.16              | 0.23   | 0.26   | 0.53               | 0.69   | 0.77   |
| 1125  | 44.82          | 44.72  | 44.59  | 0.15              | 0.23   | 0.25   | 0.51               | 0.67   | 0.75   |
| 1150  | 56.74          | 56.17  | 56.13  | 0.15              | 0.22   | 0.25   | 0.50               | 0.66   | 0.74   |
| 1175  | 56.94          | 57.57  | 57.34  | 0.15              | 0.22   | 0.24   | 0.49               | 0.65   | 0.73   |
| 1200  | 49.49          | 49.73  | 49.61  | 0.15              | 0.22   | 0.24   | 0.48               | 0.64   | 0.71   |
| 1225  | 46.56          | 46.75  | 46.65  | 0.14              | 0.21   | 0.24   | 0.48               | 0.63   | 0.70   |
| 1250  | 45.01          | 45.14  | 45.06  | 0.14              | 0.21   | 0.23   | 0.47               | 0.62   | 0.69   |
| 1275  | 44.09          | 44.20  | 44.14  | 0.13              | 0.20   | 0.23   | 0.47               | 0.62   | 0.69   |
| 1300  | 43.53          | 43.63  | 43.56  | 0.13              | 0.20   | 0.22   | 0.47               | 0.62   | 0.68   |
| 1325  | 43.20          | 43.31  | 43.27  | 0.13              | 0.20   | 0.22   | 0.48               | 0.61   | 0.67   |
| 1350  | 43.02          | 43.14  | 43.11  | 0.12              | 0.20   | 0.22   | 0.48               | 0.61   | 0.67   |
| 1375  | 43.00          | 43.09  | 43.08  | 0.12              | 0.20   | 0.22   | 0.48               | 0.61   | 0.67   |
| 1400  | 43.05          | 43.17  | 43.16  | 0.13              | 0.20   | 0.22   | 0.49               | 0.62   | 0.67   |
| 1425  | 43.16          | 43.28  | 43.32  | 0.12              | 0.19   | 0.22   | 0.50               | 0.62   | 0.67   |
| 1450  | 43.39          | 43.49  | 43.52  | 0.12              | 0.19   | 0.22   | 0.50               | 0.63   | 0.68   |
| 1475  | 43.64          | 43.76  | 43.81  | 0.12              | 0.19   | 0.22   | 0.51               | 0.63   | 0.68   |
| 1500  | 43.93          | 44.05  | 44.10  | 0.11              | 0.19   | 0.22   | 0.52               | 0.64   | 0.69   |
| 1525  | 44.27          | 44.37  | 44.42  | 0.12              | 0.19   | 0.22   | 0.53               | 0.65   | 0.70   |
| 1550  | 44.61          | 44.73  | 44.74  | 0.12              | 0.20   | 0.23   | 0.55               | 0.66   | 0.71   |
| 1575  | 44.93          | 45.05  | 45.07  | 0.11              | 0.19   | 0.22   | 0.56               | 0.67   | 0.73   |
| 1600  | 45.20          | 45.34  | 45.30  | 0.11              | 0.19   | 0.23   | 0.58               | 0.69   | 0.74   |
| 1625  | 45.32          | 45.45  | 45.42  | 0.11              | 0.20   | 0.23   | 0.59               | 0.71   | 0.76   |
| 1640  | 45.33          | 45.44  | 45.37  | 0.11              | 0.20   | 0.23   | 0.61               | 0.72   | 0.78   |
| 1650  | 45.29          | 45.40  | 45.36  | 0.11              | 0.20   | 0.24   | 0.62               | 0.73   | 0.79   |

## Typical Performance Data

| FREQ.  | GROUP DELAY |        |        |
|--------|-------------|--------|--------|
| (MHz)  | (nsec)      |        |        |
|        | @-40°C      | @+25°C | @+85°C |
| 790.00 | 6.70        | 6.64   | 6.48   |
| 792.00 | 6.57        | 6.51   | 6.36   |
| 794.00 | 6.45        | 6.40   | 6.26   |
| 796.00 | 6.34        | 6.29   | 6.17   |
| 798.00 | 6.25        | 6.20   | 6.07   |
| 800.00 | 6.16        | 6.11   | 5.99   |
| 802.00 | 6.07        | 6.03   | 5.92   |
| 804.00 | 6.00        | 5.96   | 5.85   |
| 806.00 | 5.93        | 5.88   | 5.78   |
| 808.00 | 5.86        | 5.82   | 5.72   |
| 810.00 | 5.79        | 5.76   | 5.66   |
| 812.00 | 5.73        | 5.69   | 5.60   |
| 814.00 | 5.67        | 5.63   | 5.55   |
| 816.00 | 5.62        | 5.58   | 5.50   |
| 818.00 | 5.56        | 5.53   | 5.45   |
| 820.00 | 5.51        | 5.48   | 5.41   |
| 822.00 | 5.46        | 5.44   | 5.36   |
| 824.00 | 5.42        | 5.39   | 5.32   |
| 826.00 | 5.38        | 5.35   | 5.29   |
| 828.00 | 5.34        | 5.31   | 5.25   |
| 830.00 | 5.30        | 5.28   | 5.22   |
| 832.00 | 5.27        | 5.25   | 5.19   |
| 834.00 | 5.24        | 5.22   | 5.16   |
| 836.00 | 5.22        | 5.19   | 5.14   |
| 838.00 | 5.19        | 5.16   | 5.11   |
| 840.00 | 5.17        | 5.14   | 5.09   |
| 842.00 | 5.15        | 5.13   | 5.08   |
| 844.00 | 5.13        | 5.11   | 5.06   |
| 846.00 | 5.12        | 5.10   | 5.05   |
| 848.00 | 5.11        | 5.09   | 5.04   |
| 850.00 | 5.10        | 5.08   | 5.04   |
| 852.00 | 5.09        | 5.07   | 5.03   |
| 854.00 | 5.09        | 5.07   | 5.02   |
| 856.00 | 5.08        | 5.07   | 5.02   |
| 858.00 | 5.08        | 5.06   | 5.02   |
| 860.00 | 5.08        | 5.06   | 5.02   |
| 862.00 | 5.09        | 5.06   | 5.02   |
| 864.00 | 5.09        | 5.07   | 5.03   |
| 866.00 | 5.09        | 5.07   | 5.03   |
| 868.00 | 5.10        | 5.08   | 5.04   |
| 870.00 | 5.10        | 5.09   | 5.04   |
| 872.00 | 5.11        | 5.09   | 5.05   |
| 874.00 | 5.12        | 5.10   | 5.06   |
| 876.00 | 5.13        | 5.12   | 5.07   |
| 878.00 | 5.15        | 5.14   | 5.09   |
| 880.00 | 5.17        | 5.15   | 5.11   |
| 882.00 | 5.19        | 5.17   | 5.13   |
| 884.00 | 5.21        | 5.20   | 5.16   |
| 886.00 | 5.24        | 5.22   | 5.18   |
| 888.00 | 5.27        | 5.26   | 5.22   |
| 890.00 | 5.30        | 5.29   | 5.26   |

## Typical Performance Curves




*Typical Performance Curves*

# Case Style

# HY

## Outline Dimensions

## HY1238



| CASE #. | A               | B              | C              | D               | E             | F             | G               | H              | J             | K             | L             | M               | N              | WT GRAMS |
|---------|-----------------|----------------|----------------|-----------------|---------------|---------------|-----------------|----------------|---------------|---------------|---------------|-----------------|----------------|----------|
| HY1238  | 1.20<br>(30.48) | .75<br>(19.05) | .46<br>(11.68) | 1.18<br>(29.97) | .04<br>(1.02) | .17<br>(4.32) | 1.00<br>(25.40) | .50<br>(12.70) | .35<br>(8.89) | .18<br>(4.57) | .21<br>(5.28) | 2.05<br>(52.07) | .106<br>(2.69) | 35.0     |

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .03$ ; 3Pl.  $\pm .015$   
Tolerance on hole size and interaxes dimensions to be  $\pm .005$ .

### Note:

1. Case material: Brass
2. Case finish: Nickel plate



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification              | Test/Inspection Condition                                                                               | Reference/Spec                                        |
|----------------------------|---------------------------------------------------------------------------------------------------------|-------------------------------------------------------|
| Operating Temperature      | -55° to 100°C<br>Ambient Environment                                                                    | Individual Model Data Sheet                           |
| Storage Temperature        | -55° to 100° C<br>Ambient Environment                                                                   | Individual Model Data Sheet                           |
| Humidity                   | 90 to 95% RH, 40°C, 96 hours;<br>Units may require bake-out after humidity to restore full performance. | MIL-STD-202, Method 103, Condition B                  |
| Thermal Shock              | -55° to 100°C, 100 cycles                                                                               | MIL-STD-202, Method 107, Condition A-3, except +100°C |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)                     | MIL-STD-202, Method 204, Condition D                  |
| Mechanical Shock           | 50g, 11ms half-sine, 3 shocks each direction 3 axes (total 18)                                          | MIL-STD-202, Method 213, Condition A                  |