



## Outline Dimensions


LM1848



TOP VIEW



FRONT VIEW



REAR VIEW


S/N LABEL

BRACKET OPTION  
ONE SET OF 2 EACH

INSTRUCTIONS FOR MOUNTING  
BRACKETS:  
TOOL REQUIRED: PHILLIPS  
HEAD SCREWDRIVER

STEP 1: REMOVE RUBBER FEET  
FROM THE BOTTOM OF THE  
UNIT, DO NOT DISCARD THE  
FASTENERS.

STEP 2: MOUNT THE BRACKETS  
WITH THE FASTENERS  
REMOVED IN STEP 1,  
USING THE COUNTER  
BORE HOLES IN THE  
BRACKET.



BOTTOM VIEW

TOLERANCE:  $\pm .005$

SHOWN WITH RUBBER FEET REMOVED AND BRACKETS INSTALLED.

### Notes:

1. Case material: Aluminum (with protective coating to prevent corrosion).
2. Dimensions are in inches [mm]. Tolerances: 2 Pl.  $\pm .03$  inch; 3 Pl.  $\pm .015$  inch.
3. Weight: 875 grams.
4. Marking may contain other features or characters for internal lot control.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS