


Case Style

P

P25
P26

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
P25	2.25	1.38	1.24	.50	.150	3.100	.138	1.238	3.25	.10	.78	1.47	--
	(57.15)	(35.05)	(31.50)		(3.81)	(78.74)		(31.45)	(82.55)		(19.81)	(37.34)	--
P26	1.50	1.13	1.00	(12.70)	.155	2.345	(3.51)	.987	2.50	(2.54)	.50	1.00	--
	(38.10)	(28.70)	(25.40)		(3.94)	(59.56)		(25.07)	(63.50)		(12.70)	(25.40)	--

CASE#	P	Q	R	S	WT. GRAMS
P25	.38	1.00	--	.150	110.0
	(9.65)	(25.40)	--		
P26	.31	.81	--	(3.81)	60.0
	(7.87)	(20.57)	--		

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
 - For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
 - For Non-RoHS Case Styles: Yellow hexavalent chrome based conversion coating. Due to transition from non-RoHS to RoHS, models will be supplied with either case style finish until the non-RoHS case inventory is depleted.
- Mounting bracket available on request. For bracket mounted on connector end add suffix B to part number and add \$5.00 to unit cost. For bracket mounted on the rear, add suffix BR to part number and add \$1.50 to unit cost.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified