

Coaxial

Band Stop Filter

ZX75BS-88108-S+

50Ω

88 to 108 MHz

The Big Deal

- High rejection
- Stopband (88 to 108 MHz)
- Connectorized package



CASE STYLE: KD1465

Product Overview

The ZX75BS-88108-S+ is a band stop filter built in rugged and compact connectorized package. This filter offers good rejection in stopband. It has repeatable performance across lots and consistent performance across temperature. Useful in Radio and TV broadcast systems to minimize spurious signal and avoid system jamming.

Key Features

Feature	Advantages
High rejection	ZX75BS-88108-S+ enables the filter to attenuate spurious signals without compromising pass band signal.
Connectorized package	The connectorized package is easy to interface with other devices and well suited for test setups.
Application	Can be used in broadcast and FM systems.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Band Stop Filter

50Ω

88 to 108 MHz

ZX75BS-88108-S+



CASE STYLE: KD1465

Connectors Model

SMA-MF ZX75BS-88108-S+

Features

- High rejection
- Fast roll-off
- Connectorized package


Applications

- FM radio
- Broadcast systems
- Lab use

Electrical Specifications at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band, Lower	Insertion Loss	DC-F1	DC - 66	-	0.6	1.5 dB
	VSWR	DC-F1	DC - 66	-	1.2	1.6 :1
Stop Band	Rejection	F4-F5	88 - 108	30	47	- dB
	VSWR	F4-F5	88 - 108	-	14	- :1
Pass Band, Upper	Insertion Loss	F2-F3	142 - 1000	-	0.8	1.5 dB
	VSWR	F2-F3	142 - 1000	-	1.4	1.8 :1

Functional Schematic



Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	250 mW max.

Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C



Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
1	0.02	1.01
44	0.16	1.20
61	0.33	1.11
66	0.48	1.06
72	1.02	1.24
76	2.88	2.13
78	6.91	4.57
80	14.37	9.28
84	36.84	16.56
88	60.15	20.45
108	48.07	19.98
112	38.14	14.50
116	19.28	8.12
119	9.77	3.85
122	4.28	1.63
126	2.05	1.19
135	1.02	1.27
142	0.72	1.17
180	0.36	1.27
1000	0.31	1.35

Typical Frequency Response



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes


- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Connections

INPUT	SMA-Male
OUTPUT	SMA-Female

Outline Drawing



Outline Dimensions (inch mm)

A	B	C	D	E	F	G
.74	.75	.46	1.18	.04	.17	.21
18.80	19.05	11.68	29.97	1.02	4.32	5.33
H	J	K	L	M		Wt.
1.00	.37	.18	.09	1.51		grams
25.40	9.40	4.57	2.29	38.4		21.4

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Coaxial Band Stop Filter

ZX75BS-88108-S+







Typical Performance Data

FREQ. (MHz)	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
0.5	0.02	0.02	0.02	54.86	53.62	52.52	54.60	51.90	50.78
5.0	0.02	0.03	0.04	38.13	36.88	36.21	38.16	36.97	36.30
10.0	0.03	0.04	0.04	32.54	31.45	30.78	32.55	31.48	30.85
15.0	0.04	0.05	0.07	29.13	28.17	27.55	29.14	28.18	27.58
20.0	0.05	0.07	0.08	26.63	25.82	25.24	26.65	25.84	25.27
25.0	0.06	0.09	0.09	24.65	23.99	23.46	24.68	23.99	23.51
30.0	0.08	0.10	0.11	23.01	22.50	22.09	23.03	22.50	22.13
35.0	0.11	0.13	0.14	21.67	21.31	21.02	21.70	21.33	21.07
40.0	0.13	0.16	0.17	20.61	20.41	20.23	20.62	20.43	20.29
45.0	0.16	0.19	0.20	19.86	19.84	19.81	19.86	19.87	19.86
50.0	0.19	0.22	0.23	19.56	19.75	19.91	19.54	19.78	19.97
55.0	0.23	0.26	0.28	20.04	20.53	20.96	20.04	20.57	21.07
60.0	0.28	0.32	0.36	22.31	23.39	24.41	22.29	23.43	24.55
65.0	0.38	0.45	0.50	31.17	35.38	40.11	31.35	35.96	41.03
66.0	0.42	0.50	0.56	36.52	42.69	39.15	37.04	43.28	37.88
68.0	0.52	0.62	0.69	37.43	32.00	29.26	36.51	31.12	28.32
70.0	0.67	0.79	0.88	29.57	27.40	26.01	28.21	25.99	24.50
72.0	0.89	1.05	1.17	30.83	29.71	28.93	26.12	24.55	23.38
74.0	1.34	1.58	1.78	23.02	22.31	21.57	19.86	18.68	17.65
76.0	2.85	3.34	3.75	9.81	9.45	9.13	9.29	8.79	8.32
78.0	7.79	8.58	9.26	3.64	3.68	3.70	3.46	3.44	3.39
80.0	16.44	17.32	18.07	1.75	1.89	2.00	1.65	1.77	1.84
82.0	27.32	28.25	29.06	1.20	1.34	1.45	1.14	1.27	1.35
84.0	41.62	42.79	43.78	0.97	1.10	1.19	0.93	1.05	1.13
86.0	65.35	66.36	65.89	0.84	0.95	1.04	0.80	0.92	1.00
88.0	60.64	59.79	58.42	0.74	0.86	0.94	0.72	0.83	0.91
89.0	54.85	54.23	53.59	0.71	0.82	0.89	0.69	0.80	0.87
90.0	51.75	51.25	50.87	0.68	0.79	0.86	0.66	0.78	0.85
92.0	49.30	49.11	48.93	0.63	0.74	0.81	0.63	0.74	0.81
94.0	49.70	50.07	49.98	0.59	0.69	0.77	0.63	0.74	0.81
95.0	50.87	51.01	51.28	0.59	0.68	0.76	0.66	0.78	0.86
96.0	51.46	51.96	52.22	0.58	0.68	0.75	0.79	0.93	1.02
98.0	51.94	51.33	51.08	0.57	0.67	0.75	0.92	0.95	0.97
100.0	50.07	49.88	49.59	0.56	0.66	0.74	0.61	0.70	0.76
101.0	49.99	49.58	49.66	0.56	0.66	0.75	0.59	0.68	0.74
102.0	50.22	50.01	50.06	0.56	0.67	0.75	0.58	0.67	0.74
103.0	51.08	51.21	51.29	0.57	0.68	0.77	0.59	0.68	0.74
104.0	53.12	53.76	53.44	0.59	0.70	0.79	0.60	0.69	0.75
105.0	56.30	56.92	56.82	0.60	0.71	0.81	0.61	0.70	0.77
106.0	58.07	57.88	56.94	0.62	0.73	0.83	0.63	0.72	0.78
107.0	55.15	54.56	53.91	0.64	0.76	0.86	0.65	0.74	0.80
108.0	52.19	51.55	51.36	0.67	0.79	0.90	0.68	0.77	0.83
110.0	50.56	50.39	49.96	0.76	0.89	1.01	0.75	0.85	0.92
116.0	22.63	22.13	21.72	1.44	1.65	1.86	1.37	1.50	1.58
120.0	9.55	9.38	9.26	3.74	4.17	4.59	3.40	3.66	3.85
126.0	2.07	2.18	2.27	32.48	34.76	34.37	17.46	17.36	16.96
130.0	1.34	1.43	1.51	18.76	18.36	17.91	18.12	17.66	17.10
136.0	0.91	0.97	1.04	18.69	18.55	18.32	19.90	19.32	18.64
140.0	0.73	0.79	0.85	20.93	20.94	20.83	23.52	22.58	21.53
142.0	0.67	0.73	0.77	22.27	22.47	22.45	26.12	24.86	23.41
150.0	0.49	0.53	0.57	25.96	27.46	29.20	41.96	38.79	32.84
200.0	0.24	0.27	0.29	19.73	19.87	19.94	19.58	19.87	19.96
300.0	0.14	0.19	0.22	20.87	19.60	19.12	20.71	19.52	19.04
400.0	0.11	0.17	0.20	21.31	19.86	18.87	21.14	19.75	18.84
500.0	0.13	0.19	0.22	20.75	19.62	18.54	20.66	19.54	18.50
600.0	0.11	0.18	0.22	20.06	19.23	18.29	19.99	19.19	18.29
700.0	0.11	0.19	0.23	19.23	18.73	18.00	19.20	18.72	18.01
800.0	0.12	0.21	0.25	18.64	18.13	17.58	18.64	18.14	17.62
900.0	0.16	0.26	0.31	17.88	17.48	17.17	17.91	17.53	17.22
1000.0	0.22	0.33	0.38	17.35	16.87	16.72	17.44	16.93	16.76

Typical Performance Data


FREQ.	GROUP DELAY-1			FREQ.	GROUP DELAY-2		
(MHz)	(ns)			(MHz)	(ns)		
	@-40°C	@+25°C	@+85°C		@-40°C	@+25°C	@+85°C
0.5	2.59	2.66	2.62	142.0	7.72	7.62	7.55
1.0	2.61	2.65	2.63	143.0	7.31	7.24	7.14
1.5	2.59	2.63	2.61	144.0	6.98	6.88	6.82
2.0	2.61	2.64	2.63	145.0	6.63	6.57	6.50
2.5	2.60	2.63	2.62	146.0	6.32	6.25	6.19
3.0	2.63	2.65	2.64	147.0	6.01	5.97	5.92
4.0	2.63	2.62	2.61	148.0	5.76	5.72	5.67
5.0	2.64	2.62	2.64	149.0	5.51	5.46	5.41
6.0	2.63	2.64	2.63	150.0	5.27	5.22	5.19
7.0	2.65	2.65	2.65	151.0	5.06	5.02	4.98
8.0	2.64	2.66	2.66	152.0	4.87	4.82	4.78
9.0	2.68	2.67	2.66	153.0	4.67	4.63	4.59
10.0	2.68	2.65	2.66	154.0	4.49	4.48	4.44
11.0	2.72	2.72	2.71	155.0	4.34	4.31	4.26
12.0	2.70	2.70	2.67	156.0	4.22	4.18	4.14
13.0	2.71	2.71	2.70	157.0	4.05	4.02	4.00
14.0	2.75	2.74	2.71	158.0	3.90	3.86	3.83
15.0	2.75	2.76	2.76	159.0	3.76	3.71	3.70
16.0	2.77	2.75	2.75	160.0	3.64	3.61	3.58
17.0	2.82	2.80	2.79	161.0	3.52	3.48	3.45
18.0	2.84	2.83	2.85	162.0	3.41	3.38	3.33
19.0	2.89	2.88	2.87	163.0	3.31	3.26	3.23
20.0	2.91	2.89	2.89	164.0	3.18	3.16	3.14
21.0	2.96	2.94	2.95	165.0	3.08	3.07	3.06
22.0	3.04	3.00	2.99	166.0	3.00	2.97	2.95
23.0	3.04	3.02	3.02	167.0	2.90	2.88	2.85
24.0	3.08	3.07	3.07	168.0	2.86	2.84	2.79
25.0	3.13	3.10	3.11	169.0	2.75	2.76	2.71
26.0	3.20	3.19	3.19	170.0	2.66	2.63	2.61
27.0	3.24	3.22	3.21	171.0	2.62	2.59	2.56
28.0	3.30	3.29	3.31	172.0	2.56	2.54	2.52
29.0	3.37	3.37	3.36	173.0	2.49	2.44	2.43
30.0	3.45	3.43	3.42	174.0	2.42	2.39	2.38
31.0	3.52	3.49	3.49	175.0	2.36	2.34	2.31
32.0	3.58	3.59	3.54	176.0	2.32	2.29	2.26
33.0	3.65	3.65	3.63	177.0	2.25	2.23	2.20
34.0	3.75	3.73	3.72	178.0	2.17	2.15	2.15
35.0	3.80	3.80	3.80	179.0	2.15	2.13	2.08
36.0	3.92	3.91	3.92	180.0	2.11	2.08	2.04
37.0	4.02	4.00	4.02	181.0	2.06	2.02	2.02
38.0	4.13	4.14	4.13	182.0	1.98	1.96	1.96
39.0	4.22	4.24	4.25	183.0	1.96	1.94	1.92
40.0	4.35	4.35	4.35	184.0	1.91	1.88	1.88
41.0	4.49	4.48	4.48	185.0	1.87	1.86	1.85
42.0	4.62	4.63	4.63	186.0	1.82	1.81	1.80
43.0	4.75	4.77	4.77	187.0	1.80	1.77	1.76
44.0	4.92	4.92	4.92	188.0	1.78	1.74	1.72
45.0	5.10	5.10	5.10	189.0	1.72	1.71	1.70
46.0	5.29	5.28	5.29	190.0	1.69	1.68	1.64
47.0	5.47	5.48	5.48	195.0	1.55	1.52	1.52
48.0	5.67	5.68	5.71	200.0	1.38	1.38	1.37
49.0	5.92	5.94	5.94	300.0	0.51	0.49	0.48
50.0	6.14	6.17	6.20	400.0	0.33	0.32	0.30
51.0	6.40	6.43	6.46	500.0	0.26	0.23	0.22
55.0	7.72	7.78	7.82	600.0	0.22	0.20	0.19
60.0	10.23	10.31	10.39	800.0	0.19	0.17	0.16
65.0	14.67	14.81	14.92	900.0	0.18	0.16	0.15
66.0	15.94	16.08	16.24	1000.0	0.18	0.16	0.15

Typical Performance Curves



Outline Dimensions

KD1465



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAM
KD1465	0.74 (18.80)	.75 (19.05)	.46 (11.68)	1.18 (29.97)	.04 (1.02)	.17 (4.32)	.21 (5.33)	1.00 (25.40)	.37 (9.40)	.18 (4.57)	.09 (2.29)	1.51 (38.4)	21.4

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$
Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Note:

1. Case material: Brass
2. Case finish: Gold
3. Cover: Nickel plated.



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I