



Outline Dimensions

RZ2511-1



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
RZ2511-1	.750 (19.05)	.551 (14.00)	.210 (5.33)	.139 (3.53)	.158 (4.01)	.215 (5.46)	.176 (4.47)	.218 (5.54)	.100 (2.54)	.060 (1.52)	.070 (1.78)	.150 (3.81)

CASE#	N	P	Q	R	S	T	U	V	W	Y	WT.GRAMS
RZ2511-1	.238 (6.05)	.120 (3.05)	.159 (4.04)	.331 (8.41)	.450 (11.43)	.790 (20.07)	.080 (2.03)	.591 (15.01)	.530 (13.46)	.156 (3.96)	2.4

Dimensions are in inches (mm). Tolerances: 2PL. ± .03; 3PL. ± .015

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
All models, (+) suffix.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS