


Case Style


SM20A

SM20A

Outline Dimensions



PCB Land Pattern



Suggested Layout,

Tolerance to be within $\pm .002$

Each ground pin shall have footprint

per view "A". All ground pads shall

be connected to each other per view "B".

CASE #	A	B	C	D	E	F	G	H	J	K	L	M
SM20A	.500 (12.70)	.460 (11.68)	.095 (2.41)	.575 (14.61)	.050 (1.27)	.015 (0.38)	.025 (0.64)	.070 (1.78)	.030 (0.76)	.095 (2.41)	.600 (15.24)	.120 (3.05)

CASE #	N	P	Q	R	WT. GRAM
SM20A	.160 (4.06)	--	--	.012 (0.30)	.5

Dimensions are in inches (mm). Tolerances: $\pm .005$

Notes:

1. Open style, ceramic base.
2. Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate.
For RoHS-5 Case Styles: Tin-Lead plate.

Mini-Circuits

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified