


Case Style

TS

TS2825

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
TS2825	.440 (11.18)	1.000 (25.40)	.270 (6.86)	.143 (3.63)	.060 (1.52)	.085 (2.16)	.147 (3.73)	.100 (2.54)	.355 (9.02)	.293 (7.45)	.125 (3.18)	.790 (20.07)

CASE#	N	P	Q	R	S	T	WT. GRAMS
TS2825	.230 (5.84)	.480 (12.19)	.080 (2.03)	.133 (3.37)	1.040 (26.42)	.167 (4.23)	2

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
 - For RoHS Case Styles: 3-5 μ inch Gold over 120-240 μ inch Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.



ISO 9001 ISO 14001 CERTIFIED



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS