

Coaxial High Pass Filter

ZX75HP-92-S+

50Ω 160 to 2500 MHz

The Big Deal

- Low insertion loss
- High rejection
- Connectorized package



Generic photo used for illustration purposes only

CASE STYLE: KE1467

Product Overview

ZX75HP-92-S+ is a High pass filter in a rugged connectorized package covering 160 to 2500 MHz. This filter will find its application in TV Broadcast, point-to-point military radio and cordless telephones. It has repeatable performance across production lots and consistent performance across temperature.

Key Features

Feature	Advantages
Low insertion loss	Can be used in high performance applications.
Good rejection	This enables the filter to attenuate spurious signals and reject harmonics for broad band frequency.
Connectorized package	The connectorized package is easy to interface with other devices and well suited for test setups.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial High Pass Filter

50Ω 160 to 2500 MHz

ZX75HP-92-S+



Generic photo used for illustration purposes only

CASE STYLE: KE1467

Connectors	Model
SMA-MF	ZX75HP-92-S+

Features

- Wide band, 160 MHz to 2500 MHz
- High rejection
- Connectorized package

Applications

- TV Broadcast
- Point-to-point military radio
- Cordless telephones

Electrical Specifications at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Stop Band	Rejection Loss	DC-F1	DC-64	20	31	- dB
	VSWR	DC-F1	DC-64	-	20	- :1
Pass Band	Insertion Loss	F2-F3	160-2500	-	0.5	1.2 dB
	VSWR	F2-F3	160-2500	-	1.4	- :1

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5 W.

Permanent damage may occur if any of these limits are exceeded.


Functional Schematic



Typical Performance Data at 25°C





Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
0.3	101.86	1737.18
13.0	92.49	1737.18
16.0	77.36	1737.18
30.0	80.98	434.30
37.0	69.84	289.53
46.0	56.22	144.77
55.0	42.78	82.73
64.0	31.18	45.72
73.0	20.53	23.81
82.0	10.60	9.13
88.0	5.28	3.87
92.0	3.06	2.24
97.0	1.74	1.37
108.0	1.02	1.06
143.0	0.57	1.14
160.0	0.48	1.18
360.0	0.21	1.10
1030.0	0.30	1.31
2010.0	0.42	1.28
2500.0	0.49	1.18

Typical Frequency Response



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp





www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.C
ECO-004400
ZX75HP-92-S+
EDU1688
URJ
201008
Page 2 of 3

Coaxial Connections

INPUT	SMA-Male
OUTPUT	SMA-Female

Outline Drawing



Outline Dimensions (^{inch}_{mm})

A	B	C	D	E	F	G
.74	.75	.46	1.18	.04	.362	.21
18.80	19.05	11.68	29.97	1.02	9.19	5.33
H	J	K	L	M		Wt.
.362	1.00	.37	.18	.11		grams
9.19	25.40	9.40	4.57	2.79		24.4

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
0.3	96.60	100.96	99.84	0.00	0.00	0.00	0.00	0.00	0.00
1	101.43	100.74	95.78	-0.01	0.00	-0.01	0.00	0.00	0.00
5	97.96	100.90	97.41	0.00	0.00	0.00	0.01	0.01	0.01
10	100.26	111.22	101.43	0.00	0.00	0.01	0.00	0.01	0.02
30	83.47	81.05	83.80	0.03	0.03	0.04	0.03	0.04	0.04
40	68.25	66.37	66.46	0.06	0.07	0.08	0.06	0.08	0.08
50	50.04	49.62	49.56	0.12	0.14	0.16	0.14	0.16	0.17
60	36.39	36.18	36.02	0.24	0.27	0.30	0.27	0.30	0.32
64	31.38	31.16	31.00	0.31	0.36	0.38	0.34	0.38	0.41
70	24.17	24.00	23.84	0.48	0.54	0.58	0.51	0.58	0.61
80	12.76	12.68	12.58	1.30	1.42	1.51	1.35	1.48	1.57
90	3.93	4.01	4.05	5.85	6.13	6.36	5.93	6.23	6.45
92	2.95	3.05	3.10	7.93	8.24	8.52	8.01	8.35	8.61
100	1.29	1.40	1.46	22.44	23.30	23.97	22.31	23.34	23.83
105	1.02	1.11	1.18	42.64	35.65	34.07	47.42	38.47	36.31
110	0.87	0.97	1.02	29.26	27.33	26.70	32.15	29.47	28.75
115	0.78	0.86	0.90	28.48	26.81	26.24	34.29	30.83	29.87
120	0.71	0.78	0.83	28.85	27.69	27.24	49.36	38.38	35.90
125	0.65	0.71	0.75	27.83	27.75	27.73	35.01	41.60	47.99
130	0.59	0.65	0.69	25.93	26.42	26.79	28.77	31.04	32.71
135	0.56	0.62	0.65	24.27	24.79	25.29	25.66	26.91	27.91
140	0.53	0.58	0.61	23.08	23.47	23.96	23.87	24.59	25.33
145	0.50	0.55	0.57	22.36	22.55	22.97	22.78	23.15	23.71
150	0.47	0.52	0.55	21.97	21.95	22.29	22.17	22.26	22.69
155	0.46	0.51	0.53	21.84	21.60	21.85	21.88	21.74	22.04
160	0.43	0.48	0.50	21.93	21.48	21.62	21.83	21.45	21.66
165	0.42	0.46	0.49	22.20	21.50	21.54	21.96	21.36	21.45
170	0.39	0.45	0.46	22.61	21.67	21.59	22.21	21.42	21.39
175	0.38	0.42	0.44	23.15	21.94	21.75	22.58	21.58	21.45
180	0.38	0.43	0.45	23.90	22.39	22.05	23.14	21.92	21.67
190	0.35	0.39	0.42	25.56	23.42	22.82	24.29	22.74	22.23
200	0.33	0.37	0.39	27.57	24.76	23.85	25.55	23.75	23.05
250	0.25	0.28	0.30	53.54	38.98	33.57	31.31	31.19	29.60
300	0.20	0.23	0.25	34.26	32.85	34.55	31.88	30.62	31.51
400	0.17	0.21	0.24	26.80	24.52	23.39	26.99	24.44	23.29
500	0.17	0.21	0.24	23.29	22.00	20.83	23.25	21.96	20.76
600	0.17	0.23	0.25	21.76	20.58	19.71	21.63	20.49	19.61
700	0.19	0.24	0.28	20.48	19.57	18.74	20.35	19.46	18.66
800	0.20	0.25	0.29	19.59	18.80	17.90	19.47	18.68	17.80
900	0.21	0.28	0.32	19.25	18.21	17.30	19.02	18.05	17.19
1000	0.22	0.29	0.34	18.91	17.70	16.85	18.74	17.60	16.77
1100	0.23	0.32	0.36	18.61	17.35	16.57	18.47	17.26	16.51
1200	0.24	0.33	0.38	18.27	17.08	16.36	18.15	17.02	16.31
1300	0.26	0.35	0.40	17.96	16.91	16.21	17.85	16.84	16.14
1400	0.26	0.36	0.41	17.96	16.81	16.15	17.86	16.77	16.13
1500	0.27	0.37	0.42	17.97	16.79	16.18	17.96	16.80	16.21
1600	0.28	0.38	0.43	17.78	16.85	16.30	17.88	16.94	16.37
1650	0.28	0.38	0.44	17.69	16.92	16.37	17.78	16.98	16.44
1700	0.28	0.39	0.45	17.78	17.02	16.48	17.86	17.13	16.56
1750	0.28	0.39	0.45	17.93	17.14	16.62	18.03	17.23	16.69
1800	0.28	0.39	0.45	18.13	17.27	16.77	18.23	17.38	16.84
1850	0.29	0.39	0.46	18.33	17.45	16.94	18.49	17.58	17.05
1900	0.29	0.39	0.46	18.47	17.61	17.14	18.66	17.77	17.27
1950	0.29	0.40	0.46	18.65	17.86	17.38	18.82	17.98	17.45
2000	0.29	0.40	0.46	18.89	18.09	17.66	19.07	18.25	17.75
2100	0.29	0.41	0.47	19.61	18.72	18.31	19.79	18.86	18.36
2200	0.29	0.41	0.48	20.55	19.49	19.13	20.66	19.53	19.09
2300	0.31	0.45	0.51	21.48	20.40	20.15	21.49	20.28	19.92
2400	0.31	0.45	0.52	22.59	21.58	21.45	22.16	21.06	20.79
2500	0.35	0.48	0.56	23.97	23.09	23.18	22.67	21.76	21.58

High Pass Filter **ZX75HP-92-S+**







Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(dB)		
	@-40°C	@+25°C	@+85°C
160	3.72	3.73	3.69
161	3.71	3.68	3.67
162	3.65	3.64	3.61
163	3.62	3.60	3.58
164	3.58	3.56	3.54
165	3.53	3.51	3.51
166	3.47	3.47	3.43
167	3.42	3.39	3.39
168	3.37	3.36	3.37
169	3.33	3.32	3.29
170	3.27	3.24	3.25
171	3.25	3.21	3.23
172	3.21	3.18	3.20
173	3.17	3.12	3.14
174	3.13	3.11	3.12
175	3.11	3.10	3.07
176	3.07	3.05	3.04
177	3.04	3.03	3.00
178	3.27	3.28	3.25
179	3.20	3.21	3.20
180	3.10	3.09	3.09
190	2.94	2.94	2.93
200	2.75	2.76	2.75
210	2.28	2.26	2.26
220	2.08	2.06	2.06
230	1.91	1.89	1.89
240	1.76	1.75	1.75
250	1.63	1.62	1.62
260	1.51	1.51	1.50
270	1.42	1.41	1.41
280	1.33	1.32	1.32
290	1.25	1.24	1.24
300	1.19	1.18	1.17
310	1.12	1.11	1.11
320	1.07	1.06	1.05
330	1.02	1.01	1.01
340	0.97	0.96	0.96
350	0.93	0.92	0.92
400	0.76	0.75	0.75
500	0.58	0.57	0.56
600	0.47	0.47	0.46
700	0.42	0.41	0.40
800	0.38	0.37	0.37
900	0.35	0.34	0.34
1000	0.33	0.32	0.32
1100	0.32	0.31	0.30
1200	0.30	0.30	0.29
1300	0.30	0.29	0.29
1400	0.30	0.29	0.29
1500	0.29	0.28	0.28
1600	0.28	0.27	0.27
1700	0.28	0.27	0.27
1800	0.27	0.26	0.26
1900	0.28	0.27	0.27
2000	0.27	0.27	0.27
2100	0.27	0.27	0.26
2200	0.28	0.27	0.27
2300	0.27	0.27	0.26
2400	0.28	0.27	0.27
2500	0.29	0.28	0.28

High Pass Filter

ZX75HP-92-S+


Typical Performance Curves




High Pass Filter

ZX75HP-92-S+

Typical Performance Curves



Outline Dimensions



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M
KE1467	.74 (18.80)	.75 (19.05)	.46 (11.68)	1.18 (29.97)	.04 (1.02)	.362 (9.19)	.21 (5.33)	.362 (9.19)	1.00 (25.40)	.37 (9.40)	.18 (4.57)	.11 (2.79)

CASE #.	WT. GRAM
KE1467	24.4

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Note:

1. Case material: Brass
2. Case finish: Gold
3. Cover: Nickel plated.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I