


Outline Dimensions

WA3176-1



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
WA3176-1	.700 (17.78)	.550 (13.97)	.120 (3.05)	.060 (1.52)	.170 (4.32)	.040 (1.02)	.080 (2.03)	.100 (2.54)	.275 (6.99)	.140 (3.56)	.280 (7.11)	.175 (4.45)

CASE#	N	P	Q	R	S	T	U	V	W	WT.GRAMS
WA176-1	.160 (4.06)	.380 (9.65)	.310 (7.87)	.460 (11.68)	.130 (3.30)	.620 (15.75)	.740 (18.80)	.470 (11.94)	.590 (14.99)	1.3

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
 - For RoHS Case Styles: 3-5 μ inch Gold over 120-240 μ inch Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS