

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMP-FEMALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMP-FEMALE 2 RETURN LOSS (dB)
100	0.06	36.2	35.9
200	0.08	30.8	30.4
300	0.11	28.9	28.6
400	0.13	29.1	28.8
500	0.14	31.6	31.3
600	0.15	39.3	39.2
700	0.16	42.2	42.1
800	0.18	32.2	32.0
900	0.20	28.7	28.5
1000	0.21	27.6	27.5
1100	0.22	28.3	28.4
1200	0.24	31.1	31.4
1300	0.24	38.0	37.9
1400	0.24	40.7	38.6
1500	0.24	32.7	32.3
1600	0.27	29.4	29.5
1800	0.29	29.6	30.0
2000	0.29	39.1	36.7
2500	0.32	29.3	29.4
3000	0.35	36.2	37.7
3500	0.36	31.5	28.2
4000	0.42	31.8	28.3
4500	0.44	45.9	36.0
5000	0.45	29.3	26.4
5500	0.53	30.1	26.7
6000	0.50	39.0	30.6
6500	0.55	28.5	25.6
7000	0.58	30.0	27.0
7500	0.61	32.9	27.8
8000	0.66	26.7	23.5
8500	0.66	26.4	24.3
9000	0.63	30.8	27.7
9500	0.70	21.7	21.3
10000	0.69	22.3	24.7
10500	0.67	27.5	27.4
11000	0.75	22.4	21.5
11500	0.80	19.9	24.0
12000	0.77	26.6	32.1
12500	0.78	23.9	21.7
13000	0.74	18.7	21.1
13500	0.95	24.2	38.7
14000	0.88	23.2	21.9
14500	0.73	22.4	22.4
15000	0.87	21.2	22.6
15500	0.99	38.8	35.9
16000	1.01	24.1	23.6
16500	0.89	26.0	21.8
17000	0.86	23.5	21.9
17500	0.85	27.8	27.5
18000	0.77	26.7	34.0